

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032220

Luminaire Tested: S123RDIW-B340D1535UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032220
REPORT IS A COMBINATION OF REPORTS P994270 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1535UB30-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7492.0 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032220

CATALOG NUMBER: S123RDIW-B340D1535UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1032220

CATALOG NUMBER: S123RDIW-B340D1535UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26
1	90	86	83	79	79	76	73	70	57	55	53	39	38	37	23	22	22
2	82	75	70	65	72	67	62	58	50	47	44	34	33	31	20	19	19
3	75	66	60	54	66	59	53	48	44	40	37	31	28	26	18	17	16
4	69	59	51	46	60	52	46	41	39	35	32	27	25	23	16	15	14
5	63	52	44	39	55	46	40	35	35	30	27	24	22	19	14	13	12
6	58	46	39	33	51	41	35	30	31	27	23	22	19	17	13	12	11
7	53	42	34	29	47	37	31	26	28	24	20	20	17	15	12	10	9
8	49	38	30	25	43	34	27	23	26	21	18	18	15	13	11	9	8
9	46	34	27	22	40	30	24	20	23	19	16	17	14	12	10	9	7
10	43	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6018	6018	6018
5°	6028	5804	5789
10°	5980	5586	5477
15°	5902	5316	5134
20°	5801	5023	4752
25°	5695	4719	4388
30°	5561	4394	3960
35°	5423	4075	3570
40°	5292	3729	3138
45°	5124	3391	2751
50°	4940	3029	2350
55°	4749	2643	1981
60°	4566	2247	1609
65°	4329	1840	1256
70°	4032	1391	897
75°	3606	943	711
80°	3078	656	499
85°	2305	354	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5124 cd/sqm

TEST NUMBER: P1032220

CATALOG NUMBER: S123RDIW-B340D1535UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	0.7
10°-20°	146.2	2.0
20°-30°	210.5	2.8
30°-40°	237.1	3.2
40°-50°	226.7	3.0
50°-60°	185.6	2.5
60°-70°	125.1	1.7
70°-80°	62.8	0.8
80°-90°	20.5	0.3
90°-100°	72.0	1.0
100°-110°	348.1	4.6
110°-120°	853.1	11.4
120°-130°	1083.0	14.5
130°-140°	1156.9	15.4
140°-150°	1081.9	14.4
150°-160°	872.6	11.6
160°-170°	563.2	7.5
170°-180°	194.1	2.6
0°-30°	409.2	5.5
0°-40°	646.3	8.6
0°-60°	1058.7	14.1
0°-90°	1267.1	16.9
90°-120°	1273.3	17.0
90°-150°	4595.1	61.3
90°-180°	6225.0	83.1
0°-180°	7492.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	559	559	559	559	559	
5°	559	557	551	555	554	53
15°	533	528	516	513	510	150
25°	485	474	453	443	438	223
35°	420	404	375	356	348	263
45°	345	325	290	264	253	266
55°	262	240	201	175	166	235
65°	179	154	119	97	92	177
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	2	17	36	42	46	7
95°	92	30	47	58	58	111
105°	452	469	332	64	67	479
115°	848	857	871	886	892	837
125°	1195	1208	1214	1217	1220	1068
135°	1488	1497	1503	1508	1503	1146
145°	1717	1728	1731	1734	1734	1075
155°	1892	1889	1890	1898	1889	872
165°	1995	1990	1989	2001	1990	564
175°	2042	2034	2036	2046	2034	194
180°	2042	2042	2042	2042	2042	

TEST NUMBER: P1032220

CATALOG NUMBER: S123RDIW-B340D1535UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	559.1	559.1	559.1	559.1	559.1
2.5°	561.3	559.5	554.1	559.1	558.1
5°	559.1	556.8	551.3	555.4	554.5
7.5°	555.0	552.7	545.9	548.6	547.3
10°	549.5	546.4	538.2	538.6	536.4
12.5°	541.8	538.2	527.8	527.3	524.6
15°	533.2	528.2	515.5	513.3	510.1
17.5°	522.8	517.3	501.5	496.9	492.4
20°	511.0	503.7	486.5	480.6	475.2
22.5°	497.8	489.2	470.6	462.9	457.9
25°	485.1	473.8	453.0	443.4	438.4
27.5°	469.7	457.5	434.8	422.1	414.4
30°	453.9	440.3	414.9	399.5	392.2
32.5°	438.0	422.1	394.9	377.7	370.0
35°	419.9	403.5	375.4	355.9	347.8
37.5°	401.7	384.0	354.6	332.8	322.8
40°	384.5	364.5	332.3	308.8	298.3
42.5°	365.0	345.0	311.5	285.2	276.1
45°	345.0	324.6	289.7	263.9	253.0
47.5°	325.5	302.9	268.4	240.3	230.8
50°	303.8	282.5	245.7	217.6	207.2
52.5°	284.3	260.7	224.4	195.0	185.9
55°	262.1	239.9	201.3	175.0	165.9
57.5°	242.1	218.1	179.1	154.2	146.5
60°	221.3	196.3	158.7	134.2	126.5
62.5°	200.4	175.5	137.8	115.2	107.0
65°	179.1	154.2	118.8	96.6	91.6
67.5°	157.8	132.4	97.9	81.2	75.7
70°	136.9	112.4	80.7	64.8	59.8
72.5°	116.1	92.0	63.9	51.7	50.3
75°	94.8	73.0	48.1	43.5	42.6
77.5°	75.3	55.3	37.6	34.9	34.0
80°	56.7	38.1	28.6	27.2	26.3
82.5°	39.0	23.6	20.4	19.0	19.0
85°	24.0	14.1	12.7	11.8	11.8
87.5°	10.9	5.9	5.9	5.4	5.0
90°	1.5	16.7	36.4	42.5	45.5
92.5°	34.9	25.8	39.4	50.1	51.6
95°	92.5	30.3	47.0	57.6	57.6
97.5°	168.4	125.9	48.5	60.7	62.2
100°	256.4	286.7	50.1	62.2	63.7
102.5°	356.5	376.2	112.3	62.2	65.2
105°	452.1	468.8	332.2	63.7	66.7
107.5°	553.7	567.4	590.1	356.5	157.8
110°	655.4	667.5	684.2	634.1	417.2



TEST NUMBER: P1032220

CATALOG NUMBER: S123RDIW-B340D1535UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	752.4	763.1	779.7	793.4	790.4
115°	848.0	857.1	870.8	885.9	892.0
117.5°	942.1	952.7	960.3	972.4	973.9
120°	1028.5	1042.2	1046.7	1058.9	1058.9
122.5°	1116.5	1127.1	1133.2	1140.8	1142.3
125°	1195.4	1207.5	1213.6	1216.6	1219.7
127.5°	1274.3	1286.4	1294.0	1298.6	1295.5
130°	1347.1	1359.2	1365.3	1371.4	1368.3
132.5°	1416.9	1429.0	1433.6	1439.6	1435.1
135°	1488.2	1497.3	1503.4	1507.9	1503.4
137.5°	1548.9	1561.0	1564.0	1571.6	1568.6
140°	1609.6	1618.7	1623.2	1629.3	1626.2
142.5°	1665.7	1674.8	1679.3	1683.9	1679.3
145°	1717.3	1727.9	1730.9	1734.0	1734.0
147.5°	1767.3	1774.9	1777.9	1781.0	1773.4
150°	1812.8	1817.4	1820.4	1823.5	1818.9
152.5°	1853.8	1855.3	1856.8	1862.9	1855.3
155°	1891.7	1888.7	1890.2	1897.8	1888.7
157.5°	1922.1	1922.1	1920.5	1929.6	1917.5
160°	1949.4	1947.9	1946.3	1955.4	1944.8
162.5°	1975.2	1970.6	1969.1	1979.7	1970.6
165°	1994.9	1990.3	1988.8	2000.9	1990.3
167.5°	2011.6	2005.5	2005.5	2017.6	2005.5
170°	2025.2	2019.2	2019.2	2031.3	2019.2
172.5°	2034.3	2026.7	2028.3	2040.4	2026.7
175°	2041.9	2034.3	2035.8	2046.5	2034.3
177.5°	2044.9	2037.4	2038.9	2051.0	2035.8
180°	2041.9	2041.9	2041.9	2041.9	2041.9

(END OF REPORT)