

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032227

Luminaire Tested: S123RDIW-B340D1535UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032227
REPORT IS A COMBINATION OF REPORTS P994283 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1535UB40-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6626.0 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032227

CATALOG NUMBER: S123RDIW-B340D1535UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1032227

CATALOG NUMBER: S123RDIW-B340D1535UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28
1	91	87	83	80	80	77	74	71	58	56	54	41	39	38	25	24	23
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20
3	76	67	60	54	66	59	53	49	45	41	38	32	29	27	19	18	17
4	69	59	52	46	61	52	46	41	40	36	32	28	26	23	17	16	15
5	63	52	45	39	56	47	40	35	36	31	28	25	22	20	16	14	13
6	58	47	39	34	51	42	35	30	32	27	24	23	20	18	14	13	11
7	54	42	35	29	47	38	31	27	29	24	21	21	18	15	13	11	10
8	50	38	31	26	44	34	28	23	26	22	18	19	16	14	12	10	9
9	46	35	28	23	41	31	25	21	24	19	16	17	14	12	11	9	8
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5985	5985	5985
5°	5994	5773	5756
10°	5947	5555	5446
15°	5870	5288	5106
20°	5769	4995	4725
25°	5664	4692	4364
30°	5529	4370	3938
35°	5392	4053	3550
40°	5263	3709	3121
45°	5095	3372	2736
50°	4913	3013	2337
55°	4722	2629	1971
60°	4540	2234	1600
65°	4305	1829	1249
70°	4011	1384	892
75°	3583	937	707
80°	3062	651	497
85°	2296	351	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5095 cd/sqm

TEST NUMBER: P1032227

CATALOG NUMBER: S123RDIW-B340D1535UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	0.8
10°-20°	145.4	2.2
20°-30°	209.3	3.2
30°-40°	235.7	3.6
40°-50°	225.5	3.4
50°-60°	184.6	2.8
60°-70°	124.4	1.9
70°-80°	62.4	0.9
80°-90°	20.4	0.3
90°-100°	124.7	1.9
100°-110°	377.3	5.7
110°-120°	642.3	9.7
120°-130°	845.1	12.8
130°-140°	949.9	14.3
140°-150°	933.8	14.1
150°-160°	786.2	11.9
160°-170°	523.4	7.9
170°-180°	183.3	2.8
0°-30°	407.0	6.1
0°-40°	642.7	9.7
0°-60°	1052.8	15.9
0°-90°	1260.1	19.0
90°-120°	1144.3	17.3
90°-150°	3873.1	58.5
90°-180°	5366.0	81.0
0°-180°	6626.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	556	556	556	556	556	
5°	556	554	548	552	551	53
15°	530	525	513	510	507	149
25°	482	471	450	441	436	222
35°	418	401	373	354	346	261
45°	343	323	288	262	252	265
55°	261	238	200	174	165	234
65°	178	153	118	96	91	176
75°	94	73	48	43	42	100
85°	24	14	13	12	12	26
90°	2	17	36	43	46	8
95°	90	100	113	119	119	99
105°	342	345	359	359	362	366
115°	646	651	648	650	648	640
125°	946	951	948	942	936	844
135°	1228	1237	1235	1229	1226	946
145°	1489	1492	1497	1495	1489	930
155°	1705	1705	1707	1713	1702	785
165°	1858	1853	1853	1862	1851	524
175°	1932	1926	1926	1935	1924	184
180°	1937	1937	1937	1937	1937	

TEST NUMBER: P1032227

CATALOG NUMBER: S123RDIW-B340D1535UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	556.0	556.0	556.0	556.0	556.0
2.5°	558.2	556.4	551.0	556.0	555.1
5°	556.0	553.7	548.3	552.3	551.4
7.5°	551.9	549.6	542.9	545.6	544.2
10°	546.5	543.3	535.2	535.7	533.4
12.5°	538.8	535.2	524.8	524.4	521.7
15°	530.3	525.3	512.7	510.4	507.3
17.5°	519.9	514.5	498.7	494.2	489.7
20°	508.2	500.9	483.8	477.9	472.5
22.5°	495.1	486.5	468.0	460.4	455.4
25°	482.5	471.2	450.4	441.0	436.0
27.5°	467.1	455.0	432.4	419.8	412.1
30°	451.3	437.8	412.6	397.2	390.0
32.5°	435.6	419.8	392.7	375.6	367.9
35°	417.5	401.3	373.3	354.0	345.8
37.5°	399.5	381.9	352.6	331.0	321.0
40°	382.4	362.5	330.5	307.1	296.7
42.5°	363.0	343.1	309.8	283.6	274.6
45°	343.1	322.8	288.1	262.4	251.6
47.5°	323.7	301.2	266.9	239.0	229.5
50°	302.1	280.9	244.4	216.4	206.1
52.5°	282.7	259.3	223.2	193.9	184.9
55°	260.6	238.5	200.2	174.0	165.0
57.5°	240.8	216.9	178.1	153.3	145.6
60°	220.0	195.2	157.8	133.5	125.8
62.5°	199.3	174.5	137.1	114.5	106.4
65°	178.1	153.3	118.1	96.0	91.1
67.5°	156.9	131.7	97.4	80.7	75.3
70°	136.2	111.8	80.3	64.5	59.5
72.5°	115.4	91.5	63.6	51.4	50.0
75°	94.2	72.6	47.8	43.3	42.4
77.5°	74.8	55.0	37.4	34.7	33.8
80°	56.4	37.9	28.4	27.1	26.2
82.5°	38.8	23.4	20.3	18.9	18.9
85°	23.9	14.0	12.6	11.7	11.7
87.5°	10.8	5.9	5.9	5.4	5.0
90°	1.5	16.7	36.5	42.6	45.6
92.5°	45.6	54.8	63.9	68.5	65.4
95°	89.8	100.4	112.6	118.7	118.7
97.5°	147.6	155.2	164.3	171.9	170.4
100°	206.9	216.0	223.6	228.2	231.2
102.5°	275.4	279.9	290.6	295.1	293.6
105°	342.3	345.3	359.0	359.0	362.1
107.5°	421.4	422.9	429.0	433.6	432.0
110°	494.4	497.5	500.5	506.6	503.5

TEST NUMBER: P1032227

CATALOG NUMBER: S123RDIW-B340D1535UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.5	572.0	572.0	579.6	579.6
115°	646.5	651.1	648.1	649.6	648.1
117.5°	724.1	725.6	722.6	722.6	718.0
120°	795.6	804.8	797.1	795.6	792.6
122.5°	870.2	876.3	873.2	868.6	864.1
125°	946.2	950.8	947.8	941.7	935.6
127.5°	1016.2	1025.3	1022.3	1013.2	1007.1
130°	1086.2	1098.4	1093.8	1087.7	1077.1
132.5°	1156.2	1168.3	1165.3	1157.7	1150.1
135°	1227.7	1236.8	1235.3	1229.2	1226.1
137.5°	1293.1	1300.7	1305.3	1297.6	1293.1
140°	1361.5	1369.1	1370.7	1369.1	1358.5
142.5°	1423.9	1431.5	1434.6	1433.0	1425.4
145°	1489.3	1492.4	1496.9	1495.4	1489.3
147.5°	1545.6	1551.7	1556.3	1556.3	1547.1
150°	1604.9	1608.0	1611.0	1611.0	1601.9
152.5°	1653.6	1658.2	1659.7	1662.7	1655.1
155°	1705.3	1705.3	1706.9	1713.0	1702.3
157.5°	1749.5	1747.9	1749.5	1755.5	1746.4
160°	1790.5	1787.5	1787.5	1795.1	1789.0
162.5°	1827.0	1822.5	1824.0	1831.6	1821.0
165°	1857.5	1852.9	1852.9	1862.0	1851.4
167.5°	1883.3	1877.2	1878.8	1887.9	1878.8
170°	1904.6	1898.5	1898.5	1909.2	1898.5
172.5°	1921.4	1915.3	1915.3	1924.4	1913.8
175°	1932.0	1925.9	1925.9	1935.1	1924.4
177.5°	1938.1	1932.0	1932.0	1941.1	1930.5
180°	1936.6	1936.6	1936.6	1936.6	1936.6

(END OF REPORT)