

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032672

Luminaire Tested: S124DIW-B350D470UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032672
REPORT IS A COMBINATION OF REPORTS P997504 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D470UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3387.0 lumens
Efficiency: N/A
Efficacy: 129.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032672

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1032672

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	65	57	55	54	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36
3	80	71	63	58	73	65	59	53	54	49	46	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4708	4708	4708
5°	4712	4573	4579
10°	4673	4446	4415
15°	4606	4295	4230
20°	4520	4132	4039
25°	4424	3959	3834
30°	4307	3772	3608
35°	4187	3581	3389
40°	4062	3376	3157
45°	3930	3171	2940
50°	3784	2971	2699
55°	3627	2737	2461
60°	3464	2482	2212
65°	3278	2218	1932
70°	3065	1900	1631
75°	2746	1532	1307
80°	2340	1107	919
85°	1819	618	495

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3930 cd/sqm

TEST NUMBER: P1032672

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.6
10°-20°	153.3	4.5
20°-30°	225.7	6.7
30°-40°	262.3	7.7
40°-50°	262.3	7.7
50°-60°	229.4	6.8
60°-70°	170.3	5.0
70°-80°	96.6	2.9
80°-90°	29.0	0.9
90°-100°	20.4	0.6
100°-110°	134.5	4.0
110°-120°	256.8	7.6
120°-130°	326.0	9.6
130°-140°	348.8	10.3
140°-150°	326.1	9.6
150°-160°	263.0	7.8
160°-170°	169.6	5.0
170°-180°	58.5	1.7
0°-30°	433.4	12.8
0°-40°	695.7	20.5
0°-60°	1187.4	35.1
0°-90°	1483.3	43.8
90°-120°	411.7	12.2
90°-150°	1412.7	41.7
90°-180°	1904.0	56.2
0°-180°	3387.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	577	575	570	575	574	55
15°	549	547	540	543	542	155
25°	497	494	488	488	486	229
35°	428	425	418	415	413	268
45°	349	346	339	334	332	269
55°	264	263	256	251	248	237
65°	179	177	172	168	165	177
75°	95	93	91	89	88	101
85°	25	25	24	24	24	27
90°	1	6	10	13	14	3
95°	25	10	10	13	13	31
105°	138	141	144	148	131	145
115°	259	260	260	260	260	255
125°	364	365	364	366	366	325
135°	451	450	452	453	454	347
145°	520	521	521	522	523	325
155°	570	571	569	571	570	263
165°	601	599	599	603	599	170
175°	615	612	613	617	612	59
180°	615	615	615	615	615	

TEST NUMBER: P1032672

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	577.4	577.4	577.4	577.4	577.4
2.5°	579.2	577.9	572.8	577.4	576.9
5°	576.9	575.1	570.0	575.1	574.2
7.5°	572.8	570.9	565.4	569.5	569.1
10°	566.8	564.9	558.9	562.6	561.7
12.5°	558.9	557.0	550.6	554.7	553.3
15°	549.2	547.3	540.4	543.2	541.8
17.5°	538.1	535.8	529.3	531.1	530.2
20°	525.6	523.3	516.3	517.7	516.8
22.5°	512.2	508.9	502.0	504.8	502.9
25°	497.4	494.1	487.6	488.1	486.3
27.5°	480.7	477.5	471.4	470.5	468.2
30°	464.0	460.3	454.3	452.5	450.2
32.5°	446.5	443.2	436.7	434.4	432.1
35°	428.0	424.7	418.2	415.0	412.7
37.5°	408.5	405.8	398.8	395.6	392.3
40°	389.6	385.9	378.9	374.3	372.0
42.5°	369.2	367.3	359.5	353.9	352.5
45°	349.3	346.1	338.7	333.6	332.2
47.5°	328.5	326.2	319.2	313.7	310.0
50°	307.2	305.4	298.9	292.4	289.6
52.5°	286.4	284.1	277.1	271.6	267.9
55°	264.2	262.8	256.3	250.8	248.0
57.5°	243.4	242.0	235.5	229.9	227.2
60°	221.6	219.3	213.3	209.1	206.8
62.5°	200.3	198.5	192.0	188.3	186.0
65°	179.0	176.7	172.1	167.5	165.2
67.5°	157.3	155.5	150.8	146.2	145.7
70°	137.4	134.2	130.5	126.8	125.4
72.5°	116.1	112.9	110.1	107.3	105.9
75°	95.3	93.0	90.7	88.8	88.4
77.5°	75.0	74.0	71.7	71.2	69.9
80°	56.9	55.5	54.6	53.7	53.2
82.5°	39.3	38.9	38.9	38.4	37.9
85°	25.0	25.0	24.1	24.1	23.6
87.5°	12.0	11.6	11.1	11.1	11.1
90°	1.4	6.4	10.1	12.9	13.8
92.5°	6.9	6.0	9.7	12.4	12.4
95°	25.3	9.7	10.1	12.9	13.3
97.5°	48.3	58.4	10.1	12.4	12.9
100°	75.5	83.7	20.2	12.4	12.9
102.5°	105.8	111.4	116.9	13.3	13.3
105°	138.5	141.3	143.6	147.7	131.1
107.5°	168.4	169.8	173.0	175.3	177.2
110°	198.8	200.2	202.9	203.8	205.2

TEST NUMBER: P1032672

CATALOG NUMBER: S124DIW-B350D470UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	228.2	231.0	231.9	231.5	233.3
115°	258.6	260.0	259.5	260.4	260.4
117.5°	285.8	287.6	289.0	288.5	288.5
120°	313.4	315.2	314.7	315.7	314.7
122.5°	339.1	340.1	341.0	341.4	340.5
125°	363.5	365.4	364.4	365.8	366.3
127.5°	387.0	387.5	389.8	389.3	388.8
130°	409.5	410.0	411.4	411.8	411.8
132.5°	430.2	431.2	433.0	433.5	433.0
135°	451.0	450.5	452.3	453.3	454.2
137.5°	469.4	469.4	471.7	472.6	472.1
140°	487.3	488.2	489.1	490.5	491.0
142.5°	503.4	505.3	505.7	506.6	506.6
145°	520.0	521.4	521.4	521.8	522.7
147.5°	532.9	535.6	535.2	535.6	536.1
150°	547.1	549.0	548.5	548.5	549.0
152.5°	559.1	560.5	559.5	560.5	560.0
155°	570.1	570.6	569.2	571.1	569.7
157.5°	579.8	579.8	578.0	580.3	578.0
160°	588.1	586.7	586.2	589.0	586.2
162.5°	595.4	593.6	593.1	595.9	592.7
165°	601.4	599.1	599.1	602.8	598.7
167.5°	606.5	604.2	603.7	607.9	603.3
170°	610.6	607.9	608.3	612.0	607.4
172.5°	613.4	610.6	611.1	614.8	609.7
175°	615.2	612.5	612.9	617.1	611.5
177.5°	616.6	613.4	614.3	618.0	612.5
180°	615.2	615.2	615.2	615.2	615.2

(END OF REPORT)