

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032244

Luminaire Tested: S123RDIW-B340D460UB40-4F0-XX-W2A-A

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032244
REPORT IS A COMBINATION OF REPORTS P994323 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D460UB40-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3167.0 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	43	43	42
2	88	81	75	70	80	74	69	65	62	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	59	52	47	49	44	40	40	36	34	31	29	27
5	68	57	49	43	62	52	46	41	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	31	33	29	26	26	23	21
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	20	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5672	5672	5672	5672
5°	5675	6532	5690	4846
10°	5626	7885	5650	4233
15°	5568	8949	5568	3732
20°	5453	9653	5484	3311
25°	5370	9171	5359	3021
30°	5273	6354	5262	2737
35°	5155	4079	5132	2524
40°	5010	2880	4985	2311
45°	4757	2305	4749	2104
50°	4446	1929	4431	1862
55°	4095	1590	4062	1579
60°	3751	1314	3714	1343
65°	3348	1052	3370	1138
70°	2974	730	3057	921
75°	2522	542	2625	707
80°	2009	358	2177	531
85°	1431	171	1556	330

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7571 cd/sqm

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.7	1.6
10°-20°	162.0	5.1
20°-30°	255.1	8.1
30°-40°	265.3	8.4
40°-50°	226.9	7.2
50°-60°	173.0	5.5
60°-70°	110.9	3.5
70°-80°	53.1	1.7
80°-90°	15.2	0.5
90°-100°	21.4	0.7
100°-110°	103.7	3.3
110°-120°	254.0	8.0
120°-130°	322.5	10.2
130°-140°	344.5	10.9
140°-150°	322.2	10.2
150°-160°	259.9	8.2
160°-170°	167.7	5.3
170°-180°	57.8	1.8
0°-30°	468.8	14.8
0°-40°	734.1	23.2
0°-60°	1134.1	35.8
0°-90°	1313.2	41.5
90°-120°	379.2	12.0
90°-150°	1368.4	43.2
90°-180°	1854.0	58.5
0°-180°	3167.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	527	527	527	527	527	
5°	526	626	528	464	526	50
15°	503	889	503	371	503	141
25°	457	916	456	302	457	211
35°	399	397	397	246	399	250
45°	320	212	320	194	320	247
55°	226	133	224	132	226	203
65°	138	77	139	83	138	138
75°	66	32	69	42	66	72
85°	15	8	16	15	15	17
90°	0	14	0	14	0	2
95°	28	17	28	17	28	33
105°	135	20	135	20	135	143
115°	252	266	252	266	252	249
125°	356	363	356	363	356	318
135°	443	448	443	448	443	341
145°	511	516	511	516	511	320
155°	563	562	563	562	563	260
165°	594	593	594	593	594	168
175°	608	606	608	606	608	58
180°	608	608	608	608	608	

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	528.2	531.9	534.6	536.4	540.9	543.6	545.8	549.9	549.9	550.8	552.6
5°	526.4	534.1	539.5	546.7	556.2	560.7	567.0	572.5	580.1	584.2	588.2
7.5°	522.4	533.2	544.5	555.3	569.3	578.3	584.6	598.6	608.5	620.7	630.2
10°	517.0	531.9	546.3	563.0	581.9	595.5	604.9	623.4	642.4	659.5	674.0
12.5°	510.2	528.2	549.0	569.3	595.9	609.4	624.8	647.8	674.9	696.5	715.9
15°	503.0	523.7	547.2	572.0	605.4	624.3	646.4	674.4	704.6	735.8	762.4
17.5°	491.7	517.9	544.0	580.1	619.4	630.7	649.6	687.9	725.4	753.4	785.8
20°	480.4	509.8	542.7	575.2	617.6	643.7	661.3	701.9	742.1	775.9	807.0
22.5°	470.1	500.7	535.0	576.1	615.8	641.9	664.0	706.4	752.9	790.8	829.1
25°	457.4	490.8	528.7	567.5	615.8	635.6	660.0	709.1	758.3	802.1	849.4
27.5°	443.9	477.7	515.2	554.9	599.1	628.4	652.3	705.1	765.1	812.0	860.7
30°	430.4	465.1	501.2	536.8	586.4	614.4	641.9	700.1	768.7	822.4	859.8
32.5°	417.3	446.6	482.2	517.0	566.1	596.8	627.9	695.2	770.0	815.2	833.2
35°	399.2	429.9	458.8	495.8	545.4	575.6	612.2	694.7	764.2	792.1	783.1
37.5°	382.5	408.3	435.8	468.7	519.7	558.9	596.8	683.0	744.8	746.6	695.6
40°	364.0	385.2	408.3	443.0	498.0	536.8	577.9	664.9	709.6	683.0	593.2
42.5°	342.8	361.8	379.8	413.7	473.7	517.0	561.2	642.4	658.6	597.3	503.9
45°	320.3	335.6	352.3	388.0	448.0	490.8	535.0	607.6	591.0	504.3	415.5
47.5°	296.8	309.9	326.2	358.6	420.4	464.2	506.1	558.0	515.6	422.7	348.3
50°	273.4	283.7	299.5	332.9	392.5	432.2	471.0	504.8	445.2	362.7	287.8
52.5°	250.4	258.5	274.7	303.1	360.9	398.8	426.7	439.8	379.4	299.5	249.9
55°	226.0	235.0	245.9	274.7	332.0	360.0	378.5	378.0	315.8	254.0	206.6
57.5°	202.5	210.7	220.1	249.0	295.5	314.4	330.2	322.5	263.4	208.0	177.3
60°	181.8	186.3	196.7	221.0	256.2	272.5	281.5	268.4	215.2	175.5	146.6
62.5°	159.2	163.8	172.3	195.3	217.0	225.6	233.2	216.5	177.7	143.0	125.4
65°	138.5	144.4	149.8	168.3	180.0	190.4	189.5	175.5	138.9	116.4	102.0
67.5°	120.4	122.7	127.2	138.5	143.9	151.6	152.0	136.2	111.9	94.7	86.2
70°	101.0	103.3	106.5	111.9	115.5	117.3	116.4	102.4	84.4	74.0	66.3
72.5°	84.4	83.9	86.2	86.2	89.8	89.3	86.6	75.8	64.1	55.5	51.0
75°	66.3	66.8	67.2	66.3	65.0	63.2	60.9	52.8	45.1	41.1	37.0
77.5°	51.9	51.0	51.4	48.3	46.5	44.7	41.5	37.4	31.1	30.2	28.4
80°	37.0	36.5	36.1	34.7	30.7	28.9	26.6	24.4	23.0	22.1	21.7
82.5°	24.8	24.8	23.9	21.2	18.9	17.6	17.1	16.2	14.9	14.9	14.4
85°	14.9	14.4	13.5	10.8	9.5	9.5	9.5	9.5	8.6	8.6	8.1
87.5°	5.9	5.4	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	0.5	1.5	2.5	3.5	4.5	5.0	5.6	6.9	8.2	9.5	10.8
92.5°	10.4	9.8	9.2	8.6	8.0	7.7	8.1	9.0	9.9	10.8	11.7
95°	27.6	23.5	19.3	15.2	11.1	9.0	9.6	10.7	11.8	12.9	14.0
97.5°	50.1	47.3	44.5	41.7	38.9	37.5	34.9	29.8	24.7	19.6	14.5
100°	76.3	78.3	80.3	82.4	84.4	85.4	77.6	61.9	46.2	30.6	14.9
102.5°	106.2	107.5	108.8	110.1	111.4	112.0	103.3	85.8	68.3	50.9	33.4
105°	134.6	135.7	136.8	137.9	139.0	139.6	135.1	126.0	117.0	107.9	98.9
107.5°	164.9	165.8	166.7	167.6	168.5	169.0	169.7	171.2	172.7	174.2	175.7
110°	195.2	196.0	196.8	197.6	198.4	198.8	199.3	200.4	201.5	202.6	203.7



TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	224.1	224.8	225.5	226.2	226.9	227.2	227.8	228.9	230.0	231.1	232.2
115°	252.5	253.1	253.7	254.3	254.9	255.2	255.7	256.6	257.5	258.4	259.3
117.5°	280.5	281.2	281.9	282.6	283.3	283.7	284.0	284.5	285.0	285.5	286.0
120°	306.3	307.2	308.1	309.0	309.9	310.4	310.5	310.8	311.1	311.4	311.7
122.5°	332.5	333.2	333.9	334.6	335.3	335.7	335.9	336.3	336.7	337.1	337.5
125°	356.0	356.8	357.6	358.4	359.2	359.6	359.8	360.2	360.6	361.0	361.4
127.5°	379.5	380.3	381.1	381.9	382.7	383.1	383.4	383.9	384.4	384.9	385.4
130°	401.2	402.0	402.8	403.6	404.4	404.8	405.0	405.4	405.8	406.2	406.6
132.5°	422.0	422.8	423.6	424.4	425.2	425.6	425.7	426.0	426.3	426.6	426.9
135°	443.2	443.8	444.4	445.0	445.6	445.9	446.1	446.5	446.9	447.3	447.7
137.5°	461.3	462.1	462.9	463.7	464.5	464.9	465.0	465.2	465.4	465.6	465.8
140°	479.3	479.9	480.5	481.1	481.7	482.0	482.2	482.5	482.8	483.1	483.4
142.5°	496.0	496.6	497.2	497.9	498.5	498.8	498.9	499.2	499.5	499.8	500.1
145°	511.4	512.1	512.8	513.5	514.2	514.6	514.7	514.9	515.1	515.3	515.5
147.5°	526.3	526.8	527.3	527.8	528.3	528.6	528.7	528.9	529.1	529.3	529.5
150°	539.9	540.2	540.5	540.8	541.1	541.2	541.3	541.5	541.7	541.9	542.1
152.5°	552.1	552.2	552.3	552.4	552.5	552.5	552.6	552.7	552.8	552.9	553.0
155°	563.4	563.2	563.0	562.8	562.6	562.5	562.5	562.6	562.7	562.8	562.9
157.5°	572.4	572.4	572.4	572.4	572.4	572.4	572.3	572.2	572.1	572.0	571.9
160°	580.5	580.4	580.3	580.2	580.1	580.1	580.0	579.9	579.8	579.7	579.6
162.5°	588.2	587.9	587.6	587.3	587.0	586.8	586.8	586.7	586.6	586.5	586.4
165°	594.1	593.8	593.5	593.2	592.9	592.7	592.7	592.6	592.5	592.4	592.3
167.5°	599.0	598.6	598.2	597.8	597.4	597.2	597.2	597.2	597.2	597.2	597.2
170°	603.1	602.7	602.3	601.9	601.5	601.3	601.3	601.3	601.3	601.3	601.3
172.5°	605.8	605.3	604.8	604.3	603.8	603.6	603.6	603.7	603.8	603.9	604.0
175°	608.1	607.6	607.1	606.6	606.1	605.8	605.9	606.0	606.1	606.2	606.3
177.5°	609.0	608.5	608.0	607.5	607.0	606.7	606.8	606.9	607.0	607.1	607.2
180°	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	556.2	556.2	560.3	564.3	562.1	563.4	568.4	566.6	570.2	569.8	571.1
5°	598.2	603.1	607.2	615.8	617.1	615.8	624.3	626.6	630.7	625.7	627.9
7.5°	645.5	655.9	665.8	678.5	682.5	683.4	687.9	694.3	699.7	689.7	694.7
10°	691.6	707.3	727.6	738.9	748.8	752.5	756.1	760.1	766.4	772.3	767.8
12.5°	741.2	764.2	783.6	803.9	816.1	814.7	825.1	827.8	832.7	834.1	835.9
15°	781.8	814.3	826.4	856.7	859.4	868.4	880.1	890.5	891.8	889.1	889.1
17.5°	820.6	848.5	870.2	894.6	899.5	907.2	922.1	927.0	928.8	928.4	928.4
20°	852.1	870.6	907.2	927.5	935.6	945.5	955.9	962.2	963.6	965.4	962.7
22.5°	872.9	900.9	930.6	947.3	954.1	957.7	964.5	966.3	964.0	964.5	964.9
25°	889.1	916.7	934.7	939.2	938.8	934.2	929.3	920.7	919.8	916.2	909.0
27.5°	893.6	904.0	901.8	883.3	864.8	863.0	833.2	817.0	798.5	801.2	790.8
30°	869.3	855.8	823.7	776.8	757.4	725.8	692.5	657.7	644.2	629.3	656.8
32.5°	809.7	761.5	704.6	643.7	611.3	583.3	547.6	522.4	507.9	495.8	519.2
35°	720.0	644.6	569.3	511.6	484.9	459.7	426.3	413.7	395.6	397.4	399.7
37.5°	604.5	521.5	464.6	407.8	390.2	379.8	355.5	336.1	329.8	328.0	328.0
40°	496.2	428.1	377.6	332.9	319.4	310.8	291.4	282.4	275.6	273.8	276.1
42.5°	410.5	352.3	313.1	283.3	273.8	263.0	254.9	243.6	242.2	239.1	243.1
45°	344.6	294.1	264.8	243.1	235.0	231.0	221.9	215.2	212.5	212.0	215.2
47.5°	292.3	253.1	227.4	213.8	207.5	203.5	195.8	193.1	190.4	191.3	189.9
50°	245.4	216.1	199.4	187.2	183.2	179.1	174.1	171.4	170.1	170.1	169.6
52.5°	210.7	186.3	175.5	164.2	162.4	160.1	154.7	152.9	150.7	150.2	152.0
55°	180.4	163.8	152.9	146.2	144.4	139.8	137.6	135.3	134.0	133.1	133.5
57.5°	154.3	141.6	134.4	128.6	125.4	123.6	119.5	119.1	118.2	118.2	117.7
60°	132.6	123.6	115.0	111.4	109.2	106.9	106.5	103.8	102.4	103.3	102.9
62.5°	112.3	105.1	100.1	96.1	94.7	92.9	91.6	90.7	89.3	89.8	89.8
65°	93.8	88.0	84.4	80.7	80.3	78.5	78.0	77.1	77.1	76.7	77.6
67.5°	77.1	73.1	69.9	67.7	66.3	66.8	65.0	63.6	63.6	63.2	64.5
70°	61.4	59.1	55.9	53.2	51.4	51.4	49.2	48.7	48.7	48.7	48.3
72.5°	47.4	43.3	42.0	41.1	41.1	41.1	40.1	40.1	39.7	40.1	39.7
75°	35.2	34.7	33.8	33.4	33.4	32.9	32.5	32.5	32.5	32.5	32.5
77.5°	27.5	27.5	26.6	26.2	26.2	26.2	25.7	25.7	25.3	25.3	25.3
80°	20.3	20.3	19.4	19.4	19.4	18.9	18.9	18.9	19.4	18.9	18.9
82.5°	14.0	14.0	13.5	14.0	13.5	13.1	13.1	13.1	12.6	13.1	13.1
85°	8.1	8.1	7.7	7.2	7.7	7.7	7.2	7.7	7.2	7.7	7.2
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	11.2	11.6	12.0	12.4	12.6	12.7	12.9	13.2	13.4	13.6	13.4
92.5°	12.4	13.1	13.8	14.5	14.9	15.0	15.1	15.2	15.3	15.4	15.3
95°	14.7	15.4	16.1	16.8	17.2	17.2	17.2	17.2	17.2	17.2	17.2
97.5°	15.3	16.1	16.9	17.7	18.1	18.1	18.2	18.3	18.4	18.5	18.4
100°	15.7	16.5	17.3	18.1	18.5	18.6	18.7	18.8	18.9	19.0	18.9
102.5°	30.1	26.8	23.5	20.2	18.5	18.6	18.8	19.0	19.2	19.4	19.2
105°	81.1	63.4	45.6	27.9	19.0	19.1	19.3	19.5	19.7	19.9	19.7
107.5°	160.3	144.8	129.4	113.9	106.2	99.6	86.5	73.3	60.2	47.0	60.2
110°	200.4	197.1	193.8	190.5	188.8	181.6	167.3	152.9	138.6	124.2	138.6



TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	233.1	234.0	234.9	235.8	236.3	236.2	236.0	235.8	235.6	235.4	235.6
115°	260.3	261.3	262.3	263.3	263.8	264.0	264.4	264.8	265.2	265.6	265.2
117.5°	286.8	287.6	288.4	289.2	289.6	289.6	289.7	289.8	289.9	290.0	289.9
120°	312.5	313.3	314.1	314.9	315.3	315.3	315.3	315.3	315.3	315.3	315.3
122.5°	338.0	338.5	339.0	339.5	339.7	339.8	339.9	340.0	340.1	340.2	340.1
125°	361.6	361.8	362.0	362.2	362.3	362.4	362.6	362.8	363.0	363.2	363.0
127.5°	385.7	386.0	386.3	386.6	386.7	386.6	386.4	386.2	386.0	385.8	386.0
130°	407.0	407.4	407.8	408.2	408.4	408.3	408.1	407.9	407.7	407.5	407.7
132.5°	427.3	427.7	428.1	428.5	428.7	428.6	428.3	428.0	427.7	427.4	427.7
135°	448.0	448.3	448.6	448.9	449.1	448.9	448.6	448.3	448.0	447.7	448.0
137.5°	466.3	466.8	467.3	467.8	468.0	467.9	467.7	467.5	467.3	467.1	467.3
140°	483.8	484.2	484.6	485.0	485.2	485.1	484.9	484.7	484.5	484.3	484.5
142.5°	500.4	500.7	501.0	501.3	501.5	501.3	501.0	500.7	500.4	500.1	500.4
145°	515.7	515.9	516.1	516.3	516.4	516.4	516.4	516.4	516.4	516.4	516.4
147.5°	529.7	529.9	530.1	530.3	530.4	530.1	529.6	529.1	528.6	528.1	528.6
150°	542.3	542.5	542.7	542.9	543.0	542.9	542.6	542.3	542.0	541.7	542.0
152.5°	553.4	553.8	554.2	554.6	554.8	554.5	554.0	553.5	553.0	552.5	553.0
155°	563.4	563.9	564.4	564.9	565.2	564.9	564.3	563.7	563.1	562.5	563.1
157.5°	572.5	573.1	573.7	574.3	574.6	574.2	573.4	572.6	571.8	571.0	571.8
160°	580.2	580.8	581.4	582.0	582.3	582.0	581.3	580.6	579.9	579.2	579.9
162.5°	587.1	587.8	588.5	589.2	589.6	589.3	588.7	588.0	587.4	586.8	587.4
165°	593.1	593.9	594.7	595.5	595.9	595.5	594.8	594.1	593.4	592.7	593.4
167.5°	598.0	598.8	599.7	600.5	600.9	600.5	599.7	598.8	598.0	597.2	598.0
170°	602.1	602.9	603.7	604.5	604.9	604.5	603.7	602.9	602.1	601.3	602.1
172.5°	604.8	605.6	606.4	607.2	607.6	607.2	606.3	605.4	604.5	603.6	604.5
175°	607.0	607.7	608.4	609.1	609.4	609.0	608.2	607.4	606.6	605.8	606.6
177.5°	608.0	608.8	609.6	610.4	610.8	610.3	609.3	608.3	607.3	606.3	607.3
180°	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	568.8	566.1	564.3	563.0	561.6	565.7	560.3	554.4	550.4	547.6	546.7
5°	628.4	622.5	617.6	613.5	614.4	614.4	604.9	594.6	585.5	580.6	575.2
7.5°	697.4	691.1	681.2	678.9	677.1	665.8	656.4	637.4	626.1	614.9	604.9
10°	766.0	757.9	748.4	745.2	740.7	726.7	712.3	687.9	674.0	653.2	640.1
12.5°	830.0	820.1	810.6	808.4	801.6	789.4	764.6	739.4	715.5	693.4	670.3
15°	883.7	881.0	866.6	857.6	842.7	826.0	820.6	786.3	756.1	733.1	691.6
17.5°	928.8	916.2	902.7	896.8	890.9	871.5	852.1	817.0	784.5	750.6	724.0
20°	964.9	950.9	941.5	932.9	930.2	908.1	877.4	846.3	810.6	772.8	738.0
22.5°	966.7	964.9	958.6	953.6	948.2	933.8	909.4	870.6	832.7	791.2	745.7
25°	929.3	926.6	944.6	940.1	943.7	938.3	925.2	892.7	848.5	799.8	753.8
27.5°	816.5	844.0	872.4	882.4	889.1	908.5	914.9	896.8	861.2	809.3	757.9
30°	663.1	699.7	745.7	770.5	789.4	825.5	872.4	878.3	861.6	820.1	757.0
32.5°	520.6	554.0	591.0	620.3	645.5	719.5	782.7	828.2	836.4	814.7	759.2
35°	419.5	434.0	469.2	497.1	531.4	594.6	669.0	742.5	792.1	794.9	752.5
37.5°	346.0	353.7	384.3	400.1	420.4	475.9	545.4	641.5	718.6	755.2	733.5
40°	286.5	304.0	321.6	330.7	345.1	383.4	450.2	525.5	621.2	688.8	704.2
42.5°	248.6	256.2	267.5	280.1	289.2	322.5	367.2	436.2	522.4	616.7	659.1
45°	219.2	221.9	233.7	241.8	251.3	274.7	306.3	364.0	439.8	532.8	604.9
47.5°	194.9	200.3	206.6	211.6	217.9	235.9	263.0	305.0	371.7	454.7	532.3
50°	173.2	176.4	184.5	186.8	191.3	203.9	224.7	256.7	311.7	378.0	458.3
52.5°	152.9	158.8	161.9	165.1	169.2	179.5	193.1	219.2	260.7	323.0	391.1
55°	137.1	138.9	143.5	146.2	149.3	156.5	168.3	187.7	220.1	269.8	334.3
57.5°	121.8	121.8	126.3	128.6	131.7	137.1	147.5	162.4	185.9	222.8	281.9
60°	105.6	106.0	109.6	112.3	113.2	118.6	127.2	138.9	157.0	184.1	232.3
62.5°	91.1	93.4	95.2	96.1	99.2	102.4	109.6	117.7	130.4	154.3	188.6
65°	78.9	79.4	80.7	81.7	83.0	86.6	92.0	97.4	108.3	125.9	153.8
67.5°	65.0	66.8	68.6	68.6	69.9	71.7	77.1	81.7	89.8	100.1	119.1
70°	48.7	49.6	52.3	53.7	55.5	58.6	61.4	64.1	70.4	78.0	92.5
72.5°	40.6	40.6	41.5	42.0	42.0	44.2	48.3	51.0	54.1	59.5	69.5
75°	32.5	32.5	33.8	33.4	34.3	35.2	35.6	37.4	39.2	43.3	49.2
77.5°	25.7	26.2	26.2	26.6	26.6	27.1	27.5	28.4	29.3	31.6	34.3
80°	18.9	19.4	19.4	19.8	19.8	20.3	20.8	21.2	22.1	23.0	24.4
82.5°	13.1	13.5	13.5	14.0	13.5	14.0	14.4	14.4	14.9	15.8	16.2
85°	7.7	7.7	8.1	7.7	7.7	7.7	8.1	8.1	8.6	9.9	9.9
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	13.2	12.9	12.7	12.6	12.4	12.0	11.6	11.2	10.8	9.5	8.2
92.5°	15.2	15.1	15.0	14.9	14.5	13.8	13.1	12.4	11.7	10.8	9.9
95°	17.2	17.2	17.2	17.2	16.8	16.1	15.4	14.7	14.0	12.9	11.8
97.5°	18.3	18.2	18.1	18.1	17.7	16.9	16.1	15.3	14.5	19.6	24.7
100°	18.8	18.7	18.6	18.5	18.1	17.3	16.5	15.7	14.9	30.6	46.2
102.5°	19.0	18.8	18.6	18.5	20.2	23.5	26.8	30.1	33.4	50.9	68.3
105°	19.5	19.3	19.1	19.0	27.9	45.6	63.4	81.1	98.9	107.9	117.0
107.5°	73.3	86.5	99.6	106.2	113.9	129.4	144.8	160.3	175.7	174.2	172.7
110°	152.9	167.3	181.6	188.8	190.5	193.8	197.1	200.4	203.7	202.6	201.5

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	235.8	236.0	236.2	236.3	235.8	234.9	234.0	233.1	232.2	231.1	230.0
115°	264.8	264.4	264.0	263.8	263.3	262.3	261.3	260.3	259.3	258.4	257.5
117.5°	289.8	289.7	289.6	289.6	289.2	288.4	287.6	286.8	286.0	285.5	285.0
120°	315.3	315.3	315.3	315.3	314.9	314.1	313.3	312.5	311.7	311.4	311.1
122.5°	340.0	339.9	339.8	339.7	339.5	339.0	338.5	338.0	337.5	337.1	336.7
125°	362.8	362.6	362.4	362.3	362.2	362.0	361.8	361.6	361.4	361.0	360.6
127.5°	386.2	386.4	386.6	386.7	386.6	386.3	386.0	385.7	385.4	384.9	384.4
130°	407.9	408.1	408.3	408.4	408.2	407.8	407.4	407.0	406.6	406.2	405.8
132.5°	428.0	428.3	428.6	428.7	428.5	428.1	427.7	427.3	426.9	426.6	426.3
135°	448.3	448.6	448.9	449.1	448.9	448.6	448.3	448.0	447.7	447.3	446.9
137.5°	467.5	467.7	467.9	468.0	467.8	467.3	466.8	466.3	465.8	465.6	465.4
140°	484.7	484.9	485.1	485.2	485.0	484.6	484.2	483.8	483.4	483.1	482.8
142.5°	500.7	501.0	501.3	501.5	501.3	501.0	500.7	500.4	500.1	499.8	499.5
145°	516.4	516.4	516.4	516.4	516.3	516.1	515.9	515.7	515.5	515.3	515.1
147.5°	529.1	529.6	530.1	530.4	530.3	530.1	529.9	529.7	529.5	529.3	529.1
150°	542.3	542.6	542.9	543.0	542.9	542.7	542.5	542.3	542.1	541.9	541.7
152.5°	553.5	554.0	554.5	554.8	554.6	554.2	553.8	553.4	553.0	552.9	552.8
155°	563.7	564.3	564.9	565.2	564.9	564.4	563.9	563.4	562.9	562.8	562.7
157.5°	572.6	573.4	574.2	574.6	574.3	573.7	573.1	572.5	571.9	572.0	572.1
160°	580.6	581.3	582.0	582.3	582.0	581.4	580.8	580.2	579.6	579.7	579.8
162.5°	588.0	588.7	589.3	589.6	589.2	588.5	587.8	587.1	586.4	586.5	586.6
165°	594.1	594.8	595.5	595.9	595.5	594.7	593.9	593.1	592.3	592.4	592.5
167.5°	598.8	599.7	600.5	600.9	600.5	599.7	598.8	598.0	597.2	597.2	597.2
170°	602.9	603.7	604.5	604.9	604.5	603.7	602.9	602.1	601.3	601.3	601.3
172.5°	605.4	606.3	607.2	607.6	607.2	606.4	605.6	604.8	604.0	603.9	603.8
175°	607.4	608.2	609.0	609.4	609.1	608.4	607.7	607.0	606.3	606.2	606.1
177.5°	608.3	609.3	610.3	610.8	610.4	609.6	608.8	608.0	607.2	607.1	607.0
180°	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	545.4	543.1	540.9	540.9	535.9	531.4	529.2	530.1	527.3	523.7	520.1
5°	569.3	560.3	558.5	553.5	546.7	537.3	532.3	527.8	522.4	515.2	508.4
7.5°	591.4	579.7	573.4	568.4	555.3	542.2	531.4	524.2	514.7	503.9	495.8
10°	620.3	598.6	591.9	580.6	562.1	543.6	531.0	519.2	506.1	493.5	482.7
12.5°	643.3	618.5	605.8	594.6	570.7	547.2	526.0	511.6	495.8	481.8	467.8
15°	669.4	641.5	619.4	605.8	575.6	547.2	523.3	503.0	485.4	468.3	456.1
17.5°	682.1	646.9	637.0	617.6	573.8	545.4	516.1	494.4	473.2	453.4	438.9
20°	701.9	660.9	636.1	623.0	584.2	542.2	507.9	483.1	461.0	439.8	424.5
22.5°	703.3	658.6	642.4	617.6	569.8	532.8	500.7	470.5	444.8	424.9	409.2
25°	700.1	654.6	632.0	612.2	572.5	527.3	486.3	456.5	431.3	408.3	389.8
27.5°	698.8	642.8	621.6	601.8	557.1	511.6	477.7	443.9	415.0	394.7	375.8
30°	697.0	630.2	604.5	581.5	540.4	499.4	458.8	429.5	401.9	376.2	357.3
32.5°	685.2	613.1	586.9	562.5	518.3	477.3	445.2	414.1	384.3	360.4	343.3
35°	681.6	597.3	563.0	536.8	493.5	457.0	423.1	397.4	369.5	345.5	325.2
37.5°	671.3	581.0	544.0	510.7	465.5	430.8	406.0	380.3	353.2	327.5	311.3
40°	653.2	562.1	520.1	485.8	439.4	404.2	381.2	362.2	335.6	312.6	292.8
42.5°	626.6	542.7	497.6	461.5	410.1	377.1	358.2	340.1	317.6	293.7	277.4
45°	595.9	517.0	475.0	434.9	382.5	350.5	330.7	319.8	299.1	278.8	259.8
47.5°	554.0	490.4	448.9	407.4	354.1	323.0	307.2	296.4	281.9	259.8	244.5
50°	501.2	456.1	416.8	379.8	326.2	296.4	280.6	272.5	260.3	244.5	229.6
52.5°	442.5	416.4	383.9	349.6	297.7	269.8	255.3	249.0	240.0	225.1	212.5
55°	383.4	372.2	350.1	316.2	268.0	245.0	232.3	224.2	217.4	206.6	195.8
57.5°	330.7	325.2	309.9	283.7	243.1	219.2	208.4	203.0	197.6	189.5	178.6
60°	276.1	281.9	266.2	253.1	216.1	195.3	185.9	180.0	177.3	170.1	163.3
62.5°	228.7	234.1	225.1	215.2	189.0	170.5	164.7	159.2	157.4	151.1	144.4
65°	185.9	192.6	185.9	180.4	164.7	149.3	142.1	139.4	137.6	133.5	128.1
67.5°	148.0	154.7	151.6	144.8	139.8	127.2	123.2	120.4	119.5	116.4	111.9
70°	111.4	120.9	121.8	117.7	113.2	107.4	104.7	103.8	101.5	98.8	96.1
72.5°	80.3	91.1	91.6	91.6	88.9	88.9	86.2	84.8	84.8	82.1	78.9
75°	59.1	66.3	67.2	68.1	69.5	70.8	69.0	69.0	68.6	65.9	64.5
77.5°	39.2	45.6	47.8	51.0	52.8	52.8	53.7	54.6	53.7	52.3	51.4
80°	25.3	29.8	32.5	34.3	37.0	38.3	39.7	40.1	39.2	38.8	37.4
82.5°	16.7	18.0	19.4	21.7	24.8	27.1	27.1	26.6	27.5	27.1	26.6
85°	9.5	10.4	10.8	11.3	13.1	15.3	15.8	16.2	17.1	16.2	15.3
87.5°	3.6	4.1	4.1	4.1	5.0	5.4	6.8	8.6	8.1	7.2	7.2
90°	6.9	5.6	5.0	4.5	3.5	2.5	1.5	0.5	1.5	2.5	3.5
92.5°	9.0	8.1	7.7	8.0	8.6	9.2	9.8	10.4	9.8	9.2	8.6
95°	10.7	9.6	9.0	11.1	15.2	19.3	23.5	27.6	23.5	19.3	15.2
97.5°	29.8	34.9	37.5	38.9	41.7	44.5	47.3	50.1	47.3	44.5	41.7
100°	61.9	77.6	85.4	84.4	82.4	80.3	78.3	76.3	78.3	80.3	82.4
102.5°	85.8	103.3	112.0	111.4	110.1	108.8	107.5	106.2	107.5	108.8	110.1
105°	126.0	135.1	139.6	139.0	137.9	136.8	135.7	134.6	135.7	136.8	137.9
107.5°	171.2	169.7	169.0	168.5	167.6	166.7	165.8	164.9	165.8	166.7	167.6
110°	200.4	199.3	198.8	198.4	197.6	196.8	196.0	195.2	196.0	196.8	197.6

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	228.9	227.8	227.2	226.9	226.2	225.5	224.8	224.1	224.8	225.5	226.2
115°	256.6	255.7	255.2	254.9	254.3	253.7	253.1	252.5	253.1	253.7	254.3
117.5°	284.5	284.0	283.7	283.3	282.6	281.9	281.2	280.5	281.2	281.9	282.6
120°	310.8	310.5	310.4	309.9	309.0	308.1	307.2	306.3	307.2	308.1	309.0
122.5°	336.3	335.9	335.7	335.3	334.6	333.9	333.2	332.5	333.2	333.9	334.6
125°	360.2	359.8	359.6	359.2	358.4	357.6	356.8	356.0	356.8	357.6	358.4
127.5°	383.9	383.4	383.1	382.7	381.9	381.1	380.3	379.5	380.3	381.1	381.9
130°	405.4	405.0	404.8	404.4	403.6	402.8	402.0	401.2	402.0	402.8	403.6
132.5°	426.0	425.7	425.6	425.2	424.4	423.6	422.8	422.0	422.8	423.6	424.4
135°	446.5	446.1	445.9	445.6	445.0	444.4	443.8	443.2	443.8	444.4	445.0
137.5°	465.2	465.0	464.9	464.5	463.7	462.9	462.1	461.3	462.1	462.9	463.7
140°	482.5	482.2	482.0	481.7	481.1	480.5	479.9	479.3	479.9	480.5	481.1
142.5°	499.2	498.9	498.8	498.5	497.9	497.2	496.6	496.0	496.6	497.2	497.9
145°	514.9	514.7	514.6	514.2	513.5	512.8	512.1	511.4	512.1	512.8	513.5
147.5°	528.9	528.7	528.6	528.3	527.8	527.3	526.8	526.3	526.8	527.3	527.8
150°	541.5	541.3	541.2	541.1	540.8	540.5	540.2	539.9	540.2	540.5	540.8
152.5°	552.7	552.6	552.5	552.5	552.4	552.3	552.2	552.1	552.2	552.3	552.4
155°	562.6	562.5	562.5	562.6	562.8	563.0	563.2	563.4	563.2	563.0	562.8
157.5°	572.2	572.3	572.4	572.4	572.4	572.4	572.4	572.4	572.4	572.4	572.4
160°	579.9	580.0	580.1	580.1	580.2	580.3	580.4	580.5	580.4	580.3	580.2
162.5°	586.7	586.8	586.8	587.0	587.3	587.6	587.9	588.2	587.9	587.6	587.3
165°	592.6	592.7	592.7	592.9	593.2	593.5	593.8	594.1	593.8	593.5	593.2
167.5°	597.2	597.2	597.2	597.4	597.8	598.2	598.6	599.0	598.6	598.2	597.8
170°	601.3	601.3	601.3	601.5	601.9	602.3	602.7	603.1	602.7	602.3	601.9
172.5°	603.7	603.6	603.6	603.8	604.3	604.8	605.3	605.8	605.3	604.8	604.3
175°	606.0	605.9	605.8	606.1	606.6	607.1	607.6	608.1	607.6	607.1	606.6
177.5°	606.9	606.8	606.7	607.0	607.5	608.0	608.5	609.0	608.5	608.0	607.5
180°	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	520.1	517.9	517.0	514.7	509.3	505.7	501.6	498.9	499.4	497.1	498.5
5°	503.9	503.4	500.3	495.8	488.1	484.0	476.8	473.2	471.4	471.9	469.2
7.5°	490.4	486.3	484.0	476.8	469.6	461.0	455.2	452.0	449.3	446.6	444.8
10°	475.0	471.4	467.8	460.1	450.2	442.1	434.0	430.8	426.7	424.9	423.6
12.5°	458.8	456.5	452.0	443.0	431.7	424.0	414.6	412.8	407.4	403.7	402.8
15°	443.9	442.5	434.4	424.0	412.8	405.1	397.0	391.6	382.5	384.3	381.2
17.5°	428.1	422.2	417.3	403.3	397.9	386.1	376.7	374.0	367.7	363.6	359.5
20°	410.5	406.9	400.6	391.6	378.5	364.9	357.7	353.2	349.6	343.3	341.5
22.5°	393.8	389.3	383.9	372.2	360.9	349.6	339.7	335.6	331.1	326.6	323.9
25°	380.7	374.0	368.1	353.7	342.4	332.9	326.6	319.8	313.5	310.8	309.9
27.5°	360.4	356.4	350.5	337.0	326.6	316.2	310.4	305.9	299.1	295.9	293.2
30°	347.4	339.2	332.5	321.6	311.3	300.0	294.6	289.2	285.1	281.0	277.9
32.5°	329.8	323.4	318.0	307.2	296.8	286.5	280.6	272.5	270.2	267.1	263.4
35°	312.6	308.6	302.7	291.0	279.7	272.5	266.2	258.5	255.8	253.5	250.4
37.5°	296.4	290.5	286.5	275.2	265.3	256.7	251.7	245.4	243.6	240.9	238.6
40°	282.4	276.5	272.5	261.2	250.8	241.8	238.6	232.3	229.6	226.5	225.1
42.5°	266.6	261.6	256.2	248.1	237.3	228.3	221.9	218.3	214.7	213.4	210.7
45°	249.9	245.4	241.3	232.3	221.0	214.7	209.3	204.4	201.6	199.4	197.6
47.5°	235.5	231.4	226.0	216.1	207.1	201.2	195.8	190.8	188.1	185.4	183.2
50°	218.8	216.5	210.7	201.2	192.6	185.9	180.9	176.4	174.6	171.4	167.8
52.5°	203.9	199.8	194.9	187.2	179.5	171.4	164.7	161.9	158.8	157.0	153.8
55°	186.3	183.6	178.2	171.4	163.3	156.5	151.6	148.0	143.9	142.1	138.0
57.5°	171.4	166.5	163.8	155.2	147.5	140.7	137.1	133.5	129.0	126.3	124.5
60°	155.2	150.7	146.6	139.4	134.0	126.8	121.3	118.2	115.0	111.4	109.6
62.5°	139.4	135.8	130.8	125.0	118.2	112.3	108.3	103.8	102.0	98.3	97.0
65°	122.3	119.5	115.5	108.7	103.3	98.3	94.3	90.7	88.9	87.5	86.6
67.5°	106.9	103.3	100.6	94.7	88.9	84.8	82.6	80.3	78.0	76.7	75.3
70°	91.1	88.4	85.7	80.3	76.2	72.6	70.8	69.0	67.7	66.3	65.0
72.5°	74.9	73.5	70.8	67.2	64.1	61.4	60.0	57.7	56.4	54.1	53.2
75°	61.8	59.5	58.2	55.0	52.3	50.1	48.3	45.6	43.8	42.9	42.4
77.5°	48.7	47.8	46.0	43.3	42.0	39.7	37.0	36.1	35.2	35.2	34.7
80°	36.5	35.2	33.8	31.6	30.2	28.4	28.4	28.4	28.0	28.4	28.0
82.5°	24.8	23.9	23.0	21.7	21.2	21.2	21.7	21.7	21.7	21.7	21.7
85°	14.4	14.4	14.4	14.9	14.4	14.4	14.9	15.3	14.9	14.9	14.4
87.5°	6.8	6.8	7.2	7.2	7.7	7.7	7.7	7.7	7.7	7.7	8.1
90°	4.5	5.0	5.6	6.9	8.2	9.5	10.8	11.2	11.6	12.0	12.4
92.5°	8.0	7.7	8.1	9.0	9.9	10.8	11.7	12.4	13.1	13.8	14.5
95°	11.1	9.0	9.6	10.7	11.8	12.9	14.0	14.7	15.4	16.1	16.8
97.5°	38.9	37.5	34.9	29.8	24.7	19.6	14.5	15.3	16.1	16.9	17.7
100°	84.4	85.4	77.6	61.9	46.2	30.6	14.9	15.7	16.5	17.3	18.1
102.5°	111.4	112.0	103.3	85.8	68.3	50.9	33.4	30.1	26.8	23.5	20.2
105°	139.0	139.6	135.1	126.0	117.0	107.9	98.9	81.1	63.4	45.6	27.9
107.5°	168.5	169.0	169.7	171.2	172.7	174.2	175.7	160.3	144.8	129.4	113.9
110°	198.4	198.8	199.3	200.4	201.5	202.6	203.7	200.4	197.1	193.8	190.5

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	226.9	227.2	227.8	228.9	230.0	231.1	232.2	233.1	234.0	234.9	235.8
115°	254.9	255.2	255.7	256.6	257.5	258.4	259.3	260.3	261.3	262.3	263.3
117.5°	283.3	283.7	284.0	284.5	285.0	285.5	286.0	286.8	287.6	288.4	289.2
120°	309.9	310.4	310.5	310.8	311.1	311.4	311.7	312.5	313.3	314.1	314.9
122.5°	335.3	335.7	335.9	336.3	336.7	337.1	337.5	338.0	338.5	339.0	339.5
125°	359.2	359.6	359.8	360.2	360.6	361.0	361.4	361.6	361.8	362.0	362.2
127.5°	382.7	383.1	383.4	383.9	384.4	384.9	385.4	385.7	386.0	386.3	386.6
130°	404.4	404.8	405.0	405.4	405.8	406.2	406.6	407.0	407.4	407.8	408.2
132.5°	425.2	425.6	425.7	426.0	426.3	426.6	426.9	427.3	427.7	428.1	428.5
135°	445.6	445.9	446.1	446.5	446.9	447.3	447.7	448.0	448.3	448.6	448.9
137.5°	464.5	464.9	465.0	465.2	465.4	465.6	465.8	466.3	466.8	467.3	467.8
140°	481.7	482.0	482.2	482.5	482.8	483.1	483.4	483.8	484.2	484.6	485.0
142.5°	498.5	498.8	498.9	499.2	499.5	499.8	500.1	500.4	500.7	501.0	501.3
145°	514.2	514.6	514.7	514.9	515.1	515.3	515.5	515.7	515.9	516.1	516.3
147.5°	528.3	528.6	528.7	528.9	529.1	529.3	529.5	529.7	529.9	530.1	530.3
150°	541.1	541.2	541.3	541.5	541.7	541.9	542.1	542.3	542.5	542.7	542.9
152.5°	552.5	552.5	552.6	552.7	552.8	552.9	553.0	553.4	553.8	554.2	554.6
155°	562.6	562.5	562.5	562.6	562.7	562.8	562.9	563.4	563.9	564.4	564.9
157.5°	572.4	572.4	572.3	572.2	572.1	572.0	571.9	572.5	573.1	573.7	574.3
160°	580.1	580.1	580.0	579.9	579.8	579.7	579.6	580.2	580.8	581.4	582.0
162.5°	587.0	586.8	586.8	586.7	586.6	586.5	586.4	587.1	587.8	588.5	589.2
165°	592.9	592.7	592.7	592.6	592.5	592.4	592.3	593.1	593.9	594.7	595.5
167.5°	597.4	597.2	597.2	597.2	597.2	597.2	597.2	598.0	598.8	599.7	600.5
170°	601.5	601.3	601.3	601.3	601.3	601.3	601.3	602.1	602.9	603.7	604.5
172.5°	603.8	603.6	603.6	603.7	603.8	603.9	604.0	604.8	605.6	606.4	607.2
175°	606.1	605.8	605.9	606.0	606.1	606.2	606.3	607.0	607.7	608.4	609.1
177.5°	607.0	606.7	606.8	606.9	607.0	607.1	607.2	608.0	608.8	609.6	610.4
180°	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	498.0	498.5	497.1	494.4	494.0	494.9	497.6	496.7	494.4	498.5	494.9
5°	470.5	468.3	467.3	468.3	465.5	464.2	466.9	465.5	466.9	467.3	468.7
7.5°	443.9	444.3	441.6	442.1	438.5	439.4	439.4	439.4	440.7	441.6	443.4
10°	420.9	421.8	418.6	419.1	416.4	414.6	415.9	418.6	418.6	418.6	419.5
12.5°	402.4	398.3	396.1	395.6	392.5	391.6	394.3	395.2	397.4	397.4	398.8
15°	379.4	378.5	376.7	376.7	369.0	370.8	371.7	374.9	379.4	375.8	376.7
17.5°	358.6	356.4	354.1	353.2	352.3	349.6	353.2	352.8	355.5	355.9	357.3
20°	340.1	338.3	333.8	334.3	335.2	331.1	333.4	333.4	336.1	338.8	341.9
22.5°	322.1	320.3	318.0	318.9	316.2	315.3	315.3	317.6	320.7	323.0	322.5
25°	308.1	305.0	303.6	302.2	300.9	301.8	300.4	302.7	305.0	306.3	305.0
27.5°	292.3	291.0	288.3	286.9	284.7	285.6	286.5	288.3	289.6	289.6	291.0
30°	277.0	275.2	274.3	272.9	272.9	271.1	271.6	273.4	274.7	276.1	277.9
32.5°	262.1	260.7	259.4	259.4	258.5	258.0	257.6	260.3	260.3	263.0	263.0
35°	249.9	247.7	247.7	245.4	246.3	245.9	245.0	246.8	247.2	249.0	248.6
37.5°	236.4	236.4	235.5	233.2	231.4	231.9	234.1	234.1	235.5	235.0	236.4
40°	222.8	221.9	221.9	220.6	220.1	219.7	220.1	220.6	222.8	222.4	222.8
42.5°	209.3	209.8	207.5	207.5	207.5	206.2	206.6	207.1	208.0	208.9	210.2
45°	196.2	195.3	194.9	194.0	193.1	193.5	193.1	194.9	194.4	195.3	196.7
47.5°	182.2	180.9	180.4	178.6	178.6	179.5	179.1	180.4	180.9	182.2	181.3
50°	168.7	166.9	165.6	166.0	163.3	164.2	164.2	165.6	166.9	167.4	168.3
52.5°	152.9	152.5	152.0	149.8	149.3	148.9	149.3	149.8	151.6	152.9	153.4
55°	137.6	137.1	134.4	133.5	132.2	132.2	133.1	133.5	136.7	137.1	138.9
57.5°	123.6	122.3	119.1	118.6	118.6	118.6	117.3	119.1	120.0	122.3	122.3
60°	108.3	108.3	105.6	105.6	106.0	105.6	105.6	106.0	106.0	107.8	108.7
62.5°	96.1	95.6	95.6	94.7	94.3	94.7	94.3	94.3	94.7	96.1	97.4
65°	85.3	84.8	84.4	83.9	83.0	83.0	83.5	84.4	84.4	85.3	85.7
67.5°	74.9	74.9	74.0	74.0	73.5	73.1	73.5	73.1	74.9	74.9	75.3
70°	64.5	64.1	62.7	62.3	60.9	61.4	61.4	62.7	63.2	64.1	65.0
72.5°	51.9	51.9	51.0	50.1	50.5	49.6	49.6	50.1	50.1	51.4	51.9
75°	42.9	42.0	41.5	42.0	41.5	42.4	41.5	41.5	42.4	42.4	42.4
77.5°	35.2	35.2	34.7	34.7	35.2	34.7	35.2	35.2	35.2	34.7	35.2
80°	28.9	28.4	28.4	28.4	28.0	28.0	28.0	28.0	28.0	28.0	28.0
82.5°	21.7	21.7	21.2	21.7	21.7	21.2	21.7	21.2	21.2	21.7	21.7
85°	14.4	15.3	14.4	14.4	14.9	14.9	15.3	14.9	15.3	14.4	14.9
87.5°	7.7	8.1	8.1	7.7	7.7	8.1	8.1	8.1	8.6	7.7	8.1
90°	12.6	12.7	12.9	13.2	13.4	13.6	13.4	13.2	12.9	12.7	12.6
92.5°	14.9	15.0	15.1	15.2	15.3	15.4	15.3	15.2	15.1	15.0	14.9
95°	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2	17.2
97.5°	18.1	18.1	18.2	18.3	18.4	18.5	18.4	18.3	18.2	18.1	18.1
100°	18.5	18.6	18.7	18.8	18.9	19.0	18.9	18.8	18.7	18.6	18.5
102.5°	18.5	18.6	18.8	19.0	19.2	19.4	19.2	19.0	18.8	18.6	18.5
105°	19.0	19.1	19.3	19.5	19.7	19.9	19.7	19.5	19.3	19.1	19.0
107.5°	106.2	99.6	86.5	73.3	60.2	47.0	60.2	73.3	86.5	99.6	106.2
110°	188.8	181.6	167.3	152.9	138.6	124.2	138.6	152.9	167.3	181.6	188.8

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	236.3	236.2	236.0	235.8	235.6	235.4	235.6	235.8	236.0	236.2	236.3
115°	263.8	264.0	264.4	264.8	265.2	265.6	265.2	264.8	264.4	264.0	263.8
117.5°	289.6	289.6	289.7	289.8	289.9	290.0	289.9	289.8	289.7	289.6	289.6
120°	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3	315.3
122.5°	339.7	339.8	339.9	340.0	340.1	340.2	340.1	340.0	339.9	339.8	339.7
125°	362.3	362.4	362.6	362.8	363.0	363.2	363.0	362.8	362.6	362.4	362.3
127.5°	386.7	386.6	386.4	386.2	386.0	385.8	386.0	386.2	386.4	386.6	386.7
130°	408.4	408.3	408.1	407.9	407.7	407.5	407.7	407.9	408.1	408.3	408.4
132.5°	428.7	428.6	428.3	428.0	427.7	427.4	427.7	428.0	428.3	428.6	428.7
135°	449.1	448.9	448.6	448.3	448.0	447.7	448.0	448.3	448.6	448.9	449.1
137.5°	468.0	467.9	467.7	467.5	467.3	467.1	467.3	467.5	467.7	467.9	468.0
140°	485.2	485.1	484.9	484.7	484.5	484.3	484.5	484.7	484.9	485.1	485.2
142.5°	501.5	501.3	501.0	500.7	500.4	500.1	500.4	500.7	501.0	501.3	501.5
145°	516.4	516.4	516.4	516.4	516.4	516.4	516.4	516.4	516.4	516.4	516.4
147.5°	530.4	530.1	529.6	529.1	528.6	528.1	528.6	529.1	529.6	530.1	530.4
150°	543.0	542.9	542.6	542.3	542.0	541.7	542.0	542.3	542.6	542.9	543.0
152.5°	554.8	554.5	554.0	553.5	553.0	552.5	553.0	553.5	554.0	554.5	554.8
155°	565.2	564.9	564.3	563.7	563.1	562.5	563.1	563.7	564.3	564.9	565.2
157.5°	574.6	574.2	573.4	572.6	571.8	571.0	571.8	572.6	573.4	574.2	574.6
160°	582.3	582.0	581.3	580.6	579.9	579.2	579.9	580.6	581.3	582.0	582.3
162.5°	589.6	589.3	588.7	588.0	587.4	586.8	587.4	588.0	588.7	589.3	589.6
165°	595.9	595.5	594.8	594.1	593.4	592.7	593.4	594.1	594.8	595.5	595.9
167.5°	600.9	600.5	599.7	598.8	598.0	597.2	598.0	598.8	599.7	600.5	600.9
170°	604.9	604.5	603.7	602.9	602.1	601.3	602.1	602.9	603.7	604.5	604.9
172.5°	607.6	607.2	606.3	605.4	604.5	603.6	604.5	605.4	606.3	607.2	607.6
175°	609.4	609.0	608.2	607.4	606.6	605.8	606.6	607.4	608.2	609.0	609.4
177.5°	610.8	610.3	609.3	608.3	607.3	606.3	607.3	608.3	609.3	610.3	610.8
180°	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9	526.9
2.5°	498.5	500.3	498.5	494.9	498.5	500.7	503.0	506.6	508.4	508.4	511.1
5°	470.1	473.7	472.3	471.4	475.0	477.3	480.9	485.4	490.4	493.5	497.1
7.5°	444.8	447.0	449.3	449.3	452.9	457.9	463.3	468.7	475.0	479.5	482.2
10°	422.7	424.5	425.8	427.7	433.1	438.5	445.7	452.5	457.9	462.8	467.3
12.5°	401.5	404.2	407.4	408.7	412.8	419.5	426.3	434.4	443.0	448.0	452.5
15°	381.2	382.5	386.1	390.2	393.8	401.0	409.6	418.2	425.4	433.1	437.1
17.5°	360.4	360.9	370.4	368.1	379.8	386.6	391.1	399.2	411.0	417.3	423.6
20°	340.1	344.6	348.7	351.0	357.3	364.9	378.0	384.3	393.8	399.7	405.1
22.5°	324.3	331.1	331.1	336.5	339.7	346.9	356.4	368.6	378.9	383.0	390.7
25°	310.4	313.5	318.9	320.7	326.6	332.9	339.2	352.3	363.6	369.0	374.4
27.5°	292.3	296.4	303.6	303.6	311.3	318.0	325.7	334.3	345.5	353.2	359.1
30°	278.3	282.4	285.6	290.5	293.7	300.0	313.5	319.8	329.8	336.5	343.7
32.5°	265.3	268.4	271.1	276.5	280.1	287.4	294.6	305.9	314.4	320.7	328.4
35°	250.8	254.0	257.6	261.6	267.1	273.8	280.6	290.1	298.6	304.5	310.8
37.5°	237.3	239.5	245.0	247.7	252.2	258.5	267.1	277.0	284.7	289.2	295.5
40°	224.2	226.0	230.1	235.0	238.2	243.1	252.2	260.7	270.2	275.6	280.6
42.5°	210.2	212.5	216.1	221.0	226.0	231.4	236.4	246.3	254.9	259.4	264.8
45°	198.0	199.4	202.1	207.1	212.0	216.1	223.8	232.8	240.9	244.5	250.4
47.5°	183.6	185.0	189.0	191.3	196.7	202.1	209.8	218.8	226.0	229.6	235.0
50°	168.7	170.1	172.8	177.7	181.3	187.2	194.0	201.6	210.7	215.6	218.8
52.5°	154.3	157.0	159.2	163.3	167.8	173.7	180.0	187.2	194.9	199.8	203.5
55°	139.8	142.1	144.8	147.1	152.5	157.9	165.1	171.9	178.6	183.2	187.2
57.5°	123.6	126.8	129.5	134.0	138.0	142.6	150.7	156.1	164.2	167.4	171.0
60°	109.6	112.8	115.0	118.6	122.3	128.1	133.5	140.3	147.1	151.1	155.6
62.5°	97.9	99.2	100.6	104.2	107.8	113.2	118.6	125.4	132.6	134.9	138.5
65°	86.2	87.5	89.8	92.9	95.6	98.8	104.7	110.1	116.8	120.4	121.8
67.5°	76.2	77.6	78.0	80.3	82.6	86.2	89.3	94.7	101.0	103.3	106.0
70°	65.0	67.2	67.7	69.5	70.4	72.6	76.2	80.3	85.3	89.3	91.6
72.5°	51.9	55.0	55.9	58.6	60.0	62.3	65.0	68.1	71.3	73.1	74.9
75°	42.4	43.3	43.8	46.0	48.3	51.4	52.8	54.6	57.3	59.5	61.4
77.5°	35.2	35.6	36.1	36.1	36.5	38.3	41.1	43.3	45.1	46.0	47.4
80°	28.4	28.0	28.0	28.4	28.4	28.4	29.3	32.5	33.4	35.6	35.2
82.5°	22.1	21.2	21.7	21.2	21.2	21.2	21.2	21.7	21.7	23.0	23.9
85°	14.4	14.9	14.4	14.4	14.0	14.4	14.0	14.0	13.5	13.5	13.1
87.5°	7.7	8.1	7.7	7.7	7.2	7.7	7.2	7.2	6.8	6.8	5.9
90°	12.4	12.0	11.6	11.2	10.8	9.5	8.2	6.9	5.6	5.0	4.5
92.5°	14.5	13.8	13.1	12.4	11.7	10.8	9.9	9.0	8.1	7.7	8.0
95°	16.8	16.1	15.4	14.7	14.0	12.9	11.8	10.7	9.6	9.0	11.1
97.5°	17.7	16.9	16.1	15.3	14.5	19.6	24.7	29.8	34.9	37.5	38.9
100°	18.1	17.3	16.5	15.7	14.9	30.6	46.2	61.9	77.6	85.4	84.4
102.5°	20.2	23.5	26.8	30.1	33.4	50.9	68.3	85.8	103.3	112.0	111.4
105°	27.9	45.6	63.4	81.1	98.9	107.9	117.0	126.0	135.1	139.6	139.0
107.5°	113.9	129.4	144.8	160.3	175.7	174.2	172.7	171.2	169.7	169.0	168.5
110°	190.5	193.8	197.1	200.4	203.7	202.6	201.5	200.4	199.3	198.8	198.4

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	235.8	234.9	234.0	233.1	232.2	231.1	230.0	228.9	227.8	227.2	226.9
115°	263.3	262.3	261.3	260.3	259.3	258.4	257.5	256.6	255.7	255.2	254.9
117.5°	289.2	288.4	287.6	286.8	286.0	285.5	285.0	284.5	284.0	283.7	283.3
120°	314.9	314.1	313.3	312.5	311.7	311.4	311.1	310.8	310.5	310.4	309.9
122.5°	339.5	339.0	338.5	338.0	337.5	337.1	336.7	336.3	335.9	335.7	335.3
125°	362.2	362.0	361.8	361.6	361.4	361.0	360.6	360.2	359.8	359.6	359.2
127.5°	386.6	386.3	386.0	385.7	385.4	384.9	384.4	383.9	383.4	383.1	382.7
130°	408.2	407.8	407.4	407.0	406.6	406.2	405.8	405.4	405.0	404.8	404.4
132.5°	428.5	428.1	427.7	427.3	426.9	426.6	426.3	426.0	425.7	425.6	425.2
135°	448.9	448.6	448.3	448.0	447.7	447.3	446.9	446.5	446.1	445.9	445.6
137.5°	467.8	467.3	466.8	466.3	465.8	465.6	465.4	465.2	465.0	464.9	464.5
140°	485.0	484.6	484.2	483.8	483.4	483.1	482.8	482.5	482.2	482.0	481.7
142.5°	501.3	501.0	500.7	500.4	500.1	499.8	499.5	499.2	498.9	498.8	498.5
145°	516.3	516.1	515.9	515.7	515.5	515.3	515.1	514.9	514.7	514.6	514.2
147.5°	530.3	530.1	529.9	529.7	529.5	529.3	529.1	528.9	528.7	528.6	528.3
150°	542.9	542.7	542.5	542.3	542.1	541.9	541.7	541.5	541.3	541.2	541.1
152.5°	554.6	554.2	553.8	553.4	553.0	552.9	552.8	552.7	552.6	552.5	552.5
155°	564.9	564.4	563.9	563.4	562.9	562.8	562.7	562.6	562.5	562.5	562.6
157.5°	574.3	573.7	573.1	572.5	571.9	572.0	572.1	572.2	572.3	572.4	572.4
160°	582.0	581.4	580.8	580.2	579.6	579.7	579.8	579.9	580.0	580.1	580.1
162.5°	589.2	588.5	587.8	587.1	586.4	586.5	586.6	586.7	586.8	586.8	587.0
165°	595.5	594.7	593.9	593.1	592.3	592.4	592.5	592.6	592.7	592.7	592.9
167.5°	600.5	599.7	598.8	598.0	597.2	597.2	597.2	597.2	597.2	597.2	597.4
170°	604.5	603.7	602.9	602.1	601.3	601.3	601.3	601.3	601.3	601.3	601.5
172.5°	607.2	606.4	605.6	604.8	604.0	603.9	603.8	603.7	603.6	603.6	603.8
175°	609.1	608.4	607.7	607.0	606.3	606.2	606.1	606.0	605.9	605.8	606.1
177.5°	610.4	609.6	608.8	608.0	607.2	607.1	607.0	606.9	606.8	606.7	607.0
180°	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1	608.1

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	526.9	526.9	526.9	526.9
2.5°	513.4	516.5	522.8	528.2
5°	502.5	507.5	517.0	526.4
7.5°	489.5	497.1	509.3	522.4
10°	476.8	486.7	501.6	517.0
12.5°	464.2	474.6	490.4	510.2
15°	449.3	460.1	479.1	503.0
17.5°	436.2	450.7	467.8	491.7
20°	422.2	433.1	455.2	480.4
22.5°	404.6	422.7	443.4	470.1
25°	390.7	406.4	427.2	457.4
27.5°	373.5	392.0	417.3	443.9
30°	359.5	374.9	398.3	430.4
32.5°	343.3	361.3	385.7	417.3
35°	328.9	344.2	367.2	399.2
37.5°	311.7	328.4	354.1	382.5
40°	296.8	313.1	337.4	364.0
42.5°	278.8	295.9	320.3	342.8
45°	264.4	280.1	299.5	320.3
47.5°	246.8	263.4	282.4	296.8
50°	231.0	246.3	261.2	273.4
52.5°	213.8	227.8	241.3	250.4
55°	198.0	208.9	219.7	226.0
57.5°	179.5	189.9	198.9	202.5
60°	163.3	171.9	177.7	181.8
62.5°	146.2	152.5	157.0	159.2
65°	129.5	134.0	136.2	138.5
67.5°	112.3	116.4	117.7	120.4
70°	94.3	98.8	99.7	101.0
72.5°	80.7	80.7	82.6	84.4
75°	64.5	65.4	66.3	66.3
77.5°	50.5	50.5	51.4	51.9
80°	37.0	37.4	37.4	37.0
82.5°	25.3	26.2	25.3	24.8
85°	14.0	15.8	14.9	14.9
87.5°	5.9	5.9	6.8	5.9
90°	3.5	2.5	1.5	0.5
92.5°	8.6	9.2	9.8	10.4
95°	15.2	19.3	23.5	27.6
97.5°	41.7	44.5	47.3	50.1
100°	82.4	80.3	78.3	76.3
102.5°	110.1	108.8	107.5	106.2
105°	137.9	136.8	135.7	134.6
107.5°	167.6	166.7	165.8	164.9
110°	197.6	196.8	196.0	195.2

TEST NUMBER: P1032244

CATALOG NUMBER: S123RDIW-B340D460UB40-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	226.2	225.5	224.8	224.1
115°	254.3	253.7	253.1	252.5
117.5°	282.6	281.9	281.2	280.5
120°	309.0	308.1	307.2	306.3
122.5°	334.6	333.9	333.2	332.5
125°	358.4	357.6	356.8	356.0
127.5°	381.9	381.1	380.3	379.5
130°	403.6	402.8	402.0	401.2
132.5°	424.4	423.6	422.8	422.0
135°	445.0	444.4	443.8	443.2
137.5°	463.7	462.9	462.1	461.3
140°	481.1	480.5	479.9	479.3
142.5°	497.9	497.2	496.6	496.0
145°	513.5	512.8	512.1	511.4
147.5°	527.8	527.3	526.8	526.3
150°	540.8	540.5	540.2	539.9
152.5°	552.4	552.3	552.2	552.1
155°	562.8	563.0	563.2	563.4
157.5°	572.4	572.4	572.4	572.4
160°	580.2	580.3	580.4	580.5
162.5°	587.3	587.6	587.9	588.2
165°	593.2	593.5	593.8	594.1
167.5°	597.8	598.2	598.6	599.0
170°	601.9	602.3	602.7	603.1
172.5°	604.3	604.8	605.3	605.8
175°	606.6	607.1	607.6	608.1
177.5°	607.5	608.0	608.5	609.0
180°	608.1	608.1	608.1	608.1

(END OF REPORT)