

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032298

Luminaire Tested: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032298
REPORT IS A COMBINATION OF REPORTS P994449 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D1320UB35-4F0-XX-W2A-A
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7533.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	94	90	86	83	84	80	77	75	63	61	60	48	47	45	34	33	32
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	50	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	26	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9632	9632	9632	9632
5°	9639	11092	9663	8230
10°	9553	13390	9595	7188
15°	9456	15197	9456	6338
20°	9262	16392	9314	5622
25°	9119	15574	9102	5130
30°	8954	10791	8936	4649
35°	8756	6928	8716	4286
40°	8508	4892	8465	3925
45°	8078	3914	8066	3573
50°	7548	3275	7524	3162
55°	6954	2699	6898	2681
60°	6370	2231	6308	2280
65°	5686	1785	5722	1933
70°	5053	1240	5189	1562
75°	4283	921	4458	1201
80°	3409	611	3703	901
85°	2430	288	2651	561

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12858 cd/sqm

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	1.2
10°-20°	275.1	3.7
20°-30°	433.2	5.8
30°-40°	450.5	6.0
40°-50°	385.4	5.1
50°-60°	293.8	3.9
60°-70°	188.2	2.5
70°-80°	90.2	1.2
80°-90°	27.2	0.4
90°-100°	61.3	0.8
100°-110°	296.5	3.9
110°-120°	726.6	9.6
120°-130°	922.4	12.2
130°-140°	985.3	13.1
140°-150°	921.4	12.2
150°-160°	743.2	9.9
160°-170°	479.6	6.4
170°-180°	165.3	2.2
0°-30°	796.2	10.6
0°-40°	1246.6	16.5
0°-60°	1925.8	25.6
0°-90°	2231.5	29.6
90°-120°	1084.4	14.4
90°-150°	3913.4	52.0
90°-180°	5302.0	70.4
0°-180°	7533.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	894	1062	896	788	894	85
15°	854	1510	854	630	854	240
25°	777	1556	775	512	777	358
35°	678	675	675	418	678	424
45°	544	360	543	329	544	419
55°	384	226	381	224	384	344
65°	235	130	237	141	235	235
75°	113	55	117	72	113	122
85°	25	13	28	25	25	28
90°	1	39	1	39	1	6
95°	79	49	79	49	79	94
105°	385	57	385	57	385	408
115°	722	760	722	760	722	713
125°	1018	1039	1018	1039	1018	910
135°	1267	1280	1267	1280	1267	976
145°	1462	1477	1462	1477	1462	916
155°	1611	1608	1611	1608	1611	742
165°	1699	1695	1699	1695	1699	480
175°	1739	1733	1739	1733	1739	166
180°	1739	1739	1739	1739	1739	

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	897.1	903.2	907.8	910.8	918.5	923.1	926.9	933.8	933.8	935.4	938.4
5°	894.0	907.0	916.2	928.5	944.6	952.2	962.9	972.1	985.2	992.0	998.9
7.5°	887.1	905.5	924.6	943.0	966.8	982.1	992.8	1016.6	1033.4	1054.1	1070.2
10°	877.9	903.2	927.7	956.0	988.2	1011.2	1027.3	1058.7	1090.9	1120.0	1144.5
12.5°	866.4	897.1	932.3	966.8	1012.0	1034.9	1061.0	1100.1	1146.0	1182.8	1215.7
15°	854.2	889.4	929.2	971.4	1028.1	1060.2	1097.8	1145.3	1196.6	1249.4	1294.6
17.5°	835.0	879.4	923.9	985.2	1051.8	1071.0	1103.1	1168.2	1231.8	1279.3	1334.5
20°	815.9	865.6	921.6	976.7	1048.7	1093.2	1123.0	1192.0	1260.2	1317.6	1370.5
22.5°	798.2	850.3	908.5	978.3	1045.7	1090.1	1127.6	1199.7	1278.6	1342.9	1408.0
25°	776.8	833.5	897.8	963.7	1045.7	1079.4	1120.7	1204.2	1287.7	1362.1	1442.5
27.5°	753.8	811.3	874.8	942.3	1017.3	1067.1	1107.7	1197.4	1299.2	1378.9	1461.6
30°	730.8	789.8	851.1	911.6	995.9	1043.4	1090.1	1188.9	1305.4	1396.5	1460.1
32.5°	708.6	758.4	818.9	877.9	961.4	1013.5	1066.4	1180.5	1307.7	1384.3	1414.9
35°	678.0	730.1	779.1	841.9	926.2	977.5	1039.5	1179.7	1297.7	1345.2	1329.9
37.5°	649.6	693.3	740.0	795.9	882.5	949.1	1013.5	1159.8	1264.8	1267.8	1181.3
40°	618.2	654.2	693.3	752.3	845.7	911.6	981.3	1129.2	1205.0	1159.8	1007.4
42.5°	582.2	614.4	645.0	702.5	804.4	877.9	953.0	1090.9	1118.4	1014.3	855.7
45°	543.9	569.9	598.3	658.8	760.7	833.5	908.5	1031.9	1003.5	856.5	705.5
47.5°	504.1	526.3	553.9	609.0	714.0	788.3	859.5	947.6	875.6	717.8	591.4
50°	464.2	481.9	508.7	565.4	666.5	733.9	799.8	857.2	756.1	615.9	488.7
52.5°	425.2	439.0	466.5	514.8	612.8	677.2	724.7	746.9	644.3	508.7	424.4
55°	383.8	399.1	417.5	466.5	563.8	611.3	642.7	642.0	536.2	431.3	350.9
57.5°	344.0	357.8	373.8	422.9	501.8	533.9	560.8	547.7	447.4	353.2	301.1
60°	308.7	316.4	334.0	375.4	435.1	462.7	478.0	455.8	365.4	298.0	249.0
62.5°	270.4	278.1	292.6	331.7	368.5	383.0	396.1	367.7	301.8	242.8	213.0
65°	235.2	245.1	254.3	285.7	305.7	323.3	321.7	298.0	235.9	197.6	173.1
67.5°	204.5	208.4	216.0	235.2	244.4	257.4	258.2	231.4	190.0	160.9	146.3
70°	171.6	175.4	180.8	190.0	196.1	199.2	197.6	173.9	143.3	125.6	112.6
72.5°	143.3	142.5	146.3	146.3	152.4	151.7	147.1	128.7	108.8	94.2	86.6
75°	112.6	113.4	114.1	112.6	110.3	107.2	103.4	89.6	76.6	69.7	62.8
77.5°	88.1	86.6	87.3	82.0	78.9	75.8	70.5	63.6	52.9	51.3	48.3
80°	62.8	62.1	61.3	59.0	52.1	49.0	45.2	41.4	39.1	37.5	36.8
82.5°	42.1	42.1	40.6	36.0	32.2	29.9	29.1	27.6	25.3	25.3	24.5
85°	25.3	24.5	23.0	18.4	16.1	16.1	16.1	16.1	14.6	14.6	13.8
87.5°	10.0	9.2	6.9	6.9	6.1	6.1	6.1	5.4	5.4	4.6	4.6
90°	1.3	4.2	7.0	9.9	12.8	14.2	16.1	19.8	23.5	27.3	31.0
92.5°	29.7	28.0	26.3	24.6	22.9	22.0	23.3	25.9	28.4	31.0	33.6
95°	78.8	67.0	55.2	43.5	31.7	25.8	27.4	30.6	33.7	36.9	40.1
97.5°	143.4	135.4	127.3	119.3	111.2	107.2	99.9	85.2	70.6	55.9	41.3
100°	218.3	224.1	229.8	235.6	241.3	244.2	221.8	177.0	132.2	87.4	42.6
102.5°	303.6	307.3	311.1	314.8	318.5	320.4	295.4	245.5	195.5	145.6	95.6
105°	385.0	388.2	391.3	394.5	397.6	399.2	386.3	360.4	334.6	308.7	282.9
107.5°	471.6	474.2	476.8	479.3	481.9	483.2	485.4	489.7	494.0	498.3	502.6
110°	558.1	560.4	562.7	565.0	567.3	568.5	570.1	573.2	576.4	579.5	582.7

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	640.8	642.8	644.8	646.9	648.9	649.9	651.5	654.6	657.8	660.9	664.1
115°	722.2	723.9	725.7	727.4	729.1	730.0	731.3	733.9	736.4	739.0	741.6
117.5°	802.3	804.3	806.3	808.4	810.4	811.4	812.1	813.5	815.0	816.4	817.8
120°	876.0	878.6	881.2	883.7	886.3	887.6	888.0	888.9	889.8	890.6	891.5
122.5°	950.9	952.9	954.9	956.9	958.9	959.9	960.5	961.6	962.8	963.9	965.1
125°	1018.1	1020.4	1022.7	1025.0	1027.3	1028.4	1029.0	1030.1	1031.3	1032.4	1033.6
127.5°	1085.3	1087.6	1089.9	1092.2	1094.5	1095.6	1096.3	1097.8	1099.2	1100.7	1102.1
130°	1147.3	1149.6	1151.9	1154.2	1156.5	1157.6	1158.2	1159.3	1160.5	1161.6	1162.8
132.5°	1206.7	1209.0	1211.3	1213.6	1215.9	1217.1	1217.5	1218.4	1219.2	1220.1	1220.9
135°	1267.4	1269.1	1270.9	1272.6	1274.3	1275.2	1275.8	1276.9	1278.1	1279.2	1280.4
137.5°	1319.1	1321.4	1323.7	1326.0	1328.3	1329.5	1329.8	1330.3	1330.9	1331.4	1332.0
140°	1370.8	1372.5	1374.2	1375.9	1377.6	1378.5	1378.9	1379.8	1380.7	1381.5	1382.4
142.5°	1418.6	1420.3	1422.1	1423.8	1425.5	1426.4	1426.8	1427.7	1428.5	1429.4	1430.2
145°	1462.5	1464.5	1466.5	1468.6	1470.6	1471.6	1471.9	1472.5	1473.0	1473.6	1474.2
147.5°	1505.2	1506.6	1508.0	1509.5	1510.9	1511.6	1511.9	1512.5	1513.0	1513.6	1514.2
150°	1543.9	1544.8	1545.6	1546.5	1547.4	1547.8	1548.1	1548.7	1549.2	1549.8	1550.4
152.5°	1578.8	1579.1	1579.4	1579.7	1580.0	1580.1	1580.2	1580.5	1580.8	1581.1	1581.4
155°	1611.1	1610.5	1609.9	1609.4	1608.8	1608.5	1608.6	1608.9	1609.2	1609.5	1609.8
157.5°	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.8	1636.5	1636.2	1636.0	1635.7
160°	1660.2	1659.9	1659.6	1659.3	1659.0	1658.9	1658.8	1658.5	1658.2	1657.9	1657.6
162.5°	1682.2	1681.3	1680.5	1679.6	1678.7	1678.3	1678.2	1677.9	1677.6	1677.3	1677.0
165°	1699.0	1698.1	1697.3	1696.4	1695.5	1695.1	1695.0	1694.7	1694.4	1694.1	1693.8
167.5°	1713.2	1712.0	1710.9	1709.7	1708.6	1708.0	1708.0	1708.0	1708.0	1708.0	1708.0
170°	1724.8	1723.6	1722.5	1721.3	1720.2	1719.6	1719.6	1719.6	1719.6	1719.6	1719.6
172.5°	1732.6	1731.2	1729.7	1728.3	1726.8	1726.1	1726.2	1726.5	1726.8	1727.1	1727.4
175°	1739.0	1737.6	1736.2	1734.7	1733.3	1732.6	1732.7	1733.0	1733.3	1733.5	1733.8
177.5°	1741.6	1740.2	1738.7	1737.3	1735.8	1735.1	1735.2	1735.5	1735.8	1736.1	1736.4
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	944.6	944.6	951.4	958.3	954.5	956.8	965.2	962.2	968.3	967.5	969.8
5°	1015.8	1024.2	1031.1	1045.7	1048.0	1045.7	1060.2	1064.1	1071.0	1062.5	1066.4
7.5°	1096.2	1113.9	1130.7	1152.2	1159.1	1160.6	1168.2	1179.0	1188.2	1171.3	1179.7
10°	1174.4	1201.2	1235.7	1254.8	1271.7	1277.8	1283.9	1290.8	1301.5	1311.5	1303.8
12.5°	1258.6	1297.7	1330.6	1365.1	1385.8	1383.5	1401.1	1405.7	1414.1	1416.4	1419.5
15°	1327.6	1382.7	1403.4	1454.7	1459.3	1474.7	1494.6	1512.2	1514.5	1509.9	1509.9
17.5°	1393.5	1441.0	1477.7	1519.1	1527.5	1540.5	1565.8	1574.3	1577.3	1576.6	1576.6
20°	1447.1	1478.5	1540.5	1575.0	1588.8	1605.7	1623.3	1634.0	1636.3	1639.4	1634.8
22.5°	1482.3	1529.8	1580.4	1608.7	1620.2	1626.3	1637.8	1640.9	1637.1	1637.8	1638.6
25°	1509.9	1556.6	1587.3	1594.9	1594.2	1586.5	1578.1	1563.5	1562.0	1555.9	1543.6
27.5°	1517.6	1535.2	1531.4	1499.9	1468.5	1465.5	1414.9	1387.3	1355.9	1360.5	1342.9
30°	1476.2	1453.2	1398.8	1319.2	1286.2	1232.6	1175.9	1116.9	1093.9	1068.7	1115.4
32.5°	1375.1	1293.1	1196.6	1093.2	1038.0	990.5	930.0	887.1	862.6	841.9	881.7
35°	1222.6	1094.7	966.8	868.7	823.5	780.6	723.9	702.5	671.8	674.9	678.7
37.5°	1026.5	885.6	789.0	692.5	662.6	645.0	603.7	570.7	560.0	556.9	556.9
40°	842.7	727.0	641.2	565.4	542.4	527.8	494.9	479.6	468.1	465.0	468.8
42.5°	697.1	598.3	531.6	481.1	465.0	446.6	432.8	413.7	411.4	406.0	412.9
45°	585.3	499.5	449.7	412.9	399.1	392.2	376.9	365.4	360.8	360.0	365.4
47.5°	496.4	429.8	386.1	363.1	352.4	345.5	332.5	327.9	323.3	324.8	322.5
50°	416.7	366.9	338.6	317.9	311.0	304.1	295.7	291.1	288.8	288.8	288.0
52.5°	357.8	316.4	298.0	278.8	275.8	272.0	262.8	259.7	255.9	255.1	258.2
55°	306.4	278.1	259.7	248.2	245.1	237.5	233.6	229.8	227.5	226.0	226.8
57.5°	262.0	240.5	228.3	218.3	213.0	209.9	203.0	202.2	200.7	200.7	199.9
60°	225.2	209.9	195.3	189.2	185.4	181.6	180.8	176.2	173.9	175.4	174.7
62.5°	190.7	178.5	170.1	163.2	160.9	157.8	155.5	154.0	151.7	152.4	152.4
65°	159.3	149.4	143.3	137.1	136.4	133.3	132.5	131.0	131.0	130.2	131.8
67.5°	131.0	124.1	118.7	114.9	112.6	113.4	110.3	108.0	108.0	107.2	109.5
70°	104.2	100.4	95.0	90.4	87.3	87.3	83.5	82.7	82.7	82.7	82.0
72.5°	80.4	73.5	71.2	69.7	69.7	69.7	68.2	68.2	67.4	68.2	67.4
75°	59.8	59.0	57.5	56.7	56.7	55.9	55.2	55.2	55.2	55.2	55.2
77.5°	46.7	46.7	45.2	44.4	44.4	44.4	43.7	43.7	42.9	42.9	42.9
80°	34.5	34.5	32.9	32.9	32.9	32.2	32.2	32.2	32.9	32.2	32.2
82.5°	23.7	23.7	23.0	23.7	23.0	22.2	22.2	22.2	21.4	22.2	22.2
85°	13.8	13.8	13.0	12.3	13.0	13.0	12.3	13.0	12.3	13.0	12.3
87.5°	5.4	4.6	4.6	4.6	3.8	4.6	3.8	3.8	4.6	3.8	4.6
90°	32.2	33.3	34.5	35.6	36.2	36.5	37.1	37.6	38.2	38.8	38.2
92.5°	35.6	37.6	39.6	41.6	42.6	42.7	43.0	43.3	43.6	43.9	43.6
95°	42.1	44.1	46.1	48.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1
97.5°	43.6	45.9	48.2	50.5	51.7	51.8	52.1	52.4	52.7	53.0	52.7
100°	44.9	47.2	49.5	51.8	53.0	53.1	53.4	53.7	54.0	54.3	54.0
102.5°	86.1	76.7	67.2	57.7	53.0	53.3	53.9	54.4	55.0	55.6	55.0
105°	232.1	181.3	130.5	79.7	54.3	54.6	55.1	55.7	56.2	56.8	56.2
107.5°	458.4	414.2	369.9	325.7	303.6	284.8	247.2	209.6	172.0	134.4	172.0
110°	573.2	563.7	554.2	544.7	540.0	519.5	478.4	437.4	396.3	355.3	396.3

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	666.7	669.3	671.8	674.4	675.7	675.4	674.8	674.3	673.7	673.1	673.7
115°	744.5	747.3	750.2	753.1	754.5	755.1	756.2	757.4	758.5	759.7	758.5
117.5°	820.1	822.4	824.7	827.0	828.2	828.3	828.6	828.9	829.2	829.5	829.2
120°	893.8	896.1	898.4	900.7	901.8	901.8	901.8	901.8	901.8	901.8	901.8
122.5°	966.5	968.0	969.4	970.9	971.6	971.7	972.0	972.3	972.6	972.9	972.6
125°	1034.2	1034.8	1035.3	1035.9	1036.2	1036.5	1037.1	1037.6	1038.2	1038.8	1038.2
127.5°	1102.9	1103.8	1104.6	1105.5	1105.9	1105.6	1105.1	1104.5	1104.0	1103.4	1104.0
130°	1164.0	1165.1	1166.3	1167.4	1168.0	1167.7	1167.1	1166.6	1166.0	1165.4	1166.0
132.5°	1222.1	1223.2	1224.4	1225.5	1226.1	1225.7	1224.8	1223.9	1223.1	1222.2	1223.1
135°	1281.2	1282.1	1282.9	1283.8	1284.2	1283.8	1282.9	1282.1	1281.2	1280.4	1281.2
137.5°	1333.4	1334.9	1336.3	1337.8	1338.5	1338.2	1337.6	1337.1	1336.5	1335.9	1336.5
140°	1383.6	1384.7	1385.9	1387.0	1387.6	1387.3	1386.7	1386.2	1385.6	1385.0	1385.6
142.5°	1431.1	1431.9	1432.8	1433.7	1434.1	1433.7	1432.8	1431.9	1431.1	1430.2	1431.1
145°	1474.8	1475.3	1475.9	1476.4	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
147.5°	1514.8	1515.4	1515.9	1516.5	1516.8	1516.1	1514.6	1513.2	1511.7	1510.3	1511.7
150°	1551.0	1551.6	1552.1	1552.7	1553.0	1552.6	1551.7	1550.8	1550.0	1549.1	1550.0
152.5°	1582.6	1583.7	1584.9	1586.0	1586.6	1585.9	1584.4	1583.0	1581.5	1580.1	1581.5
155°	1611.2	1612.7	1614.1	1615.6	1616.3	1615.4	1613.7	1612.0	1610.2	1608.5	1610.2
157.5°	1637.4	1639.1	1640.8	1642.5	1643.4	1642.3	1640.0	1637.7	1635.4	1633.1	1635.4
160°	1659.3	1661.1	1662.8	1664.5	1665.4	1664.4	1662.4	1660.3	1658.3	1656.3	1658.3
162.5°	1679.0	1681.0	1683.0	1685.0	1686.0	1685.1	1683.4	1681.7	1680.0	1678.3	1680.0
165°	1696.1	1698.4	1700.7	1703.0	1704.1	1703.1	1701.1	1699.1	1697.1	1695.1	1697.1
167.5°	1710.3	1712.6	1714.9	1717.2	1718.3	1717.2	1714.9	1712.6	1710.3	1708.0	1710.3
170°	1721.9	1724.2	1726.5	1728.8	1730.0	1728.8	1726.5	1724.2	1721.9	1719.6	1721.9
172.5°	1729.7	1732.0	1734.3	1736.6	1737.7	1736.4	1733.8	1731.3	1728.7	1726.1	1728.7
175°	1735.8	1737.8	1739.9	1741.9	1742.9	1741.8	1739.5	1737.2	1734.9	1732.6	1734.9
177.5°	1738.7	1741.0	1743.3	1745.6	1746.8	1745.4	1742.5	1739.6	1736.7	1733.8	1736.7
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	966.0	961.4	958.3	956.0	953.7	960.6	951.4	941.5	934.6	930.0	928.5
5°	1067.1	1057.2	1048.7	1041.8	1043.4	1043.4	1027.3	1009.7	994.3	985.9	976.7
7.5°	1184.3	1173.6	1156.8	1152.9	1149.9	1130.7	1114.6	1082.4	1063.3	1044.1	1027.3
10°	1300.8	1287.0	1270.9	1265.5	1257.9	1234.1	1209.6	1168.2	1144.5	1109.3	1087.0
12.5°	1409.6	1392.7	1376.6	1372.8	1361.3	1340.6	1298.5	1255.6	1215.0	1177.4	1138.4
15°	1500.7	1496.1	1471.6	1456.3	1431.0	1402.7	1393.5	1335.2	1283.9	1244.8	1174.4
17.5°	1577.3	1555.9	1532.9	1522.9	1513.0	1480.0	1447.1	1387.3	1332.2	1274.7	1229.5
20°	1638.6	1614.9	1598.8	1584.2	1579.6	1542.1	1490.0	1437.1	1376.6	1312.3	1253.3
22.5°	1641.7	1638.6	1627.9	1619.5	1610.3	1585.7	1544.4	1478.5	1414.1	1343.7	1266.3
25°	1578.1	1573.5	1604.1	1596.5	1602.6	1593.4	1571.2	1516.0	1441.0	1358.2	1280.1
27.5°	1386.6	1433.3	1481.6	1498.4	1509.9	1542.8	1553.6	1522.9	1462.4	1374.3	1287.0
30°	1126.1	1188.2	1266.3	1308.4	1340.6	1401.9	1481.6	1491.5	1463.2	1392.7	1285.5
32.5°	884.0	940.7	1003.5	1053.3	1096.2	1221.9	1329.1	1406.5	1420.3	1383.5	1289.3
35°	712.4	737.0	796.7	844.2	902.4	1009.7	1136.1	1260.9	1345.2	1349.8	1277.8
37.5°	587.6	600.6	652.7	679.5	714.0	808.2	926.2	1089.3	1220.3	1282.4	1245.6
40°	486.4	516.3	546.2	561.5	586.0	651.2	764.5	892.5	1054.9	1169.8	1195.8
42.5°	422.1	435.1	454.3	475.7	491.0	547.7	623.6	740.8	887.1	1047.2	1119.2
45°	372.3	376.9	396.8	410.6	426.7	466.5	520.2	618.2	746.9	904.7	1027.3
47.5°	330.9	340.1	350.9	359.3	370.0	400.6	446.6	517.9	631.2	772.2	904.0
50°	294.2	299.5	313.3	317.1	324.8	346.3	381.5	435.9	529.3	642.0	778.3
52.5°	259.7	269.7	275.0	280.4	287.3	304.9	327.9	372.3	442.8	548.5	664.2
55°	232.9	235.9	243.6	248.2	253.6	265.8	285.7	318.7	373.8	458.1	567.7
57.5°	206.8	206.8	214.5	218.3	223.7	232.9	250.5	275.8	315.6	378.4	478.8
60°	179.3	180.0	186.2	190.7	192.3	201.5	216.0	235.9	266.6	312.6	394.5
62.5°	154.7	158.6	161.6	163.2	168.5	173.9	186.2	199.9	221.4	262.0	320.2
65°	134.1	134.8	137.1	138.7	141.0	147.1	156.3	165.5	183.9	213.7	261.2
67.5°	110.3	113.4	116.4	116.4	118.7	121.8	131.0	138.7	152.4	170.1	202.2
70°	82.7	84.3	88.9	91.2	94.2	99.6	104.2	108.8	119.5	132.5	157.0
72.5°	68.9	68.9	70.5	71.2	71.2	75.1	82.0	86.6	91.9	101.1	118.0
75°	55.2	55.2	57.5	56.7	58.2	59.8	60.5	63.6	66.6	73.5	83.5
77.5°	43.7	44.4	44.4	45.2	45.2	46.0	46.7	48.3	49.8	53.6	58.2
80°	32.2	32.9	32.9	33.7	33.7	34.5	35.2	36.0	37.5	39.1	41.4
82.5°	22.2	23.0	23.0	23.7	23.0	23.7	24.5	24.5	25.3	26.8	27.6
85°	13.0	13.0	13.8	13.0	13.0	13.0	13.8	13.8	14.6	16.9	16.9
87.5°	3.8	4.6	3.8	4.6	4.6	4.6	4.6	5.4	5.4	6.1	6.9
90°	37.6	37.1	36.5	36.2	35.6	34.5	33.3	32.2	31.0	27.3	23.5
92.5°	43.3	43.0	42.7	42.6	41.6	39.6	37.6	35.6	33.6	31.0	28.4
95°	49.1	49.1	49.1	49.1	48.1	46.1	44.1	42.1	40.1	36.9	33.7
97.5°	52.4	52.1	51.8	51.7	50.5	48.2	45.9	43.6	41.3	55.9	70.6
100°	53.7	53.4	53.1	53.0	51.8	49.5	47.2	44.9	42.6	87.4	132.2
102.5°	54.4	53.9	53.3	53.0	57.7	67.2	76.7	86.1	95.6	145.6	195.5
105°	55.7	55.1	54.6	54.3	79.7	130.5	181.3	232.1	282.9	308.7	334.6
107.5°	209.6	247.2	284.8	303.6	325.7	369.9	414.2	458.4	502.6	498.3	494.0
110°	437.4	478.4	519.5	540.0	544.7	554.2	563.7	573.2	582.7	579.5	576.4

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	674.3	674.8	675.4	675.7	674.4	671.8	669.3	666.7	664.1	660.9	657.8
115°	757.4	756.2	755.1	754.5	753.1	750.2	747.3	744.5	741.6	739.0	736.4
117.5°	828.9	828.6	828.3	828.2	827.0	824.7	822.4	820.1	817.8	816.4	815.0
120°	901.8	901.8	901.8	901.8	900.7	898.4	896.1	893.8	891.5	890.6	889.8
122.5°	972.3	972.0	971.7	971.6	970.9	969.4	968.0	966.5	965.1	963.9	962.8
125°	1037.6	1037.1	1036.5	1036.2	1035.9	1035.3	1034.8	1034.2	1033.6	1032.4	1031.3
127.5°	1104.5	1105.1	1105.6	1105.9	1105.5	1104.6	1103.8	1102.9	1102.1	1100.7	1099.2
130°	1166.6	1167.1	1167.7	1168.0	1167.4	1166.3	1165.1	1164.0	1162.8	1161.6	1160.5
132.5°	1223.9	1224.8	1225.7	1226.1	1225.5	1224.4	1223.2	1222.1	1220.9	1220.1	1219.2
135°	1282.1	1282.9	1283.8	1284.2	1283.8	1282.9	1282.1	1281.2	1280.4	1279.2	1278.1
137.5°	1337.1	1337.6	1338.2	1338.5	1337.8	1336.3	1334.9	1333.4	1332.0	1331.4	1330.9
140°	1386.2	1386.7	1387.3	1387.6	1387.0	1385.9	1384.7	1383.6	1382.4	1381.5	1380.7
142.5°	1431.9	1432.8	1433.7	1434.1	1433.7	1432.8	1431.9	1431.1	1430.2	1429.4	1428.5
145°	1476.7	1476.7	1476.7	1476.7	1476.4	1475.9	1475.3	1474.8	1474.2	1473.6	1473.0
147.5°	1513.2	1514.6	1516.1	1516.8	1516.5	1515.9	1515.4	1514.8	1514.2	1513.6	1513.0
150°	1550.8	1551.7	1552.6	1553.0	1552.7	1552.1	1551.6	1551.0	1550.4	1549.8	1549.2
152.5°	1583.0	1584.4	1585.9	1586.6	1586.0	1584.9	1583.7	1582.6	1581.4	1581.1	1580.8
155°	1612.0	1613.7	1615.4	1616.3	1615.6	1614.1	1612.7	1611.2	1609.8	1609.5	1609.2
157.5°	1637.7	1640.0	1642.3	1643.4	1642.5	1640.8	1639.1	1637.4	1635.7	1636.0	1636.2
160°	1660.3	1662.4	1664.4	1665.4	1664.5	1662.8	1661.1	1659.3	1657.6	1657.9	1658.2
162.5°	1681.7	1683.4	1685.1	1686.0	1685.0	1683.0	1681.0	1679.0	1677.0	1677.3	1677.6
165°	1699.1	1701.1	1703.1	1704.1	1703.0	1700.7	1698.4	1696.1	1693.8	1694.1	1694.4
167.5°	1712.6	1714.9	1717.2	1718.3	1717.2	1714.9	1712.6	1710.3	1708.0	1708.0	1708.0
170°	1724.2	1726.5	1728.8	1730.0	1728.8	1726.5	1724.2	1721.9	1719.6	1719.6	1719.6
172.5°	1731.3	1733.8	1736.4	1737.7	1736.6	1734.3	1732.0	1729.7	1727.4	1727.1	1726.8
175°	1737.2	1739.5	1741.8	1742.9	1741.9	1739.9	1737.8	1735.8	1733.8	1733.5	1733.3
177.5°	1739.6	1742.5	1745.4	1746.8	1745.6	1743.3	1741.0	1738.7	1736.4	1736.1	1735.8
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	926.2	922.3	918.5	918.5	910.1	902.4	898.6	900.1	895.5	889.4	883.3
5°	966.8	951.4	948.4	940.0	928.5	912.4	904.0	896.3	887.1	874.8	863.4
7.5°	1004.3	984.4	973.7	965.2	943.0	920.8	902.4	890.2	874.1	855.7	841.9
10°	1053.3	1016.6	1005.1	985.9	954.5	923.1	901.7	881.7	859.5	838.1	819.7
12.5°	1092.4	1050.3	1028.8	1009.7	969.1	929.2	893.2	868.7	841.9	818.2	794.4
15°	1136.8	1089.3	1051.8	1028.8	977.5	929.2	888.6	854.2	824.3	795.2	774.5
17.5°	1158.3	1098.5	1081.7	1048.7	974.4	926.2	876.4	839.6	803.6	769.9	745.4
20°	1192.0	1122.3	1080.1	1057.9	992.0	920.8	862.6	820.5	782.9	746.9	720.9
22.5°	1194.3	1118.4	1090.9	1048.7	967.5	904.7	850.3	799.0	755.3	721.6	694.8
25°	1188.9	1111.6	1073.3	1039.5	972.1	895.5	825.8	775.3	732.4	693.3	661.9
27.5°	1186.6	1091.6	1055.6	1021.9	946.1	868.7	811.3	753.8	704.8	670.3	638.1
30°	1183.6	1070.2	1026.5	987.5	917.7	848.0	779.1	729.3	682.6	638.9	606.7
32.5°	1163.6	1041.1	996.6	955.3	880.2	810.5	756.1	703.2	652.7	612.1	583.0
35°	1157.5	1014.3	956.0	911.6	838.1	776.0	718.6	674.9	627.4	586.8	552.3
37.5°	1139.9	986.7	923.9	867.2	790.6	731.6	689.5	645.8	599.8	556.2	528.6
40°	1109.3	954.5	883.3	825.0	746.1	686.4	647.3	615.1	569.9	530.9	497.2
42.5°	1064.1	921.6	845.0	783.7	696.3	640.4	608.3	577.6	539.3	498.7	471.1
45°	1012.0	877.9	806.7	738.5	649.6	595.2	561.5	543.1	507.9	473.4	441.3
47.5°	940.7	832.7	762.2	691.8	601.4	548.5	521.7	503.3	478.8	441.3	415.2
50°	851.1	774.5	707.8	645.0	553.9	503.3	476.5	462.7	442.0	415.2	389.9
52.5°	751.5	707.1	651.9	593.7	505.6	458.1	433.6	422.9	407.5	382.3	360.8
55°	651.2	632.0	594.5	537.0	455.0	416.0	394.5	380.7	369.2	350.9	332.5
57.5°	561.5	552.3	526.3	481.9	412.9	372.3	353.9	344.7	335.5	321.7	303.4
60°	468.8	478.8	452.0	429.8	366.9	331.7	315.6	305.7	301.1	288.8	277.3
62.5°	388.4	397.6	382.3	365.4	321.0	289.6	279.6	270.4	267.4	256.6	245.1
65°	315.6	327.1	315.6	306.4	279.6	253.6	241.3	236.7	233.6	226.8	217.6
67.5°	251.3	262.8	257.4	245.9	237.5	216.0	209.1	204.5	203.0	197.6	190.0
70°	189.2	205.3	206.8	199.9	192.3	182.3	177.7	176.2	172.4	167.8	163.2
72.5°	136.4	154.7	155.5	155.5	150.9	150.9	146.3	144.0	144.0	139.4	134.1
75°	100.4	112.6	114.1	115.7	118.0	120.3	117.2	117.2	116.4	111.8	109.5
77.5°	66.6	77.4	81.2	86.6	89.6	89.6	91.2	92.7	91.2	88.9	87.3
80°	42.9	50.6	55.2	58.2	62.8	65.1	67.4	68.2	66.6	65.9	63.6
82.5°	28.3	30.6	32.9	36.8	42.1	46.0	46.0	45.2	46.7	46.0	45.2
85°	16.1	17.6	18.4	19.2	22.2	26.0	26.8	27.6	29.1	27.6	26.0
87.5°	6.1	6.9	6.9	6.9	8.4	9.2	11.5	14.6	13.8	12.3	12.3
90°	19.8	16.1	14.2	12.8	9.9	7.0	4.2	1.3	4.2	7.0	9.9
92.5°	25.9	23.3	22.0	22.9	24.6	26.3	28.0	29.7	28.0	26.3	24.6
95°	30.6	27.4	25.8	31.7	43.5	55.2	67.0	78.8	67.0	55.2	43.5
97.5°	85.2	99.9	107.2	111.2	119.3	127.3	135.4	143.4	135.4	127.3	119.3
100°	177.0	221.8	244.2	241.3	235.6	229.8	224.1	218.3	224.1	229.8	235.6
102.5°	245.5	295.4	320.4	318.5	314.8	311.1	307.3	303.6	307.3	311.1	314.8
105°	360.4	386.3	399.2	397.6	394.5	391.3	388.2	385.0	388.2	391.3	394.5
107.5°	489.7	485.4	483.2	481.9	479.3	476.8	474.2	471.6	474.2	476.8	479.3
110°	573.2	570.1	568.5	567.3	565.0	562.7	560.4	558.1	560.4	562.7	565.0

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	654.6	651.5	649.9	648.9	646.9	644.8	642.8	640.8	642.8	644.8	646.9
115°	733.9	731.3	730.0	729.1	727.4	725.7	723.9	722.2	723.9	725.7	727.4
117.5°	813.5	812.1	811.4	810.4	808.4	806.3	804.3	802.3	804.3	806.3	808.4
120°	888.9	888.0	887.6	886.3	883.7	881.2	878.6	876.0	878.6	881.2	883.7
122.5°	961.6	960.5	959.9	958.9	956.9	954.9	952.9	950.9	952.9	954.9	956.9
125°	1030.1	1029.0	1028.4	1027.3	1025.0	1022.7	1020.4	1018.1	1020.4	1022.7	1025.0
127.5°	1097.8	1096.3	1095.6	1094.5	1092.2	1089.9	1087.6	1085.3	1087.6	1089.9	1092.2
130°	1159.3	1158.2	1157.6	1156.5	1154.2	1151.9	1149.6	1147.3	1149.6	1151.9	1154.2
132.5°	1218.4	1217.5	1217.1	1215.9	1213.6	1211.3	1209.0	1206.7	1209.0	1211.3	1213.6
135°	1276.9	1275.8	1275.2	1274.3	1272.6	1270.9	1269.1	1267.4	1269.1	1270.9	1272.6
137.5°	1330.3	1329.8	1329.5	1328.3	1326.0	1323.7	1321.4	1319.1	1321.4	1323.7	1326.0
140°	1379.8	1378.9	1378.5	1377.6	1375.9	1374.2	1372.5	1370.8	1372.5	1374.2	1375.9
142.5°	1427.7	1426.8	1426.4	1425.5	1423.8	1422.1	1420.3	1418.6	1420.3	1422.1	1423.8
145°	1472.5	1471.9	1471.6	1470.6	1468.6	1466.5	1464.5	1462.5	1464.5	1466.5	1468.6
147.5°	1512.5	1511.9	1511.6	1510.9	1509.5	1508.0	1506.6	1505.2	1506.6	1508.0	1509.5
150°	1548.7	1548.1	1547.8	1547.4	1546.5	1545.6	1544.8	1543.9	1544.8	1545.6	1546.5
152.5°	1580.5	1580.2	1580.1	1580.0	1579.7	1579.4	1579.1	1578.8	1579.1	1579.4	1579.7
155°	1608.9	1608.6	1608.5	1608.8	1609.4	1609.9	1610.5	1611.1	1610.5	1609.9	1609.4
157.5°	1636.5	1636.8	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
160°	1658.5	1658.8	1658.9	1659.0	1659.3	1659.6	1659.9	1660.2	1659.9	1659.6	1659.3
162.5°	1677.9	1678.2	1678.3	1678.7	1679.6	1680.5	1681.3	1682.2	1681.3	1680.5	1679.6
165°	1694.7	1695.0	1695.1	1695.5	1696.4	1697.3	1698.1	1699.0	1698.1	1697.3	1696.4
167.5°	1708.0	1708.0	1708.0	1708.6	1709.7	1710.9	1712.0	1713.2	1712.0	1710.9	1709.7
170°	1719.6	1719.6	1719.6	1720.2	1721.3	1722.5	1723.6	1724.8	1723.6	1722.5	1721.3
172.5°	1726.5	1726.2	1726.1	1726.8	1728.3	1729.7	1731.2	1732.6	1731.2	1729.7	1728.3
175°	1733.0	1732.7	1732.6	1733.3	1734.7	1736.2	1737.6	1739.0	1737.6	1736.2	1734.7
177.5°	1735.5	1735.2	1735.1	1735.8	1737.3	1738.7	1740.2	1741.6	1740.2	1738.7	1737.3
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	883.3	879.4	877.9	874.1	864.9	858.8	851.9	847.3	848.0	844.2	846.5
5°	855.7	854.9	849.6	841.9	828.9	822.0	809.7	803.6	800.5	801.3	796.7
7.5°	832.7	825.8	822.0	809.7	797.5	782.9	773.0	767.6	763.0	758.4	755.3
10°	806.7	800.5	794.4	781.4	764.5	750.7	737.0	731.6	724.7	721.6	719.3
12.5°	779.1	775.3	767.6	752.3	733.1	720.1	704.0	700.9	691.8	685.6	684.1
15°	753.8	751.5	737.7	720.1	700.9	687.9	674.1	664.9	649.6	652.7	647.3
17.5°	727.0	717.0	708.6	684.9	675.7	655.7	639.7	635.1	624.3	617.4	610.6
20°	697.1	691.0	680.3	664.9	642.7	619.7	607.5	599.8	593.7	583.0	579.9
22.5°	668.8	661.1	651.9	632.0	612.8	593.7	576.8	569.9	562.3	554.6	550.0
25°	646.6	635.1	625.1	600.6	581.4	565.4	554.6	543.1	532.4	527.8	526.3
27.5°	612.1	605.2	595.2	572.2	554.6	537.0	527.0	519.4	507.9	502.5	497.9
30°	589.9	576.1	564.6	546.2	528.6	509.4	500.2	491.0	484.2	477.3	471.9
32.5°	560.0	549.3	540.1	521.7	504.1	486.4	476.5	462.7	458.9	453.5	447.4
35°	530.9	524.0	514.0	494.1	475.0	462.7	452.0	439.0	434.4	430.5	425.2
37.5°	503.3	493.3	486.4	467.3	450.4	435.9	427.5	416.7	413.7	409.1	405.2
40°	479.6	469.6	462.7	443.5	425.9	410.6	405.2	394.5	389.9	384.6	382.3
42.5°	452.7	444.3	435.1	421.3	402.9	387.6	376.9	370.8	364.6	362.3	357.8
45°	424.4	416.7	409.8	394.5	375.4	364.6	355.5	347.0	342.4	338.6	335.5
47.5°	399.9	393.0	383.8	366.9	351.6	341.7	332.5	324.0	319.4	314.9	311.0
50°	371.5	367.7	357.8	341.7	327.1	315.6	307.2	299.5	296.5	291.1	285.0
52.5°	346.3	339.4	330.9	317.9	304.9	291.1	279.6	275.0	269.7	266.6	261.2
55°	316.4	311.8	302.6	291.1	277.3	265.8	257.4	251.3	244.4	241.3	234.4
57.5°	291.1	282.7	278.1	263.5	250.5	239.0	232.9	226.8	219.1	214.5	211.4
60°	263.5	255.9	249.0	236.7	227.5	215.3	206.1	200.7	195.3	189.2	186.2
62.5°	236.7	230.6	222.2	212.2	200.7	190.7	183.9	176.2	173.1	167.0	164.7
65°	207.6	203.0	196.1	184.6	175.4	167.0	160.1	154.0	150.9	148.6	147.1
67.5°	181.6	175.4	170.8	160.9	150.9	144.0	140.2	136.4	132.5	130.2	127.9
70°	154.7	150.1	145.6	136.4	129.5	123.3	120.3	117.2	114.9	112.6	110.3
72.5°	127.2	124.9	120.3	114.1	108.8	104.2	101.9	98.1	95.8	91.9	90.4
75°	105.0	101.1	98.8	93.5	88.9	85.0	82.0	77.4	74.3	72.8	72.0
77.5°	82.7	81.2	78.1	73.5	71.2	67.4	62.8	61.3	59.8	59.8	59.0
80°	62.1	59.8	57.5	53.6	51.3	48.3	48.3	48.3	47.5	48.3	47.5
82.5°	42.1	40.6	39.1	36.8	36.0	36.0	36.8	36.8	36.8	36.8	36.8
85°	24.5	24.5	24.5	25.3	24.5	24.5	25.3	26.0	25.3	25.3	24.5
87.5°	11.5	11.5	12.3	12.3	13.0	13.0	13.0	13.0	13.0	13.0	13.8
90°	12.8	14.2	16.1	19.8	23.5	27.3	31.0	32.2	33.3	34.5	35.6
92.5°	22.9	22.0	23.3	25.9	28.4	31.0	33.6	35.6	37.6	39.6	41.6
95°	31.7	25.8	27.4	30.6	33.7	36.9	40.1	42.1	44.1	46.1	48.1
97.5°	111.2	107.2	99.9	85.2	70.6	55.9	41.3	43.6	45.9	48.2	50.5
100°	241.3	244.2	221.8	177.0	132.2	87.4	42.6	44.9	47.2	49.5	51.8
102.5°	318.5	320.4	295.4	245.5	195.5	145.6	95.6	86.1	76.7	67.2	57.7
105°	397.6	399.2	386.3	360.4	334.6	308.7	282.9	232.1	181.3	130.5	79.7
107.5°	481.9	483.2	485.4	489.7	494.0	498.3	502.6	458.4	414.2	369.9	325.7
110°	567.3	568.5	570.1	573.2	576.4	579.5	582.7	573.2	563.7	554.2	544.7

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	648.9	649.9	651.5	654.6	657.8	660.9	664.1	666.7	669.3	671.8	674.4
115°	729.1	730.0	731.3	733.9	736.4	739.0	741.6	744.5	747.3	750.2	753.1
117.5°	810.4	811.4	812.1	813.5	815.0	816.4	817.8	820.1	822.4	824.7	827.0
120°	886.3	887.6	888.0	888.9	889.8	890.6	891.5	893.8	896.1	898.4	900.7
122.5°	958.9	959.9	960.5	961.6	962.8	963.9	965.1	966.5	968.0	969.4	970.9
125°	1027.3	1028.4	1029.0	1030.1	1031.3	1032.4	1033.6	1034.2	1034.8	1035.3	1035.9
127.5°	1094.5	1095.6	1096.3	1097.8	1099.2	1100.7	1102.1	1102.9	1103.8	1104.6	1105.5
130°	1156.5	1157.6	1158.2	1159.3	1160.5	1161.6	1162.8	1164.0	1165.1	1166.3	1167.4
132.5°	1215.9	1217.1	1217.5	1218.4	1219.2	1220.1	1220.9	1222.1	1223.2	1224.4	1225.5
135°	1274.3	1275.2	1275.8	1276.9	1278.1	1279.2	1280.4	1281.2	1282.1	1282.9	1283.8
137.5°	1328.3	1329.5	1329.8	1330.3	1330.9	1331.4	1332.0	1333.4	1334.9	1336.3	1337.8
140°	1377.6	1378.5	1378.9	1379.8	1380.7	1381.5	1382.4	1383.6	1384.7	1385.9	1387.0
142.5°	1425.5	1426.4	1426.8	1427.7	1428.5	1429.4	1430.2	1431.1	1431.9	1432.8	1433.7
145°	1470.6	1471.6	1471.9	1472.5	1473.0	1473.6	1474.2	1474.8	1475.3	1475.9	1476.4
147.5°	1510.9	1511.6	1511.9	1512.5	1513.0	1513.6	1514.2	1514.8	1515.4	1515.9	1516.5
150°	1547.4	1547.8	1548.1	1548.7	1549.2	1549.8	1550.4	1551.0	1551.6	1552.1	1552.7
152.5°	1580.0	1580.1	1580.2	1580.5	1580.8	1581.1	1581.4	1582.6	1583.7	1584.9	1586.0
155°	1608.8	1608.5	1608.6	1608.9	1609.2	1609.5	1609.8	1611.2	1612.7	1614.1	1615.6
157.5°	1636.9	1636.9	1636.8	1636.5	1636.2	1636.0	1635.7	1637.4	1639.1	1640.8	1642.5
160°	1659.0	1658.9	1658.8	1658.5	1658.2	1657.9	1657.6	1659.3	1661.1	1662.8	1664.5
162.5°	1678.7	1678.3	1678.2	1677.9	1677.6	1677.3	1677.0	1679.0	1681.0	1683.0	1685.0
165°	1695.5	1695.1	1695.0	1694.7	1694.4	1694.1	1693.8	1696.1	1698.4	1700.7	1703.0
167.5°	1708.6	1708.0	1708.0	1708.0	1708.0	1708.0	1708.0	1710.3	1712.6	1714.9	1717.2
170°	1720.2	1719.6	1719.6	1719.6	1719.6	1719.6	1719.6	1721.9	1724.2	1726.5	1728.8
172.5°	1726.8	1726.1	1726.2	1726.5	1726.8	1727.1	1727.4	1729.7	1732.0	1734.3	1736.6
175°	1733.3	1732.6	1732.7	1733.0	1733.3	1733.5	1733.8	1735.8	1737.8	1739.9	1741.9
177.5°	1735.8	1735.1	1735.2	1735.5	1735.8	1736.1	1736.4	1738.7	1741.0	1743.3	1745.6
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	845.7	846.5	844.2	839.6	838.8	840.4	845.0	843.4	839.6	846.5	840.4
5°	799.0	795.2	793.6	795.2	790.6	788.3	792.9	790.6	792.9	793.6	795.9
7.5°	753.8	754.6	750.0	750.7	744.6	746.1	746.1	746.1	748.4	750.0	753.0
10°	714.7	716.3	710.9	711.7	707.1	704.0	706.3	710.9	710.9	710.9	712.4
12.5°	683.3	676.4	672.6	671.8	666.5	664.9	669.5	671.1	674.9	674.9	677.2
15°	644.3	642.7	639.7	639.7	626.6	629.7	631.2	636.6	644.3	638.1	639.7
17.5°	609.0	605.2	601.4	599.8	598.3	593.7	599.8	599.1	603.7	604.4	606.7
20°	577.6	574.5	566.9	567.7	569.2	562.3	566.1	566.1	570.7	575.3	580.7
22.5°	547.0	543.9	540.1	541.6	537.0	535.5	535.5	539.3	544.7	548.5	547.7
25°	523.2	517.9	515.6	513.3	511.0	512.5	510.2	514.0	517.9	520.2	517.9
27.5°	496.4	494.1	489.5	487.2	483.4	484.9	486.4	489.5	491.8	491.8	494.1
30°	470.4	467.3	465.8	463.5	463.5	460.4	461.2	464.2	466.5	468.8	471.9
32.5°	445.1	442.8	440.5	440.5	439.0	438.2	437.4	442.0	442.0	446.6	446.6
35°	424.4	420.6	420.6	416.7	418.3	417.5	416.0	419.0	419.8	422.9	422.1
37.5°	401.4	401.4	399.9	396.1	393.0	393.8	397.6	397.6	399.9	399.1	401.4
40°	378.4	376.9	376.9	374.6	373.8	373.1	373.8	374.6	378.4	377.7	378.4
42.5°	355.5	356.2	352.4	352.4	352.4	350.1	350.9	351.6	353.2	354.7	357.0
45°	333.2	331.7	330.9	329.4	327.9	328.6	327.9	330.9	330.2	331.7	334.0
47.5°	309.5	307.2	306.4	303.4	303.4	304.9	304.1	306.4	307.2	309.5	308.0
50°	286.5	283.4	281.1	281.9	277.3	278.8	278.8	281.1	283.4	284.2	285.7
52.5°	259.7	258.9	258.2	254.3	253.6	252.8	253.6	254.3	257.4	259.7	260.5
55°	233.6	232.9	228.3	226.8	224.5	224.5	226.0	226.8	232.1	232.9	235.9
57.5°	209.9	207.6	202.2	201.5	201.5	201.5	199.2	202.2	203.8	207.6	207.6
60°	183.9	183.9	179.3	179.3	180.0	179.3	179.3	180.0	180.0	183.1	184.6
62.5°	163.2	162.4	162.4	160.9	160.1	160.9	160.1	160.1	160.9	163.2	165.5
65°	144.8	144.0	143.3	142.5	141.0	141.0	141.7	143.3	143.3	144.8	145.6
67.5°	127.2	127.2	125.6	125.6	124.9	124.1	124.9	124.1	127.2	127.2	127.9
70°	109.5	108.8	106.5	105.7	103.4	104.2	104.2	106.5	107.2	108.8	110.3
72.5°	88.1	88.1	86.6	85.0	85.8	84.3	84.3	85.0	85.0	87.3	88.1
75°	72.8	71.2	70.5	71.2	70.5	72.0	70.5	70.5	72.0	72.0	72.0
77.5°	59.8	59.8	59.0	59.0	59.8	59.0	59.8	59.8	59.8	59.0	59.8
80°	49.0	48.3	48.3	48.3	47.5	47.5	47.5	47.5	47.5	47.5	47.5
82.5°	36.8	36.8	36.0	36.8	36.8	36.0	36.8	36.0	36.0	36.8	36.8
85°	24.5	26.0	24.5	24.5	25.3	25.3	26.0	25.3	26.0	24.5	25.3
87.5°	13.0	13.8	13.8	13.0	13.0	13.8	13.8	13.8	14.6	13.0	13.8
90°	36.2	36.5	37.1	37.6	38.2	38.8	38.2	37.6	37.1	36.5	36.2
92.5°	42.6	42.7	43.0	43.3	43.6	43.9	43.6	43.3	43.0	42.7	42.6
95°	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1
97.5°	51.7	51.8	52.1	52.4	52.7	53.0	52.7	52.4	52.1	51.8	51.7
100°	53.0	53.1	53.4	53.7	54.0	54.3	54.0	53.7	53.4	53.1	53.0
102.5°	53.0	53.3	53.9	54.4	55.0	55.6	55.0	54.4	53.9	53.3	53.0
105°	54.3	54.6	55.1	55.7	56.2	56.8	56.2	55.7	55.1	54.6	54.3
107.5°	303.6	284.8	247.2	209.6	172.0	134.4	172.0	209.6	247.2	284.8	303.6
110°	540.0	519.5	478.4	437.4	396.3	355.3	396.3	437.4	478.4	519.5	540.0

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	675.7	675.4	674.8	674.3	673.7	673.1	673.7	674.3	674.8	675.4	675.7
115°	754.5	755.1	756.2	757.4	758.5	759.7	758.5	757.4	756.2	755.1	754.5
117.5°	828.2	828.3	828.6	828.9	829.2	829.5	829.2	828.9	828.6	828.3	828.2
120°	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8
122.5°	971.6	971.7	972.0	972.3	972.6	972.9	972.6	972.3	972.0	971.7	971.6
125°	1036.2	1036.5	1037.1	1037.6	1038.2	1038.8	1038.2	1037.6	1037.1	1036.5	1036.2
127.5°	1105.9	1105.6	1105.1	1104.5	1104.0	1103.4	1104.0	1104.5	1105.1	1105.6	1105.9
130°	1168.0	1167.7	1167.1	1166.6	1166.0	1165.4	1166.0	1166.6	1167.1	1167.7	1168.0
132.5°	1226.1	1225.7	1224.8	1223.9	1223.1	1222.2	1223.1	1223.9	1224.8	1225.7	1226.1
135°	1284.2	1283.8	1282.9	1282.1	1281.2	1280.4	1281.2	1282.1	1282.9	1283.8	1284.2
137.5°	1338.5	1338.2	1337.6	1337.1	1336.5	1335.9	1336.5	1337.1	1337.6	1338.2	1338.5
140°	1387.6	1387.3	1386.7	1386.2	1385.6	1385.0	1385.6	1386.2	1386.7	1387.3	1387.6
142.5°	1434.1	1433.7	1432.8	1431.9	1431.1	1430.2	1431.1	1431.9	1432.8	1433.7	1434.1
145°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
147.5°	1516.8	1516.1	1514.6	1513.2	1511.7	1510.3	1511.7	1513.2	1514.6	1516.1	1516.8
150°	1553.0	1552.6	1551.7	1550.8	1550.0	1549.1	1550.0	1550.8	1551.7	1552.6	1553.0
152.5°	1586.6	1585.9	1584.4	1583.0	1581.5	1580.1	1581.5	1583.0	1584.4	1585.9	1586.6
155°	1616.3	1615.4	1613.7	1612.0	1610.2	1608.5	1610.2	1612.0	1613.7	1615.4	1616.3
157.5°	1643.4	1642.3	1640.0	1637.7	1635.4	1633.1	1635.4	1637.7	1640.0	1642.3	1643.4
160°	1665.4	1664.4	1662.4	1660.3	1658.3	1656.3	1658.3	1660.3	1662.4	1664.4	1665.4
162.5°	1686.0	1685.1	1683.4	1681.7	1680.0	1678.3	1680.0	1681.7	1683.4	1685.1	1686.0
165°	1704.1	1703.1	1701.1	1699.1	1697.1	1695.1	1697.1	1699.1	1701.1	1703.1	1704.1
167.5°	1718.3	1717.2	1714.9	1712.6	1710.3	1708.0	1710.3	1712.6	1714.9	1717.2	1718.3
170°	1730.0	1728.8	1726.5	1724.2	1721.9	1719.6	1721.9	1724.2	1726.5	1728.8	1730.0
172.5°	1737.7	1736.4	1733.8	1731.3	1728.7	1726.1	1728.7	1731.3	1733.8	1736.4	1737.7
175°	1742.9	1741.8	1739.5	1737.2	1734.9	1732.6	1734.9	1737.2	1739.5	1741.8	1742.9
177.5°	1746.8	1745.4	1742.5	1739.6	1736.7	1733.8	1736.7	1739.6	1742.5	1745.4	1746.8
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8	894.8
2.5°	846.5	849.6	846.5	840.4	846.5	850.3	854.2	860.3	863.4	863.4	867.9
5°	798.2	804.4	802.1	800.5	806.7	810.5	816.6	824.3	832.7	838.1	844.2
7.5°	755.3	759.2	763.0	763.0	769.1	777.6	786.7	795.9	806.7	814.3	818.9
10°	717.8	720.9	723.2	726.2	735.4	744.6	756.9	768.4	777.6	786.0	793.6
12.5°	681.8	686.4	691.8	694.1	700.9	712.4	723.9	737.7	752.3	760.7	768.4
15°	647.3	649.6	655.7	662.6	668.8	681.0	695.6	710.1	722.4	735.4	742.3
17.5°	612.1	612.8	628.9	625.1	645.0	656.5	664.2	678.0	697.9	708.6	719.3
20°	577.6	585.3	592.2	596.0	606.7	619.7	642.0	652.7	668.8	678.7	687.9
22.5°	550.8	562.3	562.3	571.5	576.8	589.1	605.2	625.9	643.5	650.4	663.4
25°	527.0	532.4	541.6	544.7	554.6	565.4	576.1	598.3	617.4	626.6	635.8
27.5°	496.4	503.3	515.6	515.6	528.6	540.1	553.1	567.7	586.8	599.8	609.8
30°	472.7	479.6	484.9	493.3	498.7	509.4	532.4	543.1	560.0	571.5	583.7
32.5°	450.4	455.8	460.4	469.6	475.7	488.0	500.2	519.4	533.9	544.7	557.7
35°	425.9	431.3	437.4	444.3	453.5	465.0	476.5	492.6	507.1	517.1	527.8
37.5°	402.9	406.8	416.0	420.6	428.2	439.0	453.5	470.4	483.4	491.0	501.8
40°	380.7	383.8	390.7	399.1	404.5	412.9	428.2	442.8	458.9	468.1	476.5
42.5°	357.0	360.8	366.9	375.4	383.8	393.0	401.4	418.3	432.8	440.5	449.7
45°	336.3	338.6	343.2	351.6	360.0	366.9	380.0	395.3	409.1	415.2	425.2
47.5°	311.8	314.1	321.0	324.8	334.0	343.2	356.2	371.5	383.8	389.9	399.1
50°	286.5	288.8	293.4	301.8	308.0	317.9	329.4	342.4	357.8	366.2	371.5
52.5°	262.0	266.6	270.4	277.3	285.0	294.9	305.7	317.9	330.9	339.4	345.5
55°	237.5	241.3	245.9	249.7	258.9	268.1	280.4	291.9	303.4	311.0	317.9
57.5°	209.9	215.3	219.9	227.5	234.4	242.1	255.9	265.1	278.8	284.2	290.3
60°	186.2	191.5	195.3	201.5	207.6	217.6	226.8	238.2	249.7	256.6	264.3
62.5°	166.2	168.5	170.8	177.0	183.1	192.3	201.5	213.0	225.2	229.1	235.2
65°	146.3	148.6	152.4	157.8	162.4	167.8	177.7	186.9	198.4	204.5	206.8
67.5°	129.5	131.8	132.5	136.4	140.2	146.3	151.7	160.9	171.6	175.4	180.0
70°	110.3	114.1	114.9	118.0	119.5	123.3	129.5	136.4	144.8	151.7	155.5
72.5°	88.1	93.5	95.0	99.6	101.9	105.7	110.3	115.7	121.0	124.1	127.2
75°	72.0	73.5	74.3	78.1	82.0	87.3	89.6	92.7	97.3	101.1	104.2
77.5°	59.8	60.5	61.3	61.3	62.1	65.1	69.7	73.5	76.6	78.1	80.4
80°	48.3	47.5	47.5	48.3	48.3	48.3	49.8	55.2	56.7	60.5	59.8
82.5°	37.5	36.0	36.8	36.0	36.0	36.0	36.0	36.8	36.8	39.1	40.6
85°	24.5	25.3	24.5	24.5	23.7	24.5	23.7	23.7	23.0	23.0	22.2
87.5°	13.0	13.8	13.0	13.0	12.3	13.0	12.3	12.3	11.5	11.5	10.0
90°	35.6	34.5	33.3	32.2	31.0	27.3	23.5	19.8	16.1	14.2	12.8
92.5°	41.6	39.6	37.6	35.6	33.6	31.0	28.4	25.9	23.3	22.0	22.9
95°	48.1	46.1	44.1	42.1	40.1	36.9	33.7	30.6	27.4	25.8	31.7
97.5°	50.5	48.2	45.9	43.6	41.3	55.9	70.6	85.2	99.9	107.2	111.2
100°	51.8	49.5	47.2	44.9	42.6	87.4	132.2	177.0	221.8	244.2	241.3
102.5°	57.7	67.2	76.7	86.1	95.6	145.6	195.5	245.5	295.4	320.4	318.5
105°	79.7	130.5	181.3	232.1	282.9	308.7	334.6	360.4	386.3	399.2	397.6
107.5°	325.7	369.9	414.2	458.4	502.6	498.3	494.0	489.7	485.4	483.2	481.9
110°	544.7	554.2	563.7	573.2	582.7	579.5	576.4	573.2	570.1	568.5	567.3

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	674.4	671.8	669.3	666.7	664.1	660.9	657.8	654.6	651.5	649.9	648.9
115°	753.1	750.2	747.3	744.5	741.6	739.0	736.4	733.9	731.3	730.0	729.1
117.5°	827.0	824.7	822.4	820.1	817.8	816.4	815.0	813.5	812.1	811.4	810.4
120°	900.7	898.4	896.1	893.8	891.5	890.6	889.8	888.9	888.0	887.6	886.3
122.5°	970.9	969.4	968.0	966.5	965.1	963.9	962.8	961.6	960.5	959.9	958.9
125°	1035.9	1035.3	1034.8	1034.2	1033.6	1032.4	1031.3	1030.1	1029.0	1028.4	1027.3
127.5°	1105.5	1104.6	1103.8	1102.9	1102.1	1100.7	1099.2	1097.8	1096.3	1095.6	1094.5
130°	1167.4	1166.3	1165.1	1164.0	1162.8	1161.6	1160.5	1159.3	1158.2	1157.6	1156.5
132.5°	1225.5	1224.4	1223.2	1222.1	1220.9	1220.1	1219.2	1218.4	1217.5	1217.1	1215.9
135°	1283.8	1282.9	1282.1	1281.2	1280.4	1279.2	1278.1	1276.9	1275.8	1275.2	1274.3
137.5°	1337.8	1336.3	1334.9	1333.4	1332.0	1331.4	1330.9	1330.3	1329.8	1329.5	1328.3
140°	1387.0	1385.9	1384.7	1383.6	1382.4	1381.5	1380.7	1379.8	1378.9	1378.5	1377.6
142.5°	1433.7	1432.8	1431.9	1431.1	1430.2	1429.4	1428.5	1427.7	1426.8	1426.4	1425.5
145°	1476.4	1475.9	1475.3	1474.8	1474.2	1473.6	1473.0	1472.5	1471.9	1471.6	1470.6
147.5°	1516.5	1515.9	1515.4	1514.8	1514.2	1513.6	1513.0	1512.5	1511.9	1511.6	1510.9
150°	1552.7	1552.1	1551.6	1551.0	1550.4	1549.8	1549.2	1548.7	1548.1	1547.8	1547.4
152.5°	1586.0	1584.9	1583.7	1582.6	1581.4	1581.1	1580.8	1580.5	1580.2	1580.1	1580.0
155°	1615.6	1614.1	1612.7	1611.2	1609.8	1609.5	1609.2	1608.9	1608.6	1608.5	1608.8
157.5°	1642.5	1640.8	1639.1	1637.4	1635.7	1636.0	1636.2	1636.5	1636.8	1636.9	1636.9
160°	1664.5	1662.8	1661.1	1659.3	1657.6	1657.9	1658.2	1658.5	1658.8	1658.9	1659.0
162.5°	1685.0	1683.0	1681.0	1679.0	1677.0	1677.3	1677.6	1677.9	1678.2	1678.3	1678.7
165°	1703.0	1700.7	1698.4	1696.1	1693.8	1694.1	1694.4	1694.7	1695.0	1695.1	1695.5
167.5°	1717.2	1714.9	1712.6	1710.3	1708.0	1708.0	1708.0	1708.0	1708.0	1708.0	1708.6
170°	1728.8	1726.5	1724.2	1721.9	1719.6	1719.6	1719.6	1719.6	1719.6	1719.6	1720.2
172.5°	1736.6	1734.3	1732.0	1729.7	1727.4	1727.1	1726.8	1726.5	1726.2	1726.1	1726.8
175°	1741.9	1739.9	1737.8	1735.8	1733.8	1733.5	1733.3	1733.0	1732.7	1732.6	1733.3
177.5°	1745.6	1743.3	1741.0	1738.7	1736.4	1736.1	1735.8	1735.5	1735.2	1735.1	1735.8
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	894.8	894.8	894.8	894.8
2.5°	871.8	877.1	887.9	897.1
5°	853.4	861.8	877.9	894.0
7.5°	831.2	844.2	864.9	887.1
10°	809.7	826.6	851.9	877.9
12.5°	788.3	805.9	832.7	866.4
15°	763.0	781.4	813.6	854.2
17.5°	740.8	765.3	794.4	835.0
20°	717.0	735.4	773.0	815.9
22.5°	687.2	717.8	753.0	798.2
25°	663.4	690.2	725.5	776.8
27.5°	634.3	665.7	708.6	753.8
30°	610.6	636.6	676.4	730.8
32.5°	583.0	613.6	655.0	708.6
35°	558.5	584.5	623.6	678.0
37.5°	529.3	557.7	601.4	649.6
40°	504.1	531.6	573.0	618.2
42.5°	473.4	502.5	543.9	582.2
45°	448.9	475.7	508.7	543.9
47.5°	419.0	447.4	479.6	504.1
50°	392.2	418.3	443.5	464.2
52.5°	363.1	386.9	409.8	425.2
55°	336.3	354.7	373.1	383.8
57.5°	304.9	322.5	337.8	344.0
60°	277.3	291.9	301.8	308.7
62.5°	248.2	258.9	266.6	270.4
65°	219.9	227.5	231.4	235.2
67.5°	190.7	197.6	199.9	204.5
70°	160.1	167.8	169.3	171.6
72.5°	137.1	137.1	140.2	143.3
75°	109.5	111.1	112.6	112.6
77.5°	85.8	85.8	87.3	88.1
80°	62.8	63.6	63.6	62.8
82.5°	42.9	44.4	42.9	42.1
85°	23.7	26.8	25.3	25.3
87.5°	10.0	10.0	11.5	10.0
90°	9.9	7.0	4.2	1.3
92.5°	24.6	26.3	28.0	29.7
95°	43.5	55.2	67.0	78.8
97.5°	119.3	127.3	135.4	143.4
100°	235.6	229.8	224.1	218.3
102.5°	314.8	311.1	307.3	303.6
105°	394.5	391.3	388.2	385.0
107.5°	479.3	476.8	474.2	471.6
110°	565.0	562.7	560.4	558.1

TEST NUMBER: P1032298

CATALOG NUMBER: S123RDIW-B560D1320UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	646.9	644.8	642.8	640.8
115°	727.4	725.7	723.9	722.2
117.5°	808.4	806.3	804.3	802.3
120°	883.7	881.2	878.6	876.0
122.5°	956.9	954.9	952.9	950.9
125°	1025.0	1022.7	1020.4	1018.1
127.5°	1092.2	1089.9	1087.6	1085.3
130°	1154.2	1151.9	1149.6	1147.3
132.5°	1213.6	1211.3	1209.0	1206.7
135°	1272.6	1270.9	1269.1	1267.4
137.5°	1326.0	1323.7	1321.4	1319.1
140°	1375.9	1374.2	1372.5	1370.8
142.5°	1423.8	1422.1	1420.3	1418.6
145°	1468.6	1466.5	1464.5	1462.5
147.5°	1509.5	1508.0	1506.6	1505.2
150°	1546.5	1545.6	1544.8	1543.9
152.5°	1579.7	1579.4	1579.1	1578.8
155°	1609.4	1609.9	1610.5	1611.1
157.5°	1636.9	1636.9	1636.9	1636.9
160°	1659.3	1659.6	1659.9	1660.2
162.5°	1679.6	1680.5	1681.3	1682.2
165°	1696.4	1697.3	1698.1	1699.0
167.5°	1709.7	1710.9	1712.0	1713.2
170°	1721.3	1722.5	1723.6	1724.8
172.5°	1728.3	1729.7	1731.2	1732.6
175°	1734.7	1736.2	1737.6	1739.0
177.5°	1737.3	1738.7	1740.2	1741.6
180°	1739.0	1739.0	1739.0	1739.0

(END OF REPORT)