

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032721

Luminaire Tested: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032721
REPORT IS A COMBINATION OF REPORTS P997753 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8916.0 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29		
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25		
2	85	78	72	67	76	70	65	61	55	52	49	42	39	37	29	28	27	21		
3	78	68	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18		
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15		
5	65	54	46	40	58	49	42	37	39	34	30	29	26	24	21	19	17	13		
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12		
7	55	43	36	30	49	39	33	28	31	27	23	24	21	18	17	15	13	11		
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	9		
9	48	36	29	24	43	32	26	22	26	21	18	20	17	14	15	12	11	9		
10	44	33	26	21	40	30	24	20	24	19	16	19	15	13	14	11	10	8		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7627	7627	7627	7627
5°	7608	8750	7652	6575
10°	7551	10209	7608	5769
15°	7460	11768	7512	5161
20°	7364	12762	7417	4627
25°	7223	12615	7292	4233
30°	7085	10427	7171	4030
35°	6892	7770	6968	3907
40°	6665	5853	6730	3847
45°	6321	4698	6400	3765
50°	5909	3958	5996	3727
55°	5425	3445	5510	3683
60°	4954	3033	5099	3621
65°	4512	2610	4556	3471
70°	3993	2148	4080	3197
75°	3484	1650	3461	2716
80°	2739	1085	2710	2061
85°	1805	486	1688	1201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 9863 cd/sqm

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.0	1.0
10°-20°	281.0	3.2
20°-30°	446.4	5.0
30°-40°	496.0	5.6
40°-50°	451.0	5.1
50°-60°	368.6	4.1
60°-70°	263.1	3.0
70°-80°	144.8	1.6
80°-90°	43.3	0.5
90°-100°	67.9	0.8
100°-110°	447.2	5.0
110°-120°	854.0	9.6
120°-130°	1084.2	12.2
130°-140°	1159.8	13.0
140°-150°	1084.5	12.2
150°-160°	874.6	9.8
160°-170°	564.0	6.3
170°-180°	194.4	2.2
0°-30°	818.4	9.2
0°-40°	1314.4	14.7
0°-60°	2134.0	23.9
0°-90°	2585.2	29.0
90°-120°	1369.2	15.4
90°-150°	4697.8	52.7
90°-180°	6331.0	71.0
0°-180°	8916.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	935	935	935	935	935	
5°	932	1097	937	824	932	88
15°	890	1507	896	661	890	251
25°	812	1600	820	537	812	374
35°	704	946	712	476	704	440
45°	562	531	569	425	562	433
55°	395	347	401	371	395	355
65°	246	223	249	297	246	243
75°	121	112	120	184	121	127
85°	25	23	23	57	25	29
90°	5	46	5	46	5	6
95°	84	44	84	44	84	104
105°	461	436	461	436	461	482
115°	860	866	860	866	860	847
125°	1209	1218	1209	1218	1209	1080
135°	1500	1510	1500	1510	1500	1156
145°	1729	1738	1729	1738	1729	1080
155°	1896	1894	1896	1894	1896	874
165°	2000	1991	2000	1991	2000	565
175°	2046	2034	2046	2034	2046	195
180°	2046	2046	2046	2046	2046	

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	935.3	944.6	948.5	951.6	961.7	964.8	965.6	970.2	974.1	974.9	974.9
5°	931.5	946.2	957.8	968.7	984.9	991.9	1000.4	1009.7	1022.1	1029.9	1033.8
7.5°	925.3	947.0	964.8	983.4	1005.9	1019.8	1027.6	1052.4	1069.4	1083.4	1100.4
10°	916.0	943.9	969.4	996.6	1028.3	1045.4	1062.4	1092.6	1116.7	1143.8	1165.5
12.5°	902.0	938.4	969.4	1007.4	1046.9	1067.1	1087.2	1139.9	1167.8	1191.8	1230.6
15°	889.6	926.0	970.2	1009.0	1057.8	1088.0	1117.4	1151.5	1195.7	1247.6	1284.8
17.5°	875.7	921.4	962.5	1016.7	1071.0	1099.6	1123.6	1176.3	1238.3	1289.5	1323.6
20°	856.3	902.8	957.0	1014.4	1078.7	1101.2	1132.9	1203.5	1259.3	1309.6	1365.4
22.5°	833.8	888.1	945.4	1000.4	1067.1	1114.3	1149.2	1211.2	1278.6	1336.8	1399.5
25°	812.1	871.0	921.4	996.6	1067.1	1098.8	1138.4	1212.0	1285.6	1356.1	1420.4
27.5°	788.9	843.9	912.1	971.8	1051.6	1086.4	1129.1	1209.7	1287.9	1358.4	1427.4
30°	763.3	822.2	878.8	949.3	1026.8	1071.7	1111.2	1198.8	1278.6	1352.3	1416.6
32.5°	734.6	790.4	850.9	917.5	998.9	1044.6	1094.2	1184.1	1269.3	1332.9	1382.5
35°	704.4	761.0	813.7	881.9	965.6	1011.3	1059.3	1158.5	1243.0	1294.9	1323.6
37.5°	671.1	724.6	776.5	843.9	927.6	976.4	1025.2	1121.3	1201.1	1244.5	1236.8
40°	639.3	687.4	735.4	799.0	886.5	938.4	981.1	1077.9	1147.7	1166.3	1140.7
42.5°	602.9	644.0	690.5	755.6	840.8	889.6	943.1	1031.4	1083.4	1075.6	1032.2
45°	561.8	598.2	644.7	706.0	792.8	843.1	888.1	971.8	1009.7	990.4	911.3
47.5°	522.3	557.9	595.9	657.1	741.6	784.2	829.9	905.1	926.8	885.7	806.7
50°	479.7	509.1	548.6	606.8	685.8	730.8	768.7	829.2	836.9	786.6	704.4
52.5°	438.6	463.4	501.4	558.7	632.3	668.0	705.2	758.7	752.5	700.5	621.5
55°	395.2	418.5	453.3	506.0	571.1	605.2	637.0	684.3	671.1	617.6	548.6
57.5°	358.8	375.1	409.2	458.0	511.5	548.6	575.8	613.0	592.8	539.4	475.0
60°	316.9	337.1	365.8	405.3	458.0	482.8	506.8	531.6	517.7	466.5	409.2
62.5°	279.0	294.5	319.3	357.2	398.3	420.8	446.4	461.9	447.9	400.6	352.6
65°	246.4	258.8	278.2	309.2	348.7	367.3	382.0	396.8	385.1	341.0	306.1
67.5°	210.8	221.6	237.9	262.7	296.0	309.2	323.1	333.2	320.0	290.6	256.5
70°	179.0	186.8	202.3	220.9	244.1	256.5	268.1	278.2	266.6	241.8	216.2
72.5°	146.5	152.7	166.6	179.8	200.7	209.2	217.8	225.5	221.6	198.4	177.5
75°	120.9	123.2	132.5	143.4	156.5	165.8	172.0	176.7	173.6	155.0	141.8
77.5°	91.4	94.5	101.5	110.0	121.7	127.1	131.0	135.6	131.7	117.0	107.7
80°	66.6	67.4	71.3	79.0	86.8	87.6	91.4	97.6	95.3	85.2	78.3
82.5°	42.6	44.9	46.5	51.1	56.6	58.1	60.4	62.0	61.2	55.0	52.7
85°	24.8	24.8	26.3	29.4	31.0	33.3	34.1	34.9	36.4	32.5	30.2
87.5°	10.8	11.6	11.6	12.4	13.9	13.9	14.7	15.5	16.3	15.5	13.2
90°	4.6	8.3	12.1	15.8	19.5	21.4	22.8	25.5	28.2	31.0	33.7
92.5°	23.0	22.3	21.6	20.9	20.2	19.9	21.3	24.0	26.7	29.4	32.1
95°	84.2	72.6	61.0	49.5	37.9	32.1	32.3	32.6	33.0	33.3	33.7
97.5°	160.7	168.2	175.6	183.1	190.6	194.3	176.5	140.8	105.1	69.4	33.7
100°	251.0	257.1	263.2	269.3	275.4	278.5	255.0	208.1	161.2	114.2	67.3
102.5°	352.0	356.1	360.1	364.2	368.3	370.3	372.3	376.4	380.5	384.6	388.7
105°	460.6	462.6	464.7	466.7	468.8	469.8	470.6	472.3	474.0	475.7	477.4
107.5°	560.1	561.1	562.1	563.2	564.2	564.7	565.9	568.3	570.6	573.0	575.4
110°	661.1	662.1	663.1	664.1	665.1	665.6	666.6	668.7	670.7	672.8	674.8

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	759.0	761.0	763.1	765.1	767.2	768.2	768.5	769.2	769.9	770.5	771.2
115°	860.0	861.0	862.0	863.1	864.1	864.6	864.4	864.1	863.7	863.4	863.0
117.5°	950.3	951.7	953.0	954.4	955.7	956.4	956.9	957.9	959.0	960.0	961.0
120°	1042.1	1043.5	1044.8	1046.2	1047.5	1048.2	1048.0	1047.7	1047.4	1047.0	1046.7
122.5°	1127.8	1128.5	1129.1	1129.8	1130.5	1130.8	1131.1	1131.8	1132.5	1133.2	1133.9
125°	1208.9	1210.3	1211.6	1213.0	1214.3	1215.0	1214.7	1214.0	1213.3	1212.6	1211.9
127.5°	1286.9	1287.3	1287.6	1288.0	1288.3	1288.5	1289.3	1291.0	1292.7	1294.4	1296.1
130°	1361.9	1362.2	1362.6	1362.9	1363.2	1363.4	1363.9	1364.9	1366.0	1367.0	1368.0
132.5°	1430.8	1431.5	1432.1	1432.8	1433.5	1433.8	1434.5	1435.8	1437.2	1438.5	1439.9
135°	1499.6	1499.3	1498.9	1498.6	1498.3	1498.1	1498.8	1500.1	1501.5	1502.8	1504.2
137.5°	1560.8	1560.8	1560.8	1560.8	1560.8	1560.8	1561.7	1563.4	1565.1	1566.8	1568.5
140°	1620.5	1621.2	1621.9	1622.6	1623.3	1623.6	1623.9	1624.6	1625.3	1625.9	1626.6
142.5°	1674.1	1675.5	1676.8	1678.2	1679.5	1680.2	1680.4	1680.7	1681.0	1681.4	1681.7
145°	1729.2	1730.2	1731.2	1732.2	1733.2	1733.7	1733.7	1733.7	1733.7	1733.7	1733.7
147.5°	1772.0	1774.0	1776.1	1778.1	1780.2	1781.2	1781.0	1780.7	1780.4	1780.0	1779.7
150°	1819.4	1820.8	1822.2	1823.5	1824.9	1825.6	1825.4	1825.1	1824.7	1824.4	1824.0
152.5°	1859.2	1860.2	1861.2	1862.3	1863.3	1863.8	1863.5	1862.8	1862.1	1861.5	1860.8
155°	1896.0	1896.3	1896.7	1897.0	1897.3	1897.5	1897.0	1896.0	1894.9	1893.9	1892.9
157.5°	1928.1	1928.1	1928.1	1928.1	1928.1	1928.1	1927.4	1926.1	1924.7	1923.4	1922.0
160°	1955.6	1954.6	1953.6	1952.5	1951.5	1951.0	1950.8	1950.5	1950.2	1949.8	1949.5
162.5°	1980.1	1978.7	1977.4	1976.0	1974.7	1974.0	1973.8	1973.5	1973.2	1972.8	1972.5
165°	2000.0	1998.3	1996.6	1994.9	1993.2	1992.4	1992.4	1992.4	1992.4	1992.4	1992.4
167.5°	2016.8	2015.1	2013.4	2011.7	2010.0	2009.2	2009.0	2008.7	2008.4	2008.0	2007.7
170°	2030.6	2028.6	2026.5	2024.5	2022.4	2021.4	2021.6	2021.9	2022.3	2022.6	2023.0
172.5°	2039.8	2037.8	2035.7	2033.7	2031.6	2030.6	2030.8	2031.1	2031.4	2031.8	2032.1
175°	2045.9	2043.9	2041.8	2039.8	2037.7	2036.7	2036.9	2037.2	2037.6	2037.9	2038.3
177.5°	2050.5	2048.1	2045.7	2043.4	2041.0	2039.8	2040.1	2040.8	2041.5	2042.2	2042.9
180°	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	977.2	991.1	997.3	998.9	1007.4	1002.0	1004.3	1003.5	1009.7	1010.5	1010.5
5°	1048.5	1064.8	1070.2	1077.9	1089.5	1092.6	1090.3	1095.0	1103.5	1097.3	1106.6
7.5°	1123.6	1141.5	1153.9	1170.9	1174.8	1184.9	1191.1	1196.5	1198.0	1198.8	1200.4
10°	1193.4	1215.9	1232.9	1261.6	1267.8	1273.2	1300.3	1289.5	1303.4	1298.8	1300.3
12.5°	1250.0	1294.1	1308.1	1356.1	1360.8	1379.4	1377.8	1394.9	1398.0	1404.2	1398.0
15°	1324.4	1375.5	1398.0	1425.1	1440.6	1462.3	1466.2	1489.4	1498.7	1507.2	1498.7
17.5°	1392.5	1419.7	1477.0	1498.7	1508.8	1520.4	1549.9	1558.4	1572.3	1566.9	1582.4
20°	1426.6	1465.4	1525.8	1563.0	1578.5	1589.4	1614.2	1627.4	1632.8	1632.8	1634.3
22.5°	1456.9	1512.7	1557.6	1600.2	1614.2	1621.9	1636.6	1646.7	1649.0	1650.6	1652.1
25°	1484.0	1534.4	1570.8	1594.8	1600.2	1600.2	1608.8	1602.6	1592.5	1600.2	1604.9
27.5°	1484.0	1519.6	1535.9	1544.4	1544.4	1523.5	1511.1	1485.5	1463.8	1457.6	1471.6
30°	1459.2	1475.5	1453.0	1432.1	1415.8	1401.8	1353.0	1314.3	1306.5	1301.1	1322.0
32.5°	1401.8	1380.9	1336.8	1276.3	1252.3	1220.5	1182.5	1153.1	1135.3	1129.1	1124.4
35°	1300.3	1246.1	1188.7	1107.4	1090.3	1050.0	998.1	976.4	947.0	946.2	956.3
37.5°	1189.5	1105.8	1043.8	966.3	942.3	899.7	850.9	828.4	808.3	792.8	811.4
40°	1060.1	987.3	892.7	829.2	795.1	772.6	731.5	706.7	697.4	689.7	701.3
42.5°	939.2	859.4	785.8	720.7	692.8	667.2	640.1	616.1	609.1	608.3	616.8
45°	819.1	740.8	672.6	616.8	599.0	583.5	557.2	550.2	538.6	530.8	534.7
47.5°	723.0	642.4	585.8	543.2	527.7	514.6	497.5	485.9	475.8	472.7	477.4
50°	628.5	574.2	516.1	480.5	468.8	456.4	443.3	432.4	427.8	424.7	427.8
52.5°	552.5	494.4	454.9	426.2	414.6	405.3	396.0	391.3	385.1	386.7	389.8
55°	484.3	433.2	399.9	378.9	372.0	368.1	356.5	351.0	348.7	347.2	348.7
57.5°	420.0	382.8	358.0	340.2	330.9	328.6	319.3	319.3	316.9	314.6	315.4
60°	368.9	337.1	313.1	299.1	297.6	293.7	287.5	286.7	281.3	283.6	284.4
62.5°	316.9	291.4	275.1	266.6	261.2	259.6	255.7	255.0	252.6	253.4	251.9
65°	275.9	255.0	238.7	231.7	229.4	228.6	225.5	223.2	221.6	223.2	221.6
67.5°	234.8	220.9	208.5	201.5	198.4	197.6	195.3	193.7	194.5	192.2	193.7
70°	196.1	182.1	174.4	170.5	168.9	166.6	166.6	166.6	166.6	165.1	164.3
72.5°	165.1	151.1	145.7	143.4	141.8	141.0	138.7	139.5	138.7	137.9	141.0
75°	131.0	122.4	117.0	114.7	116.2	113.9	111.6	113.1	110.8	111.6	114.7
77.5°	99.2	95.3	92.2	90.7	89.1	87.6	87.6	86.0	86.0	86.0	86.0
80°	72.1	71.3	65.9	65.1	65.1	63.5	63.5	63.5	63.5	62.8	63.5
82.5°	48.0	47.3	45.7	44.9	43.4	44.2	44.2	42.6	42.6	41.8	42.6
85°	27.9	27.9	26.3	25.6	24.8	25.6	24.0	23.2	24.0	23.2	24.0
87.5°	13.2	11.6	12.4	11.6	10.1	10.8	9.3	10.1	9.3	8.5	10.1
90°	35.7	37.7	39.8	41.8	42.8	43.1	43.8	44.5	45.2	45.9	45.2
92.5°	34.1	36.2	38.2	40.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3
95°	35.7	37.7	39.8	41.8	42.8	43.0	43.3	43.7	44.0	44.4	44.0
97.5°	35.4	37.1	38.8	40.5	41.3	41.5	41.8	42.1	42.5	42.8	42.5
100°	61.5	55.7	50.0	44.2	41.3	41.5	41.8	42.1	42.5	42.8	42.5
102.5°	312.2	235.7	159.2	82.7	44.4	44.4	44.4	44.4	44.4	44.4	44.4
105°	480.5	483.5	486.6	489.7	491.2	485.1	472.8	460.6	448.3	436.1	448.3
107.5°	577.1	578.8	580.5	582.2	583.0	583.7	585.0	586.4	587.7	589.1	587.7
110°	675.5	676.2	676.9	677.6	677.9	678.4	679.4	680.5	681.5	682.5	681.5

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	770.9	770.5	770.2	769.9	769.7	770.4	771.7	773.1	774.4	775.8	774.4
115°	863.7	864.4	865.1	865.8	866.1	866.1	866.1	866.1	866.1	866.1	866.1
117.5°	960.7	960.3	960.0	959.7	959.5	959.5	959.5	959.5	959.5	959.5	959.5
120°	1047.4	1048.0	1048.7	1049.4	1049.7	1049.4	1048.7	1048.0	1047.4	1046.7	1047.4
122.5°	1134.2	1134.6	1134.9	1135.2	1135.4	1135.1	1134.4	1133.7	1133.1	1132.4	1133.1
125°	1212.9	1213.9	1215.0	1216.0	1216.5	1216.7	1217.0	1217.4	1217.7	1218.1	1217.7
127.5°	1295.8	1295.4	1295.1	1294.8	1294.6	1294.4	1294.1	1293.7	1293.4	1293.0	1293.4
130°	1368.4	1368.7	1369.1	1369.4	1369.6	1369.6	1369.6	1369.6	1369.6	1369.6	1369.6
132.5°	1440.3	1440.6	1441.0	1441.3	1441.5	1441.3	1441.0	1440.6	1440.3	1439.9	1440.3
135°	1504.9	1505.6	1506.3	1507.0	1507.3	1507.6	1508.3	1509.0	1509.6	1510.3	1509.6
137.5°	1569.2	1569.8	1570.5	1571.2	1571.5	1571.3	1571.0	1570.7	1570.3	1570.0	1570.3
140°	1627.6	1628.6	1629.7	1630.7	1631.2	1631.4	1631.7	1632.1	1632.4	1632.8	1632.4
142.5°	1682.4	1683.1	1683.8	1684.5	1684.8	1684.8	1684.8	1684.8	1684.8	1684.8	1684.8
145°	1734.1	1734.4	1734.8	1735.1	1735.3	1735.6	1736.3	1737.0	1737.6	1738.3	1737.6
147.5°	1780.0	1780.4	1780.7	1781.0	1781.2	1781.4	1781.7	1782.0	1782.4	1782.7	1782.4
150°	1824.0	1824.0	1824.0	1824.0	1824.0	1824.2	1824.5	1824.9	1825.2	1825.6	1825.2
152.5°	1861.5	1862.1	1862.8	1863.5	1863.8	1863.6	1863.3	1863.0	1862.6	1862.3	1862.6
155°	1894.3	1895.6	1897.0	1898.3	1899.0	1898.5	1897.5	1896.4	1895.4	1894.4	1895.4
157.5°	1923.7	1925.4	1927.1	1928.8	1929.6	1928.8	1927.1	1925.4	1923.7	1922.0	1923.7
160°	1951.5	1953.6	1955.6	1957.7	1958.7	1957.7	1955.6	1953.6	1951.5	1949.5	1951.5
162.5°	1974.5	1976.5	1978.6	1980.6	1981.6	1980.4	1978.0	1975.7	1973.3	1970.9	1973.3
165°	1995.1	1997.8	2000.5	2003.2	2004.6	2003.1	2000.0	1996.9	1993.9	1990.8	1993.9
167.5°	2010.7	2013.8	2016.8	2019.9	2021.4	2019.7	2016.3	2012.9	2009.5	2006.1	2009.5
170°	2025.7	2028.4	2031.1	2033.8	2035.2	2033.5	2030.1	2026.7	2023.3	2019.9	2023.3
172.5°	2034.8	2037.6	2040.3	2043.0	2044.4	2042.5	2038.8	2035.0	2031.3	2027.5	2031.3
175°	2041.3	2044.4	2047.4	2050.5	2052.0	2050.0	2045.9	2041.8	2037.8	2033.7	2037.8
177.5°	2045.6	2048.3	2051.0	2053.7	2055.1	2053.1	2049.0	2044.9	2040.8	2036.7	2040.8
180°	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	1009.0	1006.6	1003.5	1003.5	999.7	999.7	993.5	982.6	973.3	970.2	971.8
5°	1095.0	1095.7	1091.1	1087.2	1080.3	1074.8	1064.8	1045.4	1039.2	1026.8	1018.3
7.5°	1193.4	1190.3	1181.8	1175.6	1174.0	1161.6	1139.9	1116.7	1098.1	1085.7	1067.9
10°	1304.2	1291.8	1279.4	1275.5	1266.2	1245.3	1220.5	1194.9	1169.4	1142.2	1112.0
12.5°	1397.2	1373.2	1372.4	1363.1	1345.3	1333.7	1304.2	1267.8	1223.6	1193.4	1159.3
15°	1497.2	1474.7	1456.1	1439.0	1430.5	1396.4	1371.6	1325.9	1273.2	1240.7	1217.4
17.5°	1568.5	1558.4	1526.6	1518.9	1507.2	1467.7	1428.2	1383.2	1337.5	1291.8	1229.0
20°	1625.8	1619.6	1598.7	1587.8	1569.2	1538.2	1490.2	1438.3	1385.6	1320.5	1261.6
22.5°	1650.6	1642.8	1625.8	1616.5	1604.9	1578.5	1537.5	1478.6	1409.6	1351.5	1288.7
25°	1601.8	1615.7	1611.1	1607.2	1602.6	1587.1	1556.1	1504.1	1436.7	1370.8	1292.6
27.5°	1491.7	1515.8	1539.0	1542.1	1549.9	1556.1	1543.7	1506.5	1449.9	1380.1	1294.1
30°	1343.7	1354.6	1401.8	1415.8	1426.6	1466.2	1489.4	1480.1	1436.7	1373.9	1294.9
32.5°	1153.9	1182.5	1230.6	1263.9	1293.4	1337.5	1398.0	1422.0	1406.5	1355.4	1277.1
35°	974.1	1008.2	1064.0	1106.6	1136.0	1198.8	1270.1	1322.0	1341.4	1315.8	1246.1
37.5°	826.8	867.9	917.5	933.8	967.9	1045.4	1143.8	1215.9	1263.1	1265.5	1211.2
40°	716.0	737.0	776.5	801.3	834.6	899.7	995.8	1091.1	1162.4	1186.4	1157.7
42.5°	622.3	638.5	668.0	698.2	728.4	778.0	866.4	955.5	1051.6	1099.6	1098.8
45°	547.9	564.9	585.1	609.9	630.8	684.3	754.0	845.4	928.4	1002.8	1021.4
47.5°	482.8	497.5	522.3	533.2	547.1	597.5	657.9	743.2	829.2	914.4	936.1
50°	434.7	447.1	464.2	471.2	486.7	523.9	573.4	642.4	737.7	816.0	856.3
52.5°	391.3	400.6	413.8	419.2	430.1	458.0	502.9	557.2	636.2	716.8	773.4
55°	354.1	360.3	369.6	375.8	383.6	408.4	441.7	490.5	558.7	628.5	683.5
57.5°	319.3	323.9	333.2	336.3	342.5	361.9	385.1	426.2	489.0	551.0	604.4
60°	286.7	289.8	295.2	302.2	306.9	320.0	341.7	375.8	426.2	482.8	526.2
62.5°	255.7	260.4	261.9	265.0	268.9	281.3	298.3	323.1	367.3	413.8	459.5
65°	224.0	227.8	230.9	231.7	235.6	244.9	260.4	282.1	310.7	351.0	393.7
67.5°	194.5	196.8	198.4	201.5	205.4	210.0	222.4	238.7	265.0	297.6	331.7
70°	167.4	167.4	169.7	170.5	175.1	180.6	186.0	201.5	224.7	251.1	274.3
72.5°	137.9	141.8	141.0	144.9	144.1	148.0	155.0	165.1	182.1	203.0	225.5
75°	112.4	114.7	114.7	114.7	116.2	119.3	123.2	132.5	145.7	162.7	175.9
77.5°	87.6	89.1	89.1	89.1	89.9	93.0	96.9	103.1	112.4	122.4	130.2
80°	62.8	64.3	64.3	65.9	65.9	66.6	70.5	73.6	78.3	86.0	93.8
82.5°	42.6	43.4	44.9	44.9	44.2	45.7	46.5	49.6	54.2	55.8	61.2
85°	23.2	24.0	24.8	24.8	25.6	27.1	26.3	29.4	29.4	32.5	34.1
87.5°	9.3	10.8	10.8	10.1	10.8	10.8	10.8	12.4	13.2	13.9	13.2
90°	44.5	43.8	43.1	42.8	41.8	39.8	37.7	35.7	33.7	31.0	28.2
92.5°	41.3	41.3	41.3	41.3	40.3	38.2	36.2	34.1	32.1	29.4	26.7
95°	43.7	43.3	43.0	42.8	41.8	39.8	37.7	35.7	33.7	33.3	33.0
97.5°	42.1	41.8	41.5	41.3	40.5	38.8	37.1	35.4	33.7	69.4	105.1
100°	42.1	41.8	41.5	41.3	44.2	50.0	55.7	61.5	67.3	114.2	161.2
102.5°	44.4	44.4	44.4	44.4	82.7	159.2	235.7	312.2	388.7	384.6	380.5
105°	460.6	472.8	485.1	491.2	489.7	486.6	483.5	480.5	477.4	475.7	474.0
107.5°	586.4	585.0	583.7	583.0	582.2	580.5	578.8	577.1	575.4	573.0	570.6
110°	680.5	679.4	678.4	677.9	677.6	676.9	676.2	675.5	674.8	672.8	670.7

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	773.1	771.7	770.4	769.7	769.9	770.2	770.5	770.9	771.2	770.5	769.9
115°	866.1	866.1	866.1	866.1	865.8	865.1	864.4	863.7	863.0	863.4	863.7
117.5°	959.5	959.5	959.5	959.5	959.7	960.0	960.3	960.7	961.0	960.0	959.0
120°	1048.0	1048.7	1049.4	1049.7	1049.4	1048.7	1048.0	1047.4	1046.7	1047.0	1047.4
122.5°	1133.7	1134.4	1135.1	1135.4	1135.2	1134.9	1134.6	1134.2	1133.9	1133.2	1132.5
125°	1217.4	1217.0	1216.7	1216.5	1216.0	1215.0	1213.9	1212.9	1211.9	1212.6	1213.3
127.5°	1293.7	1294.1	1294.4	1294.6	1294.8	1295.1	1295.4	1295.8	1296.1	1294.4	1292.7
130°	1369.6	1369.6	1369.6	1369.6	1369.4	1369.1	1368.7	1368.4	1368.0	1367.0	1366.0
132.5°	1440.6	1441.0	1441.3	1441.5	1441.3	1441.0	1440.6	1440.3	1439.9	1438.5	1437.2
135°	1509.0	1508.3	1507.6	1507.3	1507.0	1506.3	1505.6	1504.9	1504.2	1502.8	1501.5
137.5°	1570.7	1571.0	1571.3	1571.5	1571.2	1570.5	1569.8	1569.2	1568.5	1566.8	1565.1
140°	1632.1	1631.7	1631.4	1631.2	1630.7	1629.7	1628.6	1627.6	1626.6	1625.9	1625.3
142.5°	1684.8	1684.8	1684.8	1684.8	1684.5	1683.8	1683.1	1682.4	1681.7	1681.4	1681.0
145°	1737.0	1736.3	1735.6	1735.3	1735.1	1734.8	1734.4	1734.1	1733.7	1733.7	1733.7
147.5°	1782.0	1781.7	1781.4	1781.2	1781.0	1780.7	1780.4	1780.0	1779.7	1780.0	1780.4
150°	1824.9	1824.5	1824.2	1824.0	1824.0	1824.0	1824.0	1824.0	1824.0	1824.4	1824.7
152.5°	1863.0	1863.3	1863.6	1863.8	1863.5	1862.8	1862.1	1861.5	1860.8	1861.5	1862.1
155°	1896.4	1897.5	1898.5	1899.0	1898.3	1897.0	1895.6	1894.3	1892.9	1893.9	1894.9
157.5°	1925.4	1927.1	1928.8	1929.6	1928.8	1927.1	1925.4	1923.7	1922.0	1923.4	1924.7
160°	1953.6	1955.6	1957.7	1958.7	1957.7	1955.6	1953.6	1951.5	1949.5	1949.8	1950.2
162.5°	1975.7	1978.0	1980.4	1981.6	1980.6	1978.6	1976.5	1974.5	1972.5	1972.8	1973.2
165°	1996.9	2000.0	2003.1	2004.6	2003.2	2000.5	1997.8	1995.1	1992.4	1992.4	1992.4
167.5°	2012.9	2016.3	2019.7	2021.4	2019.9	2016.8	2013.8	2010.7	2007.7	2008.0	2008.4
170°	2026.7	2030.1	2033.5	2035.2	2033.8	2031.1	2028.4	2025.7	2023.0	2022.6	2022.3
172.5°	2035.0	2038.8	2042.5	2044.4	2043.0	2040.3	2037.6	2034.8	2032.1	2031.8	2031.4
175°	2041.8	2045.9	2050.0	2052.0	2050.5	2047.4	2044.4	2041.3	2038.3	2037.9	2037.6
177.5°	2044.9	2049.0	2053.1	2055.1	2053.7	2051.0	2048.3	2045.6	2042.9	2042.2	2041.5
180°	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	964.8	961.7	959.4	959.4	952.4	945.4	941.5	940.0	938.4	932.2	923.7
5°	1004.3	994.2	987.3	980.3	968.7	956.3	943.9	936.9	926.8	912.9	902.8
7.5°	1048.5	1024.5	1016.7	1008.2	984.9	964.0	947.0	932.2	916.0	898.1	880.3
10°	1085.7	1060.1	1043.1	1028.3	998.1	970.2	944.6	922.9	902.0	878.8	857.1
12.5°	1121.3	1084.9	1067.1	1045.4	1013.6	973.3	940.0	912.9	881.9	857.8	831.5
15°	1170.9	1109.7	1080.3	1066.3	1023.7	976.4	936.1	895.8	870.2	833.8	810.6
17.5°	1178.7	1129.1	1109.7	1074.1	1022.9	969.4	922.9	882.6	843.9	811.4	781.1
20°	1205.8	1140.7	1109.7	1087.2	1019.8	965.6	914.4	862.5	825.3	790.4	756.3
22.5°	1222.8	1149.2	1116.7	1081.0	1016.7	951.6	891.2	846.2	800.5	764.9	737.7
25°	1218.2	1144.6	1108.1	1074.8	996.6	931.5	877.2	819.9	777.3	738.5	702.9
27.5°	1215.9	1132.9	1094.2	1057.0	983.4	915.2	847.0	800.5	753.2	708.3	681.9
30°	1209.7	1118.2	1073.3	1033.0	956.3	885.0	826.8	772.6	725.3	684.3	649.4
32.5°	1188.7	1093.4	1050.0	1006.6	926.8	855.5	796.6	746.3	699.0	656.4	623.0
35°	1160.8	1064.0	1016.7	971.0	891.2	819.1	764.9	712.2	668.0	626.9	595.1
37.5°	1132.9	1029.9	985.7	933.0	859.4	784.2	728.4	681.2	640.1	597.5	562.6
40°	1092.6	989.6	940.8	895.8	809.8	739.3	688.1	645.5	605.2	564.9	535.5
42.5°	1037.6	945.4	895.0	845.4	764.9	695.1	645.5	607.5	569.6	536.3	503.7
45°	981.8	891.9	847.0	802.8	715.3	649.4	603.7	568.8	537.0	500.6	474.3
47.5°	914.4	838.5	793.5	750.1	667.2	601.3	559.5	527.0	497.5	467.3	442.5
50°	845.4	779.6	738.5	693.6	614.5	554.8	513.8	486.7	462.6	434.0	413.8
52.5°	771.1	713.7	678.8	635.4	565.7	510.7	468.8	441.7	421.6	400.6	382.8
55°	692.0	650.2	613.0	578.1	512.2	462.6	425.4	401.4	387.5	368.1	352.6
57.5°	620.7	580.4	557.9	518.4	461.1	412.3	382.8	362.7	346.4	334.8	322.4
60°	546.3	513.8	489.0	460.3	409.9	368.9	337.9	326.2	309.2	300.7	295.2
62.5°	475.0	451.8	428.5	406.8	361.9	323.1	299.9	285.2	275.1	266.6	261.9
65°	407.6	385.9	369.6	350.3	313.1	282.1	260.4	248.8	238.7	236.4	230.9
67.5°	341.7	332.4	314.6	299.1	267.4	243.3	227.1	212.3	206.9	204.6	199.9
70°	285.9	275.1	261.2	248.0	224.0	203.0	188.3	182.9	175.1	174.4	168.9
72.5°	235.6	222.4	212.3	202.3	184.4	165.8	158.1	150.3	146.5	143.4	141.0
75°	186.8	177.5	170.5	162.0	146.5	134.1	123.2	120.1	117.8	117.0	115.5
77.5°	139.5	133.3	130.2	121.7	110.8	100.0	95.3	90.7	90.7	89.1	89.9
80°	99.2	95.3	91.4	86.8	77.5	72.8	69.0	65.9	64.3	63.5	64.3
82.5°	62.8	60.4	59.7	56.6	50.4	48.0	44.9	42.6	42.6	42.6	42.6
85°	34.9	34.9	34.9	30.2	27.9	25.6	24.0	23.2	23.2	23.2	24.0
87.5°	14.7	14.7	12.4	12.4	11.6	10.1	9.3	9.3	10.1	10.1	10.8
90°	25.5	22.8	21.4	19.5	15.8	12.1	8.3	4.6	8.3	12.1	15.8
92.5°	24.0	21.3	19.9	20.2	20.9	21.6	22.3	23.0	22.3	21.6	20.9
95°	32.6	32.3	32.1	37.9	49.5	61.0	72.6	84.2	72.6	61.0	49.5
97.5°	140.8	176.5	194.3	190.6	183.1	175.6	168.2	160.7	168.2	175.6	183.1
100°	208.1	255.0	278.5	275.4	269.3	263.2	257.1	251.0	257.1	263.2	269.3
102.5°	376.4	372.3	370.3	368.3	364.2	360.1	356.1	352.0	356.1	360.1	364.2
105°	472.3	470.6	469.8	468.8	466.7	464.7	462.6	460.6	462.6	464.7	466.7
107.5°	568.3	565.9	564.7	564.2	563.2	562.1	561.1	560.1	561.1	562.1	563.2
110°	668.7	666.6	665.6	665.1	664.1	663.1	662.1	661.1	662.1	663.1	664.1

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	769.2	768.5	768.2	767.2	765.1	763.1	761.0	759.0	761.0	763.1	765.1
115°	864.1	864.4	864.6	864.1	863.1	862.0	861.0	860.0	861.0	862.0	863.1
117.5°	957.9	956.9	956.4	955.7	954.4	953.0	951.7	950.3	951.7	953.0	954.4
120°	1047.7	1048.0	1048.2	1047.5	1046.2	1044.8	1043.5	1042.1	1043.5	1044.8	1046.2
122.5°	1131.8	1131.1	1130.8	1130.5	1129.8	1129.1	1128.5	1127.8	1128.5	1129.1	1129.8
125°	1214.0	1214.7	1215.0	1214.3	1213.0	1211.6	1210.3	1208.9	1210.3	1211.6	1213.0
127.5°	1291.0	1289.3	1288.5	1288.3	1288.0	1287.6	1287.3	1286.9	1287.3	1287.6	1288.0
130°	1364.9	1363.9	1363.4	1363.2	1362.9	1362.6	1362.2	1361.9	1362.2	1362.6	1362.9
132.5°	1435.8	1434.5	1433.8	1433.5	1432.8	1432.1	1431.5	1430.8	1431.5	1432.1	1432.8
135°	1500.1	1498.8	1498.1	1498.3	1498.6	1498.9	1499.3	1499.6	1499.3	1498.9	1498.6
137.5°	1563.4	1561.7	1560.8	1560.8	1560.8	1560.8	1560.8	1560.8	1560.8	1560.8	1560.8
140°	1624.6	1623.9	1623.6	1623.3	1622.6	1621.9	1621.2	1620.5	1621.2	1621.9	1622.6
142.5°	1680.7	1680.4	1680.2	1679.5	1678.2	1676.8	1675.5	1674.1	1675.5	1676.8	1678.2
145°	1733.7	1733.7	1733.7	1733.2	1732.2	1731.2	1730.2	1729.2	1730.2	1731.2	1732.2
147.5°	1780.7	1781.0	1781.2	1780.2	1778.1	1776.1	1774.0	1772.0	1774.0	1776.1	1778.1
150°	1825.1	1825.4	1825.6	1824.9	1823.5	1822.2	1820.8	1819.4	1820.8	1822.2	1823.5
152.5°	1862.8	1863.5	1863.8	1863.3	1862.3	1861.2	1860.2	1859.2	1860.2	1861.2	1862.3
155°	1896.0	1897.0	1897.5	1897.3	1897.0	1896.7	1896.3	1896.0	1896.3	1896.7	1897.0
157.5°	1926.1	1927.4	1928.1	1928.1	1928.1	1928.1	1928.1	1928.1	1928.1	1928.1	1928.1
160°	1950.5	1950.8	1951.0	1951.5	1952.5	1953.6	1954.6	1955.6	1954.6	1953.6	1952.5
162.5°	1973.5	1973.8	1974.0	1974.7	1976.0	1977.4	1978.7	1980.1	1978.7	1977.4	1976.0
165°	1992.4	1992.4	1992.4	1993.2	1994.9	1996.6	1998.3	2000.0	1998.3	1996.6	1994.9
167.5°	2008.7	2009.0	2009.2	2010.0	2011.7	2013.4	2015.1	2016.8	2015.1	2013.4	2011.7
170°	2021.9	2021.6	2021.4	2022.4	2024.5	2026.5	2028.6	2030.6	2028.6	2026.5	2024.5
172.5°	2031.1	2030.8	2030.6	2031.6	2033.7	2035.7	2037.8	2039.8	2037.8	2035.7	2033.7
175°	2037.2	2036.9	2036.7	2037.7	2039.8	2041.8	2043.9	2045.9	2043.9	2041.8	2039.8
177.5°	2040.8	2040.1	2039.8	2041.0	2043.4	2045.7	2048.1	2050.5	2048.1	2045.7	2043.4
180°	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	921.4	918.3	919.8	912.1	905.1	895.0	886.5	885.0	883.4	888.1	885.0
5°	895.0	891.2	887.3	878.0	864.0	855.5	843.1	842.3	837.7	830.7	832.3
7.5°	866.4	864.0	858.6	843.9	831.5	816.8	806.7	798.2	794.3	788.1	785.8
10°	843.1	834.6	829.9	813.7	799.0	783.5	770.3	764.1	757.1	751.7	747.8
12.5°	811.4	809.0	795.9	782.7	770.3	752.5	742.4	724.6	715.3	719.9	718.4
15°	790.4	779.6	776.5	757.9	737.0	725.3	706.7	695.1	691.2	684.3	675.7
17.5°	762.5	755.6	744.7	727.7	703.6	687.4	674.2	663.3	658.7	649.4	642.4
20°	736.2	724.6	716.0	700.5	677.3	656.4	640.1	633.1	621.5	613.7	609.9
22.5°	712.2	703.6	691.2	668.0	647.8	627.7	608.3	598.2	587.4	582.7	576.5
25°	682.7	668.8	660.2	634.7	613.0	596.7	578.9	565.7	559.5	551.7	550.2
27.5°	654.0	640.9	630.8	608.3	582.0	561.0	550.2	540.9	530.1	530.1	526.2
30°	625.4	616.1	600.6	578.9	554.1	533.9	521.5	513.0	509.1	506.0	505.3
32.5°	596.7	584.3	575.0	545.5	527.0	508.4	499.1	492.1	487.4	486.7	487.4
35°	567.2	553.3	544.0	517.7	499.1	482.0	478.1	471.9	469.6	468.8	472.7
37.5°	536.3	525.4	513.8	492.1	471.2	461.1	453.3	451.0	450.2	454.9	456.4
40°	507.6	498.3	487.4	464.2	448.7	437.8	434.0	431.6	434.7	439.4	441.7
42.5°	480.5	467.3	458.8	437.8	423.9	417.7	413.0	413.0	416.1	421.6	425.4
45°	451.8	441.7	433.2	414.6	402.2	395.2	394.4	395.2	399.1	403.0	407.6
47.5°	423.9	413.8	404.5	389.0	378.2	374.3	373.5	374.3	380.5	385.9	391.3
50°	398.3	387.5	378.9	364.2	355.7	351.0	351.8	355.7	360.3	368.1	375.1
52.5°	368.1	360.3	352.6	339.4	331.7	328.6	330.9	334.0	342.5	347.9	356.5
55°	338.6	331.7	325.5	315.4	309.2	306.9	308.4	313.1	320.0	329.3	339.4
57.5°	311.5	303.8	297.6	290.6	283.6	284.4	285.2	291.4	299.9	308.4	320.0
60°	281.3	276.6	271.2	262.7	259.6	259.6	261.9	268.9	276.6	290.6	300.7
62.5°	254.2	248.0	244.1	238.7	234.0	234.8	240.2	246.4	255.7	267.4	280.5
65°	226.3	219.3	216.2	211.6	210.0	210.8	214.7	224.0	234.0	244.1	256.5
67.5°	195.3	193.0	189.9	185.2	186.8	187.5	191.4	199.2	210.0	220.1	234.0
70°	168.9	164.3	163.5	159.6	159.6	162.0	169.7	175.1	185.2	196.1	210.8
72.5°	141.0	137.2	137.2	134.1	136.4	138.7	142.6	150.3	159.6	170.5	182.9
75°	112.4	110.8	112.4	110.8	110.8	114.7	119.3	125.5	135.6	147.2	157.3
77.5°	86.8	86.8	86.0	88.3	88.3	90.7	96.9	103.1	110.8	120.1	131.0
80°	63.5	63.5	63.5	65.9	68.2	68.2	72.1	79.8	86.8	93.0	103.1
82.5°	43.4	43.4	43.4	44.9	48.0	48.0	52.7	57.3	65.1	70.5	75.2
85°	26.3	26.3	25.6	27.1	27.9	30.2	34.1	37.2	41.1	45.7	50.4
87.5°	11.6	11.6	12.4	13.2	13.9	15.5	17.0	18.6	22.5	24.0	26.3
90°	19.5	21.4	22.8	25.5	28.2	31.0	33.7	35.7	37.7	39.8	41.8
92.5°	20.2	19.9	21.3	24.0	26.7	29.4	32.1	34.1	36.2	38.2	40.3
95°	37.9	32.1	32.3	32.6	33.0	33.3	33.7	35.7	37.7	39.8	41.8
97.5°	190.6	194.3	176.5	140.8	105.1	69.4	33.7	35.4	37.1	38.8	40.5
100°	275.4	278.5	255.0	208.1	161.2	114.2	67.3	61.5	55.7	50.0	44.2
102.5°	368.3	370.3	372.3	376.4	380.5	384.6	388.7	312.2	235.7	159.2	82.7
105°	468.8	469.8	470.6	472.3	474.0	475.7	477.4	480.5	483.5	486.6	489.7
107.5°	564.2	564.7	565.9	568.3	570.6	573.0	575.4	577.1	578.8	580.5	582.2
110°	665.1	665.6	666.6	668.7	670.7	672.8	674.8	675.5	676.2	676.9	677.6

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	767.2	768.2	768.5	769.2	769.9	770.5	771.2	770.9	770.5	770.2	769.9
115°	864.1	864.6	864.4	864.1	863.7	863.4	863.0	863.7	864.4	865.1	865.8
117.5°	955.7	956.4	956.9	957.9	959.0	960.0	961.0	960.7	960.3	960.0	959.7
120°	1047.5	1048.2	1048.0	1047.7	1047.4	1047.0	1046.7	1047.4	1048.0	1048.7	1049.4
122.5°	1130.5	1130.8	1131.1	1131.8	1132.5	1133.2	1133.9	1134.2	1134.6	1134.9	1135.2
125°	1214.3	1215.0	1214.7	1214.0	1213.3	1212.6	1211.9	1212.9	1213.9	1215.0	1216.0
127.5°	1288.3	1288.5	1289.3	1291.0	1292.7	1294.4	1296.1	1295.8	1295.4	1295.1	1294.8
130°	1363.2	1363.4	1363.9	1364.9	1366.0	1367.0	1368.0	1368.4	1368.7	1369.1	1369.4
132.5°	1433.5	1433.8	1434.5	1435.8	1437.2	1438.5	1439.9	1440.3	1440.6	1441.0	1441.3
135°	1498.3	1498.1	1498.8	1500.1	1501.5	1502.8	1504.2	1504.9	1505.6	1506.3	1507.0
137.5°	1560.8	1560.8	1561.7	1563.4	1565.1	1566.8	1568.5	1569.2	1569.8	1570.5	1571.2
140°	1623.3	1623.6	1623.9	1624.6	1625.3	1625.9	1626.6	1627.6	1628.6	1629.7	1630.7
142.5°	1679.5	1680.2	1680.4	1680.7	1681.0	1681.4	1681.7	1682.4	1683.1	1683.8	1684.5
145°	1733.2	1733.7	1733.7	1733.7	1733.7	1733.7	1733.7	1734.1	1734.4	1734.8	1735.1
147.5°	1780.2	1781.2	1781.0	1780.7	1780.4	1780.0	1779.7	1780.0	1780.4	1780.7	1781.0
150°	1824.9	1825.6	1825.4	1825.1	1824.7	1824.4	1824.0	1824.0	1824.0	1824.0	1824.0
152.5°	1863.3	1863.8	1863.5	1862.8	1862.1	1861.5	1860.8	1861.5	1862.1	1862.8	1863.5
155°	1897.3	1897.5	1897.0	1896.0	1894.9	1893.9	1892.9	1894.3	1895.6	1897.0	1898.3
157.5°	1928.1	1928.1	1927.4	1926.1	1924.7	1923.4	1922.0	1923.7	1925.4	1927.1	1928.8
160°	1951.5	1951.0	1950.8	1950.5	1950.2	1949.8	1949.5	1951.5	1953.6	1955.6	1957.7
162.5°	1974.7	1974.0	1973.8	1973.5	1973.2	1972.8	1972.5	1974.5	1976.5	1978.6	1980.6
165°	1993.2	1992.4	1992.4	1992.4	1992.4	1992.4	1992.4	1995.1	1997.8	2000.5	2003.2
167.5°	2010.0	2009.2	2009.0	2008.7	2008.4	2008.0	2007.7	2010.7	2013.8	2016.8	2019.9
170°	2022.4	2021.4	2021.6	2021.9	2022.3	2022.6	2023.0	2025.7	2028.4	2031.1	2033.8
172.5°	2031.6	2030.6	2030.8	2031.1	2031.4	2031.8	2032.1	2034.8	2037.6	2040.3	2043.0
175°	2037.7	2036.7	2036.9	2037.2	2037.6	2037.9	2038.3	2041.3	2044.4	2047.4	2050.5
177.5°	2041.0	2039.8	2040.1	2040.8	2041.5	2042.2	2042.9	2045.6	2048.3	2051.0	2053.7
180°	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	882.6	881.9	878.0	879.5	874.9	876.4	878.8	879.5	882.6	880.3	879.5
5°	828.4	826.8	824.5	822.2	821.4	824.5	819.1	820.6	822.2	824.5	827.6
7.5°	784.2	783.5	781.1	777.3	775.7	774.2	774.9	780.4	779.6	778.8	784.2
10°	743.9	744.7	740.1	739.3	734.6	733.9	734.6	736.2	738.5	741.6	742.4
12.5°	702.1	712.2	703.6	700.5	693.6	697.4	699.0	692.0	695.9	698.2	709.8
15°	675.7	671.1	665.7	665.7	662.6	661.0	657.1	662.6	665.7	670.3	668.8
17.5°	639.3	631.6	628.5	625.4	626.1	629.2	620.7	633.1	633.1	635.4	631.6
20°	607.5	601.3	597.5	595.9	593.6	592.0	591.3	594.4	599.0	600.6	604.4
22.5°	574.2	574.2	568.0	565.7	564.1	561.8	565.7	563.4	566.5	569.6	575.8
25°	546.3	546.3	544.0	540.9	538.6	537.0	539.4	538.6	540.9	544.8	546.3
27.5°	523.9	521.5	520.8	520.0	519.2	520.0	519.2	521.5	523.9	524.6	523.1
30°	504.5	502.2	502.9	502.9	503.7	502.9	502.2	504.5	505.3	503.7	504.5
32.5°	486.7	486.7	488.2	489.0	489.0	489.8	490.5	489.0	489.8	487.4	488.2
35°	471.9	473.5	475.0	475.8	476.6	475.8	477.4	476.6	475.0	473.5	472.7
37.5°	457.2	458.8	461.9	462.6	465.0	465.7	464.2	464.2	463.4	460.3	458.8
40°	441.7	443.3	447.1	449.5	451.0	453.3	451.8	451.8	448.7	445.6	443.3
42.5°	427.0	430.1	434.0	436.3	439.4	439.4	439.4	437.8	434.0	430.9	428.5
45°	412.3	413.0	418.5	422.3	425.4	425.4	425.4	423.1	420.8	414.6	411.5
47.5°	396.0	398.3	404.5	408.4	411.5	412.3	412.3	409.9	405.3	399.9	396.0
50°	378.2	382.0	389.0	394.4	398.3	399.9	397.5	396.0	390.6	384.4	379.7
52.5°	361.1	365.8	374.3	378.9	384.4	385.1	384.4	382.0	375.8	367.3	363.4
55°	344.1	347.9	357.2	365.0	369.6	371.2	369.6	365.8	358.0	349.5	345.6
57.5°	325.5	330.9	341.0	348.7	354.1	354.9	353.4	349.5	343.3	332.4	327.0
60°	306.1	313.1	323.1	330.9	337.9	338.6	337.1	331.7	323.9	313.1	308.4
62.5°	286.7	292.1	303.8	312.3	317.7	321.6	318.5	313.1	305.3	294.5	287.5
65°	264.3	272.0	282.1	289.8	296.0	296.8	295.2	290.6	282.1	270.5	265.0
67.5°	242.6	248.0	258.1	268.1	270.5	272.8	270.5	265.8	258.8	248.8	241.0
70°	216.2	220.9	233.3	240.2	243.3	245.7	244.1	239.5	233.3	224.0	217.8
72.5°	189.9	193.7	205.4	210.8	217.0	216.2	215.4	212.3	203.8	197.6	193.7
75°	162.0	166.6	174.4	181.3	183.7	183.7	183.7	181.3	175.9	165.8	162.0
77.5°	136.4	138.7	144.9	148.8	151.1	151.9	151.1	147.2	144.1	137.2	134.8
80°	104.6	110.8	115.5	116.2	119.3	119.3	119.3	117.8	114.7	107.7	106.9
82.5°	79.0	80.6	85.2	87.6	89.1	88.3	88.3	85.2	84.5	80.6	79.0
85°	53.5	55.8	55.0	58.1	58.9	57.3	57.3	58.9	55.0	55.8	53.5
87.5°	29.4	29.4	31.0	30.2	33.3	33.3	31.8	32.5	31.0	30.2	29.4
90°	42.8	43.1	43.8	44.5	45.2	45.9	45.2	44.5	43.8	43.1	42.8
92.5°	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3
95°	42.8	43.0	43.3	43.7	44.0	44.4	44.0	43.7	43.3	43.0	42.8
97.5°	41.3	41.5	41.8	42.1	42.5	42.8	42.5	42.1	41.8	41.5	41.3
100°	41.3	41.5	41.8	42.1	42.5	42.8	42.5	42.1	41.8	41.5	41.3
102.5°	44.4	44.4	44.4	44.4	44.4	44.4	44.4	44.4	44.4	44.4	44.4
105°	491.2	485.1	472.8	460.6	448.3	436.1	448.3	460.6	472.8	485.1	491.2
107.5°	583.0	583.7	585.0	586.4	587.7	589.1	587.7	586.4	585.0	583.7	583.0
110°	677.9	678.4	679.4	680.5	681.5	682.5	681.5	680.5	679.4	678.4	677.9

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	769.7	770.4	771.7	773.1	774.4	775.8	774.4	773.1	771.7	770.4	769.7
115°	866.1	866.1	866.1	866.1	866.1	866.1	866.1	866.1	866.1	866.1	866.1
117.5°	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5	959.5
120°	1049.7	1049.4	1048.7	1048.0	1047.4	1046.7	1047.4	1048.0	1048.7	1049.4	1049.7
122.5°	1135.4	1135.1	1134.4	1133.7	1133.1	1132.4	1133.1	1133.7	1134.4	1135.1	1135.4
125°	1216.5	1216.7	1217.0	1217.4	1217.7	1218.1	1217.7	1217.4	1217.0	1216.7	1216.5
127.5°	1294.6	1294.4	1294.1	1293.7	1293.4	1293.0	1293.4	1293.7	1294.1	1294.4	1294.6
130°	1369.6	1369.6	1369.6	1369.6	1369.6	1369.6	1369.6	1369.6	1369.6	1369.6	1369.6
132.5°	1441.5	1441.3	1441.0	1440.6	1440.3	1439.9	1440.3	1440.6	1441.0	1441.3	1441.5
135°	1507.3	1507.6	1508.3	1509.0	1509.6	1510.3	1509.6	1509.0	1508.3	1507.6	1507.3
137.5°	1571.5	1571.3	1571.0	1570.7	1570.3	1570.0	1570.3	1570.7	1571.0	1571.3	1571.5
140°	1631.2	1631.4	1631.7	1632.1	1632.4	1632.8	1632.4	1632.1	1631.7	1631.4	1631.2
142.5°	1684.8	1684.8	1684.8	1684.8	1684.8	1684.8	1684.8	1684.8	1684.8	1684.8	1684.8
145°	1735.3	1735.6	1736.3	1737.0	1737.6	1738.3	1737.6	1737.0	1736.3	1735.6	1735.3
147.5°	1781.2	1781.4	1781.7	1782.0	1782.4	1782.7	1782.4	1782.0	1781.7	1781.4	1781.2
150°	1824.0	1824.2	1824.5	1824.9	1825.2	1825.6	1825.2	1824.9	1824.5	1824.2	1824.0
152.5°	1863.8	1863.6	1863.3	1863.0	1862.6	1862.3	1862.6	1863.0	1863.3	1863.6	1863.8
155°	1899.0	1898.5	1897.5	1896.4	1895.4	1894.4	1895.4	1896.4	1897.5	1898.5	1899.0
157.5°	1929.6	1928.8	1927.1	1925.4	1923.7	1922.0	1923.7	1925.4	1927.1	1928.8	1929.6
160°	1958.7	1957.7	1955.6	1953.6	1951.5	1949.5	1951.5	1953.6	1955.6	1957.7	1958.7
162.5°	1981.6	1980.4	1978.0	1975.7	1973.3	1970.9	1973.3	1975.7	1978.0	1980.4	1981.6
165°	2004.6	2003.1	2000.0	1996.9	1993.9	1990.8	1993.9	1996.9	2000.0	2003.1	2004.6
167.5°	2021.4	2019.7	2016.3	2012.9	2009.5	2006.1	2009.5	2012.9	2016.3	2019.7	2021.4
170°	2035.2	2033.5	2030.1	2026.7	2023.3	2019.9	2023.3	2026.7	2030.1	2033.5	2035.2
172.5°	2044.4	2042.5	2038.8	2035.0	2031.3	2027.5	2031.3	2035.0	2038.8	2042.5	2044.4
175°	2052.0	2050.0	2045.9	2041.8	2037.8	2033.7	2037.8	2041.8	2045.9	2050.0	2052.0
177.5°	2055.1	2053.1	2049.0	2044.9	2040.8	2036.7	2040.8	2044.9	2049.0	2053.1	2055.1
180°	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3	935.3
2.5°	879.5	884.2	879.5	882.6	884.2	888.1	889.6	896.6	898.9	904.3	904.3
5°	826.8	829.2	829.9	833.0	836.1	843.9	849.3	859.4	871.0	872.6	879.5
7.5°	784.2	788.1	794.3	792.0	797.4	809.0	816.0	828.4	840.0	846.2	854.7
10°	746.3	750.9	753.2	755.6	765.6	775.7	786.6	795.1	810.6	819.9	826.8
12.5°	715.3	711.4	716.0	724.6	736.2	742.4	757.1	770.3	781.9	792.0	798.2
15°	675.0	678.1	682.7	697.4	700.5	716.0	721.5	736.2	757.9	767.2	774.9
17.5°	636.2	646.3	655.6	661.0	670.3	682.7	698.2	714.5	728.4	739.3	748.6
20°	605.2	615.3	620.7	624.6	633.9	650.9	665.7	685.8	703.6	712.2	724.6
22.5°	580.4	580.4	588.2	599.8	605.2	621.5	633.9	655.6	675.0	685.8	697.4
25°	549.4	554.1	560.3	570.3	578.1	591.3	609.1	627.7	648.6	657.9	672.6
27.5°	523.9	529.3	537.8	540.1	547.9	559.5	578.1	598.2	619.9	630.0	642.4
30°	504.5	507.6	510.7	515.3	522.3	532.4	547.9	565.7	592.0	599.8	615.3
32.5°	487.4	489.0	490.5	494.4	498.3	508.4	520.8	540.1	561.8	573.4	587.4
35°	471.9	470.4	471.2	473.5	477.4	481.2	494.4	510.7	530.8	544.8	555.6
37.5°	457.2	454.1	453.3	453.3	454.9	459.5	469.6	483.6	505.3	516.9	527.7
40°	440.9	437.8	436.3	435.5	434.7	437.8	445.6	459.5	476.6	487.4	499.8
42.5°	425.4	422.3	418.5	417.7	416.1	417.7	423.1	436.3	451.0	461.9	471.9
45°	409.9	404.5	399.9	396.8	397.5	395.2	399.1	409.2	426.2	433.2	443.3
47.5°	392.9	386.7	380.5	377.4	374.3	375.8	377.4	385.9	400.6	407.6	417.7
50°	376.6	368.1	361.1	357.2	354.9	353.4	354.9	363.4	374.3	380.5	389.0
52.5°	358.0	349.5	342.5	336.3	333.2	330.9	331.7	339.4	349.5	355.7	364.2
55°	341.0	330.1	320.8	313.1	310.7	310.0	309.2	314.6	323.1	329.3	336.3
57.5°	321.6	310.7	300.7	291.4	286.7	285.9	285.9	287.5	298.3	303.0	306.9
60°	302.2	290.6	279.7	271.2	264.3	261.9	261.2	264.3	269.7	274.3	279.7
62.5°	280.5	268.9	255.7	248.0	241.0	234.8	237.1	237.9	245.7	248.0	252.6
65°	259.6	246.4	235.6	223.2	215.4	211.6	210.0	211.6	217.8	218.5	221.6
67.5°	235.6	223.2	210.0	201.5	194.5	187.5	186.0	186.0	189.1	191.4	195.3
70°	212.3	199.9	185.2	175.9	168.9	162.7	160.4	159.6	162.0	163.5	167.4
72.5°	185.2	172.8	162.0	151.9	143.4	138.7	136.4	134.8	137.2	138.7	139.5
75°	156.5	146.5	135.6	125.5	120.1	115.5	112.4	110.0	111.6	111.6	111.6
77.5°	129.4	119.3	110.8	103.8	96.9	91.4	89.1	86.8	87.6	87.6	89.1
80°	100.7	93.8	86.8	80.6	74.4	69.7	68.2	65.9	64.3	63.5	63.5
82.5°	74.4	69.0	62.8	57.3	54.2	49.6	48.0	44.9	44.9	44.2	44.2
85°	49.6	46.5	40.3	36.4	34.1	31.8	30.2	28.7	26.3	26.3	25.6
87.5°	26.3	24.8	23.2	18.6	18.6	16.3	15.5	14.7	12.4	13.2	13.2
90°	41.8	39.8	37.7	35.7	33.7	31.0	28.2	25.5	22.8	21.4	19.5
92.5°	40.3	38.2	36.2	34.1	32.1	29.4	26.7	24.0	21.3	19.9	20.2
95°	41.8	39.8	37.7	35.7	33.7	33.3	33.0	32.6	32.3	32.1	37.9
97.5°	40.5	38.8	37.1	35.4	33.7	69.4	105.1	140.8	176.5	194.3	190.6
100°	44.2	50.0	55.7	61.5	67.3	114.2	161.2	208.1	255.0	278.5	275.4
102.5°	82.7	159.2	235.7	312.2	388.7	384.6	380.5	376.4	372.3	370.3	368.3
105°	489.7	486.6	483.5	480.5	477.4	475.7	474.0	472.3	470.6	469.8	468.8
107.5°	582.2	580.5	578.8	577.1	575.4	573.0	570.6	568.3	565.9	564.7	564.2
110°	677.6	676.9	676.2	675.5	674.8	672.8	670.7	668.7	666.6	665.6	665.1

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	769.9	770.2	770.5	770.9	771.2	770.5	769.9	769.2	768.5	768.2	767.2
115°	865.8	865.1	864.4	863.7	863.0	863.4	863.7	864.1	864.4	864.6	864.1
117.5°	959.7	960.0	960.3	960.7	961.0	960.0	959.0	957.9	956.9	956.4	955.7
120°	1049.4	1048.7	1048.0	1047.4	1046.7	1047.0	1047.4	1047.7	1048.0	1048.2	1047.5
122.5°	1135.2	1134.9	1134.6	1134.2	1133.9	1133.2	1132.5	1131.8	1131.1	1130.8	1130.5
125°	1216.0	1215.0	1213.9	1212.9	1211.9	1212.6	1213.3	1214.0	1214.7	1215.0	1214.3
127.5°	1294.8	1295.1	1295.4	1295.8	1296.1	1294.4	1292.7	1291.0	1289.3	1288.5	1288.3
130°	1369.4	1369.1	1368.7	1368.4	1368.0	1367.0	1366.0	1364.9	1363.9	1363.4	1363.2
132.5°	1441.3	1441.0	1440.6	1440.3	1439.9	1438.5	1437.2	1435.8	1434.5	1433.8	1433.5
135°	1507.0	1506.3	1505.6	1504.9	1504.2	1502.8	1501.5	1500.1	1498.8	1498.1	1498.3
137.5°	1571.2	1570.5	1569.8	1569.2	1568.5	1566.8	1565.1	1563.4	1561.7	1560.8	1560.8
140°	1630.7	1629.7	1628.6	1627.6	1626.6	1625.9	1625.3	1624.6	1623.9	1623.6	1623.3
142.5°	1684.5	1683.8	1683.1	1682.4	1681.7	1681.4	1681.0	1680.7	1680.4	1680.2	1679.5
145°	1735.1	1734.8	1734.4	1734.1	1733.7	1733.7	1733.7	1733.7	1733.7	1733.7	1733.2
147.5°	1781.0	1780.7	1780.4	1780.0	1779.7	1780.0	1780.4	1780.7	1781.0	1781.2	1780.2
150°	1824.0	1824.0	1824.0	1824.0	1824.0	1824.4	1824.7	1825.1	1825.4	1825.6	1824.9
152.5°	1863.5	1862.8	1862.1	1861.5	1860.8	1861.5	1862.1	1862.8	1863.5	1863.8	1863.3
155°	1898.3	1897.0	1895.6	1894.3	1892.9	1893.9	1894.9	1896.0	1897.0	1897.5	1897.3
157.5°	1928.8	1927.1	1925.4	1923.7	1922.0	1923.4	1924.7	1926.1	1927.4	1928.1	1928.1
160°	1957.7	1955.6	1953.6	1951.5	1949.5	1949.8	1950.2	1950.5	1950.8	1951.0	1951.5
162.5°	1980.6	1978.6	1976.5	1974.5	1972.5	1972.8	1973.2	1973.5	1973.8	1974.0	1974.7
165°	2003.2	2000.5	1997.8	1995.1	1992.4	1992.4	1992.4	1992.4	1992.4	1992.4	1993.2
167.5°	2019.9	2016.8	2013.8	2010.7	2007.7	2008.0	2008.4	2008.7	2009.0	2009.2	2010.0
170°	2033.8	2031.1	2028.4	2025.7	2023.0	2022.6	2022.3	2021.9	2021.6	2021.4	2022.4
172.5°	2043.0	2040.3	2037.6	2034.8	2032.1	2031.8	2031.4	2031.1	2030.8	2030.6	2031.6
175°	2050.5	2047.4	2044.4	2041.3	2038.3	2037.9	2037.6	2037.2	2036.9	2036.7	2037.7
177.5°	2053.7	2051.0	2048.3	2045.6	2042.9	2042.2	2041.5	2040.8	2040.1	2039.8	2041.0
180°	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9	2045.9

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	935.3	935.3	935.3	935.3
2.5°	909.8	917.5	924.5	935.3
5°	889.6	900.5	915.2	931.5
7.5°	866.4	883.4	902.8	925.3
10°	844.7	864.0	888.8	916.0
12.5°	822.2	845.4	872.6	902.0
15°	796.6	819.9	850.1	889.6
17.5°	773.4	801.3	833.8	875.7
20°	746.3	772.6	808.3	856.3
22.5°	722.2	752.5	792.0	833.8
25°	695.9	722.2	761.8	812.1
27.5°	669.5	702.1	740.1	788.9
30°	644.0	671.1	712.2	763.3
32.5°	616.1	648.6	686.6	734.6
35°	585.8	616.8	652.5	704.4
37.5°	558.7	588.9	625.4	671.1
40°	528.5	560.3	593.6	639.3
42.5°	499.1	527.7	561.0	602.9
45°	470.4	495.2	525.4	561.8
47.5°	440.9	461.9	489.8	522.3
50°	409.2	431.6	452.6	479.7
52.5°	379.7	399.1	416.1	438.6
55°	351.0	364.2	378.2	395.2
57.5°	320.8	330.9	341.0	358.8
60°	290.6	299.9	305.3	316.9
62.5°	261.2	265.0	272.0	279.0
65°	228.6	234.0	237.9	246.4
67.5°	199.2	201.5	205.4	210.8
70°	168.2	173.6	175.1	179.0
72.5°	141.8	144.1	145.7	146.5
75°	112.4	114.7	116.2	120.9
77.5°	88.3	87.6	90.7	91.4
80°	65.1	62.8	63.5	66.6
82.5°	42.6	43.4	42.6	42.6
85°	26.3	25.6	24.0	24.8
87.5°	11.6	11.6	10.8	10.8
90°	15.8	12.1	8.3	4.6
92.5°	20.9	21.6	22.3	23.0
95°	49.5	61.0	72.6	84.2
97.5°	183.1	175.6	168.2	160.7
100°	269.3	263.2	257.1	251.0
102.5°	364.2	360.1	356.1	352.0
105°	466.7	464.7	462.6	460.6
107.5°	563.2	562.1	561.1	560.1
110°	664.1	663.1	662.1	661.1

TEST NUMBER: P1032721

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	765.1	763.1	761.0	759.0
115°	863.1	862.0	861.0	860.0
117.5°	954.4	953.0	951.7	950.3
120°	1046.2	1044.8	1043.5	1042.1
122.5°	1129.8	1129.1	1128.5	1127.8
125°	1213.0	1211.6	1210.3	1208.9
127.5°	1288.0	1287.6	1287.3	1286.9
130°	1362.9	1362.6	1362.2	1361.9
132.5°	1432.8	1432.1	1431.5	1430.8
135°	1498.6	1498.9	1499.3	1499.6
137.5°	1560.8	1560.8	1560.8	1560.8
140°	1622.6	1621.9	1621.2	1620.5
142.5°	1678.2	1676.8	1675.5	1674.1
145°	1732.2	1731.2	1730.2	1729.2
147.5°	1778.1	1776.1	1774.0	1772.0
150°	1823.5	1822.2	1820.8	1819.4
152.5°	1862.3	1861.2	1860.2	1859.2
155°	1897.0	1896.7	1896.3	1896.0
157.5°	1928.1	1928.1	1928.1	1928.1
160°	1952.5	1953.6	1954.6	1955.6
162.5°	1976.0	1977.4	1978.7	1980.1
165°	1994.9	1996.6	1998.3	2000.0
167.5°	2011.7	2013.4	2015.1	2016.8
170°	2024.5	2026.5	2028.6	2030.6
172.5°	2033.7	2035.7	2037.8	2039.8
175°	2039.8	2041.8	2043.9	2045.9
177.5°	2043.4	2045.7	2048.1	2050.5
180°	2045.9	2045.9	2045.9	2045.9

(END OF REPORT)