

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032346

Luminaire Tested: S123RDIW-B560D460UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032346
REPORT IS A COMBINATION OF REPORTS P994552 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D460UB50-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3835.9 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032346

CATALOG NUMBER: S123RDIW-B560D460UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1032346

CATALOG NUMBER: S123RDIW-B560D460UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51
2	90	83	77	72	83	77	72	68	66	62	59	56	53	51	47	45	43
3	83	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	49	52	47	43	45	41	38	38	35	32
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25
7	59	47	39	34	55	44	37	32	39	33	29	33	29	26	28	25	22
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20
9	52	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9734	9734	9734
5°	9750	9389	9364
10°	9673	9037	8858
15°	9547	8600	8305
20°	9383	8126	7685
25°	9213	7632	7099
30°	8996	7108	6406
35°	8771	6593	5774
40°	8559	6033	5077
45°	8288	5486	4450
50°	7991	4901	3801
55°	7681	4275	3206
60°	7385	3634	2602
65°	7003	2977	2032
70°	6523	2250	1451
75°	5831	1523	1149
80°	4978	1059	806
85°	3737	571	423

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8288 cd/sqm

TEST NUMBER: P1032346

CATALOG NUMBER: S123RDIW-B560D460UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	2.2
10°-20°	236.5	6.2
20°-30°	340.5	8.9
30°-40°	383.4	10.0
40°-50°	366.8	9.6
50°-60°	300.2	7.8
60°-70°	202.4	5.3
70°-80°	101.5	2.6
80°-90°	27.7	0.7
90°-100°	20.7	0.5
100°-110°	100.2	2.6
110°-120°	245.6	6.4
120°-130°	311.7	8.1
130°-140°	333.0	8.7
140°-150°	311.4	8.1
150°-160°	251.2	6.5
160°-170°	162.1	4.2
170°-180°	55.9	1.5
0°-30°	662.0	17.3
0°-40°	1045.4	27.3
0°-60°	1712.5	44.6
0°-90°	2044.2	53.3
90°-120°	366.5	9.6
90°-150°	1322.6	34.5
90°-180°	1792.0	46.7
0°-180°	3835.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	904	904	904	904	904	
5°	904	901	892	898	897	86
15°	862	854	834	830	825	243
25°	785	766	733	717	709	361
35°	679	653	607	576	562	425
45°	558	525	469	427	409	431
55°	424	388	326	283	268	380
65°	290	249	192	156	148	287
75°	153	118	78	70	69	163
85°	39	23	20	19	19	43
90°	0	5	10	12	13	4
95°	27	9	14	17	17	32
105°	130	135	96	18	19	138
115°	244	247	251	255	257	241
125°	344	348	349	350	351	307
135°	428	431	433	434	433	330
145°	494	497	498	499	499	309
155°	544	544	544	546	544	251
165°	574	573	572	576	573	162
175°	588	586	586	589	586	56
180°	588	588	588	588	588	

TEST NUMBER: P1032346

CATALOG NUMBER: S123RDIW-B560D460UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	904.3	904.3	904.3	904.3	904.3
2.5°	908.0	905.0	896.2	904.3	902.8
5°	904.3	900.6	891.8	898.4	897.0
7.5°	897.7	894.0	883.0	887.4	885.2
10°	888.9	883.8	870.6	871.3	867.6
12.5°	876.4	870.6	853.7	853.0	848.6
15°	862.5	854.4	833.9	830.2	825.1
17.5°	845.6	836.8	811.2	803.8	796.5
20°	826.6	814.8	787.0	777.4	768.6
22.5°	805.3	791.4	761.3	748.8	740.8
25°	784.8	766.4	732.7	717.3	709.2
27.5°	759.8	740.0	703.4	682.8	670.3
30°	734.2	712.2	671.1	646.1	634.4
32.5°	708.5	682.8	638.8	610.9	598.5
35°	679.2	652.7	607.3	575.7	562.5
37.5°	649.8	621.2	573.5	538.3	522.2
40°	621.9	589.7	537.6	499.5	482.6
42.5°	590.4	558.1	503.9	461.3	446.7
45°	558.1	525.1	468.7	426.9	409.3
47.5°	526.6	489.9	434.2	388.7	373.3
50°	491.4	456.9	397.5	352.0	335.2
52.5°	459.9	421.7	363.0	315.4	300.7
55°	423.9	388.0	325.6	283.1	268.4
57.5°	391.6	352.8	289.7	249.4	236.9
60°	357.9	317.6	256.7	217.1	204.6
62.5°	324.2	283.8	223.0	186.3	173.1
65°	289.7	249.4	192.2	156.2	148.2
67.5°	255.2	214.2	158.4	131.3	122.5
70°	221.5	181.9	130.5	104.9	96.8
72.5°	187.8	148.9	103.4	83.6	81.4
75°	153.3	118.1	77.7	70.4	68.9
77.5°	121.7	89.5	60.9	56.5	55.0
80°	91.7	61.6	46.2	44.0	42.5
82.5°	63.1	38.1	33.0	30.8	30.8
85°	38.9	22.7	20.5	19.1	19.1
87.5°	17.6	9.5	9.5	8.8	8.1
90°	0.4	4.8	10.5	12.2	13.1
92.5°	10.0	7.4	11.4	14.4	14.8
95°	26.6	8.7	13.5	16.6	16.6
97.5°	48.5	36.2	14.0	17.5	17.9
100°	73.8	82.5	14.4	17.9	18.3
102.5°	102.6	108.3	32.3	17.9	18.8
105°	130.1	134.9	95.6	18.3	19.2
107.5°	159.4	163.3	169.9	102.6	45.4
110°	188.6	192.1	196.9	182.5	120.1



TEST NUMBER: P1032346

CATALOG NUMBER: S123RDIW-B560D460UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	216.6	219.6	224.4	228.4	227.5
115°	244.1	246.7	250.6	255.0	256.8
117.5°	271.2	274.2	276.4	279.9	280.3
120°	296.1	300.0	301.3	304.8	304.8
122.5°	321.4	324.4	326.2	328.4	328.8
125°	344.1	347.6	349.3	350.2	351.1
127.5°	366.8	370.3	372.5	373.8	372.9
130°	387.8	391.3	393.0	394.7	393.9
132.5°	407.8	411.3	412.7	414.4	413.1
135°	428.4	431.0	432.7	434.0	432.7
137.5°	445.8	449.3	450.2	452.4	451.5
140°	463.3	465.9	467.2	469.0	468.1
142.5°	479.5	482.1	483.4	484.7	483.4
145°	494.3	497.4	498.2	499.1	499.1
147.5°	508.7	510.9	511.8	512.6	510.5
150°	521.8	523.1	524.0	524.9	523.6
152.5°	533.6	534.0	534.5	536.2	534.0
155°	544.5	543.7	544.1	546.3	543.7
157.5°	553.3	553.3	552.8	555.4	551.9
160°	561.1	560.7	560.2	562.9	559.8
162.5°	568.5	567.2	566.8	569.9	567.2
165°	574.2	572.9	572.5	576.0	572.9
167.5°	579.0	577.3	577.3	580.8	577.3
170°	583.0	581.2	581.2	584.7	581.2
172.5°	585.6	583.4	583.8	587.3	583.4
175°	587.8	585.6	586.0	589.1	585.6
177.5°	588.6	586.4	586.9	590.4	586.0
180°	587.8	587.8	587.8	587.8	587.8

(END OF REPORT)