

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032355

Luminaire Tested: S123RDIW-B560D755UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032355
REPORT IS A COMBINATION OF REPORTS P994579 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D755UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4790.0 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032355

CATALOG NUMBER: S123RDIW-B560D755UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1032355

CATALOG NUMBER: S123RDIW-B560D755UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	86	89	85	82	79	71	68	66	58	56	55	46	45	44
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	40	39	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	52	45	40	44	39	35	36	33	29	29	27	24
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	19	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8621 cd/sqm

TEST NUMBER: P1032355

CATALOG NUMBER: S123RDIW-B560D755UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	1.8
10°-20°	246.0	5.1
20°-30°	354.2	7.4
30°-40°	398.8	8.3
40°-50°	381.5	8.0
50°-60°	312.3	6.5
60°-70°	210.6	4.4
70°-80°	105.6	2.2
80°-90°	29.6	0.6
90°-100°	61.9	1.3
100°-110°	187.3	3.9
110°-120°	318.8	6.7
120°-130°	419.4	8.8
130°-140°	471.4	9.8
140°-150°	463.4	9.7
150°-160°	390.2	8.1
160°-170°	259.7	5.4
170°-180°	91.0	1.9
0°-30°	688.6	14.4
0°-40°	1087.4	22.7
0°-60°	1781.2	37.2
0°-90°	2127.0	44.4
90°-120°	567.9	11.9
90°-150°	1922.1	40.1
90°-180°	2663.0	55.6
0°-180°	4790.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	1	8	18	21	23	6
95°	44	50	56	59	59	49
105°	170	171	178	178	180	182
115°	321	323	322	322	322	318
125°	470	472	470	467	464	419
135°	609	614	613	610	608	469
145°	739	741	743	742	739	462
155°	846	846	847	850	845	390
165°	922	920	920	924	919	260
175°	959	956	956	960	955	91
180°	961	961	961	961	961	

TEST NUMBER: P1032355

CATALOG NUMBER: S123RDIW-B560D755UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	0.8	8.3	18.1	21.1	22.6
92.5°	22.6	27.2	31.7	34.0	32.5
95°	44.5	49.8	55.9	58.9	58.9
97.5°	73.2	77.0	81.5	85.3	84.6
100°	102.7	107.2	111.0	113.2	114.8
102.5°	136.6	138.9	144.2	146.5	145.7
105°	169.9	171.4	178.2	178.2	179.7
107.5°	209.1	209.9	212.9	215.2	214.4
110°	245.4	246.9	248.4	251.4	249.9

TEST NUMBER: P1032355

CATALOG NUMBER: S123RDIW-B560D755UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.1	283.9	283.9	287.6	287.6
115°	320.9	323.1	321.6	322.4	321.6
117.5°	359.4	360.1	358.6	358.6	356.3
120°	394.8	399.4	395.6	394.8	393.3
122.5°	431.8	434.9	433.4	431.1	428.8
125°	469.6	471.9	470.3	467.3	464.3
127.5°	504.3	508.8	507.3	502.8	499.8
130°	539.0	545.1	542.8	539.8	534.5
132.5°	573.8	579.8	578.3	574.5	570.8
135°	609.3	613.8	613.0	610.0	608.5
137.5°	641.7	645.5	647.8	644.0	641.7
140°	675.7	679.5	680.2	679.5	674.2
142.5°	706.7	710.4	711.9	711.2	707.4
145°	739.1	740.6	742.9	742.1	739.1
147.5°	767.0	770.1	772.3	772.3	767.8
150°	796.5	798.0	799.5	799.5	795.0
152.5°	820.7	822.9	823.7	825.2	821.4
155°	846.3	846.3	847.1	850.1	844.8
157.5°	868.2	867.5	868.2	871.2	866.7
160°	888.6	887.1	887.1	890.9	887.8
162.5°	906.7	904.5	905.2	909.0	903.7
165°	921.8	919.6	919.6	924.1	918.8
167.5°	934.7	931.6	932.4	936.9	932.4
170°	945.2	942.2	942.2	947.5	942.2
172.5°	953.5	950.5	950.5	955.0	949.8
175°	958.8	955.8	955.8	960.3	955.0
177.5°	961.8	958.8	958.8	963.3	958.1
180°	961.1	961.1	961.1	961.1	961.1

(END OF REPORT)