

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032358

Luminaire Tested: S123RDIW-B560D755UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032358
REPORT IS A COMBINATION OF REPORTS P994584 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D755UB35-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5221.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032358

CATALOG NUMBER: S123RDIW-B560D755UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1032358

CATALOG NUMBER: S123RDIW-B560D755UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41		
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35		
2	88	80	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35	30		
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30	25		
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26	22		
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	27	25	23	19		
6	62	50	42	37	56	46	39	34	39	33	30	32	28	25	25	22	20	17		
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15		
8	53	41	34	29	49	38	31	27	32	27	23	26	22	20	21	18	16	14		
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12		
10	46	35	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10168	10168	10168
5°	10184	9808	9781
10°	10104	9440	9253
15°	9972	8983	8675
20°	9801	8487	8028
25°	9623	7972	7415
30°	9396	7425	6691
35°	9161	6886	6032
40°	8940	6301	5303
45°	8658	5730	4648
50°	8347	5119	3970
55°	8023	4466	3349
60°	7715	3796	2718
65°	7315	3108	2122
70°	6814	2351	1516
75°	6090	1592	1201
80°	5201	1107	842
85°	3900	599	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8658 cd/sqm

TEST NUMBER: P1032358

CATALOG NUMBER: S123RDIW-B560D755UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	1.7
10°-20°	247.0	4.7
20°-30°	355.7	6.8
30°-40°	400.5	7.7
40°-50°	383.1	7.3
50°-60°	313.6	6.0
60°-70°	211.5	4.1
70°-80°	106.1	2.0
80°-90°	29.8	0.6
90°-100°	35.7	0.7
100°-110°	172.5	3.3
110°-120°	422.8	8.1
120°-130°	536.7	10.3
130°-140°	573.4	11.0
140°-150°	536.2	10.3
150°-160°	432.5	8.3
160°-170°	279.1	5.3
170°-180°	96.2	1.8
0°-30°	691.5	13.2
0°-40°	1092.0	20.9
0°-60°	1788.8	34.3
0°-90°	2136.0	40.9
90°-120°	631.0	12.1
90°-150°	2277.3	43.6
90°-180°	3085.0	59.1
0°-180°	5221.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	945	945	945	945	945	
5°	945	941	932	938	937	90
15°	901	892	871	867	862	254
25°	820	801	765	749	741	377
35°	709	682	634	601	588	444
45°	583	548	490	446	428	450
55°	443	405	340	296	280	397
65°	303	260	201	163	155	299
75°	160	123	81	74	72	171
85°	41	24	22	20	20	44
90°	1	8	18	21	23	5
95°	46	15	23	29	29	55
105°	224	232	165	32	33	238
115°	420	425	432	439	442	415
125°	592	598	601	603	604	529
135°	738	742	745	747	745	568
145°	851	856	858	859	859	533
155°	938	936	937	940	936	432
165°	989	986	986	992	986	279
175°	1012	1008	1009	1014	1008	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1032358

CATALOG NUMBER: S123RDIW-B560D755UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	944.6	944.6	944.6	944.6	944.6
2.5°	948.4	945.4	936.2	944.6	943.1
5°	944.6	940.8	931.6	938.5	936.9
7.5°	937.7	933.9	922.4	927.0	924.7
10°	928.5	923.1	909.4	910.1	906.3
12.5°	915.5	909.4	891.7	891.0	886.4
15°	900.9	892.5	871.0	867.2	861.9
17.5°	883.3	874.1	847.3	839.6	832.0
20°	863.4	851.1	822.0	812.1	802.9
22.5°	841.2	826.6	795.2	782.2	773.8
25°	819.7	800.6	765.3	749.2	740.8
27.5°	793.7	773.0	734.7	713.2	700.2
30°	766.9	743.9	701.0	674.9	662.7
32.5°	740.0	713.2	667.3	638.2	625.1
35°	709.4	681.8	634.3	601.4	587.6
37.5°	678.8	648.9	599.1	562.3	545.5
40°	649.6	615.9	561.5	521.7	504.1
42.5°	616.7	583.0	526.3	481.9	466.6
45°	583.0	548.5	489.5	445.9	427.5
47.5°	550.1	511.7	453.5	406.0	389.9
50°	513.3	477.3	415.2	367.7	350.1
52.5°	480.3	440.5	379.2	329.4	314.1
55°	442.8	405.3	340.1	295.7	280.4
57.5°	409.1	368.5	302.6	260.5	247.4
60°	373.9	331.7	268.1	226.8	213.7
62.5°	338.6	296.5	232.9	194.6	180.8
65°	302.6	260.5	200.7	163.2	154.8
67.5°	266.6	223.7	165.5	137.1	127.9
70°	231.4	190.0	136.4	109.6	101.1
72.5°	196.1	155.5	108.0	87.3	85.0
75°	160.1	123.3	81.2	73.5	72.0
77.5°	127.2	93.5	63.6	59.0	57.5
80°	95.8	64.4	48.3	46.0	44.4
82.5°	65.9	39.8	34.5	32.2	32.2
85°	40.6	23.7	21.5	19.9	19.9
87.5°	18.4	10.0	10.0	9.2	8.4
90°	0.8	8.3	18.0	21.1	22.6
92.5°	17.3	12.8	19.5	24.8	25.6
95°	45.9	15.0	23.3	28.6	28.6
97.5°	83.5	62.4	24.1	30.1	30.8
100°	127.1	142.1	24.8	30.8	31.6
102.5°	176.7	186.4	55.6	30.8	32.3
105°	224.0	232.3	164.6	31.6	33.1
107.5°	274.4	281.2	292.5	176.7	78.2
110°	324.8	330.8	339.1	314.3	206.7

TEST NUMBER: P1032358

CATALOG NUMBER: S123RDIW-B560D755UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.9	378.2	386.4	393.2	391.7
115°	420.3	424.8	431.5	439.1	442.1
117.5°	466.9	472.1	475.9	481.9	482.7
120°	509.7	516.5	518.7	524.8	524.8
122.5°	553.3	558.6	561.6	565.4	566.1
125°	592.4	598.4	601.4	603.0	604.5
127.5°	631.5	637.5	641.3	643.6	642.0
130°	667.6	673.6	676.6	679.6	678.1
132.5°	702.2	708.2	710.5	713.5	711.2
135°	737.5	742.0	745.0	747.3	745.0
137.5°	767.6	773.6	775.1	778.9	777.4
140°	797.7	802.2	804.4	807.4	805.9
142.5°	825.5	830.0	832.3	834.5	832.3
145°	851.1	856.3	857.8	859.3	859.3
147.5°	875.9	879.6	881.1	882.6	878.9
150°	898.4	900.7	902.2	903.7	901.4
152.5°	918.7	919.5	920.2	923.2	919.5
155°	937.5	936.0	936.8	940.5	936.0
157.5°	952.5	952.5	951.8	956.3	950.3
160°	966.1	965.3	964.6	969.1	963.8
162.5°	978.9	976.6	975.9	981.1	976.6
165°	988.6	986.4	985.6	991.6	986.4
167.5°	996.9	993.9	993.9	999.9	993.9
170°	1003.7	1000.7	1000.7	1006.7	1000.7
172.5°	1008.2	1004.4	1005.2	1011.2	1004.4
175°	1011.9	1008.2	1008.9	1014.2	1008.2
177.5°	1013.4	1009.7	1010.4	1016.4	1008.9
180°	1011.9	1011.9	1011.9	1011.9	1011.9

(END OF REPORT)