

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032744

Luminaire Tested: S124DIW-B575D470UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032744
REPORT IS A COMBINATION OF REPORTS P997830 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D470UB2750-4F0-XX-W2A-F1_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3969.0 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032744

CATALOG NUMBER: S124DIW-B575D470UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032744

CATALOG NUMBER: S124DIW-B575D470UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65	65	65	60
1	100	96	92	88	93	89	86	83	78	75	73	68	66	64	58	56	55	55	55	51
2	91	83	77	72	85	78	73	68	68	64	61	59	56	53	51	49	46	46	46	42
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40	40	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	34	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30	30	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	26	26	23
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	23	23	21
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21	21	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19	19	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	17	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7584	7584	7584
5°	7589	7366	7375
10°	7526	7161	7111
15°	7417	6918	6813
20°	7280	6655	6506
25°	7125	6377	6174
30°	6937	6077	5811
35°	6744	5769	5459
40°	6541	5438	5085
45°	6330	5106	4735
50°	6095	4785	4348
55°	5841	4408	3963
60°	5579	3997	3563
65°	5282	3572	3111
70°	4937	3059	2627
75°	4424	2467	2104
80°	3771	1783	1480
85°	2925	992	797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6330 cd/sqm

TEST NUMBER: P1032744

CATALOG NUMBER: S124DIW-B575D470UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	2.2
10°-20°	247.0	6.2
20°-30°	363.4	9.2
30°-40°	422.5	10.6
40°-50°	422.5	10.6
50°-60°	369.5	9.3
60°-70°	274.3	6.9
70°-80°	155.6	3.9
80°-90°	45.8	1.2
90°-100°	37.1	0.9
100°-110°	111.2	2.8
110°-120°	189.0	4.8
120°-130°	249.2	6.3
130°-140°	279.9	7.1
140°-150°	275.1	6.9
150°-160°	231.4	5.8
160°-170°	153.9	3.9
170°-180°	53.9	1.4
0°-30°	698.1	17.6
0°-40°	1120.5	28.2
0°-60°	1912.5	48.2
0°-90°	2388.2	60.2
90°-120°	337.3	8.5
90°-150°	1141.5	28.8
90°-180°	1581.0	39.8
0°-180°	3969.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	930	930	930	930	930	
5°	929	926	918	926	925	88
15°	884	882	870	875	873	249
25°	801	796	785	786	783	369
35°	689	684	674	668	665	431
45°	563	557	546	537	535	434
55°	426	423	413	404	399	381
65°	288	285	277	270	266	285
75°	154	150	146	143	142	163
85°	40	40	39	39	38	43
90°	1	6	10	12	13	5
95°	26	30	34	35	35	29
105°	103	103	105	106	108	109
115°	192	192	191	191	190	189
125°	280	280	279	278	278	249
135°	361	364	364	363	361	279
145°	438	440	441	440	439	274
155°	502	502	502	504	502	231
165°	547	546	545	547	546	154
175°	569	567	566	569	566	54
180°	570	570	570	570	570	

TEST NUMBER: P1032744

CATALOG NUMBER: S124DIW-B575D470UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	930.0	930.0	930.0	930.0	930.0
2.5°	933.0	930.7	922.5	930.0	929.2
5°	929.2	926.3	918.1	926.3	924.8
7.5°	922.5	919.6	910.6	917.3	916.6
10°	912.9	909.9	900.2	906.1	904.7
12.5°	900.2	897.2	886.8	893.5	891.2
15°	884.5	881.6	870.4	874.8	872.6
17.5°	866.6	862.9	852.5	855.5	854.0
20°	846.5	842.8	831.6	833.9	832.4
22.5°	824.9	819.7	808.5	813.0	810.0
25°	801.1	795.9	785.4	786.2	783.2
27.5°	774.2	769.0	759.3	757.9	754.1
30°	747.4	741.5	731.8	728.8	725.1
32.5°	719.1	713.9	703.5	699.7	696.0
35°	689.3	684.1	673.6	668.4	664.7
37.5°	658.0	653.5	642.3	637.1	631.9
40°	627.4	621.5	610.3	602.9	599.1
42.5°	594.7	591.7	579.0	570.1	567.8
45°	562.6	557.4	545.5	537.3	535.0
47.5°	529.1	525.4	514.2	505.2	499.3
50°	494.8	491.8	481.4	471.0	466.5
52.5°	461.3	457.5	446.4	437.4	431.5
55°	425.5	423.3	412.8	403.9	399.4
57.5°	392.0	389.7	379.3	370.4	365.9
60°	356.9	353.2	343.5	336.8	333.1
62.5°	322.7	319.7	309.3	303.3	299.6
65°	288.4	284.7	277.2	269.8	266.0
67.5°	253.4	250.4	242.9	235.5	234.7
70°	221.3	216.1	210.1	204.2	201.9
72.5°	187.0	181.8	177.4	172.9	170.6
75°	153.5	149.8	146.1	143.1	142.3
77.5°	120.7	119.2	115.5	114.8	112.5
80°	91.7	89.4	87.9	86.4	85.7
82.5°	63.3	62.6	62.6	61.9	61.1
85°	40.2	40.2	38.7	38.7	38.0
87.5°	19.4	18.6	17.9	17.9	17.9
90°	1.3	6.2	9.7	12.3	13.2
92.5°	11.5	17.2	19.4	20.7	21.1
95°	26.4	30.4	33.5	34.8	34.8
97.5°	42.3	45.8	49.3	51.1	51.1
100°	61.7	63.4	67.4	68.3	68.3
102.5°	82.0	82.4	85.9	87.2	87.7
105°	102.7	103.1	104.9	106.2	107.5
107.5°	124.3	124.7	125.1	126.9	126.5
110°	146.3	147.2	146.7	145.8	147.2

TEST NUMBER: P1032744

CATALOG NUMBER: S124DIW-B575D470UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	169.2	169.2	168.3	168.3	168.3
115°	192.1	192.1	191.2	190.8	190.3
117.5°	213.7	213.7	213.3	211.9	210.6
120°	235.3	237.1	235.7	233.5	234.4
122.5°	257.8	258.2	257.8	256.4	254.2
125°	279.8	279.8	279.4	278.5	277.6
127.5°	299.6	300.9	300.1	299.2	298.7
130°	320.8	322.1	322.1	321.2	319.5
132.5°	342.4	343.2	342.8	341.9	341.5
135°	360.9	363.5	363.5	362.6	361.3
137.5°	381.6	382.9	383.8	382.5	382.9
140°	402.3	403.2	403.2	402.7	402.3
142.5°	421.2	422.1	421.7	421.7	421.7
145°	438.4	440.2	440.6	440.2	438.9
147.5°	456.0	458.2	457.8	457.4	456.9
150°	471.9	473.7	473.7	473.7	473.2
152.5°	486.9	487.8	488.2	489.5	488.2
155°	502.3	502.3	501.9	503.6	501.9
157.5°	515.5	514.6	514.6	516.0	514.6
160°	527.0	526.5	526.1	527.4	525.2
162.5°	537.6	536.2	535.8	538.4	536.2
165°	546.8	545.5	544.6	547.3	545.5
167.5°	554.3	552.5	552.5	555.2	552.5
170°	560.5	558.3	558.7	561.4	558.3
172.5°	564.9	563.1	563.1	566.2	563.1
175°	568.8	566.6	566.2	569.3	566.2
177.5°	570.6	568.4	568.4	571.5	568.0
180°	569.7	569.7	569.7	569.7	569.7

(END OF REPORT)