

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032771

Luminaire Tested: S124DIW-B795D1050UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032771
REPORT IS A COMBINATION OF REPORTS P997958 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D1050UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7510.0 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032771

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032771

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47			40
1	95	90	86	82	86	82	79	75	67	64	62	53	51	50	40	39	38			32
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	31			26
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	31	28	26			22
4	71	60	52	46	64	55	48	43	45	40	36	36	32	29	27	25	22			18
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	24	22	19			16
6	60	48	40	34	54	44	37	31	36	31	26	29	25	22	22	19	17			14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	20	17	15			12
8	51	39	31	26	47	36	29	24	30	24	20	24	20	17	18	15	13			11
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12			10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	14	16	13	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7788	7788	7788
5°	7809	7585	7599
10°	7758	7435	7414
15°	7686	7268	7206
20°	7578	7086	7005
25°	7457	6886	6787
30°	7325	6687	6565
35°	7177	6485	6367
40°	7059	6289	6162
45°	6882	6107	5982
50°	6732	5899	5791
55°	6577	5698	5572
60°	6336	5450	5365
65°	6071	5181	5115
70°	5749	4874	4828
75°	5300	4533	4554
80°	4796	4186	4267
85°	4126	3836	4035

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6882 cd/sqm

TEST NUMBER: P1032771

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	1.2
10°-20°	259.3	3.5
20°-30°	392.0	5.2
30°-40°	474.3	6.3
40°-50°	501.4	6.7
50°-60°	471.9	6.3
60°-70°	391.5	5.2
70°-80°	274.8	3.7
80°-90°	157.7	2.1
90°-100°	137.8	1.8
100°-110°	368.6	4.9
110°-120°	619.3	8.2
120°-130°	753.8	10.0
130°-140°	790.0	10.5
140°-150°	730.5	9.7
150°-160°	587.3	7.8
160°-170°	378.8	5.0
170°-180°	130.5	1.7
0°-30°	741.8	9.9
0°-40°	1216.0	16.2
0°-60°	2189.2	29.2
0°-90°	3013.3	40.1
90°-120°	1125.8	15.0
90°-150°	3400.1	45.3
90°-180°	4497.0	59.9
0°-180°	7510.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	955	955	955	955	955	
5°	956	953	945	954	953	91
15°	916	918	914	924	923	258
25°	838	845	848	860	861	386
35°	734	746	757	772	775	459
45°	612	632	652	670	676	473
55°	479	502	534	555	562	427
65°	332	366	402	429	437	329
75°	184	224	268	298	308	195
85°	57	102	150	182	192	59
90°	20	74	128	166	176	15
95°	70	71	116	151	161	81
105°	319	346	391	427	399	335
115°	584	597	630	655	663	575
125°	816	819	844	867	875	729
135°	1009	1008	1020	1039	1047	778
145°	1162	1164	1164	1172	1178	726
155°	1273	1274	1271	1275	1272	587
165°	1343	1338	1338	1346	1337	380
175°	1374	1368	1369	1378	1366	131
180°	1374	1374	1374	1374	1374	

TEST NUMBER: P1032771

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	955.0	955.0	955.0	955.0	955.0
2.5°	959.3	956.1	947.5	955.0	953.9
5°	956.1	952.9	945.4	953.9	952.9
7.5°	949.7	947.5	941.1	950.7	949.7
10°	941.1	940.0	934.7	944.3	943.2
12.5°	929.3	929.3	926.1	934.7	934.7
15°	916.5	917.6	914.4	924.0	922.9
17.5°	899.4	902.6	901.5	911.2	910.1
20°	881.2	884.4	885.5	896.2	896.2
22.5°	860.9	865.2	867.3	878.0	880.1
25°	838.4	844.9	848.1	859.8	860.9
27.5°	813.8	823.5	827.7	838.4	839.5
30°	789.2	797.8	805.3	817.0	819.2
32.5°	762.5	773.2	781.8	795.7	797.8
35°	733.6	746.5	757.2	772.1	775.3
37.5°	704.8	719.7	732.6	747.5	750.7
40°	677.0	690.9	705.8	721.9	726.1
42.5°	644.9	660.9	679.1	697.3	700.5
45°	611.7	632.0	652.4	670.5	675.9
47.5°	580.7	601.0	624.5	642.7	649.1
50°	546.5	570.0	593.5	614.9	621.3
52.5°	512.3	535.8	563.6	585.0	591.4
55°	479.1	501.6	533.6	555.0	561.5
57.5°	441.7	469.5	500.5	526.2	531.5
60°	405.3	433.1	468.4	493.0	501.6
62.5°	370.0	401.0	436.3	460.9	469.5
65°	331.5	365.7	402.1	428.8	437.4
67.5°	295.2	331.5	370.0	396.8	405.3
70°	257.7	294.1	334.7	363.6	371.1
72.5°	221.4	258.8	302.6	330.5	339.0
75°	183.9	223.5	268.4	298.4	308.0
77.5°	148.7	190.4	237.4	267.4	278.1
80°	116.6	159.3	206.4	238.5	247.0
82.5°	84.5	129.4	176.5	209.6	219.2
85°	56.7	101.6	149.7	181.8	192.5
87.5°	35.3	79.1	126.2	157.2	166.8
90°	20.2	74.3	128.5	165.7	176.2
92.5°	31.4	66.9	121.1	157.1	165.7
95°	70.4	70.8	115.6	150.7	161.3
97.5°	120.7	174.3	110.3	143.2	153.9
100°	180.3	226.6	126.5	137.9	146.4
102.5°	248.1	284.0	336.9	133.5	142.1
105°	318.9	346.5	391.2	427.1	398.8
107.5°	385.7	407.0	451.6	483.5	495.1
110°	452.5	470.5	514.2	540.8	552.4

TEST NUMBER: P1032771

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	517.2	536.1	573.5	596.0	608.7
115°	583.9	596.6	629.8	655.4	662.9
117.5°	644.5	655.0	690.2	711.7	720.2
120°	705.1	712.5	742.4	765.9	772.3
122.5°	762.6	764.7	795.6	818.0	823.5
125°	816.1	819.1	843.7	867.2	874.6
127.5°	868.5	868.4	894.9	913.1	919.6
130°	917.7	917.7	937.8	958.2	964.6
132.5°	964.0	964.9	981.9	1001.2	1006.5
135°	1009.1	1008.1	1019.7	1038.8	1047.4
137.5°	1050.2	1049.2	1058.5	1076.7	1081.0
140°	1090.3	1091.3	1094.4	1111.4	1117.8
142.5°	1125.2	1129.4	1129.3	1143.1	1147.3
145°	1162.2	1164.2	1164.2	1171.7	1178.0
147.5°	1191.0	1196.1	1195.1	1197.2	1202.4
150°	1222.9	1225.9	1224.8	1224.8	1225.9
152.5°	1248.5	1251.6	1249.5	1251.6	1250.5
155°	1273.1	1274.2	1271.1	1275.2	1272.1
157.5°	1294.7	1294.7	1290.6	1295.8	1290.6
160°	1313.2	1310.1	1309.1	1315.3	1309.1
162.5°	1329.7	1325.6	1324.5	1330.7	1323.5
165°	1343.0	1337.9	1337.9	1346.1	1336.9
167.5°	1354.3	1349.2	1348.2	1357.4	1347.1
170°	1363.6	1357.4	1358.4	1366.7	1356.4
172.5°	1369.7	1363.6	1364.6	1372.8	1361.5
175°	1373.8	1367.7	1368.7	1378.0	1365.6
177.5°	1376.9	1369.7	1371.8	1380.0	1367.7
180°	1373.8	1373.8	1373.8	1373.8	1373.8

(END OF REPORT)