

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032814

Luminaire Tested: S124DIW-B795D470UB2750-4F0-XX-W2A-D1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032814
REPORT IS A COMBINATION OF REPORTS P998153 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D470UB2750-4F0-XX-W2A-D1_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4712.0 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 49.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032814

CATALOG NUMBER: S124DIW-B795D470UB2750-4F0-XX-W2A-D1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032814

CATALOG NUMBER: S124DIW-B795D470UB2750-4F0-XX-W2A-D1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	99	94	90	86	92	88	84	81	77	74	71	67	64	62	57	55	54
2	90	82	75	69	84	76	70	65	67	62	58	58	54	51	49	47	44
3	82	71	63	57	76	67	60	54	58	53	48	51	46	43	43	40	37
4	74	63	54	48	69	59	51	45	52	46	41	45	40	36	38	35	32
5	68	56	47	41	63	52	45	39	46	40	35	40	35	31	34	31	27
6	63	50	41	35	58	47	39	34	41	35	30	36	31	27	31	27	24
7	58	45	37	31	54	42	35	29	37	31	27	33	28	24	28	24	21
8	54	41	33	27	50	39	31	26	34	28	24	30	25	21	26	22	19
9	50	37	30	24	47	35	28	23	31	25	21	28	23	19	24	20	17
10	47	34	27	22	44	32	25	21	29	23	19	25	21	17	22	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7486	7486	7486
5°	7507	7291	7304
10°	7458	7147	7127
15°	7388	6986	6927
20°	7285	6812	6733
25°	7168	6619	6524
30°	7042	6428	6311
35°	6899	6234	6121
40°	6785	6046	5924
45°	6616	5870	5750
50°	6471	5671	5567
55°	6323	5478	5355
60°	6090	5239	5157
65°	5836	4980	4918
70°	5528	4686	4641
75°	5095	4357	4378
80°	4611	4024	4103
85°	3966	3687	3878

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6616 cd/sqm

TEST NUMBER: P1032814

CATALOG NUMBER: S124DIW-B795D470UB2750-4F0-XX-W2A-D1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.8
10°-20°	249.2	5.3
20°-30°	376.8	8.0
30°-40°	455.9	9.7
40°-50°	482.0	10.2
50°-60°	453.6	9.6
60°-70°	376.4	8.0
70°-80°	264.1	5.6
80°-90°	150.1	3.2
90°-100°	125.8	2.7
100°-110°	176.9	3.8
110°-120°	233.0	4.9
120°-130°	274.0	5.8
130°-140°	290.6	6.2
140°-150°	277.2	5.9
150°-160°	231.4	4.9
160°-170°	153.9	3.3
170°-180°	53.9	1.1
0°-30°	713.1	15.1
0°-40°	1169.0	24.8
0°-60°	2104.5	44.7
0°-90°	2895.2	61.4
90°-120°	535.7	11.4
90°-150°	1377.5	29.2
90°-180°	1817.0	38.6
0°-180°	4712.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	918	918	918	918	918	
5°	919	916	909	917	916	87
15°	881	882	879	888	887	248
25°	806	812	815	827	828	371
35°	705	718	728	742	745	442
45°	588	608	627	645	650	454
55°	461	482	513	534	540	410
65°	319	352	386	412	420	316
75°	177	215	258	287	296	188
85°	54	98	144	175	185	57
90°	18	64	112	144	153	13
95°	40	78	123	152	161	39
105°	112	133	173	200	209	119
115°	198	208	240	262	268	196
125°	284	283	308	327	332	253
135°	363	366	373	388	393	281
145°	439	440	441	446	449	275
155°	502	502	502	504	502	231
165°	547	546	545	547	546	154
175°	569	567	566	569	566	54
180°	570	570	570	570	570	

TEST NUMBER: P1032814

CATALOG NUMBER: S124DIW-B795D470UB2750-4F0-XX-W2A-D1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	918.0	918.0	918.0	918.0	918.0
2.5°	922.2	919.1	910.9	918.0	917.0
5°	919.1	916.0	908.8	917.0	916.0
7.5°	912.9	910.9	904.7	913.9	912.9
10°	904.7	903.7	898.5	907.8	906.7
12.5°	893.4	893.4	890.3	898.5	898.5
15°	881.0	882.1	879.0	888.2	887.2
17.5°	864.6	867.7	866.6	875.9	874.9
20°	847.1	850.2	851.2	861.5	861.5
22.5°	827.6	831.7	833.7	844.0	846.1
25°	806.0	812.2	815.2	826.6	827.6
27.5°	782.3	791.6	795.7	806.0	807.0
30°	758.7	766.9	774.1	785.4	787.5
32.5°	733.0	743.3	751.5	764.9	766.9
35°	705.2	717.6	727.9	742.3	745.3
37.5°	677.5	691.9	704.2	718.6	721.7
40°	650.8	664.1	678.5	693.9	698.0
42.5°	619.9	635.3	652.8	670.3	673.4
45°	588.0	607.6	627.1	644.6	649.7
47.5°	558.2	577.8	600.4	617.9	624.0
50°	525.3	547.9	570.6	591.1	597.3
52.5°	492.4	515.1	541.8	562.3	568.5
55°	460.6	482.2	513.0	533.6	539.7
57.5°	424.6	451.3	481.1	505.8	510.9
60°	389.6	416.4	450.3	473.9	482.2
62.5°	355.7	385.5	419.4	443.1	451.3
65°	318.7	351.6	386.5	412.2	420.5
67.5°	283.7	318.7	355.7	381.4	389.6
70°	247.8	282.7	321.8	349.5	356.7
72.5°	212.8	248.8	290.9	317.7	325.9
75°	176.8	214.9	258.0	286.8	296.1
77.5°	142.9	183.0	228.2	257.0	267.3
80°	112.1	153.2	198.4	229.3	237.5
82.5°	81.2	124.4	169.6	201.5	210.7
85°	54.5	97.7	143.9	174.8	185.0
87.5°	33.9	76.1	121.3	151.1	160.4
90°	17.7	63.8	111.5	143.9	153.0
92.5°	26.9	68.6	115.0	145.1	153.7
95°	39.8	77.7	122.9	152.0	161.2
97.5°	54.6	87.9	133.6	162.1	171.4
100°	73.0	101.4	145.5	174.2	181.4
102.5°	93.3	116.3	158.9	186.9	195.6
105°	112.0	132.9	172.8	199.8	209.3
107.5°	133.6	151.4	187.8	215.3	222.1
110°	154.5	169.8	205.3	228.0	237.7



TEST NUMBER: P1032814

CATALOG NUMBER: S124DIW-B795D470UB2750-4F0-XX-W2A-D1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	188.7	221.8	244.4	252.6
115°	198.3	207.5	239.5	261.7	268.4
117.5°	219.9	226.0	256.5	276.7	283.6
120°	240.4	245.3	273.7	292.1	301.2
122.5°	262.9	263.3	290.7	309.9	314.9
125°	283.9	282.9	308.2	326.8	332.1
127.5°	303.7	304.0	323.7	341.3	348.0
130°	323.9	324.2	340.6	358.2	362.7
132.5°	345.5	345.3	357.2	373.8	379.5
135°	363.0	365.6	372.8	388.3	393.2
137.5°	383.7	383.9	388.9	403.1	408.6
140°	404.4	404.2	405.3	418.1	422.9
142.5°	422.2	423.1	421.7	433.0	437.1
145°	439.4	440.2	440.6	446.4	449.2
147.5°	457.0	458.2	457.8	458.4	462.0
150°	472.9	473.7	473.7	473.7	473.2
152.5°	486.9	487.8	488.2	489.5	488.2
155°	502.3	502.3	501.9	503.6	501.9
157.5°	515.5	514.6	514.6	516.0	514.6
160°	527.0	526.5	526.1	527.4	525.2
162.5°	537.6	536.2	535.8	538.4	536.2
165°	546.8	545.5	544.6	547.3	545.5
167.5°	554.3	552.5	552.5	555.2	552.5
170°	560.5	558.3	558.7	561.4	558.3
172.5°	564.9	563.1	563.1	566.2	563.1
175°	568.8	566.6	566.2	569.3	566.2
177.5°	570.6	568.4	568.4	571.5	568.0
180°	569.7	569.7	569.7	569.7	569.7

(END OF REPORT)