

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032462

Luminaire Tested: S123RDIW-B775D755UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032462
REPORT IS A COMBINATION OF REPORTS P994816 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D755UB50-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5774.0 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032462

CATALOG NUMBER: S123RDIW-B775D755UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1032462

CATALOG NUMBER: S123RDIW-B775D755UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	86	83	80	73	71	69	61	59	58	49	48	47
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23
7	59	47	39	33	54	43	36	32	37	32	28	32	27	24	26	23	21
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	22	19	17
10	47	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13431	13431	13431
5°	13453	12956	12921
10°	13347	12468	12223
15°	13174	11866	11459
20°	12946	11212	10605
25°	12712	10531	9795
30°	12412	9808	8839
35°	12102	9096	7968
40°	11811	8324	7005
45°	11437	7570	6140
50°	11025	6763	5245
55°	10598	5900	4424
60°	10191	5015	3590
65°	9662	4106	2802
70°	9000	3105	2003
75°	8045	2103	1587
80°	6868	1462	1113
85°	5149	788	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11437 cd/sqm

TEST NUMBER: P1032462

CATALOG NUMBER: S123RDIW-B775D755UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.3	2.0
10°-20°	326.3	5.7
20°-30°	469.8	8.1
30°-40°	529.1	9.2
40°-50°	506.1	8.8
50°-60°	414.3	7.2
60°-70°	279.3	4.8
70°-80°	140.1	2.4
80°-90°	38.6	0.7
90°-100°	34.1	0.6
100°-110°	165.2	2.9
110°-120°	404.7	7.0
120°-130°	513.8	8.9
130°-140°	548.9	9.5
140°-150°	513.2	8.9
150°-160°	414.0	7.2
160°-170°	267.2	4.6
170°-180°	92.1	1.6
0°-30°	913.4	15.8
0°-40°	1442.6	25.0
0°-60°	2363.0	40.9
0°-90°	2820.9	48.9
90°-120°	604.0	10.5
90°-150°	2179.9	37.8
90°-180°	2953.0	51.1
0°-180°	5774.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1248	1248	1248	1248	1248	
5°	1248	1243	1231	1240	1238	118
15°	1190	1179	1151	1146	1138	335
25°	1083	1058	1011	990	979	498
35°	937	901	838	794	776	587
45°	770	725	647	589	565	594
55°	585	535	449	391	370	525
65°	400	344	265	216	204	396
75°	212	163	107	97	95	225
85°	54	31	28	26	26	59
90°	1	8	17	20	22	6
95°	44	14	22	27	27	52
105°	214	222	158	30	32	227
115°	402	407	413	420	423	397
125°	567	573	576	577	579	507
135°	706	710	713	715	713	544
145°	815	820	821	823	823	510
155°	897	896	897	900	896	414
165°	946	944	944	949	944	267
175°	969	965	966	971	965	92
180°	969	969	969	969	969	

TEST NUMBER: P1032462

CATALOG NUMBER: S123RDIW-B775D755UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1247.8	1247.8	1247.8	1247.8	1247.8
2.5°	1252.9	1248.8	1236.7	1247.8	1245.8
5°	1247.8	1242.7	1230.6	1239.7	1237.7
7.5°	1238.7	1233.6	1218.5	1224.5	1221.5
10°	1226.5	1219.5	1201.2	1202.3	1197.2
12.5°	1209.3	1201.2	1178.0	1177.0	1170.9
15°	1190.1	1179.0	1150.6	1145.6	1138.5
17.5°	1166.8	1154.7	1119.3	1109.2	1099.0
20°	1140.5	1124.3	1085.9	1072.7	1060.6
22.5°	1111.2	1092.0	1050.5	1033.3	1022.1
25°	1082.8	1057.5	1011.0	989.7	978.6
27.5°	1048.4	1021.1	970.5	942.2	925.0
30°	1013.0	982.7	926.0	891.6	875.4
32.5°	977.6	942.2	881.5	843.0	825.8
35°	937.1	900.7	837.9	794.4	776.2
37.5°	896.6	857.2	791.4	742.8	720.5
40°	858.2	813.7	741.8	689.2	665.9
42.5°	814.7	770.1	695.2	636.5	616.3
45°	770.1	724.6	646.7	589.0	564.7
47.5°	726.6	676.0	599.1	536.4	515.1
50°	678.0	630.5	548.5	485.8	462.5
52.5°	634.5	581.9	500.9	435.2	414.9
55°	584.9	535.3	449.3	390.6	370.4
57.5°	540.4	486.8	399.7	344.1	326.9
60°	493.9	438.2	354.2	299.6	282.3
62.5°	447.3	391.6	307.6	257.0	238.8
65°	399.7	344.1	265.1	215.6	204.4
67.5°	352.2	295.5	218.6	181.1	169.0
70°	305.6	251.0	180.1	144.7	133.6
72.5°	259.1	205.4	142.7	115.4	112.3
75°	211.5	162.9	107.3	97.2	95.1
77.5°	168.0	123.5	84.0	77.9	75.9
80°	126.5	85.0	63.8	60.7	58.7
82.5°	87.0	52.6	45.5	42.5	42.5
85°	53.6	31.4	28.3	26.3	26.3
87.5°	24.3	13.2	13.2	12.1	11.1
90°	0.7	7.9	17.3	20.2	21.6
92.5°	16.6	12.2	18.7	23.7	24.5
95°	43.9	14.4	22.3	27.3	27.3
97.5°	79.9	59.7	23.0	28.8	29.5
100°	121.6	136.0	23.7	29.5	30.2
102.5°	169.1	178.5	53.3	29.5	30.9
105°	214.5	222.4	157.6	30.2	31.7
107.5°	262.7	269.2	279.9	169.1	74.8
110°	310.9	316.7	324.6	300.8	197.9



TEST NUMBER: P1032462

CATALOG NUMBER: S123RDIW-B775D755UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.0	362.0	369.9	376.4	374.9
115°	402.3	406.6	413.1	420.3	423.2
117.5°	446.9	451.9	455.5	461.3	462.0
120°	487.9	494.4	496.6	502.3	502.3
122.5°	529.7	534.7	537.6	541.2	541.9
125°	567.1	572.9	575.7	577.2	578.6
127.5°	604.5	610.3	613.9	616.0	614.6
130°	639.1	644.8	647.7	650.6	649.1
132.5°	672.2	677.9	680.1	683.0	680.8
135°	706.0	710.3	713.2	715.3	713.2
137.5°	734.8	740.5	742.0	745.6	744.1
140°	763.6	767.9	770.0	772.9	771.5
142.5°	790.2	794.5	796.7	798.8	796.7
145°	814.7	819.7	821.1	822.6	822.6
147.5°	838.4	842.0	843.4	844.9	841.3
150°	860.0	862.2	863.6	865.0	862.9
152.5°	879.4	880.1	880.9	883.7	880.1
155°	897.4	896.0	896.7	900.3	896.0
157.5°	911.8	911.8	911.1	915.4	909.7
160°	924.8	924.0	923.3	927.6	922.6
162.5°	937.0	934.8	934.1	939.2	934.8
165°	946.4	944.2	943.5	949.2	944.2
167.5°	954.3	951.4	951.4	957.2	951.4
170°	960.8	957.9	957.9	963.6	957.9
172.5°	965.1	961.5	962.2	967.9	961.5
175°	968.7	965.1	965.8	970.8	965.1
177.5°	970.1	966.5	967.2	973.0	965.8
180°	968.7	968.7	968.7	968.7	968.7

(END OF REPORT)