

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032837

Luminaire Tested: S124DIW-B795D770UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032837
REPORT IS A COMBINATION OF REPORTS P998230 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D770UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6579.0 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032837

CATALOG NUMBER: S124DIW-B795D770UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1032837

CATALOG NUMBER: S124DIW-B795D770UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	51	50	49
2	89	82	76	71	83	76	71	66	65	61	57	55	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10929	10929	10929
5°	10938	10615	10627
10°	10845	10320	10247
15°	10690	9969	9820
20°	10491	9591	9376
25°	10268	9190	8898
30°	9998	8757	8374
35°	9719	8314	7867
40°	9427	7837	7328
45°	9122	7359	6824
50°	8785	6895	6266
55°	8417	6353	5711
60°	8041	5760	5134
65°	7611	5148	4484
70°	7117	4409	3786
75°	6374	3555	3032
80°	5433	2570	2133
85°	4221	1430	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9122 cd/sqm

TEST NUMBER: P1032837

CATALOG NUMBER: S124DIW-B795D770UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.9
10°-20°	355.9	5.4
20°-30°	523.8	8.0
30°-40°	608.9	9.3
40°-50°	608.8	9.3
50°-60°	532.5	8.1
60°-70°	395.3	6.0
70°-80°	224.3	3.4
80°-90°	66.3	1.0
90°-100°	33.7	0.5
100°-110°	221.6	3.4
110°-120°	423.2	6.4
120°-130°	537.2	8.2
130°-140°	574.7	8.7
140°-150°	537.4	8.2
150°-160°	433.4	6.6
160°-170°	279.5	4.2
170°-180°	96.3	1.5
0°-30°	1006.0	15.3
0°-40°	1614.9	24.5
0°-60°	2756.1	41.9
0°-90°	3442.1	52.3
90°-120°	678.5	10.3
90°-150°	2327.8	35.4
90°-180°	3137.0	47.7
0°-180°	6579.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1339	1335	1323	1335	1333	127
15°	1275	1270	1254	1261	1258	359
25°	1154	1147	1132	1133	1129	531
35°	993	986	971	963	958	621
45°	811	803	786	774	771	625
55°	613	610	595	582	576	549
65°	416	410	400	389	383	411
75°	221	216	210	206	205	235
85°	58	58	56	56	55	62
90°	2	11	17	21	23	6
95°	42	16	17	21	22	51
105°	228	233	237	243	216	239
115°	426	428	428	429	429	419
125°	599	602	600	603	604	535
135°	743	742	745	747	748	573
145°	857	859	859	860	861	535
155°	939	940	938	941	939	433
165°	991	987	987	993	986	280
175°	1014	1009	1010	1017	1008	97
180°	1014	1014	1014	1014	1014	

TEST NUMBER: P1032837

CATALOG NUMBER: S124DIW-B795D770UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.2	1340.2	1340.2	1340.2	1340.2
2.5°	1344.5	1341.3	1329.5	1340.2	1339.2
5°	1339.2	1334.9	1323.1	1334.9	1332.7
7.5°	1329.5	1325.2	1312.3	1322.0	1320.9
10°	1315.5	1311.2	1297.3	1305.9	1303.7
12.5°	1297.3	1293.0	1278.0	1287.6	1284.4
15°	1274.7	1270.4	1254.3	1260.8	1257.6
17.5°	1249.0	1243.6	1228.6	1232.9	1230.7
20°	1220.0	1214.6	1198.5	1201.7	1199.6
22.5°	1188.8	1181.3	1165.2	1171.6	1167.3
25°	1154.5	1146.9	1131.9	1133.0	1128.7
27.5°	1115.8	1108.3	1094.3	1092.2	1086.8
30°	1077.1	1068.5	1054.6	1050.3	1044.9
32.5°	1036.3	1028.8	1013.8	1008.4	1003.0
35°	993.4	985.9	970.8	963.3	957.9
37.5°	948.3	941.8	925.7	918.2	910.7
40°	904.2	895.6	879.5	868.8	863.4
42.5°	857.0	852.7	834.4	821.5	818.3
45°	810.8	803.3	786.1	774.3	771.1
47.5°	762.5	757.1	741.0	728.1	719.5
50°	713.1	708.8	693.7	678.7	672.3
52.5°	664.8	659.4	643.3	630.4	621.8
55°	613.2	610.0	594.9	582.1	575.6
57.5°	564.9	561.7	546.6	533.7	527.3
60°	514.4	509.0	495.1	485.4	480.0
62.5°	465.0	460.7	445.7	437.1	431.7
65°	415.6	410.2	399.5	388.8	383.4
67.5°	365.1	360.8	350.1	339.4	338.3
70°	319.0	311.4	302.8	294.3	291.0
72.5°	269.6	262.0	255.6	249.1	245.9
75°	221.2	215.9	210.5	206.2	205.1
77.5°	174.0	171.8	166.5	165.4	162.2
80°	132.1	128.9	126.7	124.6	123.5
82.5°	91.3	90.2	90.2	89.1	88.1
85°	58.0	58.0	55.8	55.8	54.8
87.5°	27.9	26.8	25.8	25.8	25.8
90°	2.3	10.6	16.7	21.2	22.7
92.5°	11.4	9.9	15.9	20.5	20.5
95°	41.7	15.9	16.7	21.2	22.0
97.5°	79.6	96.3	16.7	20.5	21.2
100°	124.3	138.0	33.4	20.5	21.2
102.5°	174.4	183.5	192.6	22.0	22.0
105°	228.2	232.8	236.6	243.4	216.1
107.5°	277.5	279.8	285.1	288.9	291.9
110°	327.6	329.8	334.4	335.9	338.2



TEST NUMBER: P1032837

CATALOG NUMBER: S124DIW-B795D770UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.1	380.6	382.1	381.4	384.4
115°	426.1	428.4	427.6	429.2	429.2
117.5°	470.9	473.9	476.2	475.4	475.4
120°	516.4	519.4	518.6	520.1	518.6
122.5°	558.8	560.3	561.8	562.6	561.1
125°	599.0	602.0	600.5	602.8	603.6
127.5°	637.7	638.4	642.2	641.5	640.7
130°	674.8	675.6	677.9	678.6	678.6
132.5°	708.9	710.5	713.5	714.3	713.5
135°	743.1	742.3	745.3	746.9	748.4
137.5°	773.4	773.4	777.2	778.7	777.9
140°	803.0	804.5	806.0	808.3	809.0
142.5°	829.5	832.5	833.3	834.8	834.8
145°	856.8	859.1	859.1	859.8	861.3
147.5°	878.0	882.6	881.8	882.6	883.3
150°	901.5	904.6	903.8	903.8	904.6
152.5°	921.2	923.5	922.0	923.5	922.8
155°	939.4	940.2	937.9	941.0	938.7
157.5°	955.4	955.4	952.3	956.1	952.3
160°	969.0	966.7	966.0	970.5	966.0
162.5°	981.1	978.1	977.4	981.9	976.6
165°	991.0	987.2	987.2	993.3	986.5
167.5°	999.3	995.6	994.8	1001.6	994.0
170°	1006.2	1001.6	1002.4	1008.4	1000.9
172.5°	1010.7	1006.2	1006.9	1013.0	1004.7
175°	1013.8	1009.2	1010.0	1016.8	1007.7
177.5°	1016.0	1010.7	1012.2	1018.3	1009.2
180°	1013.8	1013.8	1013.8	1013.8	1013.8

(END OF REPORT)