

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P982946

Luminaire Tested: S123IW-B1320UB2750-4F0-XX-W2A_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P982946
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IW-B1320UB2750-4F0-XX-W2A_3000K
Description: Define 3 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5282.0 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 42.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P982946

CATALOG NUMBER: S123IW-B1320UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P982946

CATALOG NUMBER: S123IW-B1320UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P982946

CATALOG NUMBER: S123IW-B1320UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.5	0.1
90°-100°	61.1	1.2
100°-110°	295.2	5.6
110°-120°	723.4	13.7
120°-130°	918.4	17.4
130°-140°	981.1	18.6
140°-150°	917.4	17.4
150°-160°	740.0	14.0
160°-170°	477.5	9.0
170°-180°	164.6	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.5	0.1
90°-120°	1079.7	20.4
90°-150°	3896.5	73.8
90°-180°	5279.0	99.9
0°-180°	5282.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	14	31	36	39	4
95°	78	26	40	49	49	94
105°	383	398	282	54	57	406
115°	719	727	738	751	756	710
125°	1014	1024	1029	1032	1034	906
135°	1262	1270	1275	1279	1275	972
145°	1456	1465	1468	1470	1470	912
155°	1604	1602	1603	1609	1602	739
165°	1692	1688	1686	1697	1688	478
175°	1732	1725	1726	1735	1725	165
180°	1732	1732	1732	1732	1732	

TEST NUMBER: P982946

CATALOG NUMBER: S123IW-B1320UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.3	14.2	30.9	36.0	38.6
92.5°	29.6	21.9	33.4	42.5	43.7
95°	78.5	25.7	39.9	48.9	48.9
97.5°	142.8	106.8	41.2	51.5	52.7
100°	217.4	243.1	42.5	52.7	54.0
102.5°	302.3	319.0	95.2	52.7	55.3
105°	383.3	397.5	281.7	54.0	56.6
107.5°	469.5	481.1	500.4	302.3	133.8
110°	555.7	566.0	580.2	537.7	353.8

TEST NUMBER: P982946

CATALOG NUMBER: S123IW-B1320UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	638.0	647.1	661.2	672.8	670.2
115°	719.1	726.8	738.4	751.2	756.4
117.5°	798.8	807.8	814.3	824.6	825.9
120°	872.2	883.7	887.6	897.9	897.9
122.5°	946.8	955.8	960.9	967.4	968.6
125°	1013.7	1024.0	1029.1	1031.7	1034.3
127.5°	1080.6	1090.9	1097.3	1101.1	1098.6
130°	1142.3	1152.6	1157.7	1162.9	1160.3
132.5°	1201.5	1211.8	1215.6	1220.8	1216.9
135°	1261.9	1269.7	1274.8	1278.7	1274.8
137.5°	1313.4	1323.7	1326.3	1332.7	1330.1
140°	1364.9	1372.6	1376.4	1381.6	1379.0
142.5°	1412.4	1420.2	1424.0	1427.9	1424.0
145°	1456.2	1465.2	1467.8	1470.3	1470.3
147.5°	1498.6	1505.1	1507.6	1510.2	1503.8
150°	1537.2	1541.1	1543.7	1546.2	1542.4
152.5°	1572.0	1573.2	1574.5	1579.7	1573.2
155°	1604.1	1601.5	1602.8	1609.3	1601.5
157.5°	1629.8	1629.8	1628.6	1636.3	1626.0
160°	1653.0	1651.7	1650.4	1658.1	1649.1
162.5°	1674.9	1671.0	1669.7	1678.7	1671.0
165°	1691.6	1687.7	1686.4	1696.7	1687.7
167.5°	1705.7	1700.6	1700.6	1710.9	1700.6
170°	1717.3	1712.2	1712.2	1722.5	1712.2
172.5°	1725.0	1718.6	1719.9	1730.2	1718.6
175°	1731.5	1725.0	1726.3	1735.3	1725.0
177.5°	1734.0	1727.6	1728.9	1739.2	1726.3
180°	1731.5	1731.5	1731.5	1731.5	1731.5



TEST NUMBER: P982946

CATALOG NUMBER: S123IW-B1320UB2750-4F0-XX-W2A_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT