

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032852

Luminaire Tested: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032852
REPORT IS A COMBINATION OF REPORTS P999873 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9725.1 lumens
Efficiency: N/A
Efficacy: 109.4 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 88.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51			45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44			38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38			33
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	34	32			28
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	30	28			25
5	68	57	49	43	62	53	46	41	45	39	35	37	33	30	30	27	25			22
6	63	51	43	38	58	47	41	35	40	35	31	33	29	26	27	24	22			19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20			17
8	54	42	35	29	50	39	32	28	33	28	24	28	24	21	23	20	18			15
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16			14
10	47	35	28	24	43	33	26	22	28	23	20	24	20	17	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13968	13968	13968	13968
5°	13968	15783	13991	12063
10°	13894	18194	13882	10491
15°	13728	20477	13728	8783
20°	13555	22202	13484	7734
25°	13343	22295	13282	6986
30°	13119	18959	13016	6470
35°	12802	14305	12639	6087
40°	12448	10367	12204	5786
45°	11864	7879	11569	5522
50°	11171	6368	10865	5133
55°	10420	5273	10080	4615
60°	9667	4458	9234	3839
65°	8721	3632	8442	3051
70°	7853	2946	7483	2478
75°	6882	2122	6403	1816
80°	5676	1406	5166	1335
85°	4119	723	3413	723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 17486 cd/sqm

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.9	1.7
10°-20°	500.9	5.2
20°-30°	784.6	8.1
30°-40°	871.3	9.0
40°-50°	772.0	7.9
50°-60°	601.7	6.2
60°-70°	393.6	4.0
70°-80°	193.1	2.0
80°-90°	50.6	0.5
90°-100°	57.8	0.6
100°-110°	380.9	3.9
110°-120°	727.3	7.5
120°-130°	923.3	9.5
130°-140°	987.7	10.2
140°-150°	923.6	9.5
150°-160°	744.8	7.7
160°-170°	480.4	4.9
170°-180°	165.5	1.7
0°-30°	1451.3	14.9
0°-40°	2322.6	23.9
0°-60°	3696.3	38.0
0°-90°	4333.6	44.6
90°-120°	1166.1	12.0
90°-150°	4000.7	41.1
90°-180°	5391.0	55.4
0°-180°	9725.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1713	1713	1713	1713	1713	
5°	1710	1979	1713	1513	1710	162
15°	1637	2622	1637	1125	1637	462
25°	1500	2828	1493	886	1500	691
35°	1308	1742	1292	741	1308	818
45°	1054	890	1028	624	1054	813
55°	759	531	734	465	759	679
65°	476	311	461	261	476	475
75°	239	144	222	123	239	253
85°	57	34	47	34	57	64
90°	4	39	4	39	4	8
95°	72	38	72	38	72	88
105°	392	371	392	371	392	411
115°	732	738	732	738	732	721
125°	1030	1037	1030	1037	1030	919
135°	1277	1286	1277	1286	1277	984
145°	1473	1480	1473	1480	1473	920
155°	1615	1613	1615	1613	1615	744
165°	1703	1695	1703	1695	1703	481
175°	1742	1732	1742	1732	1742	166
180°	1742	1742	1742	1742	1742	

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1715.7	1730.8	1739.1	1746.0	1759.8	1765.3	1776.4	1779.1	1790.2	1788.8	1784.7
5°	1710.1	1736.4	1755.7	1776.4	1801.2	1815.0	1830.2	1852.3	1863.3	1878.5	1888.2
7.5°	1700.5	1736.4	1768.1	1799.9	1839.9	1862.0	1881.3	1915.8	1944.8	1969.6	1997.2
10°	1685.3	1730.8	1777.8	1820.6	1875.8	1902.0	1931.0	1982.0	2022.1	2056.6	2100.7
12.5°	1661.8	1725.3	1777.8	1835.7	1906.1	1942.0	1980.7	2041.4	2088.3	2144.9	2200.1
15°	1637.0	1707.4	1776.4	1852.3	1932.4	1973.8	2012.4	2093.8	2165.6	2230.5	2291.2
17.5°	1609.4	1686.7	1762.6	1846.8	1943.4	1994.5	2040.0	2138.0	2216.7	2300.9	2361.6
20°	1576.3	1660.4	1747.4	1841.3	1950.3	2006.9	2058.0	2169.8	2256.7	2347.8	2423.7
22.5°	1540.4	1631.5	1726.7	1828.8	1942.0	2004.1	2063.5	2183.6	2284.3	2368.5	2470.7
25°	1500.3	1597.0	1695.0	1802.6	1929.6	1997.2	2058.0	2176.7	2284.3	2394.7	2494.1
27.5°	1458.9	1558.3	1660.4	1773.6	1903.4	1969.6	2038.6	2153.2	2278.8	2398.9	2499.6
30°	1413.4	1510.0	1617.7	1725.3	1863.3	1929.6	2000.0	2124.2	2260.9	2380.9	2490.0
32.5°	1363.7	1463.1	1565.2	1677.0	1812.3	1884.0	1948.9	2089.7	2229.1	2347.8	2450.0
35°	1308.5	1402.3	1499.0	1613.5	1747.4	1812.3	1889.6	2035.9	2176.7	2302.3	2368.5
37.5°	1249.1	1338.8	1428.6	1541.7	1670.1	1748.8	1824.7	1972.4	2121.5	2205.6	2240.2
40°	1193.9	1272.6	1351.3	1460.3	1590.1	1671.5	1748.8	1902.0	2033.1	2098.0	2071.8
42.5°	1123.5	1205.0	1275.4	1376.1	1507.2	1583.2	1661.8	1820.6	1926.8	1953.1	1888.2
45°	1054.5	1122.1	1189.8	1287.8	1425.8	1490.7	1574.9	1722.6	1810.9	1787.4	1692.2
47.5°	986.9	1042.1	1105.6	1200.8	1325.0	1402.3	1481.0	1609.4	1671.5	1638.4	1505.9
50°	906.8	962.0	1028.3	1111.1	1231.2	1305.7	1367.8	1486.5	1533.5	1452.0	1291.9
52.5°	830.9	879.2	935.8	1013.1	1127.7	1195.3	1262.9	1365.1	1380.3	1286.4	1118.0
55°	759.1	797.8	857.1	919.2	1024.1	1095.9	1142.9	1229.8	1225.7	1108.3	963.4
57.5°	684.6	720.5	760.5	825.4	924.8	978.6	1029.7	1105.6	1065.6	966.2	822.6
60°	618.4	639.1	679.1	741.2	825.4	872.3	912.3	953.8	919.2	811.6	701.2
62.5°	545.2	568.7	597.7	647.3	721.9	766.0	795.0	813.0	777.1	694.3	593.5
65°	476.2	496.9	527.3	571.4	628.0	661.1	676.3	688.7	669.4	575.6	495.5
67.5°	414.1	427.9	455.5	484.5	545.2	553.5	574.2	579.7	541.1	469.3	405.8
70°	352.0	365.8	378.2	412.7	440.3	455.5	459.6	459.6	421.0	374.0	321.6
72.5°	294.0	302.3	314.7	338.2	353.3	364.4	369.9	363.0	327.1	288.5	249.8
75°	238.8	242.9	254.0	269.1	281.6	277.4	276.1	267.8	241.5	213.9	191.9
77.5°	183.6	186.3	198.8	202.9	202.9	207.0	201.5	193.2	171.2	150.4	140.8
80°	138.0	142.2	143.5	146.3	143.5	143.5	139.4	125.6	114.6	104.9	98.0
82.5°	95.2	98.0	99.4	95.2	98.0	93.9	87.0	77.3	70.4	69.0	66.3
85°	56.6	58.0	56.6	56.6	52.4	51.1	45.5	44.2	41.4	41.4	40.0
87.5°	27.6	26.2	23.5	20.7	20.7	19.3	20.7	17.9	20.7	19.3	17.9
90°	3.9	7.1	10.3	13.4	16.6	18.2	19.4	21.7	24.0	26.4	28.7
92.5°	19.5	18.9	18.3	17.8	17.2	16.9	18.1	20.4	22.7	25.1	27.4
95°	71.7	61.9	52.0	42.2	32.3	27.4	27.5	27.8	28.1	28.4	28.7
97.5°	136.8	143.2	149.6	155.9	162.3	165.5	150.3	119.9	89.5	59.1	28.7
100°	213.7	218.9	224.1	229.4	234.6	237.2	217.2	177.2	137.3	97.3	57.3
102.5°	299.7	303.2	306.7	310.2	313.7	315.4	317.1	320.6	324.1	327.5	331.0
105°	392.3	394.0	395.8	397.5	399.2	400.1	400.8	402.3	403.7	405.2	406.6
107.5°	477.0	477.9	478.7	479.6	480.5	480.9	481.9	483.9	486.0	488.0	490.0
110°	563.0	563.9	564.7	565.6	566.5	566.9	567.8	569.5	571.2	573.0	574.7

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	646.4	648.1	649.9	651.6	653.3	654.2	654.5	655.1	655.6	656.2	656.8
115°	732.4	733.3	734.1	735.0	735.9	736.3	736.2	735.9	735.6	735.3	735.0
117.5°	809.3	810.5	811.6	812.8	813.9	814.5	814.9	815.8	816.7	817.5	818.4
120°	887.5	888.7	889.8	891.0	892.1	892.7	892.6	892.3	892.0	891.7	891.4
122.5°	960.4	961.0	961.6	962.1	962.7	963.0	963.3	963.9	964.4	965.0	965.6
125°	1029.5	1030.7	1031.8	1033.0	1034.1	1034.7	1034.4	1033.8	1033.3	1032.7	1032.1
127.5°	1096.0	1096.3	1096.6	1096.9	1097.2	1097.3	1098.0	1099.5	1100.9	1102.4	1103.8
130°	1159.8	1160.1	1160.4	1160.7	1161.0	1161.1	1161.5	1162.4	1163.3	1164.1	1165.0
132.5°	1218.5	1219.1	1219.7	1220.2	1220.8	1221.1	1221.7	1222.8	1224.0	1225.1	1226.3
135°	1277.1	1276.8	1276.5	1276.2	1275.9	1275.8	1276.4	1277.5	1278.7	1279.8	1281.0
137.5°	1329.2	1329.2	1329.2	1329.2	1329.2	1329.2	1329.9	1331.4	1332.8	1334.3	1335.7
140°	1380.1	1380.7	1381.3	1381.8	1382.4	1382.7	1383.0	1383.6	1384.1	1384.7	1385.3
142.5°	1425.7	1426.9	1428.0	1429.2	1430.3	1430.9	1431.0	1431.3	1431.6	1431.9	1432.2
145°	1472.6	1473.5	1474.3	1475.2	1476.1	1476.5	1476.5	1476.5	1476.5	1476.5	1476.5
147.5°	1509.1	1510.8	1512.6	1514.3	1516.0	1516.9	1516.8	1516.5	1516.2	1515.9	1515.6
150°	1549.5	1550.7	1551.8	1553.0	1554.1	1554.7	1554.6	1554.3	1554.0	1553.7	1553.4
152.5°	1583.3	1584.2	1585.1	1586.0	1586.9	1587.3	1587.0	1586.4	1585.9	1585.3	1584.7
155°	1614.6	1614.9	1615.2	1615.5	1615.8	1615.9	1615.5	1614.6	1613.7	1612.9	1612.0
157.5°	1642.0	1642.0	1642.0	1642.0	1642.0	1642.0	1641.4	1640.3	1639.1	1638.0	1636.8
160°	1665.4	1664.5	1663.7	1662.8	1661.9	1661.5	1661.4	1661.1	1660.8	1660.5	1660.2
162.5°	1686.3	1685.1	1684.0	1682.8	1681.7	1681.1	1681.0	1680.7	1680.4	1680.1	1679.8
165°	1703.2	1701.8	1700.3	1698.9	1697.4	1696.7	1696.7	1696.7	1696.7	1696.7	1696.7
167.5°	1717.6	1716.2	1714.7	1713.3	1711.8	1711.1	1711.0	1710.7	1710.4	1710.1	1709.8
170°	1729.3	1727.6	1725.8	1724.1	1722.4	1721.5	1721.6	1721.9	1722.2	1722.5	1722.8
172.5°	1737.1	1735.4	1733.6	1731.9	1730.2	1729.3	1729.4	1729.7	1730.0	1730.3	1730.6
175°	1742.3	1740.6	1738.8	1737.1	1735.4	1734.5	1734.6	1734.9	1735.2	1735.5	1735.8
177.5°	1746.2	1744.2	1742.2	1740.1	1738.1	1737.1	1737.4	1738.0	1738.5	1739.1	1739.7
180°	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1795.7	1810.9	1812.3	1826.1	1821.9	1815.0	1827.5	1819.2	1835.7	1830.2	1837.1
5°	1900.6	1921.3	1939.3	1950.3	1969.6	1965.5	1986.2	1979.3	1994.5	1979.3	1998.6
7.5°	2023.5	2058.0	2075.9	2104.9	2113.2	2114.6	2139.4	2144.9	2154.6	2144.9	2156.0
10°	2143.5	2184.9	2226.4	2249.8	2265.0	2285.7	2307.8	2317.4	2324.3	2314.7	2321.6
12.5°	2252.6	2317.4	2363.0	2409.9	2421.0	2438.9	2462.4	2459.6	2487.2	2481.7	2494.1
15°	2353.3	2425.1	2480.3	2517.6	2547.9	2563.1	2607.3	2610.1	2608.7	2622.5	2614.2
17.5°	2443.1	2503.8	2582.5	2630.8	2668.0	2668.0	2692.9	2743.9	2739.8	2738.4	2746.7
20°	2516.2	2585.2	2658.4	2739.8	2770.2	2775.7	2810.2	2836.4	2840.6	2840.6	2840.6
22.5°	2571.4	2652.8	2731.5	2789.5	2813.0	2832.3	2862.6	2879.2	2884.7	2882.0	2884.7
25°	2599.0	2676.3	2756.4	2808.8	2822.6	2833.7	2836.4	2846.1	2844.7	2828.1	2837.8
27.5°	2604.5	2679.1	2731.5	2745.3	2738.4	2731.5	2687.4	2691.5	2679.1	2654.2	2663.9
30°	2579.7	2619.7	2618.3	2575.6	2563.1	2534.1	2494.1	2434.8	2386.5	2365.8	2372.7
32.5°	2490.0	2490.0	2440.3	2343.7	2300.9	2248.4	2176.7	2122.8	2059.3	2045.5	2071.8
35°	2365.8	2295.4	2204.3	2077.3	2012.4	1973.8	1849.5	1810.9	1757.1	1741.9	1754.3
37.5°	2172.5	2055.2	1922.7	1804.0	1748.8	1679.8	1570.7	1515.5	1476.9	1450.6	1463.1
40°	1955.8	1813.7	1675.6	1529.3	1468.6	1412.0	1330.6	1280.9	1218.8	1221.5	1225.7
42.5°	1748.8	1581.8	1427.2	1291.9	1233.9	1187.0	1130.4	1069.7	1047.6	1040.7	1033.8
45°	1529.3	1351.3	1206.3	1105.6	1053.1	1009.0	956.5	922.0	895.8	890.3	897.2
47.5°	1322.3	1171.8	1033.8	940.0	897.2	875.1	833.7	801.9	785.4	771.6	779.8
50°	1134.6	993.8	883.4	804.7	774.3	759.1	720.5	703.9	687.4	683.2	681.8
52.5°	980.0	859.9	764.7	701.2	677.7	669.4	640.4	617.0	603.2	607.3	610.1
55°	839.2	737.1	662.5	611.5	592.1	582.5	561.8	545.2	535.5	531.4	534.2
57.5°	715.0	626.6	572.8	531.4	516.2	512.1	490.0	484.5	477.6	473.4	473.4
60°	601.8	539.7	490.0	466.5	450.0	445.8	429.3	422.4	421.0	416.8	414.1
62.5°	506.6	455.5	421.0	396.1	389.2	387.9	376.8	368.5	364.4	361.6	361.6
65°	423.7	386.5	357.5	339.5	334.0	331.3	318.8	316.1	313.3	310.6	309.2
67.5°	353.3	320.2	299.5	287.1	280.2	281.6	274.7	269.1	269.1	267.8	266.4
70°	285.7	265.0	247.1	240.2	237.4	234.6	231.9	227.7	226.4	226.4	226.4
72.5°	225.0	211.2	201.5	197.4	194.6	191.9	189.1	189.1	189.1	187.7	187.7
75°	172.5	167.0	160.1	156.0	156.0	158.7	154.6	150.4	146.3	143.5	144.9
77.5°	129.7	127.0	122.8	115.9	117.3	114.6	114.6	111.8	113.2	113.2	110.4
80°	95.2	91.1	89.7	85.6	87.0	85.6	84.2	84.2	81.4	81.4	81.4
82.5°	66.3	62.1	62.1	60.7	59.4	59.4	58.0	58.0	59.4	56.6	56.6
85°	40.0	38.6	38.6	35.9	35.9	35.9	35.9	37.3	35.9	34.5	34.5
87.5°	17.9	19.3	17.9	16.6	16.6	16.6	15.2	15.2	13.8	15.2	15.2
90°	30.4	32.2	33.9	35.6	36.5	36.8	37.4	37.9	38.5	39.1	38.5
92.5°	29.1	30.9	32.6	34.3	35.2	35.2	35.2	35.2	35.2	35.2	35.2
95°	30.4	32.2	33.9	35.6	36.5	36.6	36.9	37.2	37.5	37.8	37.5
97.5°	30.1	31.6	33.0	34.5	35.2	35.3	35.6	35.9	36.2	36.5	36.2
100°	52.4	47.5	42.6	37.7	35.2	35.3	35.6	35.9	36.2	36.5	36.2
102.5°	265.8	200.7	135.5	70.4	37.8	37.8	37.8	37.8	37.8	37.8	37.8
105°	409.2	411.8	414.4	417.0	418.3	413.1	402.7	392.2	381.8	371.4	381.8
107.5°	491.4	492.9	494.3	495.8	496.5	497.1	498.2	499.4	500.5	501.7	500.5
110°	575.3	575.9	576.4	577.0	577.3	577.7	578.6	579.5	580.3	581.2	580.3

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	656.5	656.2	655.9	655.6	655.5	656.1	657.2	658.4	659.5	660.7	659.5
115°	735.6	736.2	736.7	737.3	737.6	737.6	737.6	737.6	737.6	737.6	737.6
117.5°	818.1	817.8	817.5	817.2	817.1	817.1	817.1	817.1	817.1	817.1	817.1
120°	892.0	892.6	893.1	893.7	894.0	893.7	893.1	892.6	892.0	891.4	892.0
122.5°	965.9	966.2	966.5	966.8	967.0	966.7	966.1	965.5	964.9	964.3	964.9
125°	1033.0	1033.8	1034.7	1035.6	1036.0	1036.1	1036.4	1036.7	1037.0	1037.3	1037.0
127.5°	1103.5	1103.2	1102.9	1102.6	1102.5	1102.4	1102.1	1101.8	1101.5	1101.2	1101.5
130°	1165.3	1165.6	1165.9	1166.2	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3
132.5°	1226.6	1226.9	1227.2	1227.5	1227.6	1227.5	1227.2	1226.9	1226.6	1226.3	1226.6
135°	1281.6	1282.2	1282.7	1283.3	1283.6	1283.9	1284.5	1285.0	1285.6	1286.2	1285.6
137.5°	1336.3	1336.9	1337.5	1338.1	1338.4	1338.3	1338.0	1337.7	1337.4	1337.1	1337.4
140°	1386.2	1387.0	1387.9	1388.8	1389.2	1389.3	1389.6	1389.9	1390.2	1390.5	1390.2
142.5°	1432.8	1433.4	1433.9	1434.5	1434.8	1434.8	1434.8	1434.8	1434.8	1434.8	1434.8
145°	1476.8	1477.1	1477.4	1477.7	1477.8	1478.1	1478.7	1479.2	1479.8	1480.4	1479.8
147.5°	1515.9	1516.2	1516.5	1516.8	1516.9	1517.0	1517.3	1517.6	1517.9	1518.2	1517.9
150°	1553.4	1553.4	1553.4	1553.4	1553.4	1553.5	1553.8	1554.1	1554.4	1554.7	1554.4
152.5°	1585.3	1585.9	1586.4	1587.0	1587.3	1587.2	1586.9	1586.6	1586.3	1586.0	1586.3
155°	1613.2	1614.3	1615.5	1616.6	1617.2	1616.8	1615.9	1615.0	1614.2	1613.3	1614.2
157.5°	1638.2	1639.7	1641.1	1642.6	1643.3	1642.6	1641.1	1639.7	1638.2	1636.8	1638.2
160°	1662.0	1663.7	1665.5	1667.2	1668.1	1667.2	1665.5	1663.7	1662.0	1660.2	1662.0
162.5°	1681.5	1683.3	1685.0	1686.7	1687.6	1686.6	1684.6	1682.5	1680.5	1678.5	1680.5
165°	1699.0	1701.4	1703.7	1706.0	1707.2	1705.9	1703.3	1700.6	1698.0	1695.4	1698.0
167.5°	1712.4	1715.0	1717.6	1720.2	1721.5	1720.1	1717.2	1714.3	1711.4	1708.5	1711.4
170°	1725.1	1727.4	1729.7	1732.0	1733.2	1731.8	1728.9	1726.0	1723.1	1720.2	1723.1
172.5°	1732.9	1735.2	1737.5	1739.8	1741.0	1739.4	1736.2	1733.1	1729.9	1726.7	1729.9
175°	1738.4	1741.0	1743.6	1746.2	1747.5	1745.8	1742.3	1738.8	1735.4	1731.9	1735.4
177.5°	1742.0	1744.4	1746.7	1749.0	1750.2	1748.5	1745.0	1741.5	1738.0	1734.5	1738.0
180°	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1841.3	1831.6	1830.2	1830.2	1815.0	1823.3	1806.8	1788.8	1780.5	1780.5	1765.3
5°	1994.5	1984.8	1975.1	1960.0	1960.0	1951.7	1925.5	1899.2	1879.9	1863.3	1845.4
7.5°	2151.8	2142.2	2114.6	2099.4	2107.6	2091.1	2056.6	2012.4	1979.3	1953.1	1915.8
10°	2323.0	2296.7	2282.9	2274.7	2245.7	2227.7	2187.7	2122.8	2081.4	2046.9	1998.6
12.5°	2462.4	2470.7	2418.2	2422.3	2393.4	2368.5	2306.4	2244.3	2182.2	2133.9	2062.1
15°	2612.8	2588.0	2556.2	2531.4	2521.7	2491.4	2438.9	2356.1	2288.5	2212.5	2131.1
17.5°	2731.5	2712.2	2681.8	2658.4	2637.7	2564.5	2520.3	2447.2	2354.7	2280.2	2180.8
20°	2832.3	2814.3	2771.6	2756.4	2719.1	2666.7	2603.2	2490.0	2407.2	2325.7	2229.1
22.5°	2875.1	2857.1	2819.9	2800.5	2777.1	2726.0	2665.3	2557.6	2455.5	2353.3	2251.2
25°	2839.2	2839.2	2821.2	2814.3	2793.6	2748.1	2686.0	2594.9	2485.8	2375.4	2254.0
27.5°	2665.3	2699.8	2712.2	2719.1	2719.1	2720.5	2677.7	2589.4	2483.1	2375.4	2248.4
30°	2414.1	2472.0	2523.1	2538.3	2564.5	2593.5	2611.4	2568.7	2473.4	2360.2	2233.3
32.5°	2098.0	2172.5	2267.8	2291.2	2327.1	2414.1	2462.4	2480.3	2427.9	2328.5	2193.2
35°	1783.3	1877.1	1935.1	2006.9	2040.0	2168.4	2276.0	2340.9	2328.5	2269.1	2146.3
37.5°	1508.6	1562.4	1632.8	1708.8	1775.0	1897.9	2031.7	2157.3	2208.4	2179.4	2086.9
40°	1245.0	1308.5	1392.7	1454.8	1500.3	1623.2	1788.8	1925.5	2037.3	2055.2	1998.6
42.5°	1058.7	1122.1	1173.2	1240.8	1276.7	1395.4	1541.7	1712.9	1845.4	1915.8	1890.9
45°	915.1	953.8	995.2	1033.8	1078.0	1182.9	1318.1	1505.9	1654.9	1754.3	1764.0
47.5°	789.5	824.0	859.9	895.8	920.6	1002.1	1126.3	1279.5	1442.4	1579.0	1632.8
50°	701.2	717.7	744.0	764.7	793.6	864.0	963.4	1095.9	1268.5	1416.1	1486.5
52.5°	614.2	634.9	655.6	673.6	692.9	742.6	833.7	948.2	1097.3	1249.1	1336.1
55°	541.1	557.6	576.9	589.4	600.4	644.6	713.6	801.9	930.3	1073.8	1181.5
57.5°	481.7	488.6	505.2	512.1	524.5	560.4	610.1	688.7	792.3	931.7	1020.0
60°	416.8	430.6	443.1	448.6	458.2	483.1	517.6	590.7	680.5	782.6	883.4
62.5°	364.4	369.9	379.6	386.5	393.4	419.6	448.6	503.8	571.4	657.0	749.5
65°	316.1	318.8	324.4	334.0	338.2	357.5	374.0	414.1	477.6	542.4	634.9
67.5°	266.4	269.1	276.1	281.6	285.7	298.1	316.1	345.1	379.6	451.3	502.4
70°	227.7	227.7	231.9	234.6	238.8	244.3	254.0	276.1	307.8	353.3	400.3
72.5°	190.5	190.5	190.5	194.6	194.6	198.8	204.3	219.5	241.5	277.4	307.8
75°	147.7	149.1	151.8	151.8	153.2	158.7	162.9	167.0	178.1	201.5	229.1
77.5°	111.8	114.6	115.9	113.2	115.9	115.9	121.5	127.0	132.5	139.4	160.1
80°	82.8	84.2	81.4	82.8	82.8	85.6	88.3	87.0	89.7	98.0	103.5
82.5°	55.2	56.6	56.6	56.6	56.6	60.7	60.7	59.4	60.7	62.1	63.5
85°	34.5	33.1	33.1	34.5	33.1	33.1	34.5	35.9	34.5	35.9	37.3
87.5°	15.2	15.2	15.2	15.2	13.8	13.8	15.2	13.8	15.2	13.8	12.4
90°	37.9	37.4	36.8	36.5	35.6	33.9	32.2	30.4	28.7	26.4	24.0
92.5°	35.2	35.2	35.2	35.2	34.3	32.6	30.9	29.1	27.4	25.1	22.7
95°	37.2	36.9	36.6	36.5	35.6	33.9	32.2	30.4	28.7	28.4	28.1
97.5°	35.9	35.6	35.3	35.2	34.5	33.0	31.6	30.1	28.7	59.1	89.5
100°	35.9	35.6	35.3	35.2	37.7	42.6	47.5	52.4	57.3	97.3	137.3
102.5°	37.8	37.8	37.8	37.8	70.4	135.5	200.7	265.8	331.0	327.5	324.1
105°	392.2	402.7	413.1	418.3	417.0	414.4	411.8	409.2	406.6	405.2	403.7
107.5°	499.4	498.2	497.1	496.5	495.8	494.3	492.9	491.4	490.0	488.0	486.0
110°	579.5	578.6	577.7	577.3	577.0	576.4	575.9	575.3	574.7	573.0	571.2

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	658.4	657.2	656.1	655.5	655.6	655.9	656.2	656.5	656.8	656.2	655.6
115°	737.6	737.6	737.6	737.6	737.3	736.7	736.2	735.6	735.0	735.3	735.6
117.5°	817.1	817.1	817.1	817.1	817.2	817.5	817.8	818.1	818.4	817.5	816.7
120°	892.6	893.1	893.7	894.0	893.7	893.1	892.6	892.0	891.4	891.7	892.0
122.5°	965.5	966.1	966.7	967.0	966.8	966.5	966.2	965.9	965.6	965.0	964.4
125°	1036.7	1036.4	1036.1	1036.0	1035.6	1034.7	1033.8	1033.0	1032.1	1032.7	1033.3
127.5°	1101.8	1102.1	1102.4	1102.5	1102.6	1102.9	1103.2	1103.5	1103.8	1102.4	1100.9
130°	1166.3	1166.3	1166.3	1166.3	1166.2	1165.9	1165.6	1165.3	1165.0	1164.1	1163.3
132.5°	1226.9	1227.2	1227.5	1227.6	1227.5	1227.2	1226.9	1226.6	1226.3	1225.1	1224.0
135°	1285.0	1284.5	1283.9	1283.6	1283.3	1282.7	1282.2	1281.6	1281.0	1279.8	1278.7
137.5°	1337.7	1338.0	1338.3	1338.4	1338.1	1337.5	1336.9	1336.3	1335.7	1334.3	1332.8
140°	1389.9	1389.6	1389.3	1389.2	1388.8	1387.9	1387.0	1386.2	1385.3	1384.7	1384.1
142.5°	1434.8	1434.8	1434.8	1434.8	1434.5	1433.9	1433.4	1432.8	1432.2	1431.9	1431.6
145°	1479.2	1478.7	1478.1	1477.8	1477.7	1477.4	1477.1	1476.8	1476.5	1476.5	1476.5
147.5°	1517.6	1517.3	1517.0	1516.9	1516.8	1516.5	1516.2	1515.9	1515.6	1515.9	1516.2
150°	1554.1	1553.8	1553.5	1553.4	1553.4	1553.4	1553.4	1553.4	1553.4	1553.7	1554.0
152.5°	1586.6	1586.9	1587.2	1587.3	1587.0	1586.4	1585.9	1585.3	1584.7	1585.3	1585.9
155°	1615.0	1615.9	1616.8	1617.2	1616.6	1615.5	1614.3	1613.2	1612.0	1612.9	1613.7
157.5°	1639.7	1641.1	1642.6	1643.3	1642.6	1641.1	1639.7	1638.2	1636.8	1638.0	1639.1
160°	1663.7	1665.5	1667.2	1668.1	1667.2	1665.5	1663.7	1662.0	1660.2	1660.5	1660.8
162.5°	1682.5	1684.6	1686.6	1687.6	1686.7	1685.0	1683.3	1681.5	1679.8	1680.1	1680.4
165°	1700.6	1703.3	1705.9	1707.2	1706.0	1703.7	1701.4	1699.0	1696.7	1696.7	1696.7
167.5°	1714.3	1717.2	1720.1	1721.5	1720.2	1717.6	1715.0	1712.4	1709.8	1710.1	1710.4
170°	1726.0	1728.9	1731.8	1733.2	1732.0	1729.7	1727.4	1725.1	1722.8	1722.5	1722.2
172.5°	1733.1	1736.2	1739.4	1741.0	1739.8	1737.5	1735.2	1732.9	1730.6	1730.3	1730.0
175°	1738.8	1742.3	1745.8	1747.5	1746.2	1743.6	1741.0	1738.4	1735.8	1735.5	1735.2
177.5°	1741.5	1745.0	1748.5	1750.2	1749.0	1746.7	1744.4	1742.0	1739.7	1739.1	1738.5
180°	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1757.1	1750.2	1746.0	1744.6	1732.2	1725.3	1721.2	1718.4	1714.3	1703.2	1693.6
5°	1823.3	1804.0	1794.3	1783.3	1764.0	1741.9	1723.9	1712.9	1699.1	1677.0	1656.3
7.5°	1885.4	1856.4	1837.1	1821.9	1788.8	1752.9	1723.9	1700.5	1674.2	1643.9	1614.9
10°	1950.3	1903.4	1878.5	1855.1	1806.8	1759.8	1718.4	1683.9	1646.6	1606.6	1574.9
12.5°	2001.4	1939.3	1911.7	1878.5	1819.2	1764.0	1711.5	1664.6	1616.3	1573.5	1527.9
15°	2060.7	1983.4	1951.7	1908.9	1827.5	1755.7	1688.1	1637.0	1587.3	1523.8	1475.5
17.5°	2095.2	2005.5	1960.0	1922.7	1834.4	1747.4	1668.7	1605.2	1547.3	1483.8	1432.7
20°	2129.7	2027.6	1976.5	1924.1	1819.2	1726.7	1643.9	1568.0	1507.2	1438.2	1385.8
22.5°	2140.8	2022.1	1968.2	1919.9	1809.5	1706.0	1610.8	1533.5	1463.1	1394.1	1334.7
25°	2140.8	2020.7	1957.2	1895.1	1779.1	1672.9	1577.6	1493.4	1414.8	1345.7	1286.4
27.5°	2118.7	1993.1	1926.8	1870.2	1750.2	1635.6	1537.6	1445.1	1369.2	1300.2	1232.6
30°	2091.1	1953.1	1886.8	1819.2	1703.2	1594.2	1487.9	1402.3	1322.3	1243.6	1182.9
32.5°	2056.6	1910.3	1837.1	1768.1	1645.3	1532.1	1434.1	1349.9	1274.0	1192.5	1124.9
35°	2006.9	1846.8	1765.3	1704.6	1585.9	1468.6	1374.7	1291.9	1218.8	1134.6	1061.4
37.5°	1943.4	1788.8	1706.0	1631.5	1508.6	1401.0	1312.6	1232.6	1160.8	1083.5	1002.1
40°	1868.9	1707.4	1635.6	1556.9	1427.2	1325.0	1242.2	1170.5	1098.7	1025.5	946.9
42.5°	1784.7	1624.6	1544.5	1468.6	1344.4	1243.6	1166.3	1101.4	1035.2	967.6	883.4
45°	1683.9	1533.5	1456.2	1384.4	1264.3	1160.8	1090.4	1028.3	971.7	902.7	828.2
47.5°	1570.7	1439.6	1360.9	1283.6	1166.3	1076.6	1007.6	955.1	906.8	837.8	770.2
50°	1460.3	1330.6	1267.1	1188.4	1080.7	996.5	926.2	882.0	844.7	777.1	716.4
52.5°	1320.9	1222.9	1162.2	1094.5	991.0	905.4	850.2	811.6	767.4	715.0	661.1
55°	1198.1	1107.0	1058.7	995.2	893.0	817.1	770.2	734.3	699.8	652.9	610.1
57.5°	1058.7	1002.1	953.8	898.5	797.8	732.9	691.5	661.1	629.4	590.7	556.2
60°	912.3	886.1	839.2	795.0	709.5	652.9	618.4	590.7	560.4	528.6	499.7
62.5°	782.6	767.4	739.8	705.3	625.3	576.9	542.4	521.7	499.7	470.7	443.1
65°	659.8	652.9	626.6	601.8	546.6	503.8	473.4	461.0	436.2	414.1	389.2
67.5°	550.7	542.4	527.3	516.2	469.3	429.3	414.1	397.5	376.8	360.2	339.5
70°	440.3	438.9	429.3	415.5	390.6	361.6	346.4	335.4	314.7	302.3	287.1
72.5°	342.3	349.2	340.9	335.4	318.8	298.1	284.3	277.4	260.9	251.2	240.2
75°	255.3	260.9	265.0	255.3	251.2	241.5	229.1	222.2	213.9	200.1	196.0
77.5°	173.9	186.3	186.3	189.1	190.5	185.0	175.3	169.8	160.1	157.3	151.8
80°	114.6	125.6	127.0	129.7	133.9	133.9	127.0	125.6	115.9	114.6	110.4
82.5°	66.3	75.9	81.4	85.6	84.2	89.7	84.2	82.8	77.3	77.3	74.5
85°	35.9	37.3	40.0	42.8	45.5	48.3	48.3	46.9	45.5	44.2	41.4
87.5°	13.8	13.8	15.2	13.8	15.2	17.9	19.3	19.3	17.9	16.6	13.8
90°	21.7	19.4	18.2	16.6	13.4	10.3	7.1	3.9	7.1	10.3	13.4
92.5°	20.4	18.1	16.9	17.2	17.8	18.3	18.9	19.5	18.9	18.3	17.8
95°	27.8	27.5	27.4	32.3	42.2	52.0	61.9	71.7	61.9	52.0	42.2
97.5°	119.9	150.3	165.5	162.3	155.9	149.6	143.2	136.8	143.2	149.6	155.9
100°	177.2	217.2	237.2	234.6	229.4	224.1	218.9	213.7	218.9	224.1	229.4
102.5°	320.6	317.1	315.4	313.7	310.2	306.7	303.2	299.7	303.2	306.7	310.2
105°	402.3	400.8	400.1	399.2	397.5	395.8	394.0	392.3	394.0	395.8	397.5
107.5°	483.9	481.9	480.9	480.5	479.6	478.7	477.9	477.0	477.9	478.7	479.6
110°	569.5	567.8	566.9	566.5	565.6	564.7	563.9	563.0	563.9	564.7	565.6

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	655.1	654.5	654.2	653.3	651.6	649.9	648.1	646.4	648.1	649.9	651.6
115°	735.9	736.2	736.3	735.9	735.0	734.1	733.3	732.4	733.3	734.1	735.0
117.5°	815.8	814.9	814.5	813.9	812.8	811.6	810.5	809.3	810.5	811.6	812.8
120°	892.3	892.6	892.7	892.1	891.0	889.8	888.7	887.5	888.7	889.8	891.0
122.5°	963.9	963.3	963.0	962.7	962.1	961.6	961.0	960.4	961.0	961.6	962.1
125°	1033.8	1034.4	1034.7	1034.1	1033.0	1031.8	1030.7	1029.5	1030.7	1031.8	1033.0
127.5°	1099.5	1098.0	1097.3	1097.2	1096.9	1096.6	1096.3	1096.0	1096.3	1096.6	1096.9
130°	1162.4	1161.5	1161.1	1161.0	1160.7	1160.4	1160.1	1159.8	1160.1	1160.4	1160.7
132.5°	1222.8	1221.7	1221.1	1220.8	1220.2	1219.7	1219.1	1218.5	1219.1	1219.7	1220.2
135°	1277.5	1276.4	1275.8	1275.9	1276.2	1276.5	1276.8	1277.1	1276.8	1276.5	1276.2
137.5°	1331.4	1329.9	1329.2	1329.2	1329.2	1329.2	1329.2	1329.2	1329.2	1329.2	1329.2
140°	1383.6	1383.0	1382.7	1382.4	1381.8	1381.3	1380.7	1380.1	1380.7	1381.3	1381.8
142.5°	1431.3	1431.0	1430.9	1430.3	1429.2	1428.0	1426.9	1425.7	1426.9	1428.0	1429.2
145°	1476.5	1476.5	1476.5	1476.1	1475.2	1474.3	1473.5	1472.6	1473.5	1474.3	1475.2
147.5°	1516.5	1516.8	1516.9	1516.0	1514.3	1512.6	1510.8	1509.1	1510.8	1512.6	1514.3
150°	1554.3	1554.6	1554.7	1554.1	1553.0	1551.8	1550.7	1549.5	1550.7	1551.8	1553.0
152.5°	1586.4	1587.0	1587.3	1586.9	1586.0	1585.1	1584.2	1583.3	1584.2	1585.1	1586.0
155°	1614.6	1615.5	1615.9	1615.8	1615.5	1615.2	1614.9	1614.6	1614.9	1615.2	1615.5
157.5°	1640.3	1641.4	1642.0	1642.0	1642.0	1642.0	1642.0	1642.0	1642.0	1642.0	1642.0
160°	1661.1	1661.4	1661.5	1661.9	1662.8	1663.7	1664.5	1665.4	1664.5	1663.7	1662.8
162.5°	1680.7	1681.0	1681.1	1681.7	1682.8	1684.0	1685.1	1686.3	1685.1	1684.0	1682.8
165°	1696.7	1696.7	1696.7	1697.4	1698.9	1700.3	1701.8	1703.2	1701.8	1700.3	1698.9
167.5°	1710.7	1711.0	1711.1	1711.8	1713.3	1714.7	1716.2	1717.6	1716.2	1714.7	1713.3
170°	1721.9	1721.6	1721.5	1722.4	1724.1	1725.8	1727.6	1729.3	1727.6	1725.8	1724.1
172.5°	1729.7	1729.4	1729.3	1730.2	1731.9	1733.6	1735.4	1737.1	1735.4	1733.6	1731.9
175°	1734.9	1734.6	1734.5	1735.4	1737.1	1738.8	1740.6	1742.3	1740.6	1738.8	1737.1
177.5°	1738.0	1737.4	1737.1	1738.1	1740.1	1742.2	1744.2	1746.2	1744.2	1742.2	1740.1
180°	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1685.3	1682.5	1679.8	1668.7	1659.1	1642.5	1628.7	1623.2	1621.8	1623.2	1619.0
5°	1637.0	1635.6	1625.9	1606.6	1588.7	1569.3	1555.5	1541.7	1533.5	1533.5	1523.8
7.5°	1591.4	1581.8	1573.5	1548.6	1527.9	1501.7	1481.0	1468.6	1461.7	1446.5	1446.5
10°	1543.1	1529.3	1518.3	1494.8	1464.5	1438.2	1412.0	1396.8	1384.4	1373.4	1369.2
12.5°	1494.8	1483.8	1463.1	1438.2	1407.9	1374.7	1347.1	1336.1	1307.1	1283.6	1285.0
15°	1449.3	1424.4	1414.8	1378.9	1343.0	1311.2	1271.2	1239.5	1216.0	1200.8	1181.5
17.5°	1398.2	1373.4	1355.4	1325.0	1278.1	1228.4	1189.8	1147.0	1123.5	1097.3	1084.9
20°	1341.6	1320.9	1307.1	1258.8	1202.2	1142.9	1100.1	1073.8	1047.6	1028.3	1017.2
22.5°	1293.3	1267.1	1250.5	1185.6	1123.5	1064.2	1031.1	1009.0	986.9	970.3	964.8
25°	1231.2	1216.0	1176.0	1119.4	1043.5	1003.4	974.5	945.5	933.1	922.0	909.6
27.5°	1180.1	1142.9	1115.2	1040.7	993.8	948.2	919.2	897.2	882.0	870.9	861.3
30°	1116.6	1082.1	1043.5	981.4	938.6	895.8	869.6	851.6	835.1	828.2	819.9
32.5°	1050.4	1018.6	981.4	931.7	879.2	846.1	825.4	806.1	795.0	788.1	778.5
35°	991.0	951.0	926.2	879.2	836.4	799.2	779.8	763.3	750.9	748.1	746.7
37.5°	927.5	897.2	873.7	825.4	789.5	757.8	739.8	721.9	715.0	713.6	708.1
40°	872.3	846.1	824.0	778.5	739.8	710.8	697.0	686.0	679.1	679.1	677.7
42.5°	824.0	796.4	774.3	732.9	698.4	672.2	657.0	646.0	643.2	644.6	643.2
45°	770.2	746.7	724.6	681.8	652.9	633.5	617.0	611.5	607.3	608.7	610.1
47.5°	719.1	699.8	677.7	643.2	610.1	589.4	579.7	574.2	574.2	574.2	576.9
50°	673.6	651.5	632.2	596.3	565.9	549.3	541.1	534.2	535.5	536.9	538.3
52.5°	619.7	600.4	586.6	550.7	528.6	507.9	498.3	499.7	498.3	498.3	501.0
55°	572.8	553.5	539.7	506.6	484.5	470.7	462.4	458.2	459.6	456.9	462.4
57.5°	520.4	503.8	494.1	462.4	443.1	430.6	423.7	416.8	419.6	418.2	416.8
60°	474.8	455.5	440.3	418.2	401.7	386.5	382.3	375.4	378.2	375.4	374.0
62.5°	422.4	407.2	396.1	374.0	360.2	347.8	338.2	334.0	332.6	328.5	324.4
65°	369.9	361.6	350.6	328.5	314.7	305.0	299.5	295.4	294.0	283.0	270.5
67.5°	321.6	316.1	305.0	288.5	276.1	266.4	258.1	251.2	242.9	234.6	227.7
70°	276.1	267.8	260.9	245.7	234.6	225.0	216.7	208.4	204.3	196.0	193.2
72.5°	231.9	223.6	216.7	202.9	193.2	183.6	180.8	171.2	167.0	165.6	165.6
75°	186.3	179.4	175.3	162.9	154.6	147.7	143.5	140.8	138.0	135.3	131.1
77.5°	142.2	138.0	135.3	127.0	120.1	115.9	114.6	104.9	102.1	99.4	96.6
80°	103.5	102.1	99.4	92.5	89.7	80.1	80.1	77.3	75.9	75.9	75.9
82.5°	70.4	67.6	66.3	59.4	58.0	56.6	55.2	53.8	55.2	53.8	55.2
85°	37.3	35.9	34.5	34.5	34.5	34.5	34.5	34.5	34.5	33.1	34.5
87.5°	13.8	13.8	13.8	13.8	12.4	13.8	13.8	12.4	13.8	13.8	13.8
90°	16.6	18.2	19.4	21.7	24.0	26.4	28.7	30.4	32.2	33.9	35.6
92.5°	17.2	16.9	18.1	20.4	22.7	25.1	27.4	29.1	30.9	32.6	34.3
95°	32.3	27.4	27.5	27.8	28.1	28.4	28.7	30.4	32.2	33.9	35.6
97.5°	162.3	165.5	150.3	119.9	89.5	59.1	28.7	30.1	31.6	33.0	34.5
100°	234.6	237.2	217.2	177.2	137.3	97.3	57.3	52.4	47.5	42.6	37.7
102.5°	313.7	315.4	317.1	320.6	324.1	327.5	331.0	265.8	200.7	135.5	70.4
105°	399.2	400.1	400.8	402.3	403.7	405.2	406.6	409.2	411.8	414.4	417.0
107.5°	480.5	480.9	481.9	483.9	486.0	488.0	490.0	491.4	492.9	494.3	495.8
110°	566.5	566.9	567.8	569.5	571.2	573.0	574.7	575.3	575.9	576.4	577.0

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	653.3	654.2	654.5	655.1	655.6	656.2	656.8	656.5	656.2	655.9	655.6
115°	735.9	736.3	736.2	735.9	735.6	735.3	735.0	735.6	736.2	736.7	737.3
117.5°	813.9	814.5	814.9	815.8	816.7	817.5	818.4	818.1	817.8	817.5	817.2
120°	892.1	892.7	892.6	892.3	892.0	891.7	891.4	892.0	892.6	893.1	893.7
122.5°	962.7	963.0	963.3	963.9	964.4	965.0	965.6	965.9	966.2	966.5	966.8
125°	1034.1	1034.7	1034.4	1033.8	1033.3	1032.7	1032.1	1033.0	1033.8	1034.7	1035.6
127.5°	1097.2	1097.3	1098.0	1099.5	1100.9	1102.4	1103.8	1103.5	1103.2	1102.9	1102.6
130°	1161.0	1161.1	1161.5	1162.4	1163.3	1164.1	1165.0	1165.3	1165.6	1165.9	1166.2
132.5°	1220.8	1221.1	1221.7	1222.8	1224.0	1225.1	1226.3	1226.6	1226.9	1227.2	1227.5
135°	1275.9	1275.8	1276.4	1277.5	1278.7	1279.8	1281.0	1281.6	1282.2	1282.7	1283.3
137.5°	1329.2	1329.2	1329.9	1331.4	1332.8	1334.3	1335.7	1336.3	1336.9	1337.5	1338.1
140°	1382.4	1382.7	1383.0	1383.6	1384.1	1384.7	1385.3	1386.2	1387.0	1387.9	1388.8
142.5°	1430.3	1430.9	1431.0	1431.3	1431.6	1431.9	1432.2	1432.8	1433.4	1433.9	1434.5
145°	1476.1	1476.5	1476.5	1476.5	1476.5	1476.5	1476.5	1476.8	1477.1	1477.4	1477.7
147.5°	1516.0	1516.9	1516.8	1516.5	1516.2	1515.9	1515.6	1515.9	1516.2	1516.5	1516.8
150°	1554.1	1554.7	1554.6	1554.3	1554.0	1553.7	1553.4	1553.4	1553.4	1553.4	1553.4
152.5°	1586.9	1587.3	1587.0	1586.4	1585.9	1585.3	1584.7	1585.3	1585.9	1586.4	1587.0
155°	1615.8	1615.9	1615.5	1614.6	1613.7	1612.9	1612.0	1613.2	1614.3	1615.5	1616.6
157.5°	1642.0	1642.0	1641.4	1640.3	1639.1	1638.0	1636.8	1638.2	1639.7	1641.1	1642.6
160°	1661.9	1661.5	1661.4	1661.1	1660.8	1660.5	1660.2	1662.0	1663.7	1665.5	1667.2
162.5°	1681.7	1681.1	1681.0	1680.7	1680.4	1680.1	1679.8	1681.5	1683.3	1685.0	1686.7
165°	1697.4	1696.7	1696.7	1696.7	1696.7	1696.7	1696.7	1699.0	1701.4	1703.7	1706.0
167.5°	1711.8	1711.1	1711.0	1710.7	1710.4	1710.1	1709.8	1712.4	1715.0	1717.6	1720.2
170°	1722.4	1721.5	1721.6	1721.9	1722.2	1722.5	1722.8	1725.1	1727.4	1729.7	1732.0
172.5°	1730.2	1729.3	1729.4	1729.7	1730.0	1730.3	1730.6	1732.9	1735.2	1737.5	1739.8
175°	1735.4	1734.5	1734.6	1734.9	1735.2	1735.5	1735.8	1738.4	1741.0	1743.6	1746.2
177.5°	1738.1	1737.1	1737.4	1738.0	1738.5	1739.1	1739.7	1742.0	1744.4	1746.7	1749.0
180°	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1619.0	1624.6	1617.7	1621.8	1612.1	1610.8	1612.1	1612.1	1613.5	1614.9	1616.3
5°	1527.9	1526.6	1518.3	1512.8	1508.6	1512.8	1515.5	1518.3	1515.5	1518.3	1519.7
7.5°	1442.4	1438.2	1434.1	1424.4	1427.2	1424.4	1432.7	1428.6	1428.6	1435.5	1441.0
10°	1366.5	1358.2	1355.4	1344.4	1336.1	1334.7	1344.4	1348.5	1352.6	1355.4	1366.5
12.5°	1268.5	1256.0	1246.4	1250.5	1227.0	1236.7	1239.5	1233.9	1250.5	1269.8	1258.8
15°	1163.6	1164.9	1145.6	1138.7	1119.4	1124.9	1126.3	1140.1	1153.9	1152.5	1169.1
17.5°	1086.3	1078.0	1061.4	1060.0	1051.8	1055.9	1054.5	1065.6	1061.4	1068.3	1082.1
20°	1014.5	1009.0	995.2	989.6	992.4	989.6	991.0	992.4	996.5	1011.7	1009.0
22.5°	957.9	951.0	951.0	944.1	935.8	933.1	940.0	944.1	949.6	952.4	959.3
25°	908.2	902.7	895.8	891.6	884.7	886.1	890.3	895.8	899.9	905.4	911.0
27.5°	857.1	857.1	850.2	848.9	846.1	844.7	850.2	853.0	853.0	857.1	862.7
30°	817.1	817.1	810.2	808.8	807.4	807.4	811.6	813.0	814.4	818.5	821.3
32.5°	778.5	777.1	774.3	775.7	774.3	775.7	775.7	777.1	779.8	781.2	786.7
35°	742.6	744.0	741.2	741.2	739.8	741.2	744.0	745.3	746.7	749.5	749.5
37.5°	708.1	710.8	709.5	713.6	713.6	713.6	713.6	716.4	716.4	716.4	715.0
40°	677.7	677.7	676.3	679.1	681.8	681.8	683.2	683.2	684.6	684.6	683.2
42.5°	643.2	646.0	650.1	651.5	654.2	652.9	657.0	655.6	657.0	654.2	651.5
45°	611.5	611.5	617.0	622.5	623.9	623.9	623.9	626.6	623.9	619.7	618.4
47.5°	576.9	579.7	582.5	589.4	590.7	590.7	590.7	590.7	588.0	588.0	588.0
50°	542.4	543.8	545.2	548.0	552.1	550.7	550.7	550.7	556.2	550.7	552.1
52.5°	501.0	502.4	503.8	509.3	507.9	507.9	509.3	509.3	513.5	512.1	509.3
55°	459.6	459.6	462.4	462.4	462.4	465.1	466.5	469.3	467.9	469.3	470.7
57.5°	418.2	415.5	414.1	414.1	418.2	416.8	418.2	418.2	423.7	426.5	427.9
60°	369.9	369.9	368.5	360.2	360.2	358.9	363.0	365.8	368.5	381.0	379.6
62.5°	320.2	314.7	309.2	310.6	302.3	306.4	303.7	306.4	314.7	324.4	325.7
65°	270.5	266.4	260.9	259.5	256.7	260.9	259.5	260.9	265.0	270.5	277.4
67.5°	226.4	225.0	222.2	220.8	220.8	220.8	223.6	223.6	225.0	229.1	233.3
70°	193.2	191.9	193.2	190.5	191.9	190.5	191.9	193.2	194.6	196.0	200.1
72.5°	162.9	162.9	162.9	160.1	162.9	161.5	161.5	162.9	164.3	165.6	168.4
75°	129.7	127.0	124.2	121.5	120.1	122.8	124.2	122.8	127.0	132.5	132.5
77.5°	98.0	96.6	96.6	96.6	98.0	96.6	99.4	98.0	99.4	99.4	102.1
80°	75.9	74.5	75.9	75.9	74.5	77.3	75.9	75.9	77.3	78.7	77.3
82.5°	55.2	56.6	55.2	55.2	55.2	58.0	55.2	55.2	55.2	56.6	56.6
85°	34.5	34.5	34.5	34.5	35.9	34.5	35.9	34.5	37.3	35.9	35.9
87.5°	12.4	13.8	15.2	15.2	15.2	15.2	13.8	15.2	16.6	15.2	16.6
90°	36.5	36.8	37.4	37.9	38.5	39.1	38.5	37.9	37.4	36.8	36.5
92.5°	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2	35.2
95°	36.5	36.6	36.9	37.2	37.5	37.8	37.5	37.2	36.9	36.6	36.5
97.5°	35.2	35.3	35.6	35.9	36.2	36.5	36.2	35.9	35.6	35.3	35.2
100°	35.2	35.3	35.6	35.9	36.2	36.5	36.2	35.9	35.6	35.3	35.2
102.5°	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8	37.8
105°	418.3	413.1	402.7	392.2	381.8	371.4	381.8	392.2	402.7	413.1	418.3
107.5°	496.5	497.1	498.2	499.4	500.5	501.7	500.5	499.4	498.2	497.1	496.5
110°	577.3	577.7	578.6	579.5	580.3	581.2	580.3	579.5	578.6	577.7	577.3

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	655.5	656.1	657.2	658.4	659.5	660.7	659.5	658.4	657.2	656.1	655.5
115°	737.6	737.6	737.6	737.6	737.6	737.6	737.6	737.6	737.6	737.6	737.6
117.5°	817.1	817.1	817.1	817.1	817.1	817.1	817.1	817.1	817.1	817.1	817.1
120°	894.0	893.7	893.1	892.6	892.0	891.4	892.0	892.6	893.1	893.7	894.0
122.5°	967.0	966.7	966.1	965.5	964.9	964.3	964.9	965.5	966.1	966.7	967.0
125°	1036.0	1036.1	1036.4	1036.7	1037.0	1037.3	1037.0	1036.7	1036.4	1036.1	1036.0
127.5°	1102.5	1102.4	1102.1	1101.8	1101.5	1101.2	1101.5	1101.8	1102.1	1102.4	1102.5
130°	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3	1166.3
132.5°	1227.6	1227.5	1227.2	1226.9	1226.6	1226.3	1226.6	1226.9	1227.2	1227.5	1227.6
135°	1283.6	1283.9	1284.5	1285.0	1285.6	1286.2	1285.6	1285.0	1284.5	1283.9	1283.6
137.5°	1338.4	1338.3	1338.0	1337.7	1337.4	1337.1	1337.4	1337.7	1338.0	1338.3	1338.4
140°	1389.2	1389.3	1389.6	1389.9	1390.2	1390.5	1390.2	1389.9	1389.6	1389.3	1389.2
142.5°	1434.8	1434.8	1434.8	1434.8	1434.8	1434.8	1434.8	1434.8	1434.8	1434.8	1434.8
145°	1477.8	1478.1	1478.7	1479.2	1479.8	1480.4	1479.8	1479.2	1478.7	1478.1	1477.8
147.5°	1516.9	1517.0	1517.3	1517.6	1517.9	1518.2	1517.9	1517.6	1517.3	1517.0	1516.9
150°	1553.4	1553.5	1553.8	1554.1	1554.4	1554.7	1554.4	1554.1	1553.8	1553.5	1553.4
152.5°	1587.3	1587.2	1586.9	1586.6	1586.3	1586.0	1586.3	1586.6	1586.9	1587.2	1587.3
155°	1617.2	1616.8	1615.9	1615.0	1614.2	1613.3	1614.2	1615.0	1615.9	1616.8	1617.2
157.5°	1643.3	1642.6	1641.1	1639.7	1638.2	1636.8	1638.2	1639.7	1641.1	1642.6	1643.3
160°	1668.1	1667.2	1665.5	1663.7	1662.0	1660.2	1662.0	1663.7	1665.5	1667.2	1668.1
162.5°	1687.6	1686.6	1684.6	1682.5	1680.5	1678.5	1680.5	1682.5	1684.6	1686.6	1687.6
165°	1707.2	1705.9	1703.3	1700.6	1698.0	1695.4	1698.0	1700.6	1703.3	1705.9	1707.2
167.5°	1721.5	1720.1	1717.2	1714.3	1711.4	1708.5	1711.4	1714.3	1717.2	1720.1	1721.5
170°	1733.2	1731.8	1728.9	1726.0	1723.1	1720.2	1723.1	1726.0	1728.9	1731.8	1733.2
172.5°	1741.0	1739.4	1736.2	1733.1	1729.9	1726.7	1729.9	1733.1	1736.2	1739.4	1741.0
175°	1747.5	1745.8	1742.3	1738.8	1735.4	1731.9	1735.4	1738.8	1742.3	1745.8	1747.5
177.5°	1750.2	1748.5	1745.0	1741.5	1738.0	1734.5	1738.0	1741.5	1745.0	1748.5	1750.2
180°	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1621.8	1628.7	1625.9	1616.3	1620.4	1628.7	1637.0	1648.0	1654.9	1660.4	1663.2
5°	1526.6	1539.0	1536.2	1536.2	1541.7	1555.5	1569.3	1592.8	1601.1	1610.8	1624.6
7.5°	1442.4	1452.0	1460.3	1463.1	1471.4	1489.3	1507.2	1533.5	1554.2	1565.2	1573.5
10°	1367.8	1374.7	1387.2	1394.1	1402.3	1424.4	1450.6	1478.3	1499.0	1518.3	1529.3
12.5°	1272.6	1300.2	1316.8	1327.8	1338.8	1372.0	1392.7	1423.0	1447.9	1465.8	1482.4
15°	1166.3	1199.4	1209.1	1251.9	1279.5	1305.7	1337.5	1373.4	1396.8	1417.5	1439.6
17.5°	1076.6	1100.1	1111.1	1156.7	1180.1	1221.5	1267.1	1312.6	1348.5	1363.7	1385.8
20°	1020.0	1032.4	1054.5	1069.7	1094.5	1142.9	1192.5	1247.8	1301.6	1316.8	1338.8
22.5°	962.0	978.6	993.8	1014.5	1033.8	1066.9	1116.6	1177.4	1235.3	1262.9	1289.2
25°	909.6	926.2	935.8	957.9	975.8	1009.0	1043.5	1105.6	1174.6	1198.1	1239.5
27.5°	868.2	877.8	894.4	904.1	924.8	955.1	986.9	1033.8	1101.4	1141.5	1181.5
30°	826.8	833.7	847.5	861.3	876.5	897.2	933.1	978.6	1040.7	1075.2	1115.2
32.5°	785.4	796.4	804.7	814.4	830.9	855.8	880.6	924.8	974.5	1013.1	1053.1
35°	750.9	755.0	766.0	777.1	788.1	810.2	836.4	879.2	923.4	953.8	989.6
37.5°	713.6	720.5	728.8	732.9	750.9	764.7	792.3	825.4	877.8	897.2	933.1
40°	684.6	683.2	691.5	698.4	706.7	728.8	745.3	781.2	822.6	853.0	875.1
42.5°	648.7	648.7	651.5	659.8	670.8	684.6	703.9	734.3	777.1	799.2	825.4
45°	619.7	615.6	617.0	622.5	629.4	643.2	662.5	688.7	731.5	749.5	777.1
47.5°	585.2	581.1	581.1	586.6	592.1	601.8	617.0	647.3	681.8	705.3	726.0
50°	546.6	548.0	546.6	550.7	553.5	563.1	579.7	604.6	636.3	655.6	679.1
52.5°	510.7	507.9	506.6	509.3	514.8	521.7	539.7	561.8	592.1	611.5	632.2
55°	466.5	469.3	469.3	469.3	477.6	480.3	494.1	516.2	546.6	561.8	581.1
57.5°	426.5	425.1	427.9	426.5	433.4	443.1	454.1	470.7	501.0	516.2	534.2
60°	382.3	383.7	385.1	385.1	390.6	400.3	412.7	427.9	452.7	467.9	484.5
62.5°	328.5	335.4	342.3	345.1	353.3	360.2	368.5	385.1	407.2	418.2	433.4
65°	277.4	287.1	296.8	303.7	309.2	316.1	327.1	342.3	360.2	371.3	386.5
67.5°	233.3	240.2	252.6	259.5	270.5	278.8	285.7	298.1	320.2	324.4	336.8
70°	201.5	204.3	209.8	215.3	227.7	234.6	242.9	255.3	271.9	281.6	288.5
72.5°	169.8	171.2	173.9	179.4	185.0	193.2	202.9	213.9	229.1	233.3	242.9
75°	135.3	143.5	143.5	147.7	151.8	156.0	164.3	175.3	185.0	191.9	197.4
77.5°	100.8	104.9	107.7	114.6	120.1	124.2	129.7	138.0	143.5	149.1	153.2
80°	78.7	80.1	81.4	81.4	84.2	89.7	95.2	100.8	107.7	110.4	114.6
82.5°	58.0	58.0	58.0	60.7	62.1	63.5	63.5	66.3	73.2	75.9	80.1
85°	37.3	37.3	37.3	37.3	38.6	40.0	41.4	42.8	42.8	42.8	45.5
87.5°	15.2	17.9	16.6	17.9	17.9	17.9	17.9	19.3	19.3	20.7	20.7
90°	35.6	33.9	32.2	30.4	28.7	26.4	24.0	21.7	19.4	18.2	16.6
92.5°	34.3	32.6	30.9	29.1	27.4	25.1	22.7	20.4	18.1	16.9	17.2
95°	35.6	33.9	32.2	30.4	28.7	28.4	28.1	27.8	27.5	27.4	32.3
97.5°	34.5	33.0	31.6	30.1	28.7	59.1	89.5	119.9	150.3	165.5	162.3
100°	37.7	42.6	47.5	52.4	57.3	97.3	137.3	177.2	217.2	237.2	234.6
102.5°	70.4	135.5	200.7	265.8	331.0	327.5	324.1	320.6	317.1	315.4	313.7
105°	417.0	414.4	411.8	409.2	406.6	405.2	403.7	402.3	400.8	400.1	399.2
107.5°	495.8	494.3	492.9	491.4	490.0	488.0	486.0	483.9	481.9	480.9	480.5
110°	577.0	576.4	575.9	575.3	574.7	573.0	571.2	569.5	567.8	566.9	566.5

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	655.6	655.9	656.2	656.5	656.8	656.2	655.6	655.1	654.5	654.2	653.3
115°	737.3	736.7	736.2	735.6	735.0	735.3	735.6	735.9	736.2	736.3	735.9
117.5°	817.2	817.5	817.8	818.1	818.4	817.5	816.7	815.8	814.9	814.5	813.9
120°	893.7	893.1	892.6	892.0	891.4	891.7	892.0	892.3	892.6	892.7	892.1
122.5°	966.8	966.5	966.2	965.9	965.6	965.0	964.4	963.9	963.3	963.0	962.7
125°	1035.6	1034.7	1033.8	1033.0	1032.1	1032.7	1033.3	1033.8	1034.4	1034.7	1034.1
127.5°	1102.6	1102.9	1103.2	1103.5	1103.8	1102.4	1100.9	1099.5	1098.0	1097.3	1097.2
130°	1166.2	1165.9	1165.6	1165.3	1165.0	1164.1	1163.3	1162.4	1161.5	1161.1	1161.0
132.5°	1227.5	1227.2	1226.9	1226.6	1226.3	1225.1	1224.0	1222.8	1221.7	1221.1	1220.8
135°	1283.3	1282.7	1282.2	1281.6	1281.0	1279.8	1278.7	1277.5	1276.4	1275.8	1275.9
137.5°	1338.1	1337.5	1336.9	1336.3	1335.7	1334.3	1332.8	1331.4	1329.9	1329.2	1329.2
140°	1388.8	1387.9	1387.0	1386.2	1385.3	1384.7	1384.1	1383.6	1383.0	1382.7	1382.4
142.5°	1434.5	1433.9	1433.4	1432.8	1432.2	1431.9	1431.6	1431.3	1431.0	1430.9	1430.3
145°	1477.7	1477.4	1477.1	1476.8	1476.5	1476.5	1476.5	1476.5	1476.5	1476.5	1476.1
147.5°	1516.8	1516.5	1516.2	1515.9	1515.6	1515.9	1516.2	1516.5	1516.8	1516.9	1516.0
150°	1553.4	1553.4	1553.4	1553.4	1553.4	1553.7	1554.0	1554.3	1554.6	1554.7	1554.1
152.5°	1587.0	1586.4	1585.9	1585.3	1584.7	1585.3	1585.9	1586.4	1587.0	1587.3	1586.9
155°	1616.6	1615.5	1614.3	1613.2	1612.0	1612.9	1613.7	1614.6	1615.5	1615.9	1615.8
157.5°	1642.6	1641.1	1639.7	1638.2	1636.8	1638.0	1639.1	1640.3	1641.4	1642.0	1642.0
160°	1667.2	1665.5	1663.7	1662.0	1660.2	1660.5	1660.8	1661.1	1661.4	1661.5	1661.9
162.5°	1686.7	1685.0	1683.3	1681.5	1679.8	1680.1	1680.4	1680.7	1681.0	1681.1	1681.7
165°	1706.0	1703.7	1701.4	1699.0	1696.7	1696.7	1696.7	1696.7	1696.7	1696.7	1697.4
167.5°	1720.2	1717.6	1715.0	1712.4	1709.8	1710.1	1710.4	1710.7	1711.0	1711.1	1711.8
170°	1732.0	1729.7	1727.4	1725.1	1722.8	1722.5	1722.2	1721.9	1721.6	1721.5	1722.4
172.5°	1739.8	1737.5	1735.2	1732.9	1730.6	1730.3	1730.0	1729.7	1729.4	1729.3	1730.2
175°	1746.2	1743.6	1741.0	1738.4	1735.8	1735.5	1735.2	1734.9	1734.6	1734.5	1735.4
177.5°	1749.0	1746.7	1744.4	1742.0	1739.7	1739.1	1738.5	1738.0	1737.4	1737.1	1738.1
180°	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3	1742.3

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1712.9	1712.9	1712.9	1712.9
2.5°	1674.2	1682.5	1696.3	1715.7
5°	1635.6	1659.1	1681.2	1710.1
7.5°	1601.1	1628.7	1659.1	1700.5
10°	1561.1	1595.6	1634.2	1685.3
12.5°	1514.1	1562.4	1606.6	1661.8
15°	1479.6	1515.5	1572.1	1637.0
17.5°	1431.3	1479.6	1536.2	1609.4
20°	1385.8	1436.8	1500.3	1576.3
22.5°	1337.5	1395.4	1458.9	1540.4
25°	1287.8	1349.9	1413.4	1500.3
27.5°	1242.2	1298.8	1370.6	1458.9
30°	1187.0	1251.9	1320.9	1413.4
32.5°	1133.2	1200.8	1271.2	1363.7
35°	1075.2	1142.9	1220.1	1308.5
37.5°	1018.6	1093.2	1163.6	1249.1
40°	956.5	1033.8	1107.0	1193.9
42.5°	895.8	975.8	1049.0	1123.5
45°	839.2	917.9	984.1	1054.5
47.5°	785.4	855.8	923.4	986.9
50°	732.9	792.3	854.4	906.8
52.5°	677.7	734.3	784.0	830.9
55°	628.0	672.2	716.4	759.1
57.5°	568.7	612.8	651.5	684.6
60°	519.0	546.6	583.8	618.4
62.5°	462.4	494.1	523.1	545.2
65°	407.2	434.8	456.9	476.2
67.5°	360.2	376.8	393.4	414.1
70°	303.7	317.5	336.8	352.0
72.5°	255.3	266.4	276.1	294.0
75°	207.0	216.7	222.2	238.8
77.5°	160.1	169.8	173.9	183.6
80°	122.8	124.2	129.7	138.0
82.5°	84.2	87.0	88.3	95.2
85°	48.3	55.2	53.8	56.6
87.5°	20.7	22.1	24.8	27.6
90°	13.4	10.3	7.1	3.9
92.5°	17.8	18.3	18.9	19.5
95°	42.2	52.0	61.9	71.7
97.5°	155.9	149.6	143.2	136.8
100°	229.4	224.1	218.9	213.7
102.5°	310.2	306.7	303.2	299.7
105°	397.5	395.8	394.0	392.3
107.5°	479.6	478.7	477.9	477.0
110°	565.6	564.7	563.9	563.0

TEST NUMBER: P1032852

CATALOG NUMBER: S124RDIW-B1020D1340UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	651.6	649.9	648.1	646.4
115°	735.0	734.1	733.3	732.4
117.5°	812.8	811.6	810.5	809.3
120°	891.0	889.8	888.7	887.5
122.5°	962.1	961.6	961.0	960.4
125°	1033.0	1031.8	1030.7	1029.5
127.5°	1096.9	1096.6	1096.3	1096.0
130°	1160.7	1160.4	1160.1	1159.8
132.5°	1220.2	1219.7	1219.1	1218.5
135°	1276.2	1276.5	1276.8	1277.1
137.5°	1329.2	1329.2	1329.2	1329.2
140°	1381.8	1381.3	1380.7	1380.1
142.5°	1429.2	1428.0	1426.9	1425.7
145°	1475.2	1474.3	1473.5	1472.6
147.5°	1514.3	1512.6	1510.8	1509.1
150°	1553.0	1551.8	1550.7	1549.5
152.5°	1586.0	1585.1	1584.2	1583.3
155°	1615.5	1615.2	1614.9	1614.6
157.5°	1642.0	1642.0	1642.0	1642.0
160°	1662.8	1663.7	1664.5	1665.4
162.5°	1682.8	1684.0	1685.1	1686.3
165°	1698.9	1700.3	1701.8	1703.2
167.5°	1713.3	1714.7	1716.2	1717.6
170°	1724.1	1725.8	1727.6	1729.3
172.5°	1731.9	1733.6	1735.4	1737.1
175°	1737.1	1738.8	1740.6	1742.3
177.5°	1740.1	1742.2	1744.2	1746.2
180°	1742.3	1742.3	1742.3	1742.3

(END OF REPORT)