

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P982964

Luminaire Tested: S123IW-B1535UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P982964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IW-B1535UB2750-4F0-XX-W2A-1_5000K
Description: Define 3 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5193.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P982964

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P982964

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P982964

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	4.0	0.1
90°-100°	120.6	2.3
100°-110°	364.9	7.0
110°-120°	621.2	12.0
120°-130°	817.2	15.7
130°-140°	918.6	17.7
140°-150°	903.0	17.4
150°-160°	760.3	14.6
160°-170°	506.1	9.7
170°-180°	177.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	4.0	0.1
90°-120°	1106.6	21.3
90°-150°	3745.4	72.1
90°-180°	5189.0	99.9
0°-180°	5193.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	16	35	41	44	6
95°	87	97	109	115	115	96
105°	331	334	347	347	350	354
115°	625	630	627	628	627	619
125°	915	920	916	911	905	816
135°	1187	1196	1195	1189	1186	915
145°	1440	1443	1448	1446	1440	900
155°	1649	1649	1651	1656	1646	759
165°	1796	1792	1792	1801	1790	507
175°	1868	1862	1862	1871	1861	178
180°	1873	1873	1873	1873	1873	

TEST NUMBER: P982964

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.5	16.2	35.3	41.2	44.1
92.5°	44.1	53.0	61.8	66.2	63.3
95°	86.8	97.1	108.9	114.7	114.7
97.5°	142.7	150.1	158.9	166.2	164.8
100°	200.1	208.9	216.3	220.7	223.6
102.5°	266.3	270.7	281.0	285.4	283.9
105°	331.0	333.9	347.2	347.2	350.1
107.5°	407.5	409.0	414.9	419.3	417.8
110°	478.1	481.1	484.0	489.9	486.9

TEST NUMBER: P982964

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	551.7	553.1	553.1	560.5	560.5
115°	625.2	629.6	626.7	628.2	626.7
117.5°	700.3	701.7	698.8	698.8	694.4
120°	769.4	778.2	770.9	769.4	766.5
122.5°	841.5	847.4	844.4	840.0	835.6
125°	915.0	919.5	916.5	910.6	904.7
127.5°	982.7	991.5	988.6	979.8	973.9
130°	1050.4	1062.2	1057.7	1051.9	1041.6
132.5°	1118.1	1129.8	1126.9	1119.5	1112.2
135°	1187.2	1196.0	1194.6	1188.7	1185.7
137.5°	1250.5	1257.8	1262.2	1254.9	1250.5
140°	1316.7	1324.0	1325.5	1324.0	1313.7
142.5°	1377.0	1384.3	1387.3	1385.8	1378.4
145°	1440.2	1443.2	1447.6	1446.1	1440.2
147.5°	1494.7	1500.6	1505.0	1505.0	1496.1
150°	1552.0	1555.0	1557.9	1557.9	1549.1
152.5°	1599.1	1603.5	1605.0	1607.9	1600.6
155°	1649.1	1649.1	1650.6	1656.5	1646.2
157.5°	1691.8	1690.3	1691.8	1697.7	1688.9
160°	1731.5	1728.6	1728.6	1735.9	1730.0
162.5°	1766.8	1762.4	1763.9	1771.2	1760.9
165°	1796.2	1791.8	1791.8	1800.7	1790.4
167.5°	1821.3	1815.4	1816.8	1825.7	1816.8
170°	1841.9	1836.0	1836.0	1846.3	1836.0
172.5°	1858.0	1852.2	1852.2	1861.0	1850.7
175°	1868.3	1862.4	1862.4	1871.3	1861.0
177.5°	1874.2	1868.3	1868.3	1877.2	1866.9
180°	1872.7	1872.7	1872.7	1872.7	1872.7



TEST NUMBER: P982964

CATALOG NUMBER: S123IW-B1535UB2750-4F0-XX-W2A-1_5000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT