

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032874

Luminaire Tested: S124RDIW-B1020D470UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032874
REPORT IS A COMBINATION OF REPORTS P999964 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1020D470UB2750-4F0-XX-W2A-F1_5000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5570.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032874

CATALOG NUMBER: S124RDIW-B1020D470UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032874

CATALOG NUMBER: S124RDIW-B1020D470UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	99	95	91	98	94	90	87	84	82	79	76	74	72	68	66	65
2	94	87	81	75	89	82	77	72	74	70	66	67	64	61	60	58	55
3	86	77	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48
4	79	68	60	54	75	65	58	52	59	53	48	53	49	45	48	44	41
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	39	36
6	67	55	47	41	64	53	45	39	48	42	37	44	38	34	40	35	32
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29
8	58	45	38	32	55	44	36	31	40	34	29	37	31	28	33	29	26
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14075	14075	14075
5°	14076	13656	13657
10°	13956	13225	13068
15°	13765	12688	12372
20°	13513	12077	11579
25°	13199	11417	10804
30°	12893	10744	9934
35°	12554	10062	9084
40°	12153	9327	8210
45°	11776	8598	7345
50°	11347	7802	6466
55°	10884	6986	5560
60°	10370	6120	4664
65°	9875	5126	3802
70°	9169	4080	2905
75°	8265	2969	2032
80°	6901	1823	1461
85°	5196	1051	803

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11776 cd/sqm

TEST NUMBER: P1032874

CATALOG NUMBER: S124RDIW-B1020D470UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.9
10°-20°	452.5	8.1
20°-30°	653.3	11.7
30°-40°	740.4	13.3
40°-50°	714.9	12.8
50°-60°	594.3	10.7
60°-70°	410.2	7.4
70°-80°	207.3	3.7
80°-90°	53.9	1.0
90°-100°	37.1	0.7
100°-110°	111.2	2.0
110°-120°	189.0	3.4
120°-130°	249.2	4.5
130°-140°	279.9	5.0
140°-150°	275.1	4.9
150°-160°	231.4	4.2
160°-170°	153.9	2.8
170°-180°	53.9	1.0
0°-30°	1268.1	22.8
0°-40°	2008.6	36.1
0°-60°	3317.8	59.6
0°-90°	3989.2	71.6
90°-120°	337.3	6.1
90°-150°	1141.5	20.5
90°-180°	1581.0	28.4
0°-180°	5570.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1723	1718	1702	1715	1713	164
15°	1641	1630	1596	1594	1584	463
25°	1484	1460	1406	1384	1370	684
35°	1283	1241	1175	1130	1106	802
45°	1047	998	918	854	830	807
55°	793	740	654	585	560	709
65°	539	482	398	341	325	532
75°	287	238	176	145	137	302
85°	71	45	41	38	38	78
90°	1	6	10	12	13	6
95°	26	30	34	35	35	29
105°	103	103	105	106	108	109
115°	192	192	191	191	190	189
125°	280	280	279	278	278	249
135°	361	364	364	363	361	279
145°	438	440	441	440	439	274
155°	502	502	502	504	502	231
165°	547	546	545	547	546	154
175°	569	567	566	569	566	54
180°	570	570	570	570	570	

TEST NUMBER: P1032874

CATALOG NUMBER: S124RDIW-B1020D470UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1731.2	1726.0	1711.4	1726.0	1724.6
5°	1723.3	1718.0	1702.2	1715.4	1712.7
7.5°	1711.4	1706.1	1686.3	1695.6	1691.6
10°	1692.9	1686.3	1662.5	1667.8	1662.5
12.5°	1669.1	1661.2	1632.1	1634.8	1626.8
15°	1641.4	1629.5	1596.4	1593.8	1584.5
17.5°	1609.7	1592.5	1554.2	1547.5	1534.3
20°	1571.3	1554.2	1509.2	1498.6	1481.5
22.5°	1529.0	1509.2	1460.3	1443.1	1429.9
25°	1484.1	1460.3	1406.1	1383.7	1370.5
27.5°	1437.9	1408.8	1352.0	1325.5	1307.0
30°	1389.0	1355.9	1293.8	1260.8	1239.6
32.5°	1337.4	1299.1	1234.3	1194.7	1174.9
35°	1283.2	1240.9	1174.9	1129.9	1106.1
37.5°	1226.4	1182.8	1110.1	1061.2	1037.4
40°	1165.6	1122.0	1046.7	991.2	967.4
42.5°	1107.5	1061.2	981.9	925.1	900.0
45°	1046.7	997.8	918.5	853.7	829.9
47.5°	984.6	934.3	852.4	785.0	758.6
50°	921.1	869.6	785.0	718.9	693.8
52.5°	856.4	806.2	718.9	651.5	625.1
55°	792.9	740.1	654.2	585.4	560.3
57.5°	730.8	675.3	590.7	520.7	502.2
60°	663.4	610.6	526.0	457.3	436.1
62.5°	602.6	547.1	459.9	397.8	381.9
65°	539.2	482.4	397.8	341.0	325.1
67.5°	473.1	418.9	339.6	289.4	270.9
70°	411.0	355.5	280.2	236.6	223.3
72.5°	344.9	296.0	226.0	190.3	178.4
75°	286.8	237.9	175.8	145.4	137.4
77.5°	226.0	183.7	130.8	109.7	107.0
80°	167.8	129.5	89.9	85.9	84.6
82.5°	117.6	83.3	64.8	62.1	60.8
85°	71.4	44.9	41.0	38.3	38.3
87.5°	30.4	19.8	18.5	17.2	18.5
90°	1.3	6.2	9.7	12.3	13.2
92.5°	11.5	17.2	19.4	20.7	21.1
95°	26.4	30.4	33.5	34.8	34.8
97.5°	42.3	45.8	49.3	51.1	51.1
100°	61.7	63.4	67.4	68.3	68.3
102.5°	82.0	82.4	85.9	87.2	87.7
105°	102.7	103.1	104.9	106.2	107.5
107.5°	124.3	124.7	125.1	126.9	126.5
110°	146.3	147.2	146.7	145.8	147.2

TEST NUMBER: P1032874

CATALOG NUMBER: S124RDIW-B1020D470UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	169.2	169.2	168.3	168.3	168.3
115°	192.1	192.1	191.2	190.8	190.3
117.5°	213.7	213.7	213.3	211.9	210.6
120°	235.3	237.1	235.7	233.5	234.4
122.5°	257.8	258.2	257.8	256.4	254.2
125°	279.8	279.8	279.4	278.5	277.6
127.5°	299.6	300.9	300.1	299.2	298.7
130°	320.8	322.1	322.1	321.2	319.5
132.5°	342.4	343.2	342.8	341.9	341.5
135°	360.9	363.5	363.5	362.6	361.3
137.5°	381.6	382.9	383.8	382.5	382.9
140°	402.3	403.2	403.2	402.7	402.3
142.5°	421.2	422.1	421.7	421.7	421.7
145°	438.4	440.2	440.6	440.2	438.9
147.5°	456.0	458.2	457.8	457.4	456.9
150°	471.9	473.7	473.7	473.7	473.2
152.5°	486.9	487.8	488.2	489.5	488.2
155°	502.3	502.3	501.9	503.6	501.9
157.5°	515.5	514.6	514.6	516.0	514.6
160°	527.0	526.5	526.1	527.4	525.2
162.5°	537.6	536.2	535.8	538.4	536.2
165°	546.8	545.5	544.6	547.3	545.5
167.5°	554.3	552.5	552.5	555.2	552.5
170°	560.5	558.3	558.7	561.4	558.3
172.5°	564.9	563.1	563.1	566.2	563.1
175°	568.8	566.6	566.2	569.3	566.2
177.5°	570.6	568.4	568.4	571.5	568.0
180°	569.7	569.7	569.7	569.7	569.7

(END OF REPORT)