

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032884

Luminaire Tested: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032884
REPORT IS A COMBINATION OF REPORTS P1000008 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F1_5000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6594.0 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032884

CATALOG NUMBER: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032884

CATALOG NUMBER: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	100	96	92	89	94	90	87	84	79	76	74	68	67	65	59	57	56
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48
3	84	74	67	61	78	70	64	58	62	56	52	54	50	47	46	44	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	38	45	39	34	39	35	31	34	31	28
7	61	48	40	35	57	46	38	33	41	35	30	36	31	27	31	28	25
8	56	44	36	31	53	42	34	30	37	31	27	33	28	25	29	25	22
9	52	40	33	28	49	38	31	26	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14075	14075	14075
5°	14076	13656	13657
10°	13956	13225	13068
15°	13765	12688	12372
20°	13513	12077	11579
25°	13199	11417	10804
30°	12893	10744	9934
35°	12554	10062	9084
40°	12153	9327	8210
45°	11776	8598	7345
50°	11347	7802	6466
55°	10884	6986	5560
60°	10370	6120	4664
65°	9875	5126	3802
70°	9169	4080	2905
75°	8265	2969	2032
80°	6901	1823	1461
85°	5196	1051	803

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11776 cd/sqm

TEST NUMBER: P1032884

CATALOG NUMBER: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.5
10°-20°	452.5	6.9
20°-30°	653.3	9.9
30°-40°	740.4	11.2
40°-50°	714.9	10.8
50°-60°	594.3	9.0
60°-70°	410.2	6.2
70°-80°	207.3	3.1
80°-90°	54.7	0.8
90°-100°	61.2	0.9
100°-110°	183.2	2.8
110°-120°	311.3	4.7
120°-130°	410.5	6.2
130°-140°	461.1	7.0
140°-150°	453.2	6.9
150°-160°	381.1	5.8
160°-170°	253.6	3.8
170°-180°	88.8	1.3
0°-30°	1268.1	19.2
0°-40°	2008.6	30.5
0°-60°	3317.8	50.3
0°-90°	3990.0	60.5
90°-120°	555.7	8.4
90°-150°	1880.4	28.5
90°-180°	2604.0	39.5
0°-180°	6594.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1723	1718	1702	1715	1713	164
15°	1641	1630	1596	1594	1584	463
25°	1484	1460	1406	1384	1370	684
35°	1283	1241	1175	1130	1106	802
45°	1047	998	918	854	830	807
55°	793	740	654	585	560	709
65°	539	482	398	341	325	532
75°	287	238	176	145	137	302
85°	71	45	41	38	38	78
90°	2	10	16	20	22	7
95°	44	50	55	57	57	47
105°	169	170	173	175	177	179
115°	316	316	315	314	314	312
125°	461	461	460	459	457	411
135°	594	599	599	597	595	460
145°	722	725	726	725	723	452
155°	827	827	827	830	827	381
165°	901	899	897	902	899	254
175°	937	933	933	938	933	89
180°	938	938	938	938	938	

TEST NUMBER: P1032884

CATALOG NUMBER: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1731.2	1726.0	1711.4	1726.0	1724.6
5°	1723.3	1718.0	1702.2	1715.4	1712.7
7.5°	1711.4	1706.1	1686.3	1695.6	1691.6
10°	1692.9	1686.3	1662.5	1667.8	1662.5
12.5°	1669.1	1661.2	1632.1	1634.8	1626.8
15°	1641.4	1629.5	1596.4	1593.8	1584.5
17.5°	1609.7	1592.5	1554.2	1547.5	1534.3
20°	1571.3	1554.2	1509.2	1498.6	1481.5
22.5°	1529.0	1509.2	1460.3	1443.1	1429.9
25°	1484.1	1460.3	1406.1	1383.7	1370.5
27.5°	1437.9	1408.8	1352.0	1325.5	1307.0
30°	1389.0	1355.9	1293.8	1260.8	1239.6
32.5°	1337.4	1299.1	1234.3	1194.7	1174.9
35°	1283.2	1240.9	1174.9	1129.9	1106.1
37.5°	1226.4	1182.8	1110.1	1061.2	1037.4
40°	1165.6	1122.0	1046.7	991.2	967.4
42.5°	1107.5	1061.2	981.9	925.1	900.0
45°	1046.7	997.8	918.5	853.7	829.9
47.5°	984.6	934.3	852.4	785.0	758.6
50°	921.1	869.6	785.0	718.9	693.8
52.5°	856.4	806.2	718.9	651.5	625.1
55°	792.9	740.1	654.2	585.4	560.3
57.5°	730.8	675.3	590.7	520.7	502.2
60°	663.4	610.6	526.0	457.3	436.1
62.5°	602.6	547.1	459.9	397.8	381.9
65°	539.2	482.4	397.8	341.0	325.1
67.5°	473.1	418.9	339.6	289.4	270.9
70°	411.0	355.5	280.2	236.6	223.3
72.5°	344.9	296.0	226.0	190.3	178.4
75°	286.8	237.9	175.8	145.4	137.4
77.5°	226.0	183.7	130.8	109.7	107.0
80°	167.8	129.5	89.9	85.9	84.6
82.5°	117.6	83.3	64.8	62.1	60.8
85°	71.4	44.9	41.0	38.3	38.3
87.5°	30.4	19.8	18.5	17.2	18.5
90°	2.2	10.2	16.0	20.3	21.8
92.5°	18.9	28.3	31.9	34.1	34.8
95°	43.5	50.1	55.2	57.3	57.3
97.5°	69.7	75.5	81.3	84.2	84.2
100°	101.6	104.5	111.1	112.5	112.5
102.5°	135.0	135.7	141.5	143.7	144.4
105°	169.1	169.8	172.7	174.9	177.1
107.5°	204.7	205.4	206.1	209.0	208.3
110°	241.0	242.4	241.7	240.3	242.4

TEST NUMBER: P1032884

CATALOG NUMBER: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.7	278.7	277.3	277.3	277.3
115°	316.5	316.5	315.0	314.3	313.6
117.5°	352.0	352.0	351.3	349.1	346.9
120°	387.6	390.5	388.3	384.7	386.1
122.5°	424.6	425.3	424.6	422.4	418.8
125°	460.9	460.9	460.2	458.7	457.3
127.5°	493.6	495.7	494.3	492.8	492.1
130°	528.4	530.6	530.6	529.1	526.2
132.5°	564.0	565.4	564.7	563.2	562.5
135°	594.5	598.8	598.8	597.4	595.2
137.5°	628.6	630.7	632.2	630.0	630.7
140°	662.7	664.1	664.1	663.4	662.7
142.5°	693.9	695.3	694.6	694.6	694.6
145°	722.2	725.1	725.8	725.1	722.9
147.5°	751.2	754.9	754.1	753.4	752.7
150°	777.4	780.3	780.3	780.3	779.5
152.5°	802.0	803.5	804.2	806.4	804.2
155°	827.4	827.4	826.7	829.6	826.7
157.5°	849.2	847.8	847.8	849.9	847.8
160°	868.1	867.4	866.6	868.8	865.2
162.5°	885.5	883.3	882.6	887.0	883.3
165°	900.8	898.6	897.1	901.5	898.6
167.5°	913.1	910.2	910.2	914.5	910.2
170°	923.3	919.6	920.4	924.7	919.6
172.5°	930.5	927.6	927.6	932.7	927.6
175°	937.0	933.4	932.7	937.8	932.7
177.5°	940.0	936.3	936.3	941.4	935.6
180°	938.5	938.5	938.5	938.5	938.5

(END OF REPORT)