

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032888

Luminaire Tested: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032888
REPORT IS A COMBINATION OF REPORTS P1000014 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6994.0 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032888

CATALOG NUMBER: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032888

CATALOG NUMBER: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	100	95	92	88	93	89	86	83	77	75	72	66	64	63	56	55	54
2	91	84	78	73	85	78	73	68	68	64	60	58	55	53	50	47	46
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	41	39
4	76	66	58	52	71	61	54	49	54	48	44	46	42	39	40	36	34
5	70	59	50	45	65	55	48	42	48	42	38	42	37	34	36	32	30
6	65	53	45	39	60	50	42	37	43	38	33	38	33	30	33	29	26
7	60	48	40	34	56	45	38	33	40	34	30	35	30	26	30	26	23
8	56	43	36	30	52	41	34	29	36	30	26	32	27	24	27	24	21
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	25	22	19
10	49	37	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14075	14075	14075
5°	14076	13656	13657
10°	13956	13225	13068
15°	13765	12688	12372
20°	13513	12077	11579
25°	13199	11417	10804
30°	12893	10744	9934
35°	12554	10062	9084
40°	12153	9327	8210
45°	11776	8598	7345
50°	11347	7802	6466
55°	10884	6986	5560
60°	10370	6120	4664
65°	9875	5126	3802
70°	9169	4080	2905
75°	8265	2969	2032
80°	6901	1823	1461
85°	5196	1051	803

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11776 cd/sqm

TEST NUMBER: P1032888

CATALOG NUMBER: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	2.3
10°-20°	452.5	6.5
20°-30°	653.3	9.3
30°-40°	740.4	10.6
40°-50°	714.9	10.2
50°-60°	594.3	8.5
60°-70°	410.2	5.9
70°-80°	207.3	3.0
80°-90°	54.7	0.8
90°-100°	32.2	0.5
100°-110°	212.2	3.0
110°-120°	405.3	5.8
120°-130°	514.5	7.4
130°-140°	550.4	7.9
140°-150°	514.6	7.4
150°-160°	415.0	5.9
160°-170°	267.6	3.8
170°-180°	92.2	1.3
0°-30°	1268.1	18.1
0°-40°	2008.6	28.7
0°-60°	3317.8	47.4
0°-90°	3990.0	57.0
90°-120°	649.7	9.3
90°-150°	2229.1	31.9
90°-180°	3004.0	43.0
0°-180°	6994.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1723	1718	1702	1715	1713	164
15°	1641	1630	1596	1594	1584	463
25°	1484	1460	1406	1384	1370	684
35°	1283	1241	1175	1130	1106	802
45°	1047	998	918	854	830	807
55°	793	740	654	585	560	709
65°	539	482	398	341	325	532
75°	287	238	176	145	137	302
85°	71	45	41	38	38	78
90°	2	10	16	20	22	6
95°	40	15	16	20	21	49
105°	219	223	226	233	207	229
115°	408	410	410	411	411	402
125°	574	576	575	577	578	512
135°	712	711	714	715	717	548
145°	820	823	823	823	825	513
155°	900	900	898	901	899	415
165°	949	945	945	951	945	268
175°	971	966	967	974	965	92
180°	971	971	971	971	971	

TEST NUMBER: P1032888

CATALOG NUMBER: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1731.2	1726.0	1711.4	1726.0	1724.6
5°	1723.3	1718.0	1702.2	1715.4	1712.7
7.5°	1711.4	1706.1	1686.3	1695.6	1691.6
10°	1692.9	1686.3	1662.5	1667.8	1662.5
12.5°	1669.1	1661.2	1632.1	1634.8	1626.8
15°	1641.4	1629.5	1596.4	1593.8	1584.5
17.5°	1609.7	1592.5	1554.2	1547.5	1534.3
20°	1571.3	1554.2	1509.2	1498.6	1481.5
22.5°	1529.0	1509.2	1460.3	1443.1	1429.9
25°	1484.1	1460.3	1406.1	1383.7	1370.5
27.5°	1437.9	1408.8	1352.0	1325.5	1307.0
30°	1389.0	1355.9	1293.8	1260.8	1239.6
32.5°	1337.4	1299.1	1234.3	1194.7	1174.9
35°	1283.2	1240.9	1174.9	1129.9	1106.1
37.5°	1226.4	1182.8	1110.1	1061.2	1037.4
40°	1165.6	1122.0	1046.7	991.2	967.4
42.5°	1107.5	1061.2	981.9	925.1	900.0
45°	1046.7	997.8	918.5	853.7	829.9
47.5°	984.6	934.3	852.4	785.0	758.6
50°	921.1	869.6	785.0	718.9	693.8
52.5°	856.4	806.2	718.9	651.5	625.1
55°	792.9	740.1	654.2	585.4	560.3
57.5°	730.8	675.3	590.7	520.7	502.2
60°	663.4	610.6	526.0	457.3	436.1
62.5°	602.6	547.1	459.9	397.8	381.9
65°	539.2	482.4	397.8	341.0	325.1
67.5°	473.1	418.9	339.6	289.4	270.9
70°	411.0	355.5	280.2	236.6	223.3
72.5°	344.9	296.0	226.0	190.3	178.4
75°	286.8	237.9	175.8	145.4	137.4
77.5°	226.0	183.7	130.8	109.7	107.0
80°	167.8	129.5	89.9	85.9	84.6
82.5°	117.6	83.3	64.8	62.1	60.8
85°	71.4	44.9	41.0	38.3	38.3
87.5°	30.4	19.8	18.5	17.2	18.5
90°	2.2	10.2	16.0	20.3	21.8
92.5°	10.9	9.4	15.2	19.6	19.6
95°	39.9	15.2	16.0	20.3	21.1
97.5°	76.2	92.2	16.0	19.6	20.3
100°	119.1	132.2	31.9	19.6	20.3
102.5°	167.0	175.7	184.4	21.1	21.1
105°	218.6	222.9	226.5	233.1	206.9
107.5°	265.8	267.9	273.0	276.6	279.5
110°	313.7	315.9	320.2	321.7	323.8



TEST NUMBER: P1032888

CATALOG NUMBER: S124RDIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	360.1	364.5	366.0	365.2	368.1
115°	408.1	410.2	409.5	411.0	411.0
117.5°	450.9	453.8	456.0	455.3	455.3
120°	494.5	497.4	496.7	498.1	496.7
122.5°	535.1	536.6	538.0	538.8	537.3
125°	573.6	576.5	575.1	577.3	578.0
127.5°	610.7	611.4	615.0	614.3	613.6
130°	646.2	647.0	649.1	649.9	649.9
132.5°	678.9	680.4	683.3	684.0	683.3
135°	711.6	710.9	713.8	715.2	716.7
137.5°	740.6	740.6	744.3	745.7	745.0
140°	768.9	770.4	771.8	774.0	774.8
142.5°	794.4	797.3	798.0	799.4	799.4
145°	820.5	822.7	822.7	823.4	824.9
147.5°	840.8	845.2	844.5	845.2	845.9
150°	863.3	866.2	865.5	865.5	866.2
152.5°	882.2	884.4	882.9	884.4	883.7
155°	899.6	900.4	898.2	901.1	898.9
157.5°	914.9	914.9	912.0	915.6	912.0
160°	928.0	925.8	925.1	929.4	925.1
162.5°	939.6	936.7	935.9	940.3	935.2
165°	949.0	945.4	945.4	951.2	944.7
167.5°	957.0	953.4	952.6	959.2	951.9
170°	963.5	959.2	959.9	965.7	958.5
172.5°	967.9	963.5	964.3	970.1	962.1
175°	970.8	966.4	967.2	973.7	965.0
177.5°	973.0	967.9	969.3	975.2	966.4
180°	970.8	970.8	970.8	970.8	970.8

(END OF REPORT)