

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P982919

Luminaire Tested: S123IW-B1030UB27-4F0-XX-W2A

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P982919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IW-B1030UB27-4F0-XX-W2A
Description: Define 3 Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4147.0 lumens
Efficiency: N/A
Efficacy: 131.7 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 31.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P982919

CATALOG NUMBER: S123IW-B1030UB27-4F0-XX-W2A

Luminous Intensity Polar Plot





TEST NUMBER: P982919

CATALOG NUMBER: S123IW-B1030UB27-4F0-XX-W2A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P982919

CATALOG NUMBER: S123IW-B1030UB27-4F0-XX-W2A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.7	0.1
90°-100°	47.9	1.2
100°-110°	231.8	5.6
110°-120°	568.0	13.7
120°-130°	721.0	17.4
130°-140°	770.3	18.6
140°-150°	720.3	17.4
150°-160°	581.0	14.0
160°-170°	374.9	9.0
170°-180°	129.2	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.7	0.1
90°-120°	847.7	20.4
90°-150°	3059.2	73.8
90°-180°	4144.0	99.9
0°-180°	4147.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	11	24	28	30	3
95°	62	20	31	38	38	74
105°	301	312	221	42	44	319
115°	565	571	580	590	594	558
125°	796	804	808	810	812	711
135°	991	997	1001	1004	1001	763
145°	1143	1150	1152	1154	1154	716
155°	1259	1257	1258	1264	1257	580
165°	1328	1325	1324	1332	1325	375
175°	1359	1354	1355	1362	1354	129
180°	1359	1359	1359	1359	1359	

TEST NUMBER: P982919

CATALOG NUMBER: S123IW-B1030UB27-4F0-XX-W2A

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	11.1	24.2	28.3	30.3
92.5°	23.2	17.2	26.3	33.3	34.3
95°	61.6	20.2	31.3	38.4	38.4
97.5°	112.1	83.8	32.3	40.4	41.4
100°	170.7	190.9	33.3	41.4	42.4
102.5°	237.3	250.5	74.7	41.4	43.4
105°	301.0	312.1	221.2	42.4	44.4
107.5°	368.6	377.7	392.9	237.3	105.0
110°	436.3	444.4	455.5	422.2	277.7

TEST NUMBER: P982919

CATALOG NUMBER: S123IW-B1030UB27-4F0-XX-W2A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	500.9	508.0	519.1	528.2	526.2
115°	564.6	570.6	579.7	589.8	593.9
117.5°	627.2	634.3	639.3	647.4	648.4
120°	684.8	693.8	696.9	705.0	705.0
122.5°	743.3	750.4	754.4	759.5	760.5
125°	795.9	803.9	808.0	810.0	812.0
127.5°	848.4	856.5	861.5	864.5	862.5
130°	896.8	904.9	909.0	913.0	911.0
132.5°	943.3	951.4	954.4	958.5	955.4
135°	990.8	996.8	1000.9	1003.9	1000.9
137.5°	1031.2	1039.3	1041.3	1046.3	1044.3
140°	1071.6	1077.6	1080.7	1084.7	1082.7
142.5°	1108.9	1115.0	1118.0	1121.1	1118.0
145°	1143.3	1150.4	1152.4	1154.4	1154.4
147.5°	1176.6	1181.7	1183.7	1185.7	1180.6
150°	1206.9	1209.9	1212.0	1214.0	1210.9
152.5°	1234.2	1235.2	1236.2	1240.2	1235.2
155°	1259.4	1257.4	1258.4	1263.5	1257.4
157.5°	1279.6	1279.6	1278.6	1284.7	1276.6
160°	1297.8	1296.8	1295.8	1301.8	1294.8
162.5°	1315.0	1311.9	1310.9	1318.0	1311.9
165°	1328.1	1325.1	1324.1	1332.1	1325.1
167.5°	1339.2	1335.2	1335.2	1343.3	1335.2
170°	1348.3	1344.3	1344.3	1352.3	1344.3
172.5°	1354.4	1349.3	1350.3	1358.4	1349.3
175°	1359.4	1354.4	1355.4	1362.4	1354.4
177.5°	1361.4	1356.4	1357.4	1365.5	1355.4
180°	1359.4	1359.4	1359.4	1359.4	1359.4



TEST NUMBER: P982919

CATALOG NUMBER: S123IW-B1030UB27-4F0-XX-W2A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT