

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P982930

Luminaire Tested: S123IW-B1030UB30-4F0-XX-W2A-1

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P982930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IW-B1030UB30-4F0-XX-W2A-1
Description: Define 3 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3627.0 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 31.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P982930

CATALOG NUMBER: S123IW-B1030UB30-4F0-XX-W2A-1

Luminous Intensity Polar Plot



TEST NUMBER: P982930

CATALOG NUMBER: S123IW-B1030UB30-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P982930

CATALOG NUMBER: S123IW-B1030UB30-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.8	0.1
90°-100°	84.2	2.3
100°-110°	254.8	7.0
110°-120°	433.9	12.0
120°-130°	570.8	15.7
130°-140°	641.6	17.7
140°-150°	630.7	17.4
150°-160°	531.0	14.6
160°-170°	353.5	9.7
170°-180°	123.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.8	0.1
90°-120°	772.9	21.3
90°-150°	2615.9	72.1
90°-180°	3624.0	99.9
0°-180°	3627.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	11	25	29	31	4
95°	61	68	76	80	80	67
105°	231	233	242	242	244	247
115°	437	440	438	439	438	432
125°	639	642	640	636	632	570
135°	829	835	834	830	828	639
145°	1006	1008	1011	1010	1006	628
155°	1152	1152	1153	1157	1150	530
165°	1255	1252	1252	1258	1250	354
175°	1305	1301	1301	1307	1300	124
180°	1308	1308	1308	1308	1308	

TEST NUMBER: P982930

CATALOG NUMBER: S123IW-B1030UB30-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	11.3	24.7	28.8	30.8
92.5°	30.8	37.0	43.2	46.2	44.2
95°	60.6	67.8	76.0	80.1	80.1
97.5°	99.7	104.8	111.0	116.1	115.1
100°	139.7	145.9	151.0	154.1	156.2
102.5°	186.0	189.1	196.3	199.3	198.3
105°	231.2	233.2	242.5	242.5	244.5
107.5°	284.6	285.6	289.8	292.8	291.8
110°	333.9	336.0	338.0	342.2	340.1

TEST NUMBER: P982930

CATALOG NUMBER: S123IW-B1030UB30-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	385.3	386.3	386.3	391.5	391.5
115°	436.7	439.8	437.7	438.7	437.7
117.5°	489.1	490.1	488.1	488.1	485.0
120°	537.4	543.5	538.4	537.4	535.3
122.5°	587.7	591.8	589.8	586.7	583.6
125°	639.1	642.2	640.1	636.0	631.9
127.5°	686.4	692.5	690.5	684.3	680.2
130°	733.6	741.9	738.8	734.7	727.5
132.5°	780.9	789.1	787.1	781.9	776.8
135°	829.2	835.4	834.3	830.2	828.2
137.5°	873.4	878.5	881.6	876.5	873.4
140°	919.6	924.7	925.8	924.7	917.6
142.5°	961.7	966.9	968.9	967.9	962.8
145°	1005.9	1008.0	1011.1	1010.0	1005.9
147.5°	1043.9	1048.0	1051.1	1051.1	1045.0
150°	1084.0	1086.1	1088.1	1088.1	1082.0
152.5°	1116.9	1120.0	1121.0	1123.1	1117.9
155°	1151.8	1151.8	1152.8	1157.0	1149.8
157.5°	1181.6	1180.6	1181.6	1185.7	1179.6
160°	1209.4	1207.3	1207.3	1212.4	1208.3
162.5°	1234.0	1230.9	1232.0	1237.1	1229.9
165°	1254.6	1251.5	1251.5	1257.7	1250.5
167.5°	1272.0	1267.9	1269.0	1275.1	1269.0
170°	1286.4	1282.3	1282.3	1289.5	1282.3
172.5°	1297.7	1293.6	1293.6	1299.8	1292.6
175°	1304.9	1300.8	1300.8	1307.0	1299.8
177.5°	1309.0	1304.9	1304.9	1311.1	1303.9
180°	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P982930

CATALOG NUMBER: S123IW-B1030UB30-4F0-XX-W2A-1

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT