

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P982957

Luminaire Tested: S123IW-B1320UB50-4F0-XX-W2A

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P982957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IW-B1320UB50-4F0-XX-W2A
Description: Define 3 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5079.0 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 42.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P982957

CATALOG NUMBER: S123IW-B1320UB50-4F0-XX-W2A

Luminous Intensity Polar Plot



TEST NUMBER: P982957

CATALOG NUMBER: S123IW-B1320UB50-4F0-XX-W2A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P982957

CATALOG NUMBER: S123IW-B1320UB50-4F0-XX-W2A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.3	0.1
90°-100°	58.7	1.2
100°-110°	283.9	5.6
110°-120°	695.6	13.7
120°-130°	883.1	17.4
130°-140°	943.4	18.6
140°-150°	882.1	17.4
150°-160°	711.5	14.0
160°-170°	459.2	9.0
170°-180°	158.2	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.3	0.1
90°-120°	1038.2	20.4
90°-150°	3746.7	73.8
90°-180°	5076.0	99.9
0°-180°	5079.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	14	30	35	37	4
95°	76	25	38	47	47	90
105°	369	382	271	52	54	391
115°	692	699	710	722	727	683
125°	975	985	990	992	994	871
135°	1213	1221	1226	1230	1226	934
145°	1400	1409	1411	1414	1414	877
155°	1542	1540	1541	1547	1540	711
165°	1627	1623	1622	1632	1623	460
175°	1665	1659	1660	1669	1659	158
180°	1665	1665	1665	1665	1665	

TEST NUMBER: P982957

CATALOG NUMBER: S123IW-B1320UB50-4F0-XX-W2A

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	13.6	29.7	34.6	37.1
92.5°	28.4	21.0	32.2	40.8	42.1
95°	75.5	24.7	38.3	47.0	47.0
97.5°	137.3	102.7	39.6	49.5	50.7
100°	209.0	233.8	40.8	50.7	52.0
102.5°	290.7	306.8	91.5	50.7	53.2
105°	368.6	382.2	270.9	52.0	54.4
107.5°	451.5	462.6	481.2	290.7	128.6
110°	534.4	544.3	557.9	517.0	340.2

TEST NUMBER: P982957

CATALOG NUMBER: S123IW-B1320UB50-4F0-XX-W2A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	613.5	622.2	635.8	646.9	644.4
115°	691.5	698.9	710.0	722.4	727.3
117.5°	768.1	776.8	783.0	792.9	794.1
120°	838.6	849.8	853.5	863.4	863.4
122.5°	910.4	919.1	924.0	930.2	931.4
125°	974.7	984.6	989.6	992.0	994.5
127.5°	1039.0	1048.9	1055.1	1058.8	1056.4
130°	1098.4	1108.3	1113.3	1118.2	1115.7
132.5°	1155.3	1165.2	1168.9	1173.9	1170.2
135°	1213.4	1220.9	1225.8	1229.5	1225.8
137.5°	1262.9	1272.8	1275.3	1281.5	1279.0
140°	1312.4	1319.8	1323.5	1328.5	1326.0
142.5°	1358.2	1365.6	1369.3	1373.0	1369.3
145°	1400.2	1408.9	1411.4	1413.8	1413.8
147.5°	1441.0	1447.2	1449.7	1452.2	1446.0
150°	1478.1	1481.9	1484.3	1486.8	1483.1
152.5°	1511.5	1512.8	1514.0	1519.0	1512.8
155°	1542.5	1540.0	1541.2	1547.4	1540.0
157.5°	1567.2	1567.2	1566.0	1573.4	1563.5
160°	1589.5	1588.2	1587.0	1594.4	1585.8
162.5°	1610.5	1606.8	1605.6	1614.2	1606.8
165°	1626.6	1622.9	1621.6	1631.5	1622.9
167.5°	1640.2	1635.2	1635.2	1645.1	1635.2
170°	1651.3	1646.4	1646.4	1656.3	1646.4
172.5°	1658.7	1652.6	1653.8	1663.7	1652.6
175°	1664.9	1658.7	1660.0	1668.6	1658.7
177.5°	1667.4	1661.2	1662.5	1672.3	1660.0
180°	1664.9	1664.9	1664.9	1664.9	1664.9



TEST NUMBER: P982957

CATALOG NUMBER: S123IW-B1320UB50-4F0-XX-W2A

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT