

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032898

Luminaire Tested: S124RDIW-B1195D1050UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032898
REPORT IS A COMBINATION OF REPORTS P1000058 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1195D1050UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8734.0 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032898

CATALOG NUMBER: S124RDIW-B1195D1050UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032898

CATALOG NUMBER: S124RDIW-B1195D1050UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	87	91	88	85	82	75	73	71	63	62	60	53	52	50
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	60	54	48	52	47	43	45	40	37	37	34	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	31	28
6	64	52	44	38	59	49	42	36	42	37	32	36	32	29	31	27	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	30	26	30	26	23	26	22	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	21	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16390	16390	16390
5°	16391	15903	15905
10°	16252	15401	15218
15°	16029	14776	14408
20°	15735	14064	13484
25°	15370	13295	12581
30°	15013	12511	11568
35°	14620	11716	10578
40°	14151	10860	9561
45°	13713	10012	8554
50°	13213	9085	7530
55°	12675	8135	6475
60°	12077	7126	5432
65°	11499	5969	4428
70°	10677	4752	3384
75°	9625	3457	2367
80°	8037	2121	1701
85°	6047	1222	935

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13713 cd/sqm

TEST NUMBER: P1032898

CATALOG NUMBER: S124RDIW-B1195D1050UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	2.2
10°-20°	527.0	6.0
20°-30°	760.8	8.7
30°-40°	862.2	9.9
40°-50°	832.5	9.5
50°-60°	692.1	7.9
60°-70°	477.7	5.5
70°-80°	241.4	2.8
80°-90°	64.0	0.7
90°-100°	43.8	0.5
100°-110°	288.8	3.3
110°-120°	551.4	6.3
120°-130°	700.0	8.0
130°-140°	748.8	8.6
140°-150°	700.2	8.0
150°-160°	564.7	6.5
160°-170°	364.2	4.2
170°-180°	125.5	1.4
0°-30°	1476.7	16.9
0°-40°	2339.0	26.8
0°-60°	3863.6	44.2
0°-90°	4646.7	53.2
90°-120°	884.0	10.1
90°-150°	3033.0	34.7
90°-180°	4087.0	46.8
0°-180°	8734.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2010	2010	2010	2010	2010	
5°	2007	2001	1982	1998	1994	190
15°	1911	1898	1859	1856	1845	539
25°	1728	1700	1637	1611	1596	796
35°	1494	1445	1368	1316	1288	934
45°	1219	1162	1070	994	966	940
55°	923	862	762	682	652	826
65°	628	562	463	397	379	620
75°	334	277	205	169	160	352
85°	83	52	48	45	45	91
90°	3	14	22	28	30	8
95°	54	21	22	28	29	67
105°	297	303	308	317	282	311
115°	555	558	557	559	559	546
125°	780	784	782	785	786	697
135°	968	967	971	973	975	746
145°	1116	1119	1119	1120	1122	698
155°	1224	1225	1222	1226	1223	564
165°	1291	1286	1286	1294	1285	365
175°	1321	1315	1316	1325	1313	126
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1032898

CATALOG NUMBER: S124RDIW-B1195D1050UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2009.9	2009.9	2009.9	2009.9	2009.9
2.5°	2016.0	2009.9	1992.9	2009.9	2008.3
5°	2006.8	2000.6	1982.2	1997.6	1994.5
7.5°	1992.9	1986.8	1963.7	1974.5	1969.8
10°	1971.4	1963.7	1936.0	1942.1	1936.0
12.5°	1943.7	1934.5	1900.6	1903.7	1894.4
15°	1911.4	1897.5	1859.0	1856.0	1845.2
17.5°	1874.4	1854.4	1809.8	1802.1	1786.7
20°	1829.8	1809.8	1757.5	1745.2	1725.2
22.5°	1780.6	1757.5	1700.5	1680.5	1665.1
25°	1728.2	1700.5	1637.4	1611.3	1595.9
27.5°	1674.4	1640.5	1574.3	1543.6	1522.0
30°	1617.4	1579.0	1506.6	1468.2	1443.5
32.5°	1557.4	1512.8	1437.4	1391.2	1368.1
35°	1494.3	1445.1	1368.1	1315.8	1288.1
37.5°	1428.1	1377.4	1292.7	1235.8	1208.1
40°	1357.3	1306.6	1218.8	1154.2	1126.5
42.5°	1289.6	1235.8	1143.4	1077.3	1048.0
45°	1218.8	1161.9	1069.6	994.2	966.5
47.5°	1146.5	1088.0	992.6	914.1	883.4
50°	1072.6	1012.6	914.1	837.2	807.9
52.5°	997.2	938.8	837.2	758.7	727.9
55°	923.4	861.8	761.8	681.8	652.5
57.5°	851.0	786.4	687.9	606.3	584.8
60°	772.6	711.0	612.5	532.5	507.9
62.5°	701.8	637.1	535.6	463.2	444.8
65°	627.9	561.7	463.2	397.0	378.6
67.5°	550.9	487.8	395.5	337.0	315.5
70°	478.6	414.0	326.3	275.5	260.1
72.5°	401.7	344.7	263.2	221.6	207.8
75°	334.0	277.0	204.7	169.3	160.1
77.5°	263.2	213.9	152.4	127.7	124.7
80°	195.4	150.8	104.6	100.0	98.5
82.5°	137.0	97.0	75.4	72.3	70.8
85°	83.1	52.3	47.7	44.6	44.6
87.5°	35.4	23.1	21.5	20.0	21.5
90°	3.0	13.8	21.7	27.7	29.6
92.5°	14.8	12.8	20.7	26.7	26.7
95°	54.3	20.7	21.7	27.7	28.7
97.5°	103.7	125.5	21.7	26.7	27.7
100°	162.0	179.8	43.5	26.7	27.7
102.5°	227.2	239.1	250.9	28.7	28.7
105°	297.4	303.3	308.2	317.1	281.6
107.5°	361.6	364.6	371.5	376.4	380.4
110°	426.8	429.8	435.7	437.7	440.6

TEST NUMBER: P1032898

CATALOG NUMBER: S124RDIW-B1195D1050UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.0	495.9	497.9	496.9	500.9
115°	555.2	558.2	557.2	559.2	559.2
117.5°	613.5	617.5	620.4	619.4	619.4
120°	672.8	676.7	675.8	677.7	675.8
122.5°	728.1	730.1	732.1	733.1	731.1
125°	780.5	784.4	782.5	785.4	786.4
127.5°	830.9	831.8	836.8	835.8	834.8
130°	879.3	880.3	883.2	884.2	884.2
132.5°	923.7	925.7	929.7	930.6	929.7
135°	968.2	967.2	971.1	973.1	975.1
137.5°	1007.7	1007.7	1012.6	1014.6	1013.6
140°	1046.2	1048.2	1050.2	1053.1	1054.1
142.5°	1080.8	1084.8	1085.8	1087.7	1087.7
145°	1116.4	1119.3	1119.3	1120.3	1122.3
147.5°	1144.0	1150.0	1149.0	1150.0	1151.0
150°	1174.7	1178.6	1177.6	1177.6	1178.6
152.5°	1200.4	1203.3	1201.3	1203.3	1202.3
155°	1224.1	1225.1	1222.1	1226.0	1223.1
157.5°	1244.8	1244.8	1240.9	1245.8	1240.9
160°	1262.6	1259.6	1258.6	1264.6	1258.6
162.5°	1278.4	1274.4	1273.5	1279.4	1272.5
165°	1291.2	1286.3	1286.3	1294.2	1285.3
167.5°	1302.1	1297.2	1296.2	1305.1	1295.2
170°	1311.0	1305.1	1306.1	1314.0	1304.1
172.5°	1316.9	1311.0	1312.0	1319.9	1309.0
175°	1320.9	1315.0	1315.9	1324.8	1313.0
177.5°	1323.8	1316.9	1318.9	1326.8	1315.0
180°	1320.9	1320.9	1320.9	1320.9	1320.9

(END OF REPORT)