

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032479

Luminaire Tested: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032479
REPORT IS A COMBINATION OF REPORTS P996694 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8880.0 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 88.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	86	90	87	83	80	73	71	69	61	59	58	50	49	47
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40
3	82	72	65	59	75	67	61	56	57	52	48	48	44	41	39	37	35
4	75	64	56	50	69	60	53	47	51	46	41	43	39	36	35	32	30
5	69	57	49	43	63	53	46	41	46	40	36	38	34	31	32	29	26
6	63	51	43	38	58	48	41	36	41	36	31	35	30	27	29	26	23
7	59	46	39	33	54	43	36	31	37	32	28	32	27	24	26	23	21
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13006	13006	13006	13006
5°	12973	14921	13048	11211
10°	12876	17407	12974	9836
15°	12721	20068	12810	8801
20°	12556	21760	12647	7890
25°	12316	21511	12434	7219
30°	12081	17780	12228	6873
35°	11751	13250	11880	6663
40°	11366	9981	11476	6560
45°	10778	8010	10912	6420
50°	10076	6749	10222	6355
55°	9250	5874	9396	6280
60°	8448	5172	8696	6175
65°	7695	4451	7769	5919
70°	6809	3662	6956	5450
75°	5939	2814	5902	4631
80°	4672	1848	4619	3515
85°	3078	830	2882	2050

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 16817 cd/sqm

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	1.7
10°-20°	479.1	5.4
20°-30°	761.1	8.6
30°-40°	845.7	9.5
40°-50°	769.1	8.7
50°-60°	628.5	7.1
60°-70°	448.6	5.1
70°-80°	246.9	2.8
80°-90°	70.1	0.8
90°-100°	105.1	1.2
100°-110°	314.9	3.5
110°-120°	535.0	6.0
120°-130°	705.6	7.9
130°-140°	792.5	8.9
140°-150°	778.9	8.8
150°-160°	655.1	7.4
160°-170°	435.9	4.9
170°-180°	152.6	1.7
0°-30°	1395.4	15.7
0°-40°	2241.2	25.2
0°-60°	3638.8	41.0
0°-90°	4404.4	49.6
90°-120°	955.1	10.8
90°-150°	3232.0	36.4
90°-180°	4476.0	50.4
0°-180°	8880.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1595	1595	1595	1595	1595	
5°	1588	1871	1598	1406	1588	151
15°	1517	2570	1528	1127	1517	428
25°	1385	2729	1398	916	1385	638
35°	1201	1613	1214	811	1201	750
45°	958	905	970	725	958	739
55°	674	592	684	633	674	606
65°	420	381	424	506	420	415
75°	206	190	205	313	206	216
85°	42	40	40	98	42	49
90°	4	37	4	37	4	8
95°	75	99	75	99	75	81
105°	291	304	291	304	291	308
115°	544	539	544	539	544	536
125°	792	786	792	786	792	706
135°	1022	1023	1022	1023	1022	790
145°	1241	1242	1241	1242	1241	777
155°	1422	1421	1422	1421	1422	654
165°	1548	1544	1548	1544	1548	437
175°	1610	1603	1610	1603	1610	153
180°	1613	1613	1613	1613	1613	

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1594.9	1610.8	1617.4	1622.6	1639.8	1645.1	1646.4	1654.4	1661.0	1662.3	1662.3
5°	1588.3	1613.4	1633.2	1651.7	1679.5	1691.4	1705.9	1721.7	1742.9	1756.1	1762.7
7.5°	1577.7	1614.7	1645.1	1676.8	1715.1	1738.9	1752.1	1794.4	1823.5	1847.3	1876.3
10°	1561.9	1609.4	1653.0	1699.3	1753.5	1782.5	1811.6	1863.1	1904.1	1950.3	1987.3
12.5°	1538.1	1600.2	1653.0	1717.8	1785.2	1819.5	1853.9	1943.7	1991.3	2032.3	2098.3
15°	1516.9	1579.0	1654.4	1720.4	1803.7	1855.2	1905.4	1963.6	2038.9	2127.4	2190.8
17.5°	1493.2	1571.1	1641.1	1733.6	1826.1	1875.0	1916.0	2005.8	2111.6	2198.8	2256.9
20°	1460.1	1539.4	1631.9	1729.7	1839.3	1877.7	1931.8	2052.1	2147.2	2233.1	2328.3
22.5°	1421.8	1514.3	1612.1	1705.9	1819.5	1900.1	1959.6	2065.3	2180.3	2279.4	2386.4
25°	1384.8	1485.2	1571.1	1699.3	1819.5	1873.7	1941.1	2066.6	2192.2	2312.4	2422.1
27.5°	1345.2	1439.0	1555.3	1657.0	1793.1	1852.6	1925.2	2062.7	2196.1	2316.4	2434.0
30°	1301.6	1402.0	1498.4	1618.7	1750.8	1827.5	1894.8	2044.2	2180.3	2305.8	2415.5
32.5°	1252.7	1347.8	1450.9	1564.5	1703.2	1781.2	1865.8	2019.1	2164.4	2272.8	2357.3
35°	1201.1	1297.6	1387.4	1503.7	1646.4	1724.4	1806.3	1975.5	2119.5	2208.0	2256.9
37.5°	1144.3	1235.5	1324.0	1439.0	1581.7	1664.9	1748.2	1912.0	2048.1	2122.1	2108.9
40°	1090.1	1172.1	1254.0	1362.3	1511.6	1600.2	1672.9	1838.0	1957.0	1988.7	1945.1
42.5°	1028.0	1098.1	1177.3	1288.3	1433.7	1516.9	1608.1	1758.7	1847.3	1834.1	1760.1
45°	958.0	1020.1	1099.4	1203.8	1351.8	1437.7	1514.3	1657.0	1721.7	1688.7	1553.9
47.5°	890.6	951.4	1016.1	1120.5	1264.6	1337.2	1415.2	1543.4	1580.4	1510.3	1375.5
50°	817.9	868.1	935.5	1034.6	1169.4	1246.1	1310.8	1413.9	1427.1	1341.2	1201.1
52.5°	747.9	790.2	854.9	952.7	1078.2	1139.0	1202.4	1293.6	1283.1	1194.5	1059.7
55°	673.9	713.5	773.0	862.9	973.9	1032.0	1086.2	1166.8	1144.3	1053.1	935.5
57.5°	611.8	639.5	697.7	780.9	872.1	935.5	981.8	1045.2	1010.8	919.7	810.0
60°	540.4	574.8	623.7	691.1	780.9	823.2	864.2	906.5	882.7	795.5	697.7
62.5°	475.7	502.1	544.4	609.2	679.2	717.5	761.1	787.5	763.8	683.1	601.2
65°	420.2	441.3	474.4	527.2	594.6	626.3	651.4	676.5	656.7	581.4	521.9
67.5°	359.4	377.9	405.7	447.9	504.8	527.2	551.0	568.2	545.7	495.5	437.4
70°	305.2	318.5	344.9	376.6	416.2	437.4	457.2	474.4	454.6	412.3	368.7
72.5°	249.7	260.3	284.1	306.6	342.2	356.8	371.3	384.5	377.9	338.3	302.6
75°	206.1	210.1	226.0	244.5	266.9	282.8	293.3	301.3	296.0	264.3	241.8
77.5°	155.9	161.2	173.1	187.6	207.5	216.7	223.3	231.2	224.6	199.5	183.7
80°	113.6	115.0	121.6	134.8	148.0	149.3	155.9	166.5	162.5	145.4	133.5
82.5°	72.7	76.6	79.3	87.2	96.5	99.1	103.1	105.7	104.4	93.8	89.9
85°	42.3	42.3	44.9	50.2	52.9	56.8	58.1	59.5	62.1	55.5	51.5
87.5°	18.5	19.8	19.8	21.1	23.8	23.8	25.1	26.4	27.7	26.4	22.5
90°	3.7	6.8	9.8	12.9	16.0	17.5	18.6	20.8	23.0	25.2	27.4
92.5°	32.4	36.0	39.6	43.3	46.9	48.7	49.4	50.8	52.1	53.5	54.9
95°	74.9	77.4	79.9	82.4	84.9	86.1	87.1	89.0	90.9	92.9	94.8
97.5°	119.8	122.0	124.2	126.4	128.6	129.7	130.8	133.0	135.3	137.5	139.7
100°	174.7	175.8	176.9	178.0	179.1	179.6	180.9	183.4	185.9	188.4	190.9
102.5°	232.0	232.3	232.6	232.9	233.2	233.3	234.4	236.6	238.9	241.1	243.3
105°	290.7	291.0	291.2	291.5	291.8	291.9	292.5	293.6	294.7	295.8	296.9
107.5°	351.8	352.1	352.3	352.6	352.9	353.0	353.1	353.4	353.7	354.0	354.3
110°	414.2	414.8	415.3	415.9	416.4	416.7	416.6	416.3	416.0	415.7	415.4



TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	479.0	479.0	479.0	479.0	479.0	479.0	478.7	478.2	477.6	477.1	476.5
115°	543.9	543.9	543.9	543.9	543.9	543.9	543.6	543.1	542.5	542.0	541.4
117.5°	605.0	605.0	605.0	605.0	605.0	605.0	604.9	604.6	604.3	604.1	603.8
120°	666.2	667.3	668.4	669.5	670.6	671.2	670.8	669.9	669.1	668.2	667.4
122.5°	729.8	730.1	730.3	730.6	730.9	731.0	730.9	730.6	730.3	730.1	729.8
125°	792.2	792.2	792.2	792.2	792.2	792.2	792.1	791.8	791.5	791.2	790.9
127.5°	848.3	849.1	849.9	850.8	851.6	852.0	851.7	851.2	850.7	850.1	849.6
130°	908.2	909.0	909.8	910.7	911.5	911.9	911.9	911.9	911.9	911.9	911.9
132.5°	969.3	969.9	970.4	971.0	971.5	971.8	971.7	971.4	971.1	970.9	970.6
135°	1021.7	1023.4	1025.0	1026.7	1028.4	1029.2	1029.2	1029.2	1029.2	1029.2	1029.2
137.5°	1080.3	1081.1	1082.0	1082.8	1083.7	1084.1	1084.4	1084.9	1085.5	1086.0	1086.6
140°	1139.0	1139.6	1140.1	1140.7	1141.2	1141.5	1141.5	1141.5	1141.5	1141.5	1141.5
142.5°	1192.6	1193.2	1193.7	1194.3	1194.8	1195.1	1195.0	1194.7	1194.4	1194.2	1193.9
145°	1241.3	1242.4	1243.5	1244.6	1245.7	1246.3	1246.4	1246.7	1247.0	1247.2	1247.5
147.5°	1291.2	1292.6	1294.0	1295.3	1296.7	1297.4	1297.3	1297.0	1296.7	1296.5	1296.2
150°	1336.1	1337.2	1338.3	1339.4	1340.5	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1
152.5°	1378.5	1379.1	1379.6	1380.2	1380.7	1381.0	1381.1	1381.4	1381.7	1381.9	1382.2
155°	1422.2	1422.2	1422.2	1422.2	1422.2	1422.2	1422.1	1421.8	1421.5	1421.2	1420.9
157.5°	1459.6	1459.0	1458.5	1457.9	1457.4	1457.1	1457.1	1457.1	1457.1	1457.1	1457.1
160°	1492.0	1491.7	1491.5	1491.2	1490.9	1490.8	1490.7	1490.4	1490.1	1489.8	1489.5
162.5°	1522.0	1521.2	1520.3	1519.5	1518.6	1518.2	1518.1	1517.8	1517.5	1517.3	1517.0
165°	1548.2	1547.4	1546.5	1545.7	1544.8	1544.4	1544.1	1543.6	1543.0	1542.5	1541.9
167.5°	1569.4	1568.3	1567.2	1566.1	1565.0	1564.4	1564.4	1564.4	1564.4	1564.4	1564.4
170°	1586.8	1585.4	1584.0	1582.7	1581.3	1580.6	1580.7	1581.0	1581.3	1581.5	1581.8
172.5°	1599.3	1598.2	1597.1	1596.0	1594.9	1594.3	1594.3	1594.3	1594.3	1594.3	1594.3
175°	1610.5	1609.1	1607.7	1606.4	1605.0	1604.3	1604.2	1603.9	1603.6	1603.3	1603.0
177.5°	1615.5	1614.1	1612.7	1611.4	1610.0	1609.3	1609.3	1609.3	1609.3	1609.3	1609.3
180°	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1666.2	1690.0	1700.6	1703.2	1717.8	1708.5	1712.5	1711.2	1721.7	1723.1	1723.1
5°	1787.8	1815.6	1824.8	1838.0	1857.8	1863.1	1859.2	1867.1	1881.6	1871.1	1886.9
7.5°	1916.0	1946.4	1967.5	1996.6	2003.2	2020.4	2030.9	2040.2	2042.8	2044.2	2046.8
10°	2034.9	2073.2	2102.3	2151.2	2161.8	2171.0	2217.3	2198.8	2222.5	2214.6	2217.3
12.5°	2131.4	2206.7	2230.5	2312.4	2320.3	2352.0	2349.4	2378.5	2383.8	2394.3	2383.8
15°	2258.2	2345.4	2383.8	2430.0	2456.4	2493.4	2500.0	2539.7	2555.5	2570.1	2555.5
17.5°	2374.5	2420.8	2518.5	2555.5	2572.7	2592.5	2642.7	2657.3	2681.1	2671.8	2698.2
20°	2432.6	2498.7	2601.8	2665.2	2691.6	2710.1	2752.4	2774.9	2784.1	2784.1	2786.8
22.5°	2484.2	2579.3	2656.0	2728.6	2752.4	2765.6	2790.7	2807.9	2811.9	2814.5	2817.2
25°	2530.4	2616.3	2678.4	2719.4	2728.6	2728.6	2743.2	2732.6	2715.4	2728.6	2736.6
27.5°	2530.4	2591.2	2619.0	2633.5	2633.5	2597.8	2576.7	2533.1	2496.1	2485.5	2509.3
30°	2488.1	2515.9	2477.6	2441.9	2414.1	2390.4	2307.1	2241.0	2227.8	2218.6	2254.3
32.5°	2390.4	2354.7	2279.4	2176.3	2135.3	2081.2	2016.4	1966.2	1935.8	1925.2	1917.3
35°	2217.3	2124.8	2027.0	1888.2	1859.2	1790.5	1701.9	1664.9	1614.7	1613.4	1630.6
37.5°	2028.3	1885.6	1779.9	1647.8	1606.8	1534.1	1450.9	1412.5	1378.2	1351.8	1383.5
40°	1807.6	1683.4	1522.2	1413.9	1355.7	1317.4	1247.4	1205.1	1189.2	1176.0	1195.8
42.5°	1601.5	1465.4	1339.9	1228.9	1181.3	1137.7	1091.5	1050.5	1038.6	1037.3	1051.8
45°	1396.7	1263.2	1147.0	1051.8	1021.4	995.0	950.1	938.2	918.4	905.1	911.7
47.5°	1232.8	1095.4	999.0	926.3	899.9	877.4	848.3	828.5	811.3	806.0	814.0
50°	1071.6	979.1	880.0	819.3	799.4	778.3	755.8	737.3	729.4	724.1	729.4
52.5°	942.1	843.0	775.6	726.8	706.9	691.1	675.2	667.3	656.7	659.4	664.7
55°	825.9	738.6	681.8	646.2	634.3	627.7	607.8	598.6	594.6	592.0	594.6
57.5°	716.2	652.8	610.5	580.1	564.2	560.3	544.4	544.4	540.4	536.5	537.8
60°	629.0	574.8	533.8	510.0	507.4	500.8	490.2	488.9	479.7	483.6	484.9
62.5°	540.4	496.8	469.1	454.6	445.3	442.7	436.1	434.7	430.8	432.1	429.4
65°	470.4	434.7	407.0	395.1	391.1	389.8	384.5	380.6	377.9	380.6	377.9
67.5°	400.4	376.6	355.4	343.6	338.3	336.9	333.0	330.3	331.7	327.7	330.3
70°	334.3	310.5	297.3	290.7	288.1	284.1	284.1	284.1	284.1	281.5	280.1
72.5°	281.5	257.7	248.4	244.5	241.8	240.5	236.5	237.8	236.5	235.2	240.5
75°	223.3	208.8	199.5	195.6	198.2	194.2	190.3	192.9	189.0	190.3	195.6
77.5°	169.1	162.5	157.2	154.6	152.0	149.3	149.3	146.7	146.7	146.7	146.7
80°	122.9	121.6	112.3	111.0	111.0	108.4	108.4	108.4	108.4	107.0	108.4
82.5°	81.9	80.6	78.0	76.6	74.0	75.3	75.3	72.7	72.7	71.4	72.7
85°	47.6	47.6	44.9	43.6	42.3	43.6	41.0	39.6	41.0	39.6	41.0
87.5°	22.5	19.8	21.1	19.8	17.2	18.5	15.9	17.2	15.9	14.5	17.2
90°	29.1	30.7	32.4	34.1	34.9	35.2	35.7	36.3	36.8	37.4	36.8
92.5°	55.7	56.5	57.4	58.2	58.6	58.7	59.0	59.3	59.6	59.9	59.6
95°	95.6	96.5	97.3	98.2	98.6	98.6	98.6	98.6	98.6	98.6	98.6
97.5°	140.8	141.9	143.0	144.1	144.7	144.7	144.7	144.7	144.7	144.7	144.7
100°	191.5	192.0	192.6	193.1	193.4	193.4	193.4	193.4	193.4	193.4	193.4
102.5°	244.1	244.9	245.8	246.6	247.0	247.1	247.4	247.7	248.0	248.3	248.0
105°	297.7	298.5	299.4	300.2	300.6	301.0	301.9	302.7	303.6	304.4	303.6
107.5°	355.4	356.5	357.6	358.7	359.3	359.2	358.9	358.6	358.3	358.0	358.3
110°	414.8	414.3	413.7	413.2	412.9	413.3	414.2	415.0	415.9	416.7	415.9

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	476.5	476.5	476.5	476.5	476.5	476.5	476.5	476.5	476.5	476.5	476.5
115°	541.1	540.9	540.6	540.3	540.2	540.1	539.8	539.5	539.2	538.9	539.2
117.5°	603.0	602.2	601.3	600.5	600.1	599.7	598.8	598.0	597.1	596.3	597.1
120°	666.0	664.6	663.3	661.9	661.2	661.5	662.0	662.6	663.1	663.7	663.1
122.5°	729.0	728.1	727.3	726.4	726.0	725.3	723.9	722.6	721.2	719.8	721.2
125°	790.3	789.8	789.2	788.7	788.4	788.1	787.6	787.0	786.5	785.9	786.5
127.5°	849.0	848.5	847.9	847.4	847.1	847.0	846.7	846.4	846.1	845.8	846.1
130°	911.3	910.8	910.2	909.7	909.4	908.8	907.7	906.6	905.5	904.4	905.5
132.5°	970.0	969.5	968.9	968.4	968.1	968.0	967.7	967.4	967.1	966.8	967.1
135°	1028.6	1028.1	1027.5	1027.0	1026.7	1026.3	1025.5	1024.6	1023.8	1023.0	1023.8
137.5°	1085.8	1084.9	1084.1	1083.2	1082.8	1082.9	1083.2	1083.5	1083.8	1084.1	1083.8
140°	1141.2	1140.9	1140.6	1140.3	1140.2	1140.1	1139.8	1139.5	1139.3	1139.0	1139.3
142.5°	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9
145°	1247.2	1247.0	1246.7	1246.4	1246.3	1245.9	1245.0	1244.2	1243.3	1242.5	1243.3
147.5°	1295.9	1295.6	1295.3	1295.0	1294.9	1294.8	1294.5	1294.2	1294.0	1293.7	1294.0
150°	1341.1	1341.1	1341.1	1341.1	1341.1	1341.0	1340.7	1340.4	1340.1	1339.8	1340.1
152.5°	1383.0	1383.9	1384.7	1385.6	1386.0	1385.6	1384.7	1383.9	1383.0	1382.2	1383.0
155°	1422.0	1423.1	1424.2	1425.3	1425.9	1425.3	1424.2	1423.1	1422.0	1420.9	1422.0
157.5°	1457.9	1458.7	1459.6	1460.4	1460.8	1460.4	1459.6	1458.7	1457.9	1457.1	1457.9
160°	1490.3	1491.2	1492.0	1492.9	1493.3	1492.6	1491.2	1489.8	1488.4	1487.0	1488.4
162.5°	1518.7	1520.3	1522.0	1523.7	1524.5	1523.8	1522.4	1521.0	1519.6	1518.2	1519.6
165°	1543.6	1545.2	1546.9	1548.6	1549.4	1548.8	1547.7	1546.6	1545.5	1544.4	1545.5
167.5°	1566.1	1567.7	1569.4	1571.1	1571.9	1571.1	1569.4	1567.7	1566.1	1564.4	1566.1
170°	1583.5	1585.1	1586.8	1588.5	1589.3	1588.3	1586.4	1584.5	1582.5	1580.6	1582.5
172.5°	1596.2	1598.2	1600.1	1602.0	1603.0	1602.0	1600.1	1598.2	1596.2	1594.3	1596.2
175°	1605.0	1606.9	1608.9	1610.8	1611.8	1610.8	1608.9	1606.9	1605.0	1603.0	1605.0
177.5°	1611.2	1613.2	1615.1	1617.0	1618.0	1616.9	1614.7	1612.4	1610.2	1608.0	1610.2
180°	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1720.4	1716.5	1711.2	1711.2	1704.6	1704.6	1694.0	1675.5	1659.6	1654.4	1657.0
5°	1867.1	1868.4	1860.5	1853.9	1842.0	1832.7	1815.6	1782.5	1772.0	1750.8	1736.3
7.5°	2034.9	2029.6	2015.1	2004.5	2001.9	1980.7	1943.7	1904.1	1872.4	1851.2	1820.9
10°	2223.9	2202.7	2181.6	2175.0	2159.1	2123.4	2081.2	2037.6	1994.0	1947.7	1896.2
12.5°	2382.4	2341.5	2340.1	2324.3	2293.9	2274.1	2223.9	2161.8	2086.4	2034.9	1976.8
15°	2552.9	2514.6	2482.9	2453.8	2439.3	2381.1	2338.8	2260.9	2171.0	2115.5	2075.9
17.5°	2674.5	2657.3	2603.1	2589.9	2570.1	2502.7	2435.3	2358.6	2280.7	2202.7	2095.7
20°	2772.2	2761.7	2726.0	2707.5	2675.8	2622.9	2541.0	2452.5	2362.6	2251.6	2151.2
22.5°	2814.5	2801.3	2772.2	2756.4	2736.6	2691.6	2621.6	2521.2	2403.6	2304.5	2197.4
25°	2731.3	2755.1	2747.1	2740.5	2732.6	2706.2	2653.3	2564.8	2449.8	2337.5	2204.0
27.5°	2543.6	2584.6	2624.2	2629.5	2642.7	2653.3	2632.2	2568.7	2472.3	2353.4	2206.7
30°	2291.3	2309.8	2390.4	2414.1	2432.6	2500.0	2539.7	2523.8	2449.8	2342.8	2208.0
32.5°	1967.5	2016.4	2098.3	2155.2	2205.4	2280.7	2383.8	2424.7	2398.3	2311.1	2177.6
35°	1661.0	1719.1	1814.2	1886.9	1937.1	2044.2	2165.7	2254.3	2287.3	2243.7	2124.8
37.5°	1409.9	1479.9	1564.5	1592.3	1650.4	1782.5	1950.3	2073.2	2153.8	2157.8	2065.3
40°	1220.9	1256.6	1324.0	1366.3	1423.1	1534.1	1698.0	1860.5	1982.1	2023.0	1974.1
42.5°	1061.1	1088.8	1139.0	1190.6	1242.1	1326.7	1477.3	1629.3	1793.1	1875.0	1873.7
45°	934.2	963.3	997.6	1039.9	1075.6	1166.8	1285.7	1441.6	1583.0	1709.9	1741.6
47.5°	823.2	848.3	890.6	909.1	932.9	1018.8	1121.8	1267.2	1413.9	1559.2	1596.2
50°	741.3	762.4	791.5	803.4	829.8	893.2	977.8	1095.4	1257.9	1391.4	1460.1
52.5°	667.3	683.1	705.6	714.9	733.4	780.9	857.6	950.1	1084.8	1222.3	1318.7
55°	603.9	614.4	630.3	640.9	654.1	696.4	753.2	836.4	952.7	1071.6	1165.4
57.5°	544.4	552.3	568.2	573.5	584.0	617.1	656.7	726.8	833.8	939.5	1030.7
60°	488.9	494.2	503.4	515.3	523.3	545.7	582.7	640.9	726.8	823.2	897.2
62.5°	436.1	444.0	446.6	451.9	458.5	479.7	508.7	551.0	626.3	705.6	783.6
65°	381.9	388.5	393.8	395.1	401.7	417.6	444.0	481.0	529.9	598.6	671.3
67.5°	331.7	335.6	338.3	343.6	350.2	358.1	379.2	407.0	451.9	507.4	565.5
70°	285.4	285.4	289.4	290.7	298.6	307.9	317.1	343.6	383.2	428.1	467.8
72.5°	235.2	241.8	240.5	247.1	245.8	252.4	264.3	281.5	310.5	346.2	384.5
75°	191.6	195.6	195.6	195.6	198.2	203.5	210.1	226.0	248.4	277.5	300.0
77.5°	149.3	152.0	152.0	152.0	153.3	158.6	165.2	175.7	191.6	208.8	222.0
80°	107.0	109.7	109.7	112.3	112.3	113.6	120.2	125.5	133.5	146.7	159.9
82.5°	72.7	74.0	76.6	76.6	75.3	78.0	79.3	84.6	92.5	95.1	104.4
85°	39.6	41.0	42.3	42.3	43.6	46.2	44.9	50.2	50.2	55.5	58.1
87.5°	15.9	18.5	18.5	17.2	18.5	18.5	18.5	21.1	22.5	23.8	22.5
90°	36.3	35.7	35.2	34.9	34.1	32.4	30.7	29.1	27.4	25.2	23.0
92.5°	59.3	59.0	58.7	58.6	58.2	57.4	56.5	55.7	54.9	53.5	52.1
95°	98.6	98.6	98.6	98.6	98.2	97.3	96.5	95.6	94.8	92.9	90.9
97.5°	144.7	144.7	144.7	144.7	144.1	143.0	141.9	140.8	139.7	137.5	135.3
100°	193.4	193.4	193.4	193.4	193.1	192.6	192.0	191.5	190.9	188.4	185.9
102.5°	247.7	247.4	247.1	247.0	246.6	245.8	244.9	244.1	243.3	241.1	238.9
105°	302.7	301.9	301.0	300.6	300.2	299.4	298.5	297.7	296.9	295.8	294.7
107.5°	358.6	358.9	359.2	359.3	358.7	357.6	356.5	355.4	354.3	354.0	353.7
110°	415.0	414.2	413.3	412.9	413.2	413.7	414.3	414.8	415.4	415.7	416.0

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	476.5	476.5	476.5	476.5	476.5	476.5	476.5	476.5	476.5	477.1	477.6
115°	539.5	539.8	540.1	540.2	540.3	540.6	540.9	541.1	541.4	542.0	542.5
117.5°	598.0	598.8	599.7	600.1	600.5	601.3	602.2	603.0	603.8	604.1	604.3
120°	662.6	662.0	661.5	661.2	661.9	663.3	664.6	666.0	667.4	668.2	669.1
122.5°	722.6	723.9	725.3	726.0	726.4	727.3	728.1	729.0	729.8	730.1	730.3
125°	787.0	787.6	788.1	788.4	788.7	789.2	789.8	790.3	790.9	791.2	791.5
127.5°	846.4	846.7	847.0	847.1	847.4	847.9	848.5	849.0	849.6	850.1	850.7
130°	906.6	907.7	908.8	909.4	909.7	910.2	910.8	911.3	911.9	911.9	911.9
132.5°	967.4	967.7	968.0	968.1	968.4	968.9	969.5	970.0	970.6	970.9	971.1
135°	1024.6	1025.5	1026.3	1026.7	1027.0	1027.5	1028.1	1028.6	1029.2	1029.2	1029.2
137.5°	1083.5	1083.2	1082.9	1082.8	1083.2	1084.1	1084.9	1085.8	1086.6	1086.0	1085.5
140°	1139.5	1139.8	1140.1	1140.2	1140.3	1140.6	1140.9	1141.2	1141.5	1141.5	1141.5
142.5°	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1194.2	1194.4
145°	1244.2	1245.0	1245.9	1246.3	1246.4	1246.7	1247.0	1247.2	1247.5	1247.2	1247.0
147.5°	1294.2	1294.5	1294.8	1294.9	1295.0	1295.3	1295.6	1295.9	1296.2	1296.5	1296.7
150°	1340.4	1340.7	1341.0	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1
152.5°	1383.9	1384.7	1385.6	1386.0	1385.6	1384.7	1383.9	1383.0	1382.2	1381.9	1381.7
155°	1423.1	1424.2	1425.3	1425.9	1425.3	1424.2	1423.1	1422.0	1420.9	1421.2	1421.5
157.5°	1458.7	1459.6	1460.4	1460.8	1460.4	1459.6	1458.7	1457.9	1457.1	1457.1	1457.1
160°	1489.8	1491.2	1492.6	1493.3	1492.9	1492.0	1491.2	1490.3	1489.5	1489.8	1490.1
162.5°	1521.0	1522.4	1523.8	1524.5	1523.7	1522.0	1520.3	1518.7	1517.0	1517.3	1517.5
165°	1546.6	1547.7	1548.8	1549.4	1548.6	1546.9	1545.2	1543.6	1541.9	1542.5	1543.0
167.5°	1567.7	1569.4	1571.1	1571.9	1571.1	1569.4	1567.7	1566.1	1564.4	1564.4	1564.4
170°	1584.5	1586.4	1588.3	1589.3	1588.5	1586.8	1585.1	1583.5	1581.8	1581.5	1581.3
172.5°	1598.2	1600.1	1602.0	1603.0	1602.0	1600.1	1598.2	1596.2	1594.3	1594.3	1594.3
175°	1606.9	1608.9	1610.8	1611.8	1610.8	1608.9	1606.9	1605.0	1603.0	1603.3	1603.6
177.5°	1612.4	1614.7	1616.9	1618.0	1617.0	1615.1	1613.2	1611.2	1609.3	1609.3	1609.3
180°	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1645.1	1639.8	1635.9	1635.9	1624.0	1612.1	1605.5	1602.8	1600.2	1589.6	1575.1
5°	1712.5	1695.3	1683.4	1671.5	1651.7	1630.6	1609.4	1597.5	1580.4	1556.6	1539.4
7.5°	1787.8	1746.9	1733.6	1719.1	1679.5	1643.8	1614.7	1589.6	1561.9	1531.5	1501.1
10°	1851.2	1807.6	1778.6	1753.5	1701.9	1654.4	1610.8	1573.8	1538.1	1498.4	1461.4
12.5°	1912.0	1849.9	1819.5	1782.5	1728.4	1659.6	1602.8	1556.6	1503.7	1462.8	1417.8
15°	1996.6	1892.2	1842.0	1818.2	1745.5	1664.9	1596.2	1527.5	1483.9	1421.8	1382.2
17.5°	2009.8	1925.2	1892.2	1831.4	1744.2	1653.0	1573.8	1505.0	1439.0	1383.5	1331.9
20°	2056.1	1945.1	1892.2	1853.9	1738.9	1646.4	1559.2	1470.7	1407.3	1347.8	1289.7
22.5°	2085.1	1959.6	1904.1	1843.3	1733.6	1622.6	1519.6	1442.9	1365.0	1304.2	1257.9
25°	2077.2	1951.7	1889.6	1832.7	1699.3	1588.3	1495.8	1398.0	1325.3	1259.3	1198.5
27.5°	2073.2	1931.8	1865.8	1802.4	1676.8	1560.5	1444.3	1365.0	1284.4	1207.7	1162.8
30°	2062.7	1906.7	1830.1	1761.4	1630.6	1509.0	1409.9	1317.4	1236.8	1166.8	1107.3
32.5°	2027.0	1864.5	1790.5	1716.5	1580.4	1458.8	1358.4	1272.5	1191.9	1119.2	1062.4
35°	1979.4	1814.2	1733.6	1655.7	1519.6	1396.7	1304.2	1214.3	1139.0	1069.0	1014.8
37.5°	1931.8	1756.1	1680.8	1590.9	1465.4	1337.2	1242.1	1161.5	1091.5	1018.8	959.3
40°	1863.1	1687.4	1604.1	1527.5	1380.8	1260.6	1173.4	1100.7	1032.0	963.3	913.1
42.5°	1769.3	1612.1	1526.2	1441.6	1304.2	1185.3	1100.7	1036.0	971.2	914.4	858.9
45°	1674.2	1520.9	1444.3	1368.9	1219.6	1107.3	1029.3	969.9	915.7	853.6	808.7
47.5°	1559.2	1429.7	1353.1	1279.1	1137.7	1025.4	954.0	898.5	848.3	796.8	754.5
50°	1441.6	1329.3	1259.3	1182.6	1047.8	946.1	876.1	829.8	788.9	740.0	705.6
52.5°	1314.8	1217.0	1157.5	1083.5	964.6	870.8	799.4	753.2	718.8	683.1	652.8
55°	1180.0	1108.6	1045.2	985.7	873.4	788.9	725.4	684.5	660.7	627.7	601.2
57.5°	1058.4	989.7	951.4	884.0	786.2	703.0	652.8	618.4	590.7	570.8	549.7
60°	931.6	876.1	833.8	784.9	699.0	629.0	576.1	556.3	527.2	512.7	503.4
62.5°	810.0	770.4	730.7	693.7	617.1	551.0	511.4	486.3	469.1	454.6	446.6
65°	695.0	658.0	630.3	597.3	533.8	481.0	444.0	424.2	407.0	403.0	393.8
67.5°	582.7	566.9	536.5	510.0	455.9	414.9	387.2	362.1	352.8	348.8	340.9
70°	487.6	469.1	445.3	422.8	381.9	346.2	321.1	311.8	298.6	297.3	288.1
72.5°	401.7	379.2	362.1	344.9	314.5	282.8	269.6	256.3	249.7	244.5	240.5
75°	318.5	302.6	290.7	276.2	249.7	228.6	210.1	204.8	200.8	199.5	196.9
77.5°	237.8	227.3	222.0	207.5	189.0	170.5	162.5	154.6	154.6	152.0	153.3
80°	169.1	162.5	155.9	148.0	132.1	124.2	117.6	112.3	109.7	108.4	109.7
82.5°	107.0	103.1	101.7	96.5	85.9	81.9	76.6	72.7	72.7	72.7	72.7
85°	59.5	59.5	59.5	51.5	47.6	43.6	41.0	39.6	39.6	39.6	41.0
87.5°	25.1	25.1	21.1	21.1	19.8	17.2	15.9	15.9	17.2	17.2	18.5
90°	20.8	18.6	17.5	16.0	12.9	9.8	6.8	3.7	6.8	9.8	12.9
92.5°	50.8	49.4	48.7	46.9	43.3	39.6	36.0	32.4	36.0	39.6	43.3
95°	89.0	87.1	86.1	84.9	82.4	79.9	77.4	74.9	77.4	79.9	82.4
97.5°	133.0	130.8	129.7	128.6	126.4	124.2	122.0	119.8	122.0	124.2	126.4
100°	183.4	180.9	179.6	179.1	178.0	176.9	175.8	174.7	175.8	176.9	178.0
102.5°	236.6	234.4	233.3	233.2	232.9	232.6	232.3	232.0	232.3	232.6	232.9
105°	293.6	292.5	291.9	291.8	291.5	291.2	291.0	290.7	291.0	291.2	291.5
107.5°	353.4	353.1	353.0	352.9	352.6	352.3	352.1	351.8	352.1	352.3	352.6
110°	416.3	416.6	416.7	416.4	415.9	415.3	414.8	414.2	414.8	415.3	415.9

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	478.2	478.7	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0
115°	543.1	543.6	543.9	543.9	543.9	543.9	543.9	543.9	543.9	543.9	543.9
117.5°	604.6	604.9	605.0	605.0	605.0	605.0	605.0	605.0	605.0	605.0	605.0
120°	669.9	670.8	671.2	670.6	669.5	668.4	667.3	666.2	667.3	668.4	669.5
122.5°	730.6	730.9	731.0	730.9	730.6	730.3	730.1	729.8	730.1	730.3	730.6
125°	791.8	792.1	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2	792.2
127.5°	851.2	851.7	852.0	851.6	850.8	849.9	849.1	848.3	849.1	849.9	850.8
130°	911.9	911.9	911.9	911.5	910.7	909.8	909.0	908.2	909.0	909.8	910.7
132.5°	971.4	971.7	971.8	971.5	971.0	970.4	969.9	969.3	969.9	970.4	971.0
135°	1029.2	1029.2	1029.2	1028.4	1026.7	1025.0	1023.4	1021.7	1023.4	1025.0	1026.7
137.5°	1084.9	1084.4	1084.1	1083.7	1082.8	1082.0	1081.1	1080.3	1081.1	1082.0	1082.8
140°	1141.5	1141.5	1141.5	1141.2	1140.7	1140.1	1139.6	1139.0	1139.6	1140.1	1140.7
142.5°	1194.7	1195.0	1195.1	1194.8	1194.3	1193.7	1193.2	1192.6	1193.2	1193.7	1194.3
145°	1246.7	1246.4	1246.3	1245.7	1244.6	1243.5	1242.4	1241.3	1242.4	1243.5	1244.6
147.5°	1297.0	1297.3	1297.4	1296.7	1295.3	1294.0	1292.6	1291.2	1292.6	1294.0	1295.3
150°	1341.1	1341.1	1341.1	1340.5	1339.4	1338.3	1337.2	1336.1	1337.2	1338.3	1339.4
152.5°	1381.4	1381.1	1381.0	1380.7	1380.2	1379.6	1379.1	1378.5	1379.1	1379.6	1380.2
155°	1421.8	1422.1	1422.2	1422.2	1422.2	1422.2	1422.2	1422.2	1422.2	1422.2	1422.2
157.5°	1457.1	1457.1	1457.1	1457.4	1457.9	1458.5	1459.0	1459.6	1459.0	1458.5	1457.9
160°	1490.4	1490.7	1490.8	1490.9	1491.2	1491.5	1491.7	1492.0	1491.7	1491.5	1491.2
162.5°	1517.8	1518.1	1518.2	1518.6	1519.5	1520.3	1521.2	1522.0	1521.2	1520.3	1519.5
165°	1543.6	1544.1	1544.4	1544.8	1545.7	1546.5	1547.4	1548.2	1547.4	1546.5	1545.7
167.5°	1564.4	1564.4	1564.4	1565.0	1566.1	1567.2	1568.3	1569.4	1568.3	1567.2	1566.1
170°	1581.0	1580.7	1580.6	1581.3	1582.7	1584.0	1585.4	1586.8	1585.4	1584.0	1582.7
172.5°	1594.3	1594.3	1594.3	1594.9	1596.0	1597.1	1598.2	1599.3	1598.2	1597.1	1596.0
175°	1603.9	1604.2	1604.3	1605.0	1606.4	1607.7	1609.1	1610.5	1609.1	1607.7	1606.4
177.5°	1609.3	1609.3	1609.3	1610.0	1611.4	1612.7	1614.1	1615.5	1614.1	1612.7	1611.4
180°	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1571.1	1565.8	1568.5	1555.3	1543.4	1526.2	1511.6	1509.0	1506.4	1514.3	1509.0
5°	1526.2	1519.6	1513.0	1497.1	1473.3	1458.8	1437.7	1436.3	1428.4	1416.5	1419.2
7.5°	1477.3	1473.3	1464.1	1439.0	1417.8	1392.7	1375.5	1361.0	1354.4	1343.8	1339.9
10°	1437.7	1423.1	1415.2	1387.4	1362.3	1335.9	1313.4	1302.9	1291.0	1281.7	1275.1
12.5°	1383.5	1379.5	1357.0	1334.6	1313.4	1283.1	1265.9	1235.5	1219.6	1227.6	1224.9
15°	1347.8	1329.3	1324.0	1292.3	1256.6	1236.8	1205.1	1185.3	1178.7	1166.8	1152.2
17.5°	1300.2	1288.3	1269.8	1240.8	1199.8	1172.1	1149.6	1131.1	1123.2	1107.3	1095.4
20°	1255.3	1235.5	1220.9	1194.5	1154.9	1119.2	1091.5	1079.6	1059.7	1046.5	1039.9
22.5°	1214.3	1199.8	1178.7	1139.0	1104.7	1070.3	1037.3	1020.1	1001.6	993.7	983.1
25°	1164.1	1140.3	1125.8	1082.2	1045.2	1017.5	987.1	964.6	954.0	940.8	938.2
27.5°	1115.2	1092.8	1075.6	1037.3	992.4	956.7	938.2	922.3	903.8	903.8	897.2
30°	1066.3	1050.5	1024.1	987.1	944.8	910.4	889.3	874.7	868.1	862.9	861.5
32.5°	1017.5	996.3	980.5	930.2	898.5	866.8	851.0	839.1	831.1	829.8	831.1
35°	967.2	943.5	927.6	882.7	851.0	821.9	815.3	804.7	800.8	799.4	806.0
37.5°	914.4	895.9	876.1	839.1	803.4	786.2	773.0	769.0	767.7	775.6	778.3
40°	865.5	849.6	831.1	791.5	765.1	746.6	740.0	736.0	741.3	749.2	753.2
42.5°	819.3	796.8	782.3	746.6	722.8	712.2	704.3	704.3	709.6	718.8	725.4
45°	770.4	753.2	738.6	706.9	685.8	673.9	672.6	673.9	680.5	687.1	695.0
47.5°	722.8	705.6	689.8	663.3	644.8	638.2	636.9	638.2	648.8	658.0	667.3
50°	679.2	660.7	646.2	621.0	606.5	598.6	599.9	606.5	614.4	627.7	639.5
52.5°	627.7	614.4	601.2	578.8	565.5	560.3	564.2	569.5	584.0	593.3	607.8
55°	577.4	565.5	555.0	537.8	527.2	523.3	525.9	533.8	545.7	561.6	578.8
57.5°	531.2	518.0	507.4	495.5	483.6	484.9	486.3	496.8	511.4	525.9	545.7
60°	479.7	471.7	462.5	447.9	442.7	442.7	446.6	458.5	471.7	495.5	512.7
62.5°	433.4	422.8	416.2	407.0	399.1	400.4	409.6	420.2	436.1	455.9	478.3
65°	385.8	373.9	368.7	360.7	358.1	359.4	366.0	381.9	399.1	416.2	437.4
67.5°	333.0	329.0	323.7	315.8	318.5	319.8	326.4	339.6	358.1	375.3	399.1
70°	288.1	280.1	278.8	272.2	272.2	276.2	289.4	298.6	315.8	334.3	359.4
72.5°	240.5	233.9	233.9	228.6	232.6	236.5	243.1	256.3	272.2	290.7	311.8
75°	191.6	189.0	191.6	189.0	189.0	195.6	203.5	214.1	231.2	251.1	268.2
77.5°	148.0	148.0	146.7	150.6	150.6	154.6	165.2	175.7	189.0	204.8	223.3
80°	108.4	108.4	108.4	112.3	116.3	116.3	122.9	136.1	148.0	158.6	175.7
82.5°	74.0	74.0	74.0	76.6	81.9	81.9	89.9	97.8	111.0	120.2	128.2
85°	44.9	44.9	43.6	46.2	47.6	51.5	58.1	63.4	70.0	78.0	85.9
87.5°	19.8	19.8	21.1	22.5	23.8	26.4	29.1	31.7	38.3	41.0	44.9
90°	16.0	17.5	18.6	20.8	23.0	25.2	27.4	29.1	30.7	32.4	34.1
92.5°	46.9	48.7	49.4	50.8	52.1	53.5	54.9	55.7	56.5	57.4	58.2
95°	84.9	86.1	87.1	89.0	90.9	92.9	94.8	95.6	96.5	97.3	98.2
97.5°	128.6	129.7	130.8	133.0	135.3	137.5	139.7	140.8	141.9	143.0	144.1
100°	179.1	179.6	180.9	183.4	185.9	188.4	190.9	191.5	192.0	192.6	193.1
102.5°	233.2	233.3	234.4	236.6	238.9	241.1	243.3	244.1	244.9	245.8	246.6
105°	291.8	291.9	292.5	293.6	294.7	295.8	296.9	297.7	298.5	299.4	300.2
107.5°	352.9	353.0	353.1	353.4	353.7	354.0	354.3	355.4	356.5	357.6	358.7
110°	416.4	416.7	416.6	416.3	416.0	415.7	415.4	414.8	414.3	413.7	413.2

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	479.0	479.0	478.7	478.2	477.6	477.1	476.5	476.5	476.5	476.5	476.5
115°	543.9	543.9	543.6	543.1	542.5	542.0	541.4	541.1	540.9	540.6	540.3
117.5°	605.0	605.0	604.9	604.6	604.3	604.1	603.8	603.0	602.2	601.3	600.5
120°	670.6	671.2	670.8	669.9	669.1	668.2	667.4	666.0	664.6	663.3	661.9
122.5°	730.9	731.0	730.9	730.6	730.3	730.1	729.8	729.0	728.1	727.3	726.4
125°	792.2	792.2	792.1	791.8	791.5	791.2	790.9	790.3	789.8	789.2	788.7
127.5°	851.6	852.0	851.7	851.2	850.7	850.1	849.6	849.0	848.5	847.9	847.4
130°	911.5	911.9	911.9	911.9	911.9	911.9	911.9	911.3	910.8	910.2	909.7
132.5°	971.5	971.8	971.7	971.4	971.1	970.9	970.6	970.0	969.5	968.9	968.4
135°	1028.4	1029.2	1029.2	1029.2	1029.2	1029.2	1029.2	1028.6	1028.1	1027.5	1027.0
137.5°	1083.7	1084.1	1084.4	1084.9	1085.5	1086.0	1086.6	1085.8	1084.9	1084.1	1083.2
140°	1141.2	1141.5	1141.5	1141.5	1141.5	1141.5	1141.5	1141.2	1140.9	1140.6	1140.3
142.5°	1194.8	1195.1	1195.0	1194.7	1194.4	1194.2	1193.9	1193.9	1193.9	1193.9	1193.9
145°	1245.7	1246.3	1246.4	1246.7	1247.0	1247.2	1247.5	1247.2	1247.0	1246.7	1246.4
147.5°	1296.7	1297.4	1297.3	1297.0	1296.7	1296.5	1296.2	1295.9	1295.6	1295.3	1295.0
150°	1340.5	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1
152.5°	1380.7	1381.0	1381.1	1381.4	1381.7	1381.9	1382.2	1383.0	1383.9	1384.7	1385.6
155°	1422.2	1422.2	1422.1	1421.8	1421.5	1421.2	1420.9	1422.0	1423.1	1424.2	1425.3
157.5°	1457.4	1457.1	1457.1	1457.1	1457.1	1457.1	1457.1	1457.9	1458.7	1459.6	1460.4
160°	1490.9	1490.8	1490.7	1490.4	1490.1	1489.8	1489.5	1490.3	1491.2	1492.0	1492.9
162.5°	1518.6	1518.2	1518.1	1517.8	1517.5	1517.3	1517.0	1518.7	1520.3	1522.0	1523.7
165°	1544.8	1544.4	1544.1	1543.6	1543.0	1542.5	1541.9	1543.6	1545.2	1546.9	1548.6
167.5°	1565.0	1564.4	1564.4	1564.4	1564.4	1564.4	1564.4	1566.1	1567.7	1569.4	1571.1
170°	1581.3	1580.6	1580.7	1581.0	1581.3	1581.5	1581.8	1583.5	1585.1	1586.8	1588.5
172.5°	1594.9	1594.3	1594.3	1594.3	1594.3	1594.3	1594.3	1596.2	1598.2	1600.1	1602.0
175°	1605.0	1604.3	1604.2	1603.9	1603.6	1603.3	1603.0	1605.0	1606.9	1608.9	1610.8
177.5°	1610.0	1609.3	1609.3	1609.3	1609.3	1609.3	1609.3	1611.2	1613.2	1615.1	1617.0
180°	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1505.0	1503.7	1497.1	1499.8	1491.8	1494.5	1498.4	1499.8	1505.0	1501.1	1499.8
5°	1412.5	1409.9	1405.9	1402.0	1400.7	1405.9	1396.7	1399.3	1402.0	1405.9	1411.2
7.5°	1337.2	1335.9	1331.9	1325.3	1322.7	1320.1	1321.4	1330.6	1329.3	1328.0	1337.2
10°	1268.5	1269.8	1261.9	1260.6	1252.7	1251.3	1252.7	1255.3	1259.3	1264.6	1265.9
12.5°	1197.2	1214.3	1199.8	1194.5	1182.6	1189.2	1191.9	1180.0	1186.6	1190.6	1210.4
15°	1152.2	1144.3	1135.1	1135.1	1129.8	1127.1	1120.5	1129.8	1135.1	1143.0	1140.3
17.5°	1090.1	1076.9	1071.6	1066.3	1067.7	1073.0	1058.4	1079.6	1079.6	1083.5	1076.9
20°	1036.0	1025.4	1018.8	1016.1	1012.2	1009.5	1008.2	1013.5	1021.4	1024.1	1030.7
22.5°	979.1	979.1	968.6	964.6	962.0	958.0	964.6	960.6	965.9	971.2	981.8
25°	931.6	931.6	927.6	922.3	918.4	915.7	919.7	918.4	922.3	928.9	931.6
27.5°	893.2	889.3	888.0	886.6	885.3	886.6	885.3	889.3	893.2	894.6	891.9
30°	860.2	856.2	857.6	857.6	858.9	857.6	856.2	860.2	861.5	858.9	860.2
32.5°	829.8	829.8	832.5	833.8	833.8	835.1	836.4	833.8	835.1	831.1	832.5
35°	804.7	807.4	810.0	811.3	812.6	811.3	814.0	812.6	810.0	807.4	806.0
37.5°	779.6	782.3	787.5	788.9	792.8	794.1	791.5	791.5	790.2	784.9	782.3
40°	753.2	755.8	762.4	766.4	769.0	773.0	770.4	770.4	765.1	759.8	755.8
42.5°	728.1	733.4	740.0	743.9	749.2	749.2	749.2	746.6	740.0	734.7	730.7
45°	703.0	704.3	713.5	720.1	725.4	725.4	725.4	721.5	717.5	706.9	701.6
47.5°	675.2	679.2	689.8	696.4	701.6	703.0	703.0	699.0	691.1	681.8	675.2
50°	644.8	651.4	663.3	672.6	679.2	681.8	677.9	675.2	666.0	655.4	647.5
52.5°	615.8	623.7	638.2	646.2	655.4	656.7	655.4	651.4	640.9	626.3	619.7
55°	586.7	593.3	609.2	622.4	630.3	632.9	630.3	623.7	610.5	595.9	589.3
57.5°	555.0	564.2	581.4	594.6	603.9	605.2	602.5	595.9	585.4	566.9	557.6
60°	521.9	533.8	551.0	564.2	576.1	577.4	574.8	565.5	552.3	533.8	525.9
62.5°	488.9	498.2	518.0	532.5	541.8	548.4	543.1	533.8	520.6	502.1	490.2
65°	450.6	463.8	481.0	494.2	504.8	506.1	503.4	495.5	481.0	461.2	451.9
67.5°	413.6	422.8	440.0	457.2	461.2	465.1	461.2	453.2	441.3	424.2	410.9
70°	368.7	376.6	397.7	409.6	414.9	418.9	416.2	408.3	397.7	381.9	371.3
72.5°	323.7	330.3	350.2	359.4	370.0	368.7	367.3	362.1	347.5	336.9	330.3
75°	276.2	284.1	297.3	309.2	313.2	313.2	313.2	309.2	300.0	282.8	276.2
77.5°	232.6	236.5	247.1	253.7	257.7	259.0	257.7	251.1	245.8	233.9	229.9
80°	178.4	189.0	196.9	198.2	203.5	203.5	203.5	200.8	195.6	183.7	182.3
82.5°	134.8	137.4	145.4	149.3	152.0	150.6	150.6	145.4	144.0	137.4	134.8
85°	91.2	95.1	93.8	99.1	100.4	97.8	97.8	100.4	93.8	95.1	91.2
87.5°	50.2	50.2	52.9	51.5	56.8	56.8	54.2	55.5	52.9	51.5	50.2
90°	34.9	35.2	35.7	36.3	36.8	37.4	36.8	36.3	35.7	35.2	34.9
92.5°	58.6	58.7	59.0	59.3	59.6	59.9	59.6	59.3	59.0	58.7	58.6
95°	98.6	98.6	98.6	98.6	98.6	98.6	98.6	98.6	98.6	98.6	98.6
97.5°	144.7	144.7	144.7	144.7	144.7	144.7	144.7	144.7	144.7	144.7	144.7
100°	193.4	193.4	193.4	193.4	193.4	193.4	193.4	193.4	193.4	193.4	193.4
102.5°	247.0	247.1	247.4	247.7	248.0	248.3	248.0	247.7	247.4	247.1	247.0
105°	300.6	301.0	301.9	302.7	303.6	304.4	303.6	302.7	301.9	301.0	300.6
107.5°	359.3	359.2	358.9	358.6	358.3	358.0	358.3	358.6	358.9	359.2	359.3
110°	412.9	413.3	414.2	415.0	415.9	416.7	415.9	415.0	414.2	413.3	412.9

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	476.5	476.5	476.5	476.5	476.5	476.5	476.5	476.5	476.5	476.5	476.5
115°	540.2	540.1	539.8	539.5	539.2	538.9	539.2	539.5	539.8	540.1	540.2
117.5°	600.1	599.7	598.8	598.0	597.1	596.3	597.1	598.0	598.8	599.7	600.1
120°	661.2	661.5	662.0	662.6	663.1	663.7	663.1	662.6	662.0	661.5	661.2
122.5°	726.0	725.3	723.9	722.6	721.2	719.8	721.2	722.6	723.9	725.3	726.0
125°	788.4	788.1	787.6	787.0	786.5	785.9	786.5	787.0	787.6	788.1	788.4
127.5°	847.1	847.0	846.7	846.4	846.1	845.8	846.1	846.4	846.7	847.0	847.1
130°	909.4	908.8	907.7	906.6	905.5	904.4	905.5	906.6	907.7	908.8	909.4
132.5°	968.1	968.0	967.7	967.4	967.1	966.8	967.1	967.4	967.7	968.0	968.1
135°	1026.7	1026.3	1025.5	1024.6	1023.8	1023.0	1023.8	1024.6	1025.5	1026.3	1026.7
137.5°	1082.8	1082.9	1083.2	1083.5	1083.8	1084.1	1083.8	1083.5	1083.2	1082.9	1082.8
140°	1140.2	1140.1	1139.8	1139.5	1139.3	1139.0	1139.3	1139.5	1139.8	1140.1	1140.2
142.5°	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9	1193.9
145°	1246.3	1245.9	1245.0	1244.2	1243.3	1242.5	1243.3	1244.2	1245.0	1245.9	1246.3
147.5°	1294.9	1294.8	1294.5	1294.2	1294.0	1293.7	1294.0	1294.2	1294.5	1294.8	1294.9
150°	1341.1	1341.0	1340.7	1340.4	1340.1	1339.8	1340.1	1340.4	1340.7	1341.0	1341.1
152.5°	1386.0	1385.6	1384.7	1383.9	1383.0	1382.2	1383.0	1383.9	1384.7	1385.6	1386.0
155°	1425.9	1425.3	1424.2	1423.1	1422.0	1420.9	1422.0	1423.1	1424.2	1425.3	1425.9
157.5°	1460.8	1460.4	1459.6	1458.7	1457.9	1457.1	1457.9	1458.7	1459.6	1460.4	1460.8
160°	1493.3	1492.6	1491.2	1489.8	1488.4	1487.0	1488.4	1489.8	1491.2	1492.6	1493.3
162.5°	1524.5	1523.8	1522.4	1521.0	1519.6	1518.2	1519.6	1521.0	1522.4	1523.8	1524.5
165°	1549.4	1548.8	1547.7	1546.6	1545.5	1544.4	1545.5	1546.6	1547.7	1548.8	1549.4
167.5°	1571.9	1571.1	1569.4	1567.7	1566.1	1564.4	1566.1	1567.7	1569.4	1571.1	1571.9
170°	1589.3	1588.3	1586.4	1584.5	1582.5	1580.6	1582.5	1584.5	1586.4	1588.3	1589.3
172.5°	1603.0	1602.0	1600.1	1598.2	1596.2	1594.3	1596.2	1598.2	1600.1	1602.0	1603.0
175°	1611.8	1610.8	1608.9	1606.9	1605.0	1603.0	1605.0	1606.9	1608.9	1610.8	1611.8
177.5°	1618.0	1616.9	1614.7	1612.4	1610.2	1608.0	1610.2	1612.4	1614.7	1616.9	1618.0
180°	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
2.5°	1499.8	1507.7	1499.8	1505.0	1507.7	1514.3	1516.9	1528.8	1532.8	1542.0	1542.0
5°	1409.9	1413.9	1415.2	1420.5	1425.8	1439.0	1448.2	1465.4	1485.2	1487.9	1499.8
7.5°	1337.2	1343.8	1354.4	1350.4	1359.7	1379.5	1391.4	1412.5	1432.4	1442.9	1457.5
10°	1272.5	1280.4	1284.4	1288.3	1305.5	1322.7	1341.2	1355.7	1382.2	1398.0	1409.9
12.5°	1219.6	1213.0	1220.9	1235.5	1255.3	1265.9	1291.0	1313.4	1333.3	1350.4	1361.0
15°	1150.9	1156.2	1164.1	1189.2	1194.5	1220.9	1230.2	1255.3	1292.3	1308.2	1321.4
17.5°	1084.8	1102.0	1117.9	1127.1	1143.0	1164.1	1190.6	1218.3	1242.1	1260.6	1276.4
20°	1032.0	1049.2	1058.4	1065.0	1080.9	1110.0	1135.1	1169.4	1199.8	1214.3	1235.5
22.5°	989.7	989.7	1002.9	1022.7	1032.0	1059.7	1080.9	1117.9	1150.9	1169.4	1189.2
25°	936.9	944.8	955.4	972.5	985.7	1008.2	1038.6	1070.3	1106.0	1121.8	1147.0
27.5°	893.2	902.5	917.0	921.0	934.2	954.0	985.7	1020.1	1057.1	1074.3	1095.4
30°	860.2	865.5	870.8	878.7	890.6	907.8	934.2	964.6	1009.5	1022.7	1049.2
32.5°	831.1	833.8	836.4	843.0	849.6	866.8	888.0	921.0	958.0	977.8	1001.6
35°	804.7	802.1	803.4	807.4	814.0	820.6	843.0	870.8	905.1	928.9	947.4
37.5°	779.6	774.3	773.0	773.0	775.6	783.6	800.8	824.5	861.5	881.4	899.9
40°	751.9	746.6	743.9	742.6	741.3	746.6	759.8	783.6	812.6	831.1	852.3
42.5°	725.4	720.1	713.5	712.2	709.6	712.2	721.5	743.9	769.0	787.5	804.7
45°	699.0	689.8	681.8	676.5	677.9	673.9	680.5	697.7	726.8	738.6	755.8
47.5°	669.9	659.4	648.8	643.5	638.2	640.9	643.5	658.0	683.1	695.0	712.2
50°	642.2	627.7	615.8	609.2	605.2	602.5	605.2	619.7	638.2	648.8	663.3
52.5°	610.5	595.9	584.0	573.5	568.2	564.2	565.5	578.8	595.9	606.5	621.0
55°	581.4	562.9	547.0	533.8	529.9	528.5	527.2	536.5	551.0	561.6	573.5
57.5°	548.4	529.9	512.7	496.8	488.9	487.6	487.6	490.2	508.7	516.7	523.3
60°	515.3	495.5	477.0	462.5	450.6	446.6	445.3	450.6	459.8	467.8	477.0
62.5°	478.3	458.5	436.1	422.8	410.9	400.4	404.3	405.7	418.9	422.8	430.8
65°	442.7	420.2	401.7	380.6	367.3	360.7	358.1	360.7	371.3	372.6	377.9
67.5°	401.7	380.6	358.1	343.6	331.7	319.8	317.1	317.1	322.4	326.4	333.0
70°	362.1	340.9	315.8	300.0	288.1	277.5	273.5	272.2	276.2	278.8	285.4
72.5°	315.8	294.7	276.2	259.0	244.5	236.5	232.6	229.9	233.9	236.5	237.8
75°	266.9	249.7	231.2	214.1	204.8	196.9	191.6	187.6	190.3	190.3	190.3
77.5°	220.7	203.5	189.0	177.1	165.2	155.9	152.0	148.0	149.3	149.3	152.0
80°	171.8	159.9	148.0	137.4	126.9	118.9	116.3	112.3	109.7	108.4	108.4
82.5°	126.9	117.6	107.0	97.8	92.5	84.6	81.9	76.6	76.6	75.3	75.3
85°	84.6	79.3	68.7	62.1	58.1	54.2	51.5	48.9	44.9	44.9	43.6
87.5°	44.9	42.3	39.6	31.7	31.7	27.7	26.4	25.1	21.1	22.5	22.5
90°	34.1	32.4	30.7	29.1	27.4	25.2	23.0	20.8	18.6	17.5	16.0
92.5°	58.2	57.4	56.5	55.7	54.9	53.5	52.1	50.8	49.4	48.7	46.9
95°	98.2	97.3	96.5	95.6	94.8	92.9	90.9	89.0	87.1	86.1	84.9
97.5°	144.1	143.0	141.9	140.8	139.7	137.5	135.3	133.0	130.8	129.7	128.6
100°	193.1	192.6	192.0	191.5	190.9	188.4	185.9	183.4	180.9	179.6	179.1
102.5°	246.6	245.8	244.9	244.1	243.3	241.1	238.9	236.6	234.4	233.3	233.2
105°	300.2	299.4	298.5	297.7	296.9	295.8	294.7	293.6	292.5	291.9	291.8
107.5°	358.7	357.6	356.5	355.4	354.3	354.0	353.7	353.4	353.1	353.0	352.9
110°	413.2	413.7	414.3	414.8	415.4	415.7	416.0	416.3	416.6	416.7	416.4

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	476.5	476.5	476.5	476.5	476.5	477.1	477.6	478.2	478.7	479.0	479.0
115°	540.3	540.6	540.9	541.1	541.4	542.0	542.5	543.1	543.6	543.9	543.9
117.5°	600.5	601.3	602.2	603.0	603.8	604.1	604.3	604.6	604.9	605.0	605.0
120°	661.9	663.3	664.6	666.0	667.4	668.2	669.1	669.9	670.8	671.2	670.6
122.5°	726.4	727.3	728.1	729.0	729.8	730.1	730.3	730.6	730.9	731.0	730.9
125°	788.7	789.2	789.8	790.3	790.9	791.2	791.5	791.8	792.1	792.2	792.2
127.5°	847.4	847.9	848.5	849.0	849.6	850.1	850.7	851.2	851.7	852.0	851.6
130°	909.7	910.2	910.8	911.3	911.9	911.9	911.9	911.9	911.9	911.9	911.5
132.5°	968.4	968.9	969.5	970.0	970.6	970.9	971.1	971.4	971.7	971.8	971.5
135°	1027.0	1027.5	1028.1	1028.6	1029.2	1029.2	1029.2	1029.2	1029.2	1029.2	1028.4
137.5°	1083.2	1084.1	1084.9	1085.8	1086.6	1086.0	1085.5	1084.9	1084.4	1084.1	1083.7
140°	1140.3	1140.6	1140.9	1141.2	1141.5	1141.5	1141.5	1141.5	1141.5	1141.5	1141.2
142.5°	1193.9	1193.9	1193.9	1193.9	1193.9	1194.2	1194.4	1194.7	1195.0	1195.1	1194.8
145°	1246.4	1246.7	1247.0	1247.2	1247.5	1247.2	1247.0	1246.7	1246.4	1246.3	1245.7
147.5°	1295.0	1295.3	1295.6	1295.9	1296.2	1296.5	1296.7	1297.0	1297.3	1297.4	1296.7
150°	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1341.1	1340.5
152.5°	1385.6	1384.7	1383.9	1383.0	1382.2	1381.9	1381.7	1381.4	1381.1	1381.0	1380.7
155°	1425.3	1424.2	1423.1	1422.0	1420.9	1421.2	1421.5	1421.8	1422.1	1422.2	1422.2
157.5°	1460.4	1459.6	1458.7	1457.9	1457.1	1457.1	1457.1	1457.1	1457.1	1457.1	1457.4
160°	1492.9	1492.0	1491.2	1490.3	1489.5	1489.8	1490.1	1490.4	1490.7	1490.8	1490.9
162.5°	1523.7	1522.0	1520.3	1518.7	1517.0	1517.3	1517.5	1517.8	1518.1	1518.2	1518.6
165°	1548.6	1546.9	1545.2	1543.6	1541.9	1542.5	1543.0	1543.6	1544.1	1544.4	1544.8
167.5°	1571.1	1569.4	1567.7	1566.1	1564.4	1564.4	1564.4	1564.4	1564.4	1564.4	1565.0
170°	1588.5	1586.8	1585.1	1583.5	1581.8	1581.5	1581.3	1581.0	1580.7	1580.6	1581.3
172.5°	1602.0	1600.1	1598.2	1596.2	1594.3	1594.3	1594.3	1594.3	1594.3	1594.3	1594.9
175°	1610.8	1608.9	1606.9	1605.0	1603.0	1603.3	1603.6	1603.9	1604.2	1604.3	1605.0
177.5°	1617.0	1615.1	1613.2	1611.2	1609.3	1609.3	1609.3	1609.3	1609.3	1609.3	1610.0
180°	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0	1613.0

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1594.9	1594.9	1594.9	1594.9
2.5°	1551.3	1564.5	1576.4	1594.9
5°	1516.9	1535.4	1560.5	1588.3
7.5°	1477.3	1506.4	1539.4	1577.7
10°	1440.3	1473.3	1515.6	1561.9
12.5°	1402.0	1441.6	1487.9	1538.1
15°	1358.4	1398.0	1449.5	1516.9
17.5°	1318.7	1366.3	1421.8	1493.2
20°	1272.5	1317.4	1378.2	1460.1
22.5°	1231.5	1283.1	1350.4	1421.8
25°	1186.6	1231.5	1298.9	1384.8
27.5°	1141.7	1197.2	1261.9	1345.2
30°	1098.1	1144.3	1214.3	1301.6
32.5°	1050.5	1106.0	1170.7	1252.7
35°	999.0	1051.8	1112.6	1201.1
37.5°	952.7	1004.2	1066.3	1144.3
40°	901.2	955.4	1012.2	1090.1
42.5°	851.0	899.9	956.7	1028.0
45°	802.1	844.4	895.9	958.0
47.5°	751.9	787.5	835.1	890.6
50°	697.7	736.0	771.7	817.9
52.5°	647.5	680.5	709.6	747.9
55°	598.6	621.0	644.8	673.9
57.5°	547.0	564.2	581.4	611.8
60°	495.5	511.4	520.6	540.4
62.5°	445.3	451.9	463.8	475.7
65°	389.8	399.1	405.7	420.2
67.5°	339.6	343.6	350.2	359.4
70°	286.7	296.0	298.6	305.2
72.5°	241.8	245.8	248.4	249.7
75°	191.6	195.6	198.2	206.1
77.5°	150.6	149.3	154.6	155.9
80°	111.0	107.0	108.4	113.6
82.5°	72.7	74.0	72.7	72.7
85°	44.9	43.6	41.0	42.3
87.5°	19.8	19.8	18.5	18.5
90°	12.9	9.8	6.8	3.7
92.5°	43.3	39.6	36.0	32.4
95°	82.4	79.9	77.4	74.9
97.5°	126.4	124.2	122.0	119.8
100°	178.0	176.9	175.8	174.7
102.5°	232.9	232.6	232.3	232.0
105°	291.5	291.2	291.0	290.7
107.5°	352.6	352.3	352.1	351.8
110°	415.9	415.3	414.8	414.2

TEST NUMBER: P1032479

CATALOG NUMBER: S124DIW-B1020D1340UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	479.0	479.0	479.0	479.0
115°	543.9	543.9	543.9	543.9
117.5°	605.0	605.0	605.0	605.0
120°	669.5	668.4	667.3	666.2
122.5°	730.6	730.3	730.1	729.8
125°	792.2	792.2	792.2	792.2
127.5°	850.8	849.9	849.1	848.3
130°	910.7	909.8	909.0	908.2
132.5°	971.0	970.4	969.9	969.3
135°	1026.7	1025.0	1023.4	1021.7
137.5°	1082.8	1082.0	1081.1	1080.3
140°	1140.7	1140.1	1139.6	1139.0
142.5°	1194.3	1193.7	1193.2	1192.6
145°	1244.6	1243.5	1242.4	1241.3
147.5°	1295.3	1294.0	1292.6	1291.2
150°	1339.4	1338.3	1337.2	1336.1
152.5°	1380.2	1379.6	1379.1	1378.5
155°	1422.2	1422.2	1422.2	1422.2
157.5°	1457.9	1458.5	1459.0	1459.6
160°	1491.2	1491.5	1491.7	1492.0
162.5°	1519.5	1520.3	1521.2	1522.0
165°	1545.7	1546.5	1547.4	1548.2
167.5°	1566.1	1567.2	1568.3	1569.4
170°	1582.7	1584.0	1585.4	1586.8
172.5°	1596.0	1597.1	1598.2	1599.3
175°	1606.4	1607.7	1609.1	1610.5
177.5°	1611.4	1612.7	1614.1	1615.5
180°	1613.0	1613.0	1613.0	1613.0

(END OF REPORT)