

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032918

Luminaire Tested: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032918
REPORT IS A COMBINATION OF REPORTS P1000146 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10735.0 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032918

CATALOG NUMBER: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032918

CATALOG NUMBER: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	28	26	24
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16390	16390	16390
5°	16391	15903	15905
10°	16252	15401	15218
15°	16029	14776	14408
20°	15735	14064	13484
25°	15370	13295	12581
30°	15013	12511	11568
35°	14620	11716	10578
40°	14151	10860	9561
45°	13713	10012	8554
50°	13213	9085	7530
55°	12675	8135	6475
60°	12077	7126	5432
65°	11499	5969	4428
70°	10677	4752	3384
75°	9625	3457	2367
80°	8037	2121	1701
85°	6047	1222	935

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13713 cd/sqm

TEST NUMBER: P1032918

CATALOG NUMBER: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	1.8
10°-20°	527.0	4.9
20°-30°	760.8	7.1
30°-40°	862.2	8.0
40°-50°	832.5	7.8
50°-60°	692.1	6.4
60°-70°	477.7	4.5
70°-80°	241.4	2.2
80°-90°	65.3	0.6
90°-100°	65.3	0.6
100°-110°	430.0	4.0
110°-120°	821.2	7.6
120°-130°	1042.4	9.7
130°-140°	1115.2	10.4
140°-150°	1042.8	9.7
150°-160°	840.9	7.8
160°-170°	542.3	5.1
170°-180°	186.9	1.7
0°-30°	1476.7	13.8
0°-40°	2339.0	21.8
0°-60°	3863.6	36.0
0°-90°	4648.1	43.3
90°-120°	1316.5	12.3
90°-150°	4516.8	42.1
90°-180°	6087.0	56.7
0°-180°	10735.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2010	2010	2010	2010	2010	
5°	2007	2001	1982	1998	1994	190
15°	1911	1898	1859	1856	1845	539
25°	1728	1700	1637	1611	1596	796
35°	1494	1445	1368	1316	1288	934
45°	1219	1162	1070	994	966	940
55°	923	862	762	682	652	826
65°	628	562	463	397	379	620
75°	334	277	205	169	160	352
85°	83	52	48	45	45	91
90°	4	21	32	41	44	9
95°	81	31	32	41	43	100
105°	443	452	459	472	419	463
115°	827	831	830	833	833	814
125°	1162	1168	1165	1170	1171	1038
135°	1442	1440	1446	1449	1452	1111
145°	1663	1667	1667	1668	1671	1039
155°	1823	1824	1820	1826	1822	841
165°	1923	1916	1916	1927	1914	543
175°	1967	1958	1960	1973	1955	187
180°	1967	1967	1967	1967	1967	

TEST NUMBER: P1032918

CATALOG NUMBER: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2009.9	2009.9	2009.9	2009.9	2009.9
2.5°	2016.0	2009.9	1992.9	2009.9	2008.3
5°	2006.8	2000.6	1982.2	1997.6	1994.5
7.5°	1992.9	1986.8	1963.7	1974.5	1969.8
10°	1971.4	1963.7	1936.0	1942.1	1936.0
12.5°	1943.7	1934.5	1900.6	1903.7	1894.4
15°	1911.4	1897.5	1859.0	1856.0	1845.2
17.5°	1874.4	1854.4	1809.8	1802.1	1786.7
20°	1829.8	1809.8	1757.5	1745.2	1725.2
22.5°	1780.6	1757.5	1700.5	1680.5	1665.1
25°	1728.2	1700.5	1637.4	1611.3	1595.9
27.5°	1674.4	1640.5	1574.3	1543.6	1522.0
30°	1617.4	1579.0	1506.6	1468.2	1443.5
32.5°	1557.4	1512.8	1437.4	1391.2	1368.1
35°	1494.3	1445.1	1368.1	1315.8	1288.1
37.5°	1428.1	1377.4	1292.7	1235.8	1208.1
40°	1357.3	1306.6	1218.8	1154.2	1126.5
42.5°	1289.6	1235.8	1143.4	1077.3	1048.0
45°	1218.8	1161.9	1069.6	994.2	966.5
47.5°	1146.5	1088.0	992.6	914.1	883.4
50°	1072.6	1012.6	914.1	837.2	807.9
52.5°	997.2	938.8	837.2	758.7	727.9
55°	923.4	861.8	761.8	681.8	652.5
57.5°	851.0	786.4	687.9	606.3	584.8
60°	772.6	711.0	612.5	532.5	507.9
62.5°	701.8	637.1	535.6	463.2	444.8
65°	627.9	561.7	463.2	397.0	378.6
67.5°	550.9	487.8	395.5	337.0	315.5
70°	478.6	414.0	326.3	275.5	260.1
72.5°	401.7	344.7	263.2	221.6	207.8
75°	334.0	277.0	204.7	169.3	160.1
77.5°	263.2	213.9	152.4	127.7	124.7
80°	195.4	150.8	104.6	100.0	98.5
82.5°	137.0	97.0	75.4	72.3	70.8
85°	83.1	52.3	47.7	44.6	44.6
87.5°	35.4	23.1	21.5	20.0	21.5
90°	4.4	20.6	32.4	41.2	44.1
92.5°	22.1	19.1	30.9	39.7	39.7
95°	80.9	30.9	32.4	41.2	42.7
97.5°	154.5	186.9	32.4	39.7	41.2
100°	241.3	267.8	64.7	39.7	41.2
102.5°	338.4	356.1	373.7	42.7	42.7
105°	442.9	451.7	459.0	472.3	419.3
107.5°	538.5	542.9	553.2	560.6	566.4
110°	635.6	640.0	648.8	651.8	656.2



TEST NUMBER: P1032918

CATALOG NUMBER: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	729.8	738.6	741.5	740.1	745.9
115°	826.9	831.3	829.8	832.7	832.7
117.5°	913.7	919.6	924.0	922.5	922.5
120°	1001.9	1007.8	1006.4	1009.3	1006.4
122.5°	1084.3	1087.3	1090.2	1091.7	1088.8
125°	1162.3	1168.2	1165.3	1169.7	1171.1
127.5°	1237.4	1238.8	1246.2	1244.7	1243.2
130°	1309.4	1310.9	1315.3	1316.8	1316.8
132.5°	1375.7	1378.6	1384.5	1386.0	1384.5
135°	1441.9	1440.4	1446.3	1449.2	1452.2
137.5°	1500.7	1500.7	1508.1	1511.0	1509.5
140°	1558.1	1561.0	1564.0	1568.4	1569.9
142.5°	1609.6	1615.5	1616.9	1619.9	1619.9
145°	1662.6	1667.0	1667.0	1668.4	1671.4
147.5°	1703.8	1712.6	1711.1	1712.6	1714.1
150°	1749.4	1755.2	1753.8	1753.8	1755.2
152.5°	1787.6	1792.0	1789.1	1792.0	1790.6
155°	1822.9	1824.4	1820.0	1825.9	1821.5
157.5°	1853.8	1853.8	1847.9	1855.3	1847.9
160°	1880.3	1875.9	1874.4	1883.2	1874.4
162.5°	1903.8	1898.0	1896.5	1905.3	1895.0
165°	1923.0	1915.6	1915.6	1927.4	1914.1
167.5°	1939.2	1931.8	1930.3	1943.6	1928.9
170°	1952.4	1943.6	1945.0	1956.8	1942.1
172.5°	1961.2	1952.4	1953.9	1965.6	1949.5
175°	1967.1	1958.3	1959.8	1973.0	1955.3
177.5°	1971.5	1961.2	1964.2	1975.9	1958.3
180°	1967.1	1967.1	1967.1	1967.1	1967.1

(END OF REPORT)