

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032935

Luminaire Tested: S124RDIW-B1195D770UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032935
REPORT IS A COMBINATION OF REPORTS P1000230 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1195D770UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7887.0 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032935

CATALOG NUMBER: S124RDIW-B1195D770UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1032935

CATALOG NUMBER: S124RDIW-B1195D770UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	101	96	92	89	94	90	87	84	79	76	74	68	67	65	59	58	56
2	92	84	78	73	86	79	74	69	70	65	62	61	57	55	52	50	48
3	84	75	67	61	78	70	64	58	62	57	52	54	50	47	47	44	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36
5	71	59	51	45	66	56	48	43	49	44	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	38	45	39	34	39	35	31	34	31	28
7	61	48	40	35	57	46	38	33	41	35	30	36	31	28	31	28	25
8	56	44	36	31	53	42	34	30	37	31	27	33	28	25	29	25	22
9	53	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	32	26	22	28	24	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16898	16898	16898
5°	16899	16395	16397
10°	16756	15878	15689
15°	16525	15234	14854
20°	16223	14500	13902
25°	15847	13707	12972
30°	15479	12899	11927
35°	15073	12079	10906
40°	14590	11197	9857
45°	14138	10322	8818
50°	13624	9367	7764
55°	13068	8387	6675
60°	12451	7347	5600
65°	11856	6154	4565
70°	11010	4899	3488
75°	9922	3563	2440
80°	8287	2188	1753
85°	6236	1261	964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14138 cd/sqm

TEST NUMBER: P1032935

CATALOG NUMBER: S124RDIW-B1195D770UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.9	2.5
10°-20°	543.3	6.9
20°-30°	784.4	9.9
30°-40°	889.0	11.3
40°-50°	858.3	10.9
50°-60°	713.6	9.0
60°-70°	492.5	6.2
70°-80°	248.9	3.2
80°-90°	65.3	0.8
90°-100°	33.2	0.4
100°-110°	218.8	2.8
110°-120°	417.8	5.3
120°-130°	530.4	6.7
130°-140°	567.4	7.2
140°-150°	530.5	6.7
150°-160°	427.8	5.4
160°-170°	275.9	3.5
170°-180°	95.1	1.2
0°-30°	1522.5	19.3
0°-40°	2411.5	30.6
0°-60°	3983.4	50.5
0°-90°	4790.0	60.7
90°-120°	669.8	8.5
90°-150°	2298.1	29.1
90°-180°	3097.0	39.3
0°-180°	7887.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2072	2072	2072	2072	2072	
5°	2069	2063	2044	2060	2056	196
15°	1971	1956	1917	1914	1902	555
25°	1782	1753	1688	1661	1645	821
35°	1541	1490	1410	1357	1328	963
45°	1257	1198	1103	1025	996	969
55°	952	888	785	703	673	852
65°	647	579	478	409	390	639
75°	344	286	211	174	165	363
85°	86	54	49	46	46	94
90°	2	10	16	21	22	7
95°	41	16	16	21	22	51
105°	225	230	234	240	213	236
115°	421	423	422	424	424	414
125°	591	594	593	595	596	528
135°	734	733	736	737	739	565
145°	846	848	848	849	850	529
155°	928	928	926	929	927	428
165°	978	975	975	981	974	276
175°	1001	996	997	1004	995	95
180°	1001	1001	1001	1001	1001	

TEST NUMBER: P1032935

CATALOG NUMBER: S124RDIW-B1195D770UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2072.2	2072.2	2072.2	2072.2	2072.2
2.5°	2078.5	2072.2	2054.7	2072.2	2070.6
5°	2069.0	2062.7	2043.6	2059.5	2056.3
7.5°	2054.7	2048.4	2024.6	2035.7	2030.9
10°	2032.5	2024.6	1996.0	2002.4	1996.0
12.5°	2004.0	1994.4	1959.5	1962.7	1953.2
15°	1970.6	1956.4	1916.7	1913.5	1902.4
17.5°	1932.6	1911.9	1865.9	1858.0	1842.1
20°	1886.5	1865.9	1812.0	1799.3	1778.7
22.5°	1835.8	1812.0	1753.3	1732.6	1716.8
25°	1781.8	1753.3	1688.2	1661.2	1645.4
27.5°	1726.3	1691.4	1623.2	1591.4	1569.2
30°	1667.6	1627.9	1553.3	1513.7	1488.3
32.5°	1605.7	1559.7	1481.9	1434.3	1410.5
35°	1540.7	1489.9	1410.5	1356.6	1328.0
37.5°	1472.4	1420.1	1332.8	1274.1	1245.5
40°	1399.4	1347.1	1256.6	1190.0	1161.4
42.5°	1329.6	1274.1	1178.9	1110.7	1080.5
45°	1256.6	1197.9	1102.7	1025.0	996.4
47.5°	1182.1	1121.8	1023.4	942.5	910.7
50°	1105.9	1044.0	942.5	863.1	833.0
52.5°	1028.2	967.9	863.1	782.2	750.5
55°	952.0	888.5	785.4	702.9	672.7
57.5°	877.4	810.8	709.2	625.1	602.9
60°	796.5	733.0	631.5	549.0	523.6
62.5°	723.5	656.9	552.2	477.6	458.5
65°	647.4	579.1	477.6	409.4	390.3
67.5°	568.0	503.0	407.8	347.5	325.3
70°	493.5	426.8	336.4	284.0	268.1
72.5°	414.1	355.4	271.3	228.5	214.2
75°	344.3	285.6	211.0	174.5	165.0
77.5°	271.3	220.5	157.1	131.7	128.5
80°	201.5	155.5	107.9	103.1	101.5
82.5°	141.2	100.0	77.7	74.6	73.0
85°	85.7	53.9	49.2	46.0	46.0
87.5°	36.5	23.8	22.2	20.6	22.2
90°	2.2	10.5	16.5	21.0	22.5
92.5°	11.2	9.7	15.7	20.2	20.2
95°	41.2	15.7	16.5	21.0	21.7
97.5°	78.6	95.1	16.5	20.2	21.0
100°	122.8	136.2	32.9	20.2	21.0
102.5°	172.2	181.2	190.1	21.7	21.7
105°	225.3	229.8	233.6	240.3	213.3
107.5°	274.0	276.2	281.5	285.2	288.2
110°	323.4	325.6	330.1	331.6	333.9

TEST NUMBER: P1032935

CATALOG NUMBER: S124RDIW-B1195D770UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.3	375.8	377.3	376.5	379.5
115°	420.7	422.9	422.2	423.7	423.7
117.5°	464.9	467.9	470.1	469.4	469.4
120°	509.8	512.8	512.0	513.5	512.0
122.5°	551.7	553.2	554.7	555.4	553.9
125°	591.4	594.4	592.9	595.1	595.9
127.5°	629.5	630.3	634.0	633.3	632.5
130°	666.2	667.0	669.2	670.0	670.0
132.5°	699.9	701.4	704.4	705.2	704.4
135°	733.6	732.8	735.8	737.3	738.8
137.5°	763.5	763.5	767.3	768.8	768.0
140°	792.7	794.2	795.7	798.0	798.7
142.5°	818.9	821.9	822.7	824.2	824.2
145°	845.9	848.1	848.1	848.9	850.4
147.5°	866.8	871.3	870.6	871.3	872.1
150°	890.0	893.0	892.3	892.3	893.0
152.5°	909.5	911.8	910.3	911.8	911.0
155°	927.5	928.2	926.0	929.0	926.7
157.5°	943.2	943.2	940.2	943.9	940.2
160°	956.7	954.4	953.7	958.2	953.7
162.5°	968.6	965.7	964.9	969.4	964.2
165°	978.4	974.6	974.6	980.6	973.9
167.5°	986.6	982.9	982.1	988.9	981.4
170°	993.3	988.9	989.6	995.6	988.1
172.5°	997.8	993.3	994.1	1000.1	991.9
175°	1000.8	996.3	997.1	1003.8	994.8
177.5°	1003.1	997.8	999.3	1005.3	996.3
180°	1000.8	1000.8	1000.8	1000.8	1000.8

(END OF REPORT)