

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032504

Luminaire Tested: S124DIW-B1020D1560UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032504
REPORT IS A COMBINATION OF REPORTS P996774 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D1560UB2750-4F0-XX-W2A-F1_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9515.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032504

CATALOG NUMBER: S124DIW-B1020D1560UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032504

CATALOG NUMBER: S124DIW-B1020D1560UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43
2	88	80	74	69	80	74	69	64	62	58	54	50	48	45	40	38	36
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	31	29	27
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	19	22	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13448	13448	13448
5°	13460	13062	13078
10°	13345	12698	12610
15°	13154	12268	12082
20°	12910	11802	11537
25°	12635	11309	10949
30°	12302	10776	10304
35°	11959	10230	9681
40°	11601	9644	9017
45°	11225	9055	8397
50°	10810	8485	7710
55°	10358	7818	7028
60°	9895	7088	6318
65°	9365	6335	5518
70°	8757	5427	4659
75°	7844	4374	3732
80°	6683	3162	2626
85°	5196	1760	1413

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11225 cd/sqm

TEST NUMBER: P1032504

CATALOG NUMBER: S124DIW-B1020D1560UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.4	1.6
10°-20°	437.9	4.6
20°-30°	644.5	6.8
30°-40°	749.2	7.9
40°-50°	749.1	7.9
50°-60°	655.2	6.9
60°-70°	486.5	5.1
70°-80°	276.0	2.9
80°-90°	83.1	0.9
90°-100°	124.0	1.3
100°-110°	371.4	3.9
110°-120°	630.9	6.6
120°-130°	832.1	8.7
130°-140°	934.5	9.8
140°-150°	918.5	9.7
150°-160°	772.5	8.1
160°-170°	514.0	5.4
170°-180°	180.0	1.9
0°-30°	1237.9	13.0
0°-40°	1987.1	20.9
0°-60°	3391.5	35.6
0°-90°	4237.1	44.5
90°-120°	1126.3	11.8
90°-150°	3811.4	40.1
90°-180°	5278.0	55.5
0°-180°	9515.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1649	1649	1649	1649	1649	
5°	1648	1643	1628	1643	1640	156
15°	1569	1563	1544	1551	1547	442
25°	1421	1411	1393	1394	1389	654
35°	1222	1213	1195	1185	1179	764
45°	998	988	967	953	949	769
55°	755	751	732	716	708	676
65°	511	505	492	478	472	506
75°	272	266	259	254	252	289
85°	71	71	69	69	67	77
90°	4	21	32	41	44	11
95°	88	102	112	116	116	96
105°	343	344	350	354	359	363
115°	641	641	638	637	636	633
125°	934	934	933	930	927	833
135°	1205	1214	1214	1211	1206	932
145°	1464	1470	1471	1470	1465	916
155°	1677	1677	1676	1682	1676	772
165°	1826	1821	1818	1827	1821	515
175°	1899	1892	1890	1901	1890	180
180°	1902	1902	1902	1902	1902	

TEST NUMBER: P1032504

CATALOG NUMBER: S124DIW-B1020D1560UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1649.2	1649.2	1649.2	1649.2	1649.2
2.5°	1654.5	1650.5	1636.0	1649.2	1647.9
5°	1647.9	1642.6	1628.1	1642.6	1640.0
7.5°	1636.0	1630.7	1614.8	1626.7	1625.4
10°	1618.8	1613.5	1596.3	1606.9	1604.3
12.5°	1596.3	1591.1	1572.6	1584.5	1580.5
15°	1568.6	1563.3	1543.5	1551.4	1547.4
17.5°	1536.9	1530.3	1511.8	1517.1	1514.4
20°	1501.2	1494.6	1474.8	1478.7	1476.1
22.5°	1462.9	1453.6	1433.8	1441.7	1436.4
25°	1420.6	1411.3	1392.8	1394.2	1388.9
27.5°	1373.0	1363.8	1346.6	1343.9	1337.3
30°	1325.4	1314.9	1297.7	1292.4	1285.8
32.5°	1275.2	1266.0	1247.5	1240.9	1234.3
35°	1222.4	1213.1	1194.6	1185.4	1178.8
37.5°	1166.9	1158.9	1139.1	1129.9	1120.6
40°	1112.7	1102.1	1082.3	1069.1	1062.5
42.5°	1054.5	1049.3	1026.8	1010.9	1007.0
45°	997.7	988.5	967.3	952.8	948.8
47.5°	938.2	931.6	911.8	896.0	885.4
50°	877.5	872.2	853.7	835.2	827.2
52.5°	818.0	811.4	791.6	775.7	765.1
55°	754.6	750.6	732.1	716.2	708.3
57.5°	695.1	691.1	672.6	656.8	648.8
60°	633.0	626.4	609.2	597.3	590.7
62.5°	572.2	566.9	548.4	537.8	531.2
65°	511.4	504.8	491.6	478.4	471.8
67.5°	449.3	444.0	430.8	417.6	416.3
70°	392.5	383.2	372.7	362.1	358.1
72.5°	331.7	322.4	314.5	306.6	302.6
75°	272.2	265.6	259.0	253.7	252.4
77.5°	214.1	211.4	204.8	203.5	199.5
80°	162.5	158.6	155.9	153.3	152.0
82.5°	112.3	111.0	111.0	109.7	108.4
85°	71.4	71.4	68.7	68.7	67.4
87.5°	34.4	33.0	31.7	31.7	31.7
90°	4.4	20.6	32.4	41.2	44.1
92.5°	38.3	57.4	64.7	69.1	70.6
95°	88.3	101.5	111.8	116.2	116.2
97.5°	141.2	153.0	164.8	170.7	170.7
100°	206.0	211.8	225.1	228.0	228.0
102.5°	273.6	275.1	286.9	291.3	292.8
105°	342.8	344.3	350.1	354.5	359.0
107.5°	414.9	416.3	417.8	423.7	422.2
110°	488.4	491.4	489.9	487.0	491.4

TEST NUMBER: P1032504

CATALOG NUMBER: S124DIW-B1020D1560UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	564.9	564.9	562.0	562.0	562.0
115°	641.4	641.4	638.5	637.0	635.5
117.5°	713.5	713.5	712.0	707.6	703.2
120°	785.6	791.5	787.1	779.7	782.7
122.5°	860.6	862.1	860.6	856.2	848.9
125°	934.2	934.2	932.7	929.8	926.8
127.5°	1000.4	1004.8	1001.9	998.9	997.4
130°	1071.0	1075.4	1075.4	1072.5	1066.6
132.5°	1143.1	1146.0	1144.6	1141.6	1140.1
135°	1204.9	1213.7	1213.7	1210.8	1206.4
137.5°	1274.0	1278.4	1281.4	1277.0	1278.4
140°	1343.2	1346.1	1346.1	1344.6	1343.2
142.5°	1406.4	1409.4	1407.9	1407.9	1407.9
145°	1463.8	1469.7	1471.2	1469.7	1465.3
147.5°	1522.7	1530.0	1528.5	1527.1	1525.6
150°	1575.6	1581.5	1581.5	1581.5	1580.0
152.5°	1625.6	1628.6	1630.0	1634.5	1630.0
155°	1677.1	1677.1	1675.7	1681.5	1675.7
157.5°	1721.3	1718.3	1718.3	1722.7	1718.3
160°	1759.5	1758.0	1756.6	1761.0	1753.6
162.5°	1794.8	1790.4	1788.9	1797.8	1790.4
165°	1825.7	1821.3	1818.4	1827.2	1821.3
167.5°	1850.7	1844.8	1844.8	1853.7	1844.8
170°	1871.3	1864.0	1865.4	1874.3	1864.0
172.5°	1886.0	1880.1	1880.1	1890.4	1880.1
175°	1899.3	1891.9	1890.4	1900.7	1890.4
177.5°	1905.2	1897.8	1897.8	1908.1	1896.3
180°	1902.2	1902.2	1902.2	1902.2	1902.2

(END OF REPORT)