

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033005

Luminaire Tested: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033005
REPORT IS A COMBINATION OF REPORTS P1000538 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7644.0 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033005

CATALOG NUMBER: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1033005

CATALOG NUMBER: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	102	102	102	102		92	92	92	92		72	72	72		55	55	55		38	38	38
1	94	89	86	82		84	80	77	75		64	62	60		48	47	46		34	33	32
2	85	78	72	67		76	70	66	61		56	52	50		42	40	38		30	29	28
3	78	69	62	56		70	62	56	51		49	45	42		38	35	33		27	25	24
4	71	61	53	48		64	55	49	44		44	39	36		34	30	28		24	22	20
5	65	54	46	41		58	49	42	37		39	34	31		30	27	24		22	20	18
6	60	49	41	35		54	44	37	32		35	30	27		27	24	21		20	17	16
7	55	44	36	31		50	40	33	28		32	27	23		25	21	19		18	16	14
8	51	40	32	27		46	36	29	25		29	24	21		23	19	17		16	14	13
9	48	36	29	24		43	33	26	22		27	22	19		21	17	15		15	13	11
10	45	33	26	21		40	30	24	20		24	20	17		19	16	13		14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8181	8181	8181
5°	8182	7938	7938
10°	8112	7687	7595
15°	8000	7375	7191
20°	7854	7020	6730
25°	7672	6636	6280
30°	7493	6245	5774
35°	7298	5848	5280
40°	7064	5421	4772
45°	6845	4998	4269
50°	6596	4535	3759
55°	6327	4060	3232
60°	6028	3557	2711
65°	5739	2979	2210
70°	5330	2371	1689
75°	4804	1726	1181
80°	4014	1059	850
85°	3020	610	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6845 cd/sqm

TEST NUMBER: P1033005

CATALOG NUMBER: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	1.2
10°-20°	263.0	3.4
20°-30°	379.7	5.0
30°-40°	430.4	5.6
40°-50°	415.5	5.4
50°-60°	345.5	4.5
60°-70°	238.4	3.1
70°-80°	120.5	1.6
80°-90°	34.2	0.4
90°-100°	57.1	0.7
100°-110°	376.0	4.9
110°-120°	718.0	9.4
120°-130°	911.5	11.9
130°-140°	975.1	12.8
140°-150°	911.8	11.9
150°-160°	735.3	9.6
160°-170°	474.2	6.2
170°-180°	163.4	2.1
0°-30°	737.1	9.6
0°-40°	1167.5	15.3
0°-60°	1928.5	25.2
0°-90°	2321.6	30.4
90°-120°	1151.1	15.1
90°-150°	3949.5	51.7
90°-180°	5322.0	69.6
0°-180°	7644.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1002	999	989	997	996	95
15°	954	947	928	926	921	269
25°	863	849	817	804	797	397
35°	746	721	683	657	643	466
45°	608	580	534	496	482	469
55°	461	430	380	340	326	412
65°	313	280	231	198	189	309
75°	167	138	102	84	80	176
85°	42	26	24	22	22	46
90°	4	18	28	36	39	6
95°	71	27	28	36	37	87
105°	387	395	401	413	367	405
115°	723	727	726	728	728	712
125°	1016	1022	1019	1023	1024	908
135°	1261	1260	1265	1267	1270	971
145°	1454	1458	1458	1459	1462	908
155°	1594	1595	1591	1596	1593	735
165°	1682	1675	1675	1685	1674	475
175°	1720	1712	1714	1725	1710	164
180°	1720	1720	1720	1720	1720	

TEST NUMBER: P1033005

CATALOG NUMBER: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1003.2	1003.2	1003.2	1003.2	1003.2
2.5°	1006.3	1003.2	994.8	1003.2	1002.4
5°	1001.7	998.6	989.4	997.1	995.5
7.5°	994.8	991.7	980.2	985.5	983.2
10°	984.0	980.2	966.3	969.4	966.3
12.5°	970.2	965.6	948.7	950.2	945.6
15°	954.0	947.1	927.9	926.4	921.0
17.5°	935.6	925.6	903.3	899.5	891.8
20°	913.3	903.3	877.2	871.1	861.1
22.5°	888.7	877.2	848.8	838.8	831.1
25°	862.6	848.8	817.3	804.2	796.6
27.5°	835.7	818.8	785.8	770.5	759.7
30°	807.3	788.1	752.0	732.8	720.5
32.5°	777.4	755.1	717.4	694.4	682.9
35°	745.9	721.3	682.9	656.8	642.9
37.5°	712.8	687.5	645.2	616.8	603.0
40°	677.5	652.2	608.4	576.1	562.3
42.5°	643.7	616.8	570.7	537.7	523.1
45°	608.4	580.0	533.9	496.2	482.4
47.5°	572.3	543.1	495.5	456.3	440.9
50°	535.4	505.4	456.3	417.9	403.3
52.5°	497.8	468.6	417.9	378.7	363.3
55°	460.9	430.2	380.2	340.3	325.7
57.5°	424.8	392.5	343.4	302.6	291.9
60°	385.6	354.9	305.7	265.8	253.5
62.5°	350.3	318.0	267.3	231.2	222.0
65°	313.4	280.4	231.2	198.2	189.0
67.5°	275.0	243.5	197.4	168.2	157.5
70°	238.9	206.6	162.8	137.5	129.8
72.5°	200.5	172.1	131.4	110.6	103.7
75°	166.7	138.3	102.2	84.5	79.9
77.5°	131.4	106.8	76.0	63.8	62.2
80°	97.6	75.3	52.2	49.9	49.2
82.5°	68.4	48.4	37.6	36.1	35.3
85°	41.5	26.1	23.8	22.3	22.3
87.5°	17.7	11.5	10.8	10.0	10.8
90°	3.9	18.0	28.3	36.0	38.6
92.5°	19.3	16.7	27.0	34.7	34.7
95°	70.8	27.0	28.3	36.0	37.3
97.5°	135.1	163.4	28.3	34.7	36.0
100°	211.0	234.1	56.6	34.7	36.0
102.5°	295.9	311.3	326.8	37.3	37.3
105°	387.2	395.0	401.4	413.0	366.7
107.5°	470.9	474.7	483.7	490.2	495.3
110°	555.8	559.6	567.3	569.9	573.8

TEST NUMBER: P1033005

CATALOG NUMBER: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	638.1	645.8	648.4	647.1	652.3
115°	723.0	726.9	725.6	728.2	728.2
117.5°	798.9	804.1	807.9	806.6	806.6
120°	876.1	881.3	880.0	882.5	880.0
122.5°	948.2	950.7	953.3	954.6	952.0
125°	1016.3	1021.5	1018.9	1022.8	1024.1
127.5°	1081.9	1083.2	1089.7	1088.4	1087.1
130°	1145.0	1146.3	1150.1	1151.4	1151.4
132.5°	1202.9	1205.5	1210.6	1211.9	1210.6
135°	1260.8	1259.5	1264.6	1267.2	1269.8
137.5°	1312.2	1312.2	1318.7	1321.2	1320.0
140°	1362.4	1365.0	1367.6	1371.4	1372.7
142.5°	1407.4	1412.6	1413.9	1416.4	1416.4
145°	1453.7	1457.6	1457.6	1458.9	1461.5
147.5°	1489.8	1497.5	1496.2	1497.5	1498.8
150°	1529.6	1534.8	1533.5	1533.5	1534.8
152.5°	1563.1	1567.0	1564.4	1567.0	1565.7
155°	1594.0	1595.3	1591.4	1596.5	1592.7
157.5°	1621.0	1621.0	1615.8	1622.3	1615.8
160°	1644.1	1640.3	1639.0	1646.7	1639.0
162.5°	1664.7	1659.6	1658.3	1666.0	1657.0
165°	1681.5	1675.0	1675.0	1685.3	1673.7
167.5°	1695.6	1689.2	1687.9	1699.5	1686.6
170°	1707.2	1699.5	1700.8	1711.0	1698.2
172.5°	1714.9	1707.2	1708.5	1718.8	1704.6
175°	1720.1	1712.3	1713.6	1725.2	1709.8
177.5°	1723.9	1714.9	1717.5	1727.8	1712.3
180°	1720.1	1720.1	1720.1	1720.1	1720.1

(END OF REPORT)