

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032538

Luminaire Tested: S124DIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032538
REPORT IS A COMBINATION OF REPORTS P996912 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D770UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7239.0 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032538

CATALOG NUMBER: S124DIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032538

CATALOG NUMBER: S124DIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	86	82	77	75	72	66	65	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	50	47	45
3	83	73	66	60	77	68	62	57	60	55	50	52	48	44	44	41	39
4	76	65	57	51	70	61	54	48	53	47	43	46	42	38	39	36	33
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	26
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13448	13448	13448
5°	13460	13062	13078
10°	13345	12698	12610
15°	13154	12268	12082
20°	12910	11802	11537
25°	12635	11309	10949
30°	12302	10776	10304
35°	11959	10230	9681
40°	11601	9644	9017
45°	11225	9055	8397
50°	10810	8485	7710
55°	10358	7818	7028
60°	9895	7088	6318
65°	9365	6335	5518
70°	8757	5427	4659
75°	7844	4374	3732
80°	6683	3162	2626
85°	5196	1760	1413

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11225 cd/sqm

TEST NUMBER: P1032538

CATALOG NUMBER: S124DIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.4	2.1
10°-20°	437.9	6.0
20°-30°	644.5	8.9
30°-40°	749.2	10.3
40°-50°	749.1	10.3
50°-60°	655.2	9.1
60°-70°	486.5	6.7
70°-80°	276.0	3.8
80°-90°	81.1	1.1
90°-100°	32.2	0.4
100°-110°	212.2	2.9
110°-120°	405.3	5.6
120°-130°	514.5	7.1
130°-140°	550.4	7.6
140°-150°	514.6	7.1
150°-160°	415.0	5.7
160°-170°	267.6	3.7
170°-180°	92.2	1.3
0°-30°	1237.9	17.1
0°-40°	1987.1	27.5
0°-60°	3391.5	46.9
0°-90°	4235.0	58.5
90°-120°	649.7	9.0
90°-150°	2229.1	30.8
90°-180°	3004.0	41.5
0°-180°	7239.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1649	1649	1649	1649	1649	
5°	1648	1643	1628	1643	1640	156
15°	1569	1563	1544	1551	1547	442
25°	1421	1411	1393	1394	1389	654
35°	1222	1213	1195	1185	1179	764
45°	998	988	967	953	949	769
55°	755	751	732	716	708	676
65°	511	505	492	478	472	506
75°	272	266	259	254	252	289
85°	71	71	69	69	67	77
90°	2	10	16	20	22	7
95°	40	15	16	20	21	49
105°	219	223	226	233	207	229
115°	408	410	410	411	411	402
125°	574	576	575	577	578	512
135°	712	711	714	715	717	548
145°	820	823	823	823	825	513
155°	900	900	898	901	899	415
165°	949	945	945	951	945	268
175°	971	966	967	974	965	92
180°	971	971	971	971	971	

TEST NUMBER: P1032538

CATALOG NUMBER: S124DIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1649.2	1649.2	1649.2	1649.2	1649.2
2.5°	1654.5	1650.5	1636.0	1649.2	1647.9
5°	1647.9	1642.6	1628.1	1642.6	1640.0
7.5°	1636.0	1630.7	1614.8	1626.7	1625.4
10°	1618.8	1613.5	1596.3	1606.9	1604.3
12.5°	1596.3	1591.1	1572.6	1584.5	1580.5
15°	1568.6	1563.3	1543.5	1551.4	1547.4
17.5°	1536.9	1530.3	1511.8	1517.1	1514.4
20°	1501.2	1494.6	1474.8	1478.7	1476.1
22.5°	1462.9	1453.6	1433.8	1441.7	1436.4
25°	1420.6	1411.3	1392.8	1394.2	1388.9
27.5°	1373.0	1363.8	1346.6	1343.9	1337.3
30°	1325.4	1314.9	1297.7	1292.4	1285.8
32.5°	1275.2	1266.0	1247.5	1240.9	1234.3
35°	1222.4	1213.1	1194.6	1185.4	1178.8
37.5°	1166.9	1158.9	1139.1	1129.9	1120.6
40°	1112.7	1102.1	1082.3	1069.1	1062.5
42.5°	1054.5	1049.3	1026.8	1010.9	1007.0
45°	997.7	988.5	967.3	952.8	948.8
47.5°	938.2	931.6	911.8	896.0	885.4
50°	877.5	872.2	853.7	835.2	827.2
52.5°	818.0	811.4	791.6	775.7	765.1
55°	754.6	750.6	732.1	716.2	708.3
57.5°	695.1	691.1	672.6	656.8	648.8
60°	633.0	626.4	609.2	597.3	590.7
62.5°	572.2	566.9	548.4	537.8	531.2
65°	511.4	504.8	491.6	478.4	471.8
67.5°	449.3	444.0	430.8	417.6	416.3
70°	392.5	383.2	372.7	362.1	358.1
72.5°	331.7	322.4	314.5	306.6	302.6
75°	272.2	265.6	259.0	253.7	252.4
77.5°	214.1	211.4	204.8	203.5	199.5
80°	162.5	158.6	155.9	153.3	152.0
82.5°	112.3	111.0	111.0	109.7	108.4
85°	71.4	71.4	68.7	68.7	67.4
87.5°	34.4	33.0	31.7	31.7	31.7
90°	2.2	10.2	16.0	20.3	21.8
92.5°	10.9	9.4	15.2	19.6	19.6
95°	39.9	15.2	16.0	20.3	21.1
97.5°	76.2	92.2	16.0	19.6	20.3
100°	119.1	132.2	31.9	19.6	20.3
102.5°	167.0	175.7	184.4	21.1	21.1
105°	218.6	222.9	226.5	233.1	206.9
107.5°	265.8	267.9	273.0	276.6	279.5
110°	313.7	315.9	320.2	321.7	323.8



TEST NUMBER: P1032538

CATALOG NUMBER: S124DIW-B1020D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	360.1	364.5	366.0	365.2	368.1
115°	408.1	410.2	409.5	411.0	411.0
117.5°	450.9	453.8	456.0	455.3	455.3
120°	494.5	497.4	496.7	498.1	496.7
122.5°	535.1	536.6	538.0	538.8	537.3
125°	573.6	576.5	575.1	577.3	578.0
127.5°	610.7	611.4	615.0	614.3	613.6
130°	646.2	647.0	649.1	649.9	649.9
132.5°	678.9	680.4	683.3	684.0	683.3
135°	711.6	710.9	713.8	715.2	716.7
137.5°	740.6	740.6	744.3	745.7	745.0
140°	768.9	770.4	771.8	774.0	774.8
142.5°	794.4	797.3	798.0	799.4	799.4
145°	820.5	822.7	822.7	823.4	824.9
147.5°	840.8	845.2	844.5	845.2	845.9
150°	863.3	866.2	865.5	865.5	866.2
152.5°	882.2	884.4	882.9	884.4	883.7
155°	899.6	900.4	898.2	901.1	898.9
157.5°	914.9	914.9	912.0	915.6	912.0
160°	928.0	925.8	925.1	929.4	925.1
162.5°	939.6	936.7	935.9	940.3	935.2
165°	949.0	945.4	945.4	951.2	944.7
167.5°	957.0	953.4	952.6	959.2	951.9
170°	963.5	959.2	959.9	965.7	958.5
172.5°	967.9	963.5	964.3	970.1	962.1
175°	970.8	966.4	967.2	973.7	965.0
177.5°	973.0	967.9	969.3	975.2	966.4
180°	970.8	970.8	970.8	970.8	970.8

(END OF REPORT)