

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033037

Luminaire Tested: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033037
REPORT IS A COMBINATION OF REPORTS P1000672 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5488.0 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033037

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1033037

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	56	55	54	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	74	63	55	50	67	58	51	46	48	43	39	40	36	33	31	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	35	30	26	29	25	22	23	21	18
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8290	8290	8290
5°	8291	8044	8044
10°	8221	7790	7698
15°	8108	7474	7287
20°	7959	7114	6820
25°	7775	6724	6364
30°	7594	6328	5852
35°	7394	5926	5350
40°	7159	5493	4836
45°	6936	5064	4326
50°	6684	4596	3809
55°	6412	4115	3275
60°	6109	3604	2748
65°	5816	3019	2240
70°	5401	2403	1712
75°	4867	1748	1198
80°	4068	1073	860
85°	3056	618	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6936 cd/sqm

TEST NUMBER: P1033037

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	1.7
10°-20°	266.5	4.9
20°-30°	384.8	7.0
30°-40°	436.1	7.9
40°-50°	421.1	7.7
50°-60°	350.1	6.4
60°-70°	241.6	4.4
70°-80°	122.1	2.2
80°-90°	33.1	0.6
90°-100°	33.7	0.6
100°-110°	221.6	4.0
110°-120°	423.2	7.7
120°-130°	537.2	9.8
130°-140°	574.7	10.5
140°-150°	537.4	9.8
150°-160°	433.4	7.9
160°-170°	279.5	5.1
170°-180°	96.3	1.8
0°-30°	747.0	13.6
0°-40°	1183.1	21.6
0°-60°	1954.3	35.6
0°-90°	2351.1	42.8
90°-120°	678.5	12.4
90°-150°	2327.8	42.4
90°-180°	3137.0	57.2
0°-180°	5488.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1017	1017	1017	1017	1017	
5°	1015	1012	1003	1010	1009	96
15°	967	960	940	939	933	272
25°	874	860	828	815	807	403
35°	756	731	692	666	652	472
45°	616	588	541	503	489	475
55°	467	436	385	345	330	418
65°	318	284	234	201	192	314
75°	169	140	104	86	81	178
85°	42	26	24	23	23	46
90°	2	11	17	21	23	5
95°	42	16	17	21	22	51
105°	228	233	237	243	216	239
115°	426	428	428	429	429	419
125°	599	602	600	603	604	535
135°	743	742	745	747	748	573
145°	857	859	859	860	861	535
155°	939	940	938	941	939	433
165°	991	987	987	993	986	280
175°	1014	1009	1010	1017	1008	97
180°	1014	1014	1014	1014	1014	

TEST NUMBER: P1033037

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1016.6	1016.6	1016.6	1016.6	1016.6
2.5°	1019.7	1016.6	1008.1	1016.6	1015.8
5°	1015.1	1011.9	1002.6	1010.4	1008.8
7.5°	1008.1	1004.9	993.3	998.7	996.4
10°	997.2	993.3	979.3	982.4	979.3
12.5°	983.1	978.5	961.3	962.9	958.2
15°	966.8	959.8	940.3	938.8	933.3
17.5°	948.1	938.0	915.4	911.5	903.7
20°	925.5	915.4	889.0	882.7	872.6
22.5°	900.6	889.0	860.2	850.0	842.3
25°	874.2	860.2	828.2	815.0	807.2
27.5°	846.9	829.8	796.3	780.8	769.9
30°	818.1	798.7	762.1	742.6	730.2
32.5°	787.8	765.2	727.0	703.7	692.0
35°	755.8	730.9	692.0	665.5	651.5
37.5°	722.4	696.7	653.9	625.1	611.1
40°	686.6	660.9	616.5	583.8	569.8
42.5°	652.3	625.1	578.4	544.9	530.1
45°	616.5	587.7	541.0	502.9	488.8
47.5°	579.9	550.3	502.1	462.4	446.8
50°	542.6	512.2	462.4	423.5	408.7
52.5°	504.4	474.8	423.5	383.8	368.2
55°	467.1	435.9	385.3	344.8	330.1
57.5°	430.5	397.8	348.0	306.7	295.8
60°	390.8	359.6	309.8	269.3	256.9
62.5°	355.0	322.3	270.9	234.3	225.0
65°	317.6	284.1	234.3	200.8	191.5
67.5°	278.7	246.8	200.1	170.5	159.6
70°	242.1	209.4	165.0	139.3	131.6
72.5°	203.2	174.4	133.1	112.1	105.1
75°	168.9	140.1	103.5	85.6	81.0
77.5°	133.1	108.2	77.1	64.6	63.1
80°	98.9	76.3	52.9	50.6	49.8
82.5°	69.3	49.0	38.1	36.6	35.8
85°	42.0	26.5	24.1	22.6	22.6
87.5°	17.9	11.7	10.9	10.1	10.9
90°	2.3	10.6	16.7	21.2	22.7
92.5°	11.4	9.9	15.9	20.5	20.5
95°	41.7	15.9	16.7	21.2	22.0
97.5°	79.6	96.3	16.7	20.5	21.2
100°	124.3	138.0	33.4	20.5	21.2
102.5°	174.4	183.5	192.6	22.0	22.0
105°	228.2	232.8	236.6	243.4	216.1
107.5°	277.5	279.8	285.1	288.9	291.9
110°	327.6	329.8	334.4	335.9	338.2



TEST NUMBER: P1033037

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.1	380.6	382.1	381.4	384.4
115°	426.1	428.4	427.6	429.2	429.2
117.5°	470.9	473.9	476.2	475.4	475.4
120°	516.4	519.4	518.6	520.1	518.6
122.5°	558.8	560.3	561.8	562.6	561.1
125°	599.0	602.0	600.5	602.8	603.6
127.5°	637.7	638.4	642.2	641.5	640.7
130°	674.8	675.6	677.9	678.6	678.6
132.5°	708.9	710.5	713.5	714.3	713.5
135°	743.1	742.3	745.3	746.9	748.4
137.5°	773.4	773.4	777.2	778.7	777.9
140°	803.0	804.5	806.0	808.3	809.0
142.5°	829.5	832.5	833.3	834.8	834.8
145°	856.8	859.1	859.1	859.8	861.3
147.5°	878.0	882.6	881.8	882.6	883.3
150°	901.5	904.6	903.8	903.8	904.6
152.5°	921.2	923.5	922.0	923.5	922.8
155°	939.4	940.2	937.9	941.0	938.7
157.5°	955.4	955.4	952.3	956.1	952.3
160°	969.0	966.7	966.0	970.5	966.0
162.5°	981.1	978.1	977.4	981.9	976.6
165°	991.0	987.2	987.2	993.3	986.5
167.5°	999.3	995.6	994.8	1001.6	994.0
170°	1006.2	1001.6	1002.4	1008.4	1000.9
172.5°	1010.7	1006.2	1006.9	1013.0	1004.7
175°	1013.8	1009.2	1010.0	1016.8	1007.7
177.5°	1016.0	1010.7	1012.2	1018.3	1009.2
180°	1013.8	1013.8	1013.8	1013.8	1013.8

(END OF REPORT)