

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032578

Luminaire Tested: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032578
REPORT IS A COMBINATION OF REPORTS P997103 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10776.0 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032578

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032578

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47			40
1	95	90	86	82	86	82	79	75	67	64	62	53	51	50	40	39	38			32
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	31			26
3	78	68	61	55	71	62	56	51	51	46	42	41	37	34	31	28	26			22
4	71	60	52	46	64	55	48	43	45	40	36	36	32	29	27	25	22			19
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	24	22	19			16
6	60	48	40	34	54	44	37	31	36	31	26	29	25	22	22	19	17			14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	20	17	15			12
8	51	39	31	26	47	36	29	24	30	24	20	24	20	17	18	16	13			11
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12			10
10	45	32	25	20	40	30	23	19	25	20	16	20	16	14	16	13	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11205	11205	11205
5°	11236	10913	10933
10°	11163	10699	10668
15°	11059	10457	10369
20°	10904	10196	10078
25°	10729	9908	9765
30°	10541	9622	9446
35°	10327	9330	9162
40°	10156	9050	8867
45°	9903	8787	8607
50°	9686	8488	8332
55°	9463	8201	8017
60°	9117	7842	7719
65°	8735	7456	7361
70°	8272	7013	6947
75°	7628	6522	6553
80°	6897	6023	6141
85°	5938	5520	5806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9903 cd/sqm

TEST NUMBER: P1032578

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	1.2
10°-20°	373.1	3.5
20°-30°	564.1	5.2
30°-40°	682.4	6.3
40°-50°	721.4	6.7
50°-60°	678.9	6.3
60°-70°	563.4	5.2
70°-80°	395.4	3.7
80°-90°	227.0	2.1
90°-100°	198.0	1.8
100°-110°	528.3	4.9
110°-120°	887.1	8.2
120°-130°	1079.6	10.0
130°-140°	1131.2	10.5
140°-150°	1045.9	9.7
150°-160°	840.9	7.8
160°-170°	542.3	5.0
170°-180°	186.9	1.7
0°-30°	1067.3	9.9
0°-40°	1749.7	16.2
0°-60°	3150.1	29.2
0°-90°	4335.8	40.2
90°-120°	1613.4	15.0
90°-150°	4870.1	45.2
90°-180°	6440.0	59.8
0°-180°	10776.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1374	1374	1374	1374	1374	
5°	1376	1371	1360	1373	1371	131
15°	1319	1320	1316	1330	1328	372
25°	1206	1216	1220	1237	1239	556
35°	1056	1074	1090	1111	1116	661
45°	880	909	939	965	972	680
55°	689	722	768	799	808	614
65°	477	526	579	617	629	473
75°	265	322	386	429	443	281
85°	82	146	215	262	277	85
90°	29	107	185	238	253	21
95°	101	102	166	217	232	116
105°	457	496	561	612	572	479
115°	836	854	902	939	950	824
125°	1168	1173	1208	1242	1253	1044
135°	1445	1444	1460	1488	1500	1114
145°	1664	1667	1667	1678	1687	1040
155°	1823	1824	1820	1826	1822	841
165°	1923	1916	1916	1927	1914	543
175°	1967	1958	1960	1973	1955	187
180°	1967	1967	1967	1967	1967	

TEST NUMBER: P1032578

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1374.1	1374.1	1374.1	1374.1	1374.1
2.5°	1380.3	1375.7	1363.4	1374.1	1372.6
5°	1375.7	1371.1	1360.3	1372.6	1371.1
7.5°	1366.4	1363.4	1354.1	1368.0	1366.4
10°	1354.1	1352.6	1344.9	1358.8	1357.2
12.5°	1337.2	1337.2	1332.6	1344.9	1344.9
15°	1318.7	1320.3	1315.7	1329.5	1328.0
17.5°	1294.1	1298.7	1297.2	1311.0	1309.5
20°	1268.0	1272.6	1274.1	1289.5	1289.5
22.5°	1238.7	1244.9	1248.0	1263.3	1266.4
25°	1206.4	1215.6	1220.3	1237.2	1238.7
27.5°	1171.0	1184.9	1191.0	1206.4	1207.9
30°	1135.6	1147.9	1158.7	1175.6	1178.7
32.5°	1097.2	1112.5	1124.9	1144.9	1147.9
35°	1055.6	1074.1	1089.5	1111.0	1115.6
37.5°	1014.1	1035.6	1054.1	1075.6	1080.2
40°	974.1	994.1	1015.6	1038.7	1044.8
42.5°	927.9	951.0	977.1	1003.3	1007.9
45°	880.2	909.4	938.7	964.8	972.5
47.5°	835.6	864.8	898.7	924.8	934.0
50°	786.3	820.2	854.0	884.8	894.0
52.5°	737.1	770.9	810.9	841.7	850.9
55°	689.4	721.7	767.9	798.6	807.9
57.5°	635.5	675.5	720.2	757.1	764.8
60°	583.2	623.2	674.0	709.4	721.7
62.5°	532.4	577.0	627.8	663.2	675.5
65°	477.0	526.3	578.6	617.1	629.4
67.5°	424.7	477.0	532.4	570.9	583.2
70°	370.8	423.2	481.6	523.2	534.0
72.5°	318.5	372.4	435.5	475.5	487.8
75°	264.7	321.6	386.2	429.3	443.2
77.5°	213.9	273.9	341.6	384.7	400.1
80°	167.7	229.3	297.0	343.1	355.5
82.5°	121.6	186.2	253.9	301.6	315.5
85°	81.6	146.2	215.4	261.6	277.0
87.5°	50.8	113.9	181.6	226.2	240.1
90°	29.0	106.8	184.7	238.2	253.4
92.5°	45.2	96.0	174.0	225.9	238.2
95°	100.9	101.7	166.3	216.6	232.0
97.5°	173.0	250.0	158.6	205.9	221.2
100°	258.2	324.7	181.6	198.2	210.5
102.5°	355.3	406.9	483.0	192.0	204.3
105°	456.7	496.3	560.6	612.3	571.6
107.5°	552.3	582.9	647.1	692.9	709.5
110°	647.9	673.9	736.5	774.9	791.6

TEST NUMBER: P1032578

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	740.6	767.8	821.5	854.0	872.1
115°	836.1	854.4	902.1	938.9	949.6
117.5°	922.9	938.1	988.6	1019.4	1031.8
120°	1009.6	1020.1	1063.3	1097.0	1106.4
122.5°	1092.0	1095.0	1139.4	1171.7	1179.6
125°	1168.5	1172.8	1208.4	1242.0	1252.7
127.5°	1243.6	1243.4	1281.6	1307.8	1317.1
130°	1314.0	1314.0	1343.0	1372.2	1381.4
132.5°	1380.3	1381.7	1406.0	1433.7	1441.4
135°	1445.0	1443.5	1460.1	1487.7	1499.9
137.5°	1503.8	1502.2	1515.8	1541.8	1548.0
140°	1561.2	1562.5	1567.1	1591.5	1600.7
142.5°	1611.1	1617.0	1616.9	1636.8	1643.0
145°	1664.1	1667.0	1667.0	1677.6	1686.8
147.5°	1705.3	1712.6	1711.1	1714.1	1721.8
150°	1750.9	1755.2	1753.8	1753.8	1755.2
152.5°	1787.6	1792.0	1789.1	1792.0	1790.6
155°	1822.9	1824.4	1820.0	1825.9	1821.5
157.5°	1853.8	1853.8	1847.9	1855.3	1847.9
160°	1880.3	1875.9	1874.4	1883.2	1874.4
162.5°	1903.8	1898.0	1896.5	1905.3	1895.0
165°	1923.0	1915.6	1915.6	1927.4	1914.1
167.5°	1939.2	1931.8	1930.3	1943.6	1928.9
170°	1952.4	1943.6	1945.0	1956.8	1942.1
172.5°	1961.2	1952.4	1953.9	1965.6	1949.5
175°	1967.1	1958.3	1959.8	1973.0	1955.3
177.5°	1971.5	1961.2	1964.2	1975.9	1958.3
180°	1967.1	1967.1	1967.1	1967.1	1967.1

(END OF REPORT)