

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033045

Luminaire Tested: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033045
REPORT IS A COMBINATION OF REPORTS P1000714 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7416.0 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033045

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1033045

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27
5	68	56	48	43	62	52	45	40	43	38	34	36	32	29	28	26	24
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11290	11290	11290
5°	11291	10954	10956
10°	11195	10609	10482
15°	11041	10178	9925
20°	10840	9688	9288
25°	10588	9158	8666
30°	10342	8618	7969
35°	10071	8071	7287
40°	9749	7481	6586
45°	9446	6897	5892
50°	9103	6258	5188
55°	8732	5603	4460
60°	8319	4909	3741
65°	7921	4112	3050
70°	7356	3272	2331
75°	6628	2381	1629
80°	5536	1462	1171
85°	4162	843	643

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9446 cd/sqm

TEST NUMBER: P1033045

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	1.8
10°-20°	363.0	4.9
20°-30°	524.1	7.1
30°-40°	593.9	8.0
40°-50°	573.5	7.7
50°-60°	476.8	6.4
60°-70°	329.1	4.4
70°-80°	166.3	2.2
80°-90°	45.0	0.6
90°-100°	45.2	0.6
100°-110°	297.7	4.0
110°-120°	568.5	7.7
120°-130°	721.7	9.7
130°-140°	772.1	10.4
140°-150°	721.9	9.7
150°-160°	582.2	7.9
160°-170°	375.5	5.1
170°-180°	129.4	1.7
0°-30°	1017.2	13.7
0°-40°	1611.2	21.7
0°-60°	2661.4	35.9
0°-90°	3201.8	43.2
90°-120°	911.4	12.3
90°-150°	3127.1	42.2
90°-180°	4214.0	56.8
0°-180°	7416.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1384	1384	1384	1384	1384	
5°	1382	1378	1365	1376	1374	131
15°	1317	1307	1281	1278	1271	371
25°	1190	1171	1128	1110	1099	549
35°	1029	995	942	906	887	643
45°	840	800	737	685	666	647
55°	636	594	525	470	450	569
65°	432	387	319	274	261	427
75°	230	191	141	117	110	243
85°	57	36	33	31	31	63
90°	3	14	22	28	31	6
95°	56	21	22	28	30	69
105°	307	313	318	327	290	321
115°	572	576	574	576	576	563
125°	805	809	807	810	811	719
135°	998	997	1001	1003	1005	769
145°	1151	1154	1154	1155	1157	719
155°	1262	1263	1260	1264	1261	582
165°	1331	1326	1326	1334	1325	376
175°	1362	1356	1357	1366	1354	130
180°	1362	1362	1362	1362	1362	

TEST NUMBER: P1033045

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1384.5	1384.5	1384.5	1384.5	1384.5
2.5°	1388.7	1384.5	1372.8	1384.5	1383.4
5°	1382.4	1378.1	1365.4	1376.0	1373.9
7.5°	1372.8	1368.6	1352.7	1360.1	1356.9
10°	1358.0	1352.7	1333.6	1337.8	1333.6
12.5°	1338.9	1332.5	1309.2	1311.3	1305.0
15°	1316.6	1307.1	1280.6	1278.5	1271.1
17.5°	1291.2	1277.4	1246.7	1241.4	1230.8
20°	1260.5	1246.7	1210.6	1202.1	1188.4
22.5°	1226.5	1210.6	1171.4	1157.6	1147.0
25°	1190.5	1171.4	1127.9	1109.9	1099.3
27.5°	1153.4	1130.1	1084.5	1063.3	1048.4
30°	1114.2	1087.7	1037.8	1011.3	994.4
32.5°	1072.8	1042.1	990.1	958.3	942.4
35°	1029.4	995.4	942.4	906.4	887.3
37.5°	983.8	948.8	890.5	851.3	832.2
40°	935.0	900.0	839.6	795.1	776.0
42.5°	888.4	851.3	787.7	742.1	721.9
45°	839.6	800.4	736.8	684.8	665.7
47.5°	789.8	749.5	683.8	629.7	608.5
50°	738.9	697.5	629.7	576.7	556.6
52.5°	686.9	646.7	576.7	522.6	501.4
55°	636.1	593.7	524.7	469.6	449.5
57.5°	586.2	541.7	473.9	417.7	402.8
60°	532.2	489.8	421.9	366.8	349.8
62.5°	483.4	438.9	368.9	319.1	306.4
65°	432.5	386.9	319.1	273.5	260.8
67.5°	379.5	336.1	272.4	232.2	217.3
70°	329.7	285.2	224.7	189.8	179.2
72.5°	276.7	237.5	181.3	152.7	143.1
75°	230.0	190.8	141.0	116.6	110.2
77.5°	181.3	147.4	104.9	88.0	85.9
80°	134.6	103.9	72.1	68.9	67.8
82.5°	94.3	66.8	51.9	49.8	48.8
85°	57.2	36.0	32.9	30.7	30.7
87.5°	24.4	15.9	14.8	13.8	14.8
90°	3.1	14.3	22.4	28.5	30.6
92.5°	15.3	13.2	21.4	27.5	27.5
95°	56.0	21.4	22.4	28.5	29.5
97.5°	107.0	129.4	22.4	27.5	28.5
100°	167.1	185.4	44.8	27.5	28.5
102.5°	234.3	246.5	258.7	29.5	29.5
105°	306.6	312.7	317.8	327.0	290.3
107.5°	372.8	375.9	383.0	388.1	392.2
110°	440.0	443.1	449.2	451.2	454.3

TEST NUMBER: P1033045

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	505.2	511.3	513.4	512.4	516.4
115°	572.5	575.5	574.5	576.5	576.5
117.5°	632.6	636.6	639.7	638.7	638.7
120°	693.7	697.8	696.7	698.8	696.7
122.5°	750.7	752.8	754.8	755.8	753.8
125°	804.7	808.8	806.7	809.8	810.8
127.5°	856.7	857.7	862.8	861.8	860.7
130°	906.6	907.6	910.6	911.7	911.7
132.5°	952.4	954.4	958.5	959.5	958.5
135°	998.2	997.2	1001.3	1003.3	1005.4
137.5°	1039.0	1039.0	1044.1	1046.1	1045.1
140°	1078.7	1080.8	1082.8	1085.9	1086.9
142.5°	1114.4	1118.4	1119.5	1121.5	1121.5
145°	1151.0	1154.1	1154.1	1155.1	1157.2
147.5°	1179.6	1185.7	1184.7	1185.7	1186.7
150°	1211.1	1215.2	1214.2	1214.2	1215.2
152.5°	1237.6	1240.7	1238.6	1240.7	1239.7
155°	1262.1	1263.1	1260.0	1264.1	1261.1
157.5°	1283.5	1283.5	1279.4	1284.5	1279.4
160°	1301.8	1298.7	1297.7	1303.8	1297.7
162.5°	1318.1	1314.0	1313.0	1319.1	1312.0
165°	1331.3	1326.2	1326.2	1334.4	1325.2
167.5°	1342.5	1337.4	1336.4	1345.6	1335.4
170°	1351.7	1345.6	1346.6	1354.8	1344.6
172.5°	1357.8	1351.7	1352.7	1360.9	1349.7
175°	1361.9	1355.8	1356.8	1366.0	1353.7
177.5°	1365.0	1357.8	1359.9	1368.0	1355.8
180°	1361.9	1361.9	1361.9	1361.9	1361.9

(END OF REPORT)