

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033048

Luminaire Tested: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033048
REPORT IS A COMBINATION OF REPORTS P1000718 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7193.0 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033048

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1033048

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27
5	68	56	48	43	62	52	45	40	43	38	34	36	32	29	28	26	24
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	10952	10625	10627
10°	10859	10290	10168
15°	10710	9873	9627
20°	10514	9397	9009
25°	10271	8883	8406
30°	10031	8360	7729
35°	9769	7828	7068
40°	9456	7257	6388
45°	9163	6690	5716
50°	8829	6071	5031
55°	8469	5436	4326
60°	8069	4762	3629
65°	7682	3988	2959
70°	7135	3175	2261
75°	6429	2310	1581
80°	5371	1418	1137
85°	4039	817	625

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9163 cd/sqm

TEST NUMBER: P1033048

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.8
10°-20°	352.1	4.9
20°-30°	508.3	7.1
30°-40°	576.1	8.0
40°-50°	556.3	7.7
50°-60°	462.5	6.4
60°-70°	319.2	4.4
70°-80°	161.3	2.2
80°-90°	43.7	0.6
90°-100°	43.8	0.6
100°-110°	288.8	4.0
110°-120°	551.4	7.7
120°-130°	700.0	9.7
130°-140°	748.8	10.4
140°-150°	700.2	9.7
150°-160°	564.7	7.9
160°-170°	364.2	5.1
170°-180°	125.5	1.7
0°-30°	986.7	13.7
0°-40°	1562.8	21.7
0°-60°	2581.6	35.9
0°-90°	3105.7	43.2
90°-120°	884.0	12.3
90°-150°	3033.0	42.2
90°-180°	4087.0	56.8
0°-180°	7193.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1343	1343	1343	1343	1343	
5°	1341	1337	1324	1335	1333	127
15°	1277	1268	1242	1240	1233	360
25°	1155	1136	1094	1077	1066	532
35°	998	966	914	879	861	624
45°	814	776	715	664	646	628
55°	617	576	509	456	436	552
65°	420	375	310	265	253	414
75°	223	185	137	113	107	235
85°	56	35	32	30	30	61
90°	3	14	22	28	30	6
95°	54	21	22	28	29	67
105°	297	303	308	317	282	311
115°	555	558	557	559	559	546
125°	780	784	782	785	786	697
135°	968	967	971	973	975	746
145°	1116	1119	1119	1120	1122	698
155°	1224	1225	1222	1226	1223	564
165°	1291	1286	1286	1294	1285	365
175°	1321	1315	1316	1325	1313	126
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1033048

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1342.9	1342.9	1342.9	1342.9	1342.9
2.5°	1347.1	1342.9	1331.6	1342.9	1341.9
5°	1340.9	1336.8	1324.4	1334.7	1332.7
7.5°	1331.6	1327.5	1312.1	1319.3	1316.2
10°	1317.2	1312.1	1293.6	1297.7	1293.6
12.5°	1298.7	1292.6	1269.9	1272.0	1265.8
15°	1277.1	1267.9	1242.2	1240.1	1232.9
17.5°	1252.4	1239.1	1209.3	1204.1	1193.8
20°	1222.6	1209.3	1174.3	1166.1	1152.7
22.5°	1189.7	1174.3	1136.3	1122.9	1112.6
25°	1154.8	1136.3	1094.1	1076.6	1066.3
27.5°	1118.8	1096.1	1051.9	1031.4	1017.0
30°	1080.7	1055.0	1006.7	981.0	964.5
32.5°	1040.6	1010.8	960.4	929.6	914.1
35°	998.5	965.6	914.1	879.2	860.7
37.5°	954.2	920.3	863.8	825.7	807.2
40°	906.9	873.0	814.4	771.2	752.7
42.5°	861.7	825.7	764.0	719.8	700.3
45°	814.4	776.4	714.7	664.3	645.8
47.5°	766.1	727.0	663.2	610.8	590.2
50°	716.7	676.6	610.8	559.4	539.8
52.5°	666.3	627.3	559.4	506.9	486.4
55°	617.0	575.8	509.0	455.5	436.0
57.5°	568.6	525.5	459.6	405.1	390.7
60°	516.2	475.1	409.3	355.8	339.3
62.5°	468.9	425.7	357.8	309.5	297.2
65°	419.5	375.3	309.5	265.3	253.0
67.5°	368.1	326.0	264.3	225.2	210.8
70°	319.8	276.6	218.0	184.1	173.8
72.5°	268.4	230.3	175.8	148.1	138.8
75°	223.1	185.1	136.8	113.1	106.9
77.5°	175.8	142.9	101.8	85.3	83.3
80°	130.6	100.8	69.9	66.8	65.8
82.5°	91.5	64.8	50.4	48.3	47.3
85°	55.5	35.0	31.9	29.8	29.8
87.5°	23.7	15.4	14.4	13.4	14.4
90°	3.0	13.8	21.7	27.7	29.6
92.5°	14.8	12.8	20.7	26.7	26.7
95°	54.3	20.7	21.7	27.7	28.7
97.5°	103.7	125.5	21.7	26.7	27.7
100°	162.0	179.8	43.5	26.7	27.7
102.5°	227.2	239.1	250.9	28.7	28.7
105°	297.4	303.3	308.2	317.1	281.6
107.5°	361.6	364.6	371.5	376.4	380.4
110°	426.8	429.8	435.7	437.7	440.6



TEST NUMBER: P1033048

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.0	495.9	497.9	496.9	500.9
115°	555.2	558.2	557.2	559.2	559.2
117.5°	613.5	617.5	620.4	619.4	619.4
120°	672.8	676.7	675.8	677.7	675.8
122.5°	728.1	730.1	732.1	733.1	731.1
125°	780.5	784.4	782.5	785.4	786.4
127.5°	830.9	831.8	836.8	835.8	834.8
130°	879.3	880.3	883.2	884.2	884.2
132.5°	923.7	925.7	929.7	930.6	929.7
135°	968.2	967.2	971.1	973.1	975.1
137.5°	1007.7	1007.7	1012.6	1014.6	1013.6
140°	1046.2	1048.2	1050.2	1053.1	1054.1
142.5°	1080.8	1084.8	1085.8	1087.7	1087.7
145°	1116.4	1119.3	1119.3	1120.3	1122.3
147.5°	1144.0	1150.0	1149.0	1150.0	1151.0
150°	1174.7	1178.6	1177.6	1177.6	1178.6
152.5°	1200.4	1203.3	1201.3	1203.3	1202.3
155°	1224.1	1225.1	1222.1	1226.0	1223.1
157.5°	1244.8	1244.8	1240.9	1245.8	1240.9
160°	1262.6	1259.6	1258.6	1264.6	1258.6
162.5°	1278.4	1274.4	1273.5	1279.4	1272.5
165°	1291.2	1286.3	1286.3	1294.2	1285.3
167.5°	1302.1	1297.2	1296.2	1305.1	1295.2
170°	1311.0	1305.1	1306.1	1314.0	1304.1
172.5°	1316.9	1311.0	1312.0	1319.9	1309.0
175°	1320.9	1315.0	1315.9	1324.8	1313.0
177.5°	1323.8	1316.9	1318.9	1326.8	1315.0
180°	1320.9	1320.9	1320.9	1320.9	1320.9

(END OF REPORT)