

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033058

Luminaire Tested: S124RDIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033058
REPORT IS A COMBINATION OF REPORTS P1000762 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D1340UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8268.0 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033058

CATALOG NUMBER: S124RDIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1033058

CATALOG NUMBER: S124RDIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	104	104	104	104	95	95	95	95	76	76	76		60	60	60		45
1	95	91	87	84	86	83	80	77	67	65	63		53	52	50		40
2	87	80	74	69	79	73	68	63	59	56	52		47	44	42		35
3	79	70	63	58	72	64	58	53	52	48	44		41	38	36		31
4	73	62	55	49	66	57	50	45	47	42	38		37	34	31		28
5	67	55	48	42	60	51	44	39	42	37	33		33	30	27		25
6	61	50	42	36	56	45	39	34	37	32	28		30	26	23		23
7	57	45	37	32	51	41	34	29	34	29	25		27	24	21		21
8	53	41	33	28	48	37	31	26	31	26	22		25	21	19		19
9	49	37	30	25	44	34	28	23	28	23	20		23	19	17		18
10	46	34	27	22	41	31	25	21	26	21	18		21	18	15		17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	10952	10625	10627
10°	10859	10290	10168
15°	10710	9873	9627
20°	10514	9397	9009
25°	10271	8883	8406
30°	10031	8360	7729
35°	9769	7828	7068
40°	9456	7257	6388
45°	9163	6690	5716
50°	8829	6071	5031
55°	8469	5436	4326
60°	8069	4762	3629
65°	7682	3988	2959
70°	7135	3175	2261
75°	6429	2310	1581
80°	5371	1418	1137
85°	4039	817	625

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9163 cd/sqm

TEST NUMBER: P1033058

CATALOG NUMBER: S124RDIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.5
10°-20°	352.1	4.3
20°-30°	508.3	6.1
30°-40°	576.1	7.0
40°-50°	556.3	6.7
50°-60°	462.5	5.6
60°-70°	319.2	3.9
70°-80°	161.3	2.0
80°-90°	44.4	0.5
90°-100°	55.4	0.7
100°-110°	364.6	4.4
110°-120°	696.3	8.4
120°-130°	883.9	10.7
130°-140°	945.6	11.4
140°-150°	884.2	10.7
150°-160°	713.1	8.6
160°-170°	459.9	5.6
170°-180°	158.5	1.9
0°-30°	986.7	11.9
0°-40°	1562.8	18.9
0°-60°	2581.6	31.2
0°-90°	3106.4	37.6
90°-120°	1116.3	13.5
90°-150°	3830.1	46.3
90°-180°	5162.0	62.4
0°-180°	8268.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1343	1343	1343	1343	1343	
5°	1341	1337	1324	1335	1333	127
15°	1277	1268	1242	1240	1233	360
25°	1155	1136	1094	1077	1066	532
35°	998	966	914	879	861	624
45°	814	776	715	664	646	628
55°	617	576	509	456	436	552
65°	420	375	310	265	253	414
75°	223	185	137	113	107	235
85°	56	35	32	30	30	61
90°	4	18	27	35	37	7
95°	69	26	27	35	36	85
105°	376	383	389	400	356	393
115°	701	705	704	706	706	690
125°	986	991	988	992	993	880
135°	1223	1221	1226	1229	1231	942
145°	1410	1414	1414	1415	1417	881
155°	1546	1547	1543	1548	1544	713
165°	1631	1624	1624	1634	1623	461
175°	1668	1661	1662	1673	1658	159
180°	1668	1668	1668	1668	1668	

TEST NUMBER: P1033058

CATALOG NUMBER: S124RDIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1342.9	1342.9	1342.9	1342.9	1342.9
2.5°	1347.1	1342.9	1331.6	1342.9	1341.9
5°	1340.9	1336.8	1324.4	1334.7	1332.7
7.5°	1331.6	1327.5	1312.1	1319.3	1316.2
10°	1317.2	1312.1	1293.6	1297.7	1293.6
12.5°	1298.7	1292.6	1269.9	1272.0	1265.8
15°	1277.1	1267.9	1242.2	1240.1	1232.9
17.5°	1252.4	1239.1	1209.3	1204.1	1193.8
20°	1222.6	1209.3	1174.3	1166.1	1152.7
22.5°	1189.7	1174.3	1136.3	1122.9	1112.6
25°	1154.8	1136.3	1094.1	1076.6	1066.3
27.5°	1118.8	1096.1	1051.9	1031.4	1017.0
30°	1080.7	1055.0	1006.7	981.0	964.5
32.5°	1040.6	1010.8	960.4	929.6	914.1
35°	998.5	965.6	914.1	879.2	860.7
37.5°	954.2	920.3	863.8	825.7	807.2
40°	906.9	873.0	814.4	771.2	752.7
42.5°	861.7	825.7	764.0	719.8	700.3
45°	814.4	776.4	714.7	664.3	645.8
47.5°	766.1	727.0	663.2	610.8	590.2
50°	716.7	676.6	610.8	559.4	539.8
52.5°	666.3	627.3	559.4	506.9	486.4
55°	617.0	575.8	509.0	455.5	436.0
57.5°	568.6	525.5	459.6	405.1	390.7
60°	516.2	475.1	409.3	355.8	339.3
62.5°	468.9	425.7	357.8	309.5	297.2
65°	419.5	375.3	309.5	265.3	253.0
67.5°	368.1	326.0	264.3	225.2	210.8
70°	319.8	276.6	218.0	184.1	173.8
72.5°	268.4	230.3	175.8	148.1	138.8
75°	223.1	185.1	136.8	113.1	106.9
77.5°	175.8	142.9	101.8	85.3	83.3
80°	130.6	100.8	69.9	66.8	65.8
82.5°	91.5	64.8	50.4	48.3	47.3
85°	55.5	35.0	31.9	29.8	29.8
87.5°	23.7	15.4	14.4	13.4	14.4
90°	3.7	17.5	27.4	34.9	37.4
92.5°	18.7	16.2	26.2	33.7	33.7
95°	68.6	26.2	27.4	34.9	36.2
97.5°	131.0	158.4	27.4	33.7	34.9
100°	204.6	227.1	54.9	33.7	34.9
102.5°	287.0	301.9	316.9	36.2	36.2
105°	375.5	383.0	389.3	400.5	355.6
107.5°	456.6	460.4	469.1	475.3	480.3
110°	539.0	542.7	550.2	552.7	556.4

TEST NUMBER: P1033058

CATALOG NUMBER: S124RDIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	618.8	626.3	628.8	627.5	632.5
115°	701.2	704.9	703.7	706.1	706.1
117.5°	774.8	779.8	783.5	782.3	782.3
120°	849.6	854.6	853.4	855.9	853.4
122.5°	919.5	922.0	924.5	925.7	923.2
125°	985.6	990.6	988.1	991.9	993.1
127.5°	1049.2	1050.5	1056.7	1055.5	1054.2
130°	1110.4	1111.6	1115.4	1116.6	1116.6
132.5°	1166.5	1169.0	1174.0	1175.3	1174.0
135°	1222.7	1221.4	1226.4	1228.9	1231.4
137.5°	1272.6	1272.6	1278.8	1281.3	1280.0
140°	1321.2	1323.7	1326.2	1330.0	1331.2
142.5°	1364.9	1369.9	1371.1	1373.6	1373.6
145°	1409.8	1413.5	1413.5	1414.8	1417.3
147.5°	1444.7	1452.2	1451.0	1452.2	1453.5
150°	1483.4	1488.4	1487.2	1487.2	1488.4
152.5°	1515.8	1519.6	1517.1	1519.6	1518.3
155°	1545.8	1547.0	1543.3	1548.3	1544.5
157.5°	1572.0	1572.0	1567.0	1573.2	1567.0
160°	1594.4	1590.7	1589.5	1596.9	1589.5
162.5°	1614.4	1609.4	1608.2	1615.7	1606.9
165°	1630.6	1624.4	1624.4	1634.4	1623.1
167.5°	1644.4	1638.1	1636.9	1648.1	1635.6
170°	1655.6	1648.1	1649.3	1659.3	1646.8
172.5°	1663.1	1655.6	1656.8	1666.8	1653.1
175°	1668.1	1660.6	1661.8	1673.0	1658.1
177.5°	1671.8	1663.1	1665.6	1675.5	1660.6
180°	1668.1	1668.1	1668.1	1668.1	1668.1

(END OF REPORT)