

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032583

Luminaire Tested: S124DIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032583
REPORT IS A COMBINATION OF REPORTS P997110 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11020.0 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032583

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032583

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15660	15660	15660
5°	15672	15209	15228
10°	15540	14787	14684
15°	15317	14285	14069
20°	15032	13742	13434
25°	14712	13168	12749
30°	14326	12548	11998
35°	13926	11912	11272
40°	13508	11229	10500
45°	13071	10544	9778
50°	12586	9879	8978
55°	12060	9104	8184
60°	11522	8254	7356
65°	10906	7376	6424
70°	10196	6318	5425
75°	9135	5093	4345
80°	7786	3683	3057
85°	6047	2050	1645

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13071 cd/sqm

TEST NUMBER: P1032583

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	1.6
10°-20°	509.9	4.6
20°-30°	750.5	6.8
30°-40°	872.4	7.9
40°-50°	872.3	7.9
50°-60°	763.0	6.9
60°-70°	566.4	5.1
70°-80°	321.4	2.9
80°-90°	96.1	0.9
90°-100°	65.3	0.6
100°-110°	430.0	3.9
110°-120°	821.2	7.5
120°-130°	1042.4	9.5
130°-140°	1115.2	10.1
140°-150°	1042.8	9.5
150°-160°	840.9	7.6
160°-170°	542.3	4.9
170°-180°	186.9	1.7
0°-30°	1441.4	13.1
0°-40°	2313.8	21.0
0°-60°	3949.1	35.8
0°-90°	4933.1	44.8
90°-120°	1316.5	11.9
90°-150°	4516.8	41.0
90°-180°	6087.0	55.2
0°-180°	11020.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1920	1920	1920	1920	1920	
5°	1919	1913	1896	1913	1910	182
15°	1826	1820	1797	1806	1802	515
25°	1654	1643	1622	1623	1617	761
35°	1423	1413	1391	1380	1373	890
45°	1162	1151	1126	1109	1105	896
55°	879	874	852	834	825	787
65°	596	588	572	557	549	589
75°	317	309	302	295	294	336
85°	83	83	80	80	78	89
90°	4	21	32	41	44	10
95°	81	31	32	41	43	100
105°	443	452	459	472	419	463
115°	827	831	830	833	833	814
125°	1162	1168	1165	1170	1171	1038
135°	1442	1440	1446	1449	1452	1111
145°	1663	1667	1667	1668	1671	1039
155°	1823	1824	1820	1826	1822	841
165°	1923	1916	1916	1927	1914	543
175°	1967	1958	1960	1973	1955	187
180°	1967	1967	1967	1967	1967	

TEST NUMBER: P1032583

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1920.4	1920.4	1920.4	1920.4	1920.4
2.5°	1926.5	1921.9	1905.0	1920.4	1918.8
5°	1918.8	1912.7	1895.7	1912.7	1909.6
7.5°	1905.0	1898.8	1880.4	1894.2	1892.7
10°	1885.0	1878.8	1858.8	1871.1	1868.1
12.5°	1858.8	1852.7	1831.1	1845.0	1840.4
15°	1826.5	1820.3	1797.3	1806.5	1801.9
17.5°	1789.6	1781.9	1760.3	1766.5	1763.4
20°	1748.0	1740.3	1717.3	1721.9	1718.8
22.5°	1703.4	1692.6	1669.6	1678.8	1672.6
25°	1654.2	1643.4	1621.8	1623.4	1617.2
27.5°	1598.8	1588.0	1568.0	1564.9	1557.2
30°	1543.4	1531.1	1511.1	1504.9	1497.2
32.5°	1484.9	1474.1	1452.6	1444.9	1437.2
35°	1423.4	1412.6	1391.0	1380.3	1372.6
37.5°	1358.7	1349.5	1326.4	1315.6	1304.9
40°	1295.6	1283.3	1260.2	1244.9	1237.2
42.5°	1227.9	1221.8	1195.6	1177.1	1172.5
45°	1161.8	1151.0	1126.4	1109.4	1104.8
47.5°	1092.5	1084.8	1061.7	1043.3	1031.0
50°	1021.7	1015.6	994.0	972.5	963.3
52.5°	952.5	944.8	921.7	903.3	890.9
55°	878.6	874.0	852.5	834.0	824.8
57.5°	809.4	804.8	783.2	764.8	755.5
60°	737.1	729.4	709.4	695.5	687.8
62.5°	666.3	660.1	638.6	626.3	618.6
65°	595.5	587.8	572.4	557.0	549.3
67.5°	523.2	517.0	501.6	486.2	484.7
70°	457.0	446.2	433.9	421.6	417.0
72.5°	386.2	375.5	366.2	357.0	352.4
75°	317.0	309.3	301.6	295.4	293.9
77.5°	249.3	246.2	238.5	237.0	232.4
80°	189.3	184.7	181.6	178.5	177.0
82.5°	130.8	129.3	129.3	127.7	126.2
85°	83.1	83.1	80.0	80.0	78.5
87.5°	40.0	38.5	36.9	36.9	36.9
90°	4.4	20.6	32.4	41.2	44.1
92.5°	22.1	19.1	30.9	39.7	39.7
95°	80.9	30.9	32.4	41.2	42.7
97.5°	154.5	186.9	32.4	39.7	41.2
100°	241.3	267.8	64.7	39.7	41.2
102.5°	338.4	356.1	373.7	42.7	42.7
105°	442.9	451.7	459.0	472.3	419.3
107.5°	538.5	542.9	553.2	560.6	566.4
110°	635.6	640.0	648.8	651.8	656.2

TEST NUMBER: P1032583

CATALOG NUMBER: S124DIW-B1195D1560UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	729.8	738.6	741.5	740.1	745.9
115°	826.9	831.3	829.8	832.7	832.7
117.5°	913.7	919.6	924.0	922.5	922.5
120°	1001.9	1007.8	1006.4	1009.3	1006.4
122.5°	1084.3	1087.3	1090.2	1091.7	1088.8
125°	1162.3	1168.2	1165.3	1169.7	1171.1
127.5°	1237.4	1238.8	1246.2	1244.7	1243.2
130°	1309.4	1310.9	1315.3	1316.8	1316.8
132.5°	1375.7	1378.6	1384.5	1386.0	1384.5
135°	1441.9	1440.4	1446.3	1449.2	1452.2
137.5°	1500.7	1500.7	1508.1	1511.0	1509.5
140°	1558.1	1561.0	1564.0	1568.4	1569.9
142.5°	1609.6	1615.5	1616.9	1619.9	1619.9
145°	1662.6	1667.0	1667.0	1668.4	1671.4
147.5°	1703.8	1712.6	1711.1	1712.6	1714.1
150°	1749.4	1755.2	1753.8	1753.8	1755.2
152.5°	1787.6	1792.0	1789.1	1792.0	1790.6
155°	1822.9	1824.4	1820.0	1825.9	1821.5
157.5°	1853.8	1853.8	1847.9	1855.3	1847.9
160°	1880.3	1875.9	1874.4	1883.2	1874.4
162.5°	1903.8	1898.0	1896.5	1905.3	1895.0
165°	1923.0	1915.6	1915.6	1927.4	1914.1
167.5°	1939.2	1931.8	1930.3	1943.6	1928.9
170°	1952.4	1943.6	1945.0	1956.8	1942.1
172.5°	1961.2	1952.4	1953.9	1965.6	1949.5
175°	1967.1	1958.3	1959.8	1973.0	1955.3
177.5°	1971.5	1961.2	1964.2	1975.9	1958.3
180°	1967.1	1967.1	1967.1	1967.1	1967.1

(END OF REPORT)