

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033076

Luminaire Tested: S124RDIW-B795D470UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033076
REPORT IS A COMBINATION OF REPORTS P1000847 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D470UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5124.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 49.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033076

CATALOG NUMBER: S124RDIW-B795D470UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1033076

CATALOG NUMBER: S124RDIW-B795D470UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	89	95	91	88	85	80	78	75	70	68	66	61	59	58
2	92	85	79	74	86	80	75	70	71	66	63	62	59	56	54	52	50
3	84	75	68	62	79	71	64	59	63	57	53	55	51	48	48	45	43
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	40	37
5	71	60	51	45	67	56	49	43	50	44	40	44	40	36	39	35	32
6	66	54	45	40	62	51	43	38	45	39	35	40	35	32	35	32	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	29	26
8	57	44	36	31	53	42	35	30	38	32	28	34	29	25	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21
10	49	37	30	25	46	35	29	24	32	26	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11389	11389	11389
5°	11390	11051	11051
10°	11293	10702	10574
15°	11138	10267	10012
20°	10934	9772	9370
25°	10681	9238	8742
30°	10432	8693	8039
35°	10159	8142	7351
40°	9834	7546	6644
45°	9528	6957	5944
50°	9183	6313	5232
55°	8807	5653	4499
60°	8391	4952	3774
65°	7990	4148	3077
70°	7420	3301	2351
75°	6689	2401	1644
80°	5585	1474	1182
85°	4199	851	650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9528 cd/sqm

TEST NUMBER: P1033076

CATALOG NUMBER: S124RDIW-B795D470UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.6
10°-20°	366.2	7.1
20°-30°	528.7	10.3
30°-40°	599.1	11.7
40°-50°	578.5	11.3
50°-60°	480.9	9.4
60°-70°	331.9	6.5
70°-80°	167.7	3.3
80°-90°	43.9	0.9
90°-100°	20.3	0.4
100°-110°	133.9	2.6
110°-120°	255.7	5.0
120°-130°	324.6	6.3
130°-140°	347.3	6.8
140°-150°	324.8	6.3
150°-160°	261.9	5.1
160°-170°	168.9	3.3
170°-180°	58.2	1.1
0°-30°	1026.2	20.0
0°-40°	1625.3	31.7
0°-60°	2684.7	52.4
0°-90°	3228.3	63.0
90°-120°	410.0	8.0
90°-150°	1406.7	27.5
90°-180°	1896.0	37.0
0°-180°	5124.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1397	1397	1397	1397	1397	
5°	1394	1390	1377	1388	1386	132
15°	1328	1318	1292	1290	1282	374
25°	1201	1182	1138	1120	1109	553
35°	1038	1004	951	914	895	649
45°	847	807	743	691	672	653
55°	642	599	529	474	453	574
65°	436	390	322	276	263	431
75°	232	192	142	118	111	245
85°	58	36	33	31	31	63
90°	1	6	10	13	14	5
95°	25	10	10	13	13	31
105°	138	141	143	147	131	144
115°	258	259	258	259	259	253
125°	362	364	363	364	365	323
135°	449	449	450	451	452	346
145°	518	519	519	520	520	324
155°	568	568	567	569	567	262
165°	599	597	597	600	596	169
175°	613	610	610	614	609	58
180°	613	613	613	613	613	

TEST NUMBER: P1033076

CATALOG NUMBER: S124RDIW-B795D470UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1400.9	1396.6	1384.8	1396.6	1395.5
5°	1394.5	1390.2	1377.4	1388.0	1385.9
7.5°	1384.8	1380.6	1364.5	1372.0	1368.8
10°	1369.9	1364.5	1345.3	1349.6	1345.3
12.5°	1350.6	1344.2	1320.7	1322.8	1316.4
15°	1328.2	1318.5	1291.8	1289.7	1282.2
17.5°	1302.5	1288.6	1257.6	1252.2	1241.5
20°	1271.5	1257.6	1221.2	1212.7	1198.8
22.5°	1237.3	1221.2	1181.7	1167.8	1157.1
25°	1200.9	1181.7	1137.8	1119.6	1108.9
27.5°	1163.5	1140.0	1094.0	1072.6	1057.6
30°	1123.9	1097.2	1046.9	1020.2	1003.1
32.5°	1082.2	1051.2	998.8	966.7	950.7
35°	1038.4	1004.1	950.7	914.3	895.1
37.5°	992.4	957.1	898.3	858.7	839.5
40°	943.2	907.9	846.9	802.0	782.8
42.5°	896.1	858.7	794.5	748.6	728.2
45°	846.9	807.4	743.2	690.8	671.6
47.5°	796.7	756.0	689.7	635.2	613.8
50°	745.4	703.6	635.2	581.7	561.4
52.5°	693.0	652.3	581.7	527.2	505.8
55°	641.6	598.8	529.3	473.7	453.4
57.5°	591.4	546.5	478.0	421.3	406.4
60°	536.8	494.1	425.6	370.0	352.9
62.5°	487.6	442.7	372.1	321.9	309.0
65°	436.3	390.3	321.9	275.9	263.1
67.5°	382.8	339.0	274.8	234.2	219.2
70°	332.6	287.7	226.7	191.4	180.7
72.5°	279.1	239.5	182.9	154.0	144.4
75°	232.1	192.5	142.2	117.6	111.2
77.5°	182.9	148.6	105.9	88.8	86.6
80°	135.8	104.8	72.7	69.5	68.4
82.5°	95.2	67.4	52.4	50.3	49.2
85°	57.7	36.4	33.2	31.0	31.0
87.5°	24.6	16.0	15.0	13.9	15.0
90°	1.4	6.4	10.1	12.8	13.7
92.5°	6.9	6.0	9.6	12.4	12.4
95°	25.2	9.6	10.1	12.8	13.3
97.5°	48.1	58.2	10.1	12.4	12.8
100°	75.1	83.4	20.2	12.4	12.8
102.5°	105.4	110.9	116.4	13.3	13.3
105°	137.9	140.7	143.0	147.1	130.6
107.5°	167.7	169.1	172.3	174.6	176.4
110°	198.0	199.3	202.1	203.0	204.4

TEST NUMBER: P1033076

CATALOG NUMBER: S124RDIW-B795D470UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	227.3	230.0	230.9	230.5	232.3
115°	257.5	258.9	258.4	259.4	259.4
117.5°	284.6	286.4	287.8	287.3	287.3
120°	312.0	313.9	313.4	314.3	313.4
122.5°	337.7	338.6	339.5	340.0	339.1
125°	362.0	363.8	362.9	364.3	364.7
127.5°	385.4	385.8	388.1	387.7	387.2
130°	407.8	408.3	409.7	410.1	410.1
132.5°	428.4	429.4	431.2	431.6	431.2
135°	449.1	448.6	450.4	451.3	452.3
137.5°	467.4	467.4	469.7	470.6	470.1
140°	485.3	486.2	487.1	488.5	488.9
142.5°	501.3	503.1	503.6	504.5	504.5
145°	517.8	519.2	519.2	519.6	520.5
147.5°	530.6	533.4	532.9	533.4	533.8
150°	544.8	546.7	546.2	546.2	546.7
152.5°	556.7	558.1	557.2	558.1	557.7
155°	567.7	568.2	566.8	568.7	567.3
157.5°	577.4	577.4	575.5	577.8	575.5
160°	585.6	584.2	583.8	586.5	583.8
162.5°	592.9	591.1	590.6	593.4	590.2
165°	598.9	596.6	596.6	600.3	596.1
167.5°	603.9	601.6	601.2	605.3	600.7
170°	608.1	605.3	605.8	609.4	604.9
172.5°	610.8	608.1	608.5	612.2	607.1
175°	612.6	609.9	610.4	614.5	609.0
177.5°	614.0	610.8	611.7	615.4	609.9
180°	612.6	612.6	612.6	612.6	612.6

(END OF REPORT)