

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033084

Luminaire Tested: S124RDIW-B795D770UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033084
REPORT IS A COMBINATION OF REPORTS P1000888 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D770UB2750-4F0-XX-W2A-F1_5000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5709.0 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033084

CATALOG NUMBER: S124RDIW-B795D770UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1033084

CATALOG NUMBER: S124RDIW-B795D770UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	52	51
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	38
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	34	31	29
6	64	52	44	38	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	23
8	55	43	35	30	51	40	33	29	35	30	26	31	26	23	26	23	20
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	10952	10625	10627
10°	10859	10290	10168
15°	10710	9873	9627
20°	10514	9397	9009
25°	10271	8883	8406
30°	10031	8360	7729
35°	9769	7828	7068
40°	9456	7257	6388
45°	9163	6690	5716
50°	8829	6071	5031
55°	8469	5436	4326
60°	8069	4762	3629
65°	7682	3988	2959
70°	7135	3175	2261
75°	6429	2310	1581
80°	5371	1418	1137
85°	4039	817	625

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9163 cd/sqm

TEST NUMBER: P1033084

CATALOG NUMBER: S124RDIW-B795D770UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.2
10°-20°	352.1	6.2
20°-30°	508.3	8.9
30°-40°	576.1	10.1
40°-50°	556.3	9.7
50°-60°	462.5	8.1
60°-70°	319.2	5.6
70°-80°	161.3	2.8
80°-90°	43.0	0.8
90°-100°	61.2	1.1
100°-110°	183.2	3.2
110°-120°	311.3	5.5
120°-130°	410.5	7.2
130°-140°	461.1	8.1
140°-150°	453.2	7.9
150°-160°	381.1	6.7
160°-170°	253.6	4.4
170°-180°	88.8	1.6
0°-30°	986.7	17.3
0°-40°	1562.8	27.4
0°-60°	2581.6	45.2
0°-90°	3105.0	54.4
90°-120°	555.7	9.7
90°-150°	1880.4	32.9
90°-180°	2604.0	45.6
0°-180°	5709.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1343	1343	1343	1343	1343	
5°	1341	1337	1324	1335	1333	127
15°	1277	1268	1242	1240	1233	360
25°	1155	1136	1094	1077	1066	532
35°	998	966	914	879	861	624
45°	814	776	715	664	646	628
55°	617	576	509	456	436	552
65°	420	375	310	265	253	414
75°	223	185	137	113	107	235
85°	56	35	32	30	30	61
90°	2	10	16	20	22	6
95°	44	50	55	57	57	47
105°	169	170	173	175	177	179
115°	316	316	315	314	314	312
125°	461	461	460	459	457	411
135°	594	599	599	597	595	460
145°	722	725	726	725	723	452
155°	827	827	827	830	827	381
165°	901	899	897	902	899	254
175°	937	933	933	938	933	89
180°	938	938	938	938	938	

TEST NUMBER: P1033084

CATALOG NUMBER: S124RDIW-B795D770UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1342.9	1342.9	1342.9	1342.9	1342.9
2.5°	1347.1	1342.9	1331.6	1342.9	1341.9
5°	1340.9	1336.8	1324.4	1334.7	1332.7
7.5°	1331.6	1327.5	1312.1	1319.3	1316.2
10°	1317.2	1312.1	1293.6	1297.7	1293.6
12.5°	1298.7	1292.6	1269.9	1272.0	1265.8
15°	1277.1	1267.9	1242.2	1240.1	1232.9
17.5°	1252.4	1239.1	1209.3	1204.1	1193.8
20°	1222.6	1209.3	1174.3	1166.1	1152.7
22.5°	1189.7	1174.3	1136.3	1122.9	1112.6
25°	1154.8	1136.3	1094.1	1076.6	1066.3
27.5°	1118.8	1096.1	1051.9	1031.4	1017.0
30°	1080.7	1055.0	1006.7	981.0	964.5
32.5°	1040.6	1010.8	960.4	929.6	914.1
35°	998.5	965.6	914.1	879.2	860.7
37.5°	954.2	920.3	863.8	825.7	807.2
40°	906.9	873.0	814.4	771.2	752.7
42.5°	861.7	825.7	764.0	719.8	700.3
45°	814.4	776.4	714.7	664.3	645.8
47.5°	766.1	727.0	663.2	610.8	590.2
50°	716.7	676.6	610.8	559.4	539.8
52.5°	666.3	627.3	559.4	506.9	486.4
55°	617.0	575.8	509.0	455.5	436.0
57.5°	568.6	525.5	459.6	405.1	390.7
60°	516.2	475.1	409.3	355.8	339.3
62.5°	468.9	425.7	357.8	309.5	297.2
65°	419.5	375.3	309.5	265.3	253.0
67.5°	368.1	326.0	264.3	225.2	210.8
70°	319.8	276.6	218.0	184.1	173.8
72.5°	268.4	230.3	175.8	148.1	138.8
75°	223.1	185.1	136.8	113.1	106.9
77.5°	175.8	142.9	101.8	85.3	83.3
80°	130.6	100.8	69.9	66.8	65.8
82.5°	91.5	64.8	50.4	48.3	47.3
85°	55.5	35.0	31.9	29.8	29.8
87.5°	23.7	15.4	14.4	13.4	14.4
90°	2.2	10.2	16.0	20.3	21.8
92.5°	18.9	28.3	31.9	34.1	34.8
95°	43.5	50.1	55.2	57.3	57.3
97.5°	69.7	75.5	81.3	84.2	84.2
100°	101.6	104.5	111.1	112.5	112.5
102.5°	135.0	135.7	141.5	143.7	144.4
105°	169.1	169.8	172.7	174.9	177.1
107.5°	204.7	205.4	206.1	209.0	208.3
110°	241.0	242.4	241.7	240.3	242.4

TEST NUMBER: P1033084

CATALOG NUMBER: S124RDIW-B795D770UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	278.7	278.7	277.3	277.3	277.3
115°	316.5	316.5	315.0	314.3	313.6
117.5°	352.0	352.0	351.3	349.1	346.9
120°	387.6	390.5	388.3	384.7	386.1
122.5°	424.6	425.3	424.6	422.4	418.8
125°	460.9	460.9	460.2	458.7	457.3
127.5°	493.6	495.7	494.3	492.8	492.1
130°	528.4	530.6	530.6	529.1	526.2
132.5°	564.0	565.4	564.7	563.2	562.5
135°	594.5	598.8	598.8	597.4	595.2
137.5°	628.6	630.7	632.2	630.0	630.7
140°	662.7	664.1	664.1	663.4	662.7
142.5°	693.9	695.3	694.6	694.6	694.6
145°	722.2	725.1	725.8	725.1	722.9
147.5°	751.2	754.9	754.1	753.4	752.7
150°	777.4	780.3	780.3	780.3	779.5
152.5°	802.0	803.5	804.2	806.4	804.2
155°	827.4	827.4	826.7	829.6	826.7
157.5°	849.2	847.8	847.8	849.9	847.8
160°	868.1	867.4	866.6	868.8	865.2
162.5°	885.5	883.3	882.6	887.0	883.3
165°	900.8	898.6	897.1	901.5	898.6
167.5°	913.1	910.2	910.2	914.5	910.2
170°	923.3	919.6	920.4	924.7	919.6
172.5°	930.5	927.6	927.6	932.7	927.6
175°	937.0	933.4	932.7	937.8	932.7
177.5°	940.0	936.3	936.3	941.4	935.6
180°	938.5	938.5	938.5	938.5	938.5

(END OF REPORT)