

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033086

Luminaire Tested: S124RDIW-B795D770UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033086
REPORT IS A COMBINATION OF REPORTS P1000891 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D770UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6353.0 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033086

CATALOG NUMBER: S124RDIW-B795D770UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1033086

CATALOG NUMBER: S124RDIW-B795D770UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41
3	82	73	65	60	75	67	61	56	58	53	49	49	45	42	40	38	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	58	50	44	64	54	46	41	46	41	36	39	35	32	32	29	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	51	40	33	28	34	29	25	30	25	22	25	22	19
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11389	11389	11389
5°	11390	11051	11051
10°	11293	10702	10574
15°	11138	10267	10012
20°	10934	9772	9370
25°	10681	9238	8742
30°	10432	8693	8039
35°	10159	8142	7351
40°	9834	7546	6644
45°	9528	6957	5944
50°	9183	6313	5232
55°	8807	5653	4499
60°	8391	4952	3774
65°	7990	4148	3077
70°	7420	3301	2351
75°	6689	2401	1644
80°	5585	1474	1182
85°	4199	851	650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9528 cd/sqm

TEST NUMBER: P1033086

CATALOG NUMBER: S124RDIW-B795D770UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.1
10°-20°	366.2	5.8
20°-30°	528.7	8.3
30°-40°	599.1	9.4
40°-50°	578.5	9.1
50°-60°	480.9	7.6
60°-70°	331.9	5.2
70°-80°	167.7	2.6
80°-90°	44.7	0.7
90°-100°	33.5	0.5
100°-110°	220.7	3.5
110°-120°	421.4	6.6
120°-130°	535.0	8.4
130°-140°	572.3	9.0
140°-150°	535.2	8.4
150°-160°	431.6	6.8
160°-170°	278.3	4.4
170°-180°	95.9	1.5
0°-30°	1026.2	16.2
0°-40°	1625.3	25.6
0°-60°	2684.7	42.3
0°-90°	3229.1	50.8
90°-120°	675.6	10.6
90°-150°	2318.1	36.5
90°-180°	3124.0	49.2
0°-180°	6353.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1397	1397	1397	1397	1397	
5°	1394	1390	1377	1388	1386	132
15°	1328	1318	1292	1290	1282	374
25°	1201	1182	1138	1120	1109	553
35°	1038	1004	951	914	895	649
45°	847	807	743	691	672	653
55°	642	599	529	474	453	574
65°	436	390	322	276	263	431
75°	232	192	142	118	111	245
85°	58	36	33	31	31	63
90°	2	11	17	21	23	6
95°	42	16	17	21	22	51
105°	227	232	236	242	215	238
115°	424	427	426	427	427	418
125°	596	600	598	600	601	533
135°	740	739	742	744	745	570
145°	853	856	856	856	858	533
155°	936	936	934	937	935	431
165°	987	983	983	989	982	279
175°	1010	1005	1006	1013	1004	96
180°	1010	1010	1010	1010	1010	

TEST NUMBER: P1033086

CATALOG NUMBER: S124RDIW-B795D770UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1400.9	1396.6	1384.8	1396.6	1395.5
5°	1394.5	1390.2	1377.4	1388.0	1385.9
7.5°	1384.8	1380.6	1364.5	1372.0	1368.8
10°	1369.9	1364.5	1345.3	1349.6	1345.3
12.5°	1350.6	1344.2	1320.7	1322.8	1316.4
15°	1328.2	1318.5	1291.8	1289.7	1282.2
17.5°	1302.5	1288.6	1257.6	1252.2	1241.5
20°	1271.5	1257.6	1221.2	1212.7	1198.8
22.5°	1237.3	1221.2	1181.7	1167.8	1157.1
25°	1200.9	1181.7	1137.8	1119.6	1108.9
27.5°	1163.5	1140.0	1094.0	1072.6	1057.6
30°	1123.9	1097.2	1046.9	1020.2	1003.1
32.5°	1082.2	1051.2	998.8	966.7	950.7
35°	1038.4	1004.1	950.7	914.3	895.1
37.5°	992.4	957.1	898.3	858.7	839.5
40°	943.2	907.9	846.9	802.0	782.8
42.5°	896.1	858.7	794.5	748.6	728.2
45°	846.9	807.4	743.2	690.8	671.6
47.5°	796.7	756.0	689.7	635.2	613.8
50°	745.4	703.6	635.2	581.7	561.4
52.5°	693.0	652.3	581.7	527.2	505.8
55°	641.6	598.8	529.3	473.7	453.4
57.5°	591.4	546.5	478.0	421.3	406.4
60°	536.8	494.1	425.6	370.0	352.9
62.5°	487.6	442.7	372.1	321.9	309.0
65°	436.3	390.3	321.9	275.9	263.1
67.5°	382.8	339.0	274.8	234.2	219.2
70°	332.6	287.7	226.7	191.4	180.7
72.5°	279.1	239.5	182.9	154.0	144.4
75°	232.1	192.5	142.2	117.6	111.2
77.5°	182.9	148.6	105.9	88.8	86.6
80°	135.8	104.8	72.7	69.5	68.4
82.5°	95.2	67.4	52.4	50.3	49.2
85°	57.7	36.4	33.2	31.0	31.0
87.5°	24.6	16.0	15.0	13.9	15.0
90°	2.3	10.6	16.6	21.1	22.7
92.5°	11.3	9.8	15.9	20.4	20.4
95°	41.5	15.9	16.6	21.1	21.9
97.5°	79.3	95.9	16.6	20.4	21.1
100°	123.8	137.4	33.2	20.4	21.1
102.5°	173.7	182.7	191.8	21.9	21.9
105°	227.3	231.8	235.6	242.4	215.2
107.5°	276.4	278.6	283.9	287.7	290.7
110°	326.2	328.5	333.0	334.5	336.8

TEST NUMBER: P1033086

CATALOG NUMBER: S124RDIW-B795D770UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	374.5	379.1	380.6	379.8	382.8
115°	424.4	426.6	425.9	427.4	427.4
117.5°	468.9	471.9	474.2	473.4	473.4
120°	514.2	517.2	516.5	518.0	516.5
122.5°	556.5	558.0	559.5	560.3	558.8
125°	596.5	599.5	598.0	600.3	601.1
127.5°	635.0	635.8	639.6	638.8	638.1
130°	672.0	672.8	675.0	675.8	675.8
132.5°	706.0	707.5	710.5	711.3	710.5
135°	740.0	739.2	742.3	743.8	745.3
137.5°	770.2	770.2	774.0	775.5	774.7
140°	799.6	801.1	802.7	804.9	805.7
142.5°	826.1	829.1	829.8	831.4	831.4
145°	853.3	855.5	855.5	856.3	857.8
147.5°	874.4	878.9	878.2	878.9	879.7
150°	897.8	900.8	900.1	900.1	900.8
152.5°	917.4	919.7	918.2	919.7	918.9
155°	935.6	936.3	934.0	937.1	934.8
157.5°	951.4	951.4	948.4	952.2	948.4
160°	965.0	962.7	962.0	966.5	962.0
162.5°	977.1	974.1	973.3	977.8	972.6
165°	986.9	983.1	983.1	989.2	982.4
167.5°	995.2	991.4	990.7	997.5	989.9
170°	1002.0	997.5	998.2	1004.3	996.7
172.5°	1006.5	1002.0	1002.8	1008.8	1000.5
175°	1009.6	1005.0	1005.8	1012.6	1003.5
177.5°	1011.8	1006.5	1008.0	1014.1	1005.0
180°	1009.6	1009.6	1009.6	1009.6	1009.6

(END OF REPORT)