

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033094

Luminaire Tested: S124DIW-B1020D1050UB27-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033094
REPORT IS A COMBINATION OF REPORTS P996626 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D1050UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8021.0 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033094

CATALOG NUMBER: S124DIW-B1020D1050UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033094

CATALOG NUMBER: S124DIW-B1020D1050UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	49	46	43	41	39	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	39	32	28	35	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13864	13864	13864
5°	13876	13466	13482
10°	13758	13091	13000
15°	13561	12648	12456
20°	13310	12167	11894
25°	13026	11658	11288
30°	12684	11109	10623
35°	12329	10547	9980
40°	11960	9942	9296
45°	11573	9336	8657
50°	11144	8747	7948
55°	10678	8061	7246
60°	10201	7308	6513
65°	9655	6530	5688
70°	9027	5595	4803
75°	8086	4509	3847
80°	6893	3261	2707
85°	5356	1814	1457

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11573 cd/sqm

TEST NUMBER: P1033094

CATALOG NUMBER: S124DIW-B1020D1050UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.3	2.0
10°-20°	451.5	5.6
20°-30°	664.5	8.3
30°-40°	772.4	9.6
40°-50°	772.3	9.6
50°-60°	675.5	8.4
60°-70°	501.5	6.3
70°-80°	284.5	3.5
80°-90°	84.3	1.1
90°-100°	85.9	1.1
100°-110°	257.1	3.2
110°-120°	436.8	5.4
120°-130°	576.1	7.2
130°-140°	647.0	8.1
140°-150°	635.9	7.9
150°-160°	534.9	6.7
160°-170°	355.9	4.4
170°-180°	124.6	1.6
0°-30°	1276.2	15.9
0°-40°	2048.6	25.5
0°-60°	3496.5	43.6
0°-90°	4366.8	54.4
90°-120°	779.8	9.7
90°-150°	2638.8	32.9
90°-180°	3654.0	45.6
0°-180°	8021.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1699	1693	1678	1693	1691	161
15°	1617	1612	1591	1599	1595	456
25°	1465	1455	1436	1437	1432	674
35°	1260	1251	1232	1222	1215	788
45°	1029	1019	997	982	978	793
55°	778	774	755	738	730	697
65°	527	520	507	493	486	522
75°	281	274	267	262	260	298
85°	74	74	71	71	70	79
90°	3	14	22	28	31	9
95°	61	70	77	80	80	66
105°	237	238	242	246	248	252
115°	444	444	442	441	440	438
125°	647	647	646	644	642	577
135°	834	840	840	838	835	645
145°	1014	1018	1019	1018	1014	634
155°	1161	1161	1160	1164	1160	534
165°	1264	1261	1259	1265	1261	356
175°	1315	1310	1309	1316	1309	125
180°	1317	1317	1317	1317	1317	

TEST NUMBER: P1033094

CATALOG NUMBER: S124DIW-B1020D1050UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1705.7	1701.6	1686.6	1700.2	1698.9
5°	1698.9	1693.4	1678.4	1693.4	1690.7
7.5°	1686.6	1681.2	1664.8	1677.1	1675.7
10°	1668.9	1663.5	1645.7	1656.6	1653.9
12.5°	1645.7	1640.3	1621.2	1633.5	1629.4
15°	1617.1	1611.7	1591.3	1599.4	1595.3
17.5°	1584.4	1577.6	1558.6	1564.0	1561.3
20°	1547.7	1540.8	1520.4	1524.5	1521.8
22.5°	1508.1	1498.6	1478.2	1486.3	1480.9
25°	1464.6	1455.0	1435.9	1437.3	1431.9
27.5°	1415.5	1406.0	1388.3	1385.5	1378.7
30°	1366.5	1355.6	1337.8	1332.4	1325.6
32.5°	1314.7	1305.2	1286.1	1279.3	1272.5
35°	1260.2	1250.7	1231.6	1222.0	1215.2
37.5°	1203.0	1194.8	1174.4	1164.8	1155.3
40°	1147.1	1136.2	1115.8	1102.2	1095.3
42.5°	1087.2	1081.7	1058.6	1042.2	1038.1
45°	1028.6	1019.1	997.3	982.3	978.2
47.5°	967.3	960.5	940.0	923.7	912.8
50°	904.6	899.2	880.1	861.0	852.8
52.5°	843.3	836.5	816.1	799.7	788.8
55°	777.9	773.8	754.8	738.4	730.2
57.5°	716.6	712.5	693.4	677.1	668.9
60°	652.6	645.8	628.1	615.8	609.0
62.5°	589.9	584.5	565.4	554.5	547.7
65°	527.2	520.4	506.8	493.2	486.4
67.5°	463.2	457.8	444.1	430.5	429.1
70°	404.6	395.1	384.2	373.3	369.2
72.5°	342.0	332.4	324.2	316.1	312.0
75°	280.6	273.8	267.0	261.6	260.2
77.5°	220.7	218.0	211.2	209.8	205.7
80°	167.6	163.5	160.8	158.0	156.7
82.5°	115.8	114.4	114.4	113.1	111.7
85°	73.6	73.6	70.8	70.8	69.5
87.5°	35.4	34.1	32.7	32.7	32.7
90°	3.1	14.3	22.4	28.5	30.6
92.5°	26.5	39.7	44.8	47.9	48.9
95°	61.1	70.3	77.4	80.5	80.5
97.5°	97.8	105.9	114.1	118.2	118.2
100°	142.6	146.7	155.8	157.9	157.9
102.5°	189.5	190.5	198.6	201.7	202.7
105°	237.3	238.3	242.4	245.5	248.5
107.5°	287.2	288.3	289.3	293.3	292.3
110°	338.2	340.2	339.2	337.1	340.2



TEST NUMBER: P1033094

CATALOG NUMBER: S124DIW-B1020D1050UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	391.1	391.1	389.1	389.1	389.1
115°	444.1	444.1	442.1	441.0	440.0
117.5°	494.0	494.0	493.0	489.9	486.9
120°	543.9	548.0	544.9	539.8	541.9
122.5°	595.9	596.9	595.9	592.8	587.7
125°	646.8	646.8	645.8	643.7	641.7
127.5°	692.6	695.7	693.6	691.6	690.6
130°	741.5	744.6	744.6	742.5	738.5
132.5°	791.4	793.5	792.4	790.4	789.4
135°	834.2	840.3	840.3	838.3	835.2
137.5°	882.1	885.1	887.2	884.1	885.1
140°	929.9	932.0	932.0	931.0	929.9
142.5°	973.7	975.8	974.8	974.8	974.8
145°	1013.5	1017.5	1018.6	1017.5	1014.5
147.5°	1054.2	1059.3	1058.3	1057.3	1056.2
150°	1090.9	1095.0	1095.0	1095.0	1093.9
152.5°	1125.5	1127.5	1128.6	1131.6	1128.6
155°	1161.2	1161.2	1160.1	1164.2	1160.1
157.5°	1191.7	1189.7	1189.7	1192.7	1189.7
160°	1218.2	1217.2	1216.2	1219.2	1214.1
162.5°	1242.6	1239.6	1238.6	1244.7	1239.6
165°	1264.0	1261.0	1258.9	1265.1	1261.0
167.5°	1281.3	1277.3	1277.3	1283.4	1277.3
170°	1295.6	1290.5	1291.5	1297.6	1290.5
172.5°	1305.8	1301.7	1301.7	1308.8	1301.7
175°	1315.0	1309.9	1308.8	1316.0	1308.8
177.5°	1319.0	1313.9	1313.9	1321.1	1312.9
180°	1317.0	1317.0	1317.0	1317.0	1317.0

(END OF REPORT)