

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033112

Luminaire Tested: S124DIW-B1020D1050UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033112
REPORT IS A COMBINATION OF REPORTS P996674 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D1050UB40-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8045.0 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033112

CATALOG NUMBER: S124DIW-B1020D1050UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033112

CATALOG NUMBER: S124DIW-B1020D1050UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	67	61	56	58	53	49	49	46	43	41	39	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	40	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	39	32	28	35	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13906	13906	13906
5°	13917	13506	13522
10°	13800	13130	13039
15°	13602	12685	12494
20°	13349	12203	11929
25°	13064	11693	11321
30°	12721	11142	10654
35°	12365	10579	10010
40°	11995	9972	9324
45°	11608	9363	8683
50°	11177	8773	7973
55°	10710	8084	7267
60°	10231	7329	6533
65°	9684	6550	5705
70°	9053	5611	4818
75°	8112	4522	3859
80°	6914	3269	2714
85°	5370	1822	1461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11608 cd/sqm

TEST NUMBER: P1033112

CATALOG NUMBER: S124DIW-B1020D1050UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.7	2.0
10°-20°	452.8	5.6
20°-30°	666.4	8.3
30°-40°	774.7	9.6
40°-50°	774.6	9.6
50°-60°	677.5	8.4
60°-70°	503.0	6.3
70°-80°	285.4	3.5
80°-90°	84.6	1.1
90°-100°	86.1	1.1
100°-110°	257.9	3.2
110°-120°	438.1	5.4
120°-130°	577.8	7.2
130°-140°	649.0	8.1
140°-150°	637.9	7.9
150°-160°	536.5	6.7
160°-170°	356.9	4.4
170°-180°	125.0	1.6
0°-30°	1280.0	15.9
0°-40°	2054.7	25.5
0°-60°	3506.8	43.6
0°-90°	4379.8	54.4
90°-120°	782.1	9.7
90°-150°	2646.7	32.9
90°-180°	3665.0	45.6
0°-180°	8045.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1704	1698	1683	1698	1696	162
15°	1622	1616	1596	1604	1600	457
25°	1469	1459	1440	1442	1436	676
35°	1264	1254	1235	1226	1219	790
45°	1032	1022	1000	985	981	795
55°	780	776	757	741	732	699
65°	529	522	508	495	488	523
75°	282	275	268	262	261	299
85°	74	74	71	71	70	79
90°	3	14	22	29	31	9
95°	61	70	78	81	81	66
105°	238	239	243	246	249	252
115°	445	445	443	442	441	439
125°	649	649	648	646	644	578
135°	837	843	843	841	838	647
145°	1016	1021	1022	1021	1018	636
155°	1165	1165	1164	1168	1164	536
165°	1268	1265	1263	1269	1265	357
175°	1319	1314	1313	1320	1313	125
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1033112

CATALOG NUMBER: S124DIW-B1020D1050UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1705.3	1705.3	1705.3	1705.3	1705.3
2.5°	1710.8	1706.7	1691.6	1705.3	1703.9
5°	1703.9	1698.5	1683.4	1698.5	1695.7
7.5°	1691.6	1686.2	1669.8	1682.1	1680.7
10°	1673.9	1668.4	1650.6	1661.6	1658.8
12.5°	1650.6	1645.2	1626.1	1638.4	1634.3
15°	1622.0	1616.5	1596.0	1604.2	1600.1
17.5°	1589.2	1582.3	1563.2	1568.7	1565.9
20°	1552.3	1545.4	1524.9	1529.0	1526.3
22.5°	1512.6	1503.1	1482.6	1490.8	1485.3
25°	1468.9	1459.3	1440.2	1441.6	1436.1
27.5°	1419.7	1410.2	1392.4	1389.7	1382.8
30°	1370.5	1359.6	1341.8	1336.4	1329.5
32.5°	1318.6	1309.0	1289.9	1283.1	1276.2
35°	1263.9	1254.4	1235.3	1225.7	1218.9
37.5°	1206.6	1198.4	1177.9	1168.3	1158.7
40°	1150.5	1139.6	1119.1	1105.4	1098.6
42.5°	1090.4	1084.9	1061.7	1045.3	1041.2
45°	1031.7	1022.1	1000.2	985.2	981.1
47.5°	970.2	963.3	942.8	926.4	915.5
50°	907.3	901.8	882.7	863.6	855.4
52.5°	845.8	839.0	818.5	802.1	791.2
55°	780.2	776.1	757.0	740.6	732.4
57.5°	718.7	714.6	695.5	679.1	670.9
60°	654.5	647.7	629.9	617.6	610.8
62.5°	591.7	586.2	567.1	556.1	549.3
65°	528.8	522.0	508.3	494.6	487.8
67.5°	464.6	459.1	445.5	431.8	430.4
70°	405.8	396.3	385.3	374.4	370.3
72.5°	343.0	333.4	325.2	317.0	312.9
75°	281.5	274.7	267.8	262.4	261.0
77.5°	221.4	218.6	211.8	210.4	206.3
80°	168.1	164.0	161.2	158.5	157.1
82.5°	116.1	114.8	114.8	113.4	112.0
85°	73.8	73.8	71.1	71.1	69.7
87.5°	35.5	34.2	32.8	32.8	32.8
90°	3.1	14.3	22.5	28.6	30.6
92.5°	26.6	39.8	45.0	48.0	49.0
95°	61.3	70.5	77.6	80.7	80.7
97.5°	98.1	106.2	114.4	118.5	118.5
100°	143.0	147.1	156.3	158.4	158.4
102.5°	190.0	191.0	199.2	202.3	203.3
105°	238.0	239.1	243.1	246.2	249.3
107.5°	288.1	289.1	290.1	294.2	293.2
110°	339.2	341.2	340.2	338.2	341.2

TEST NUMBER: P1033112

CATALOG NUMBER: S124DIW-B1020D1050UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	392.3	392.3	390.3	390.3	390.3
115°	445.4	445.4	443.4	442.4	441.3
117.5°	495.5	495.5	494.5	491.4	488.3
120°	545.5	549.6	546.6	541.5	543.5
122.5°	597.6	598.7	597.6	594.6	589.5
125°	648.7	648.7	647.7	645.7	643.6
127.5°	694.7	697.8	695.7	693.7	692.7
130°	743.7	746.8	746.8	744.8	740.7
132.5°	793.8	795.8	794.8	792.8	791.8
135°	836.7	842.8	842.8	840.8	837.7
137.5°	884.7	887.8	889.8	886.8	887.8
140°	932.7	934.8	934.8	933.8	932.7
142.5°	976.7	978.7	977.7	977.7	977.7
145°	1016.5	1020.6	1021.6	1020.6	1017.5
147.5°	1057.4	1062.5	1061.5	1060.4	1059.4
150°	1094.2	1098.2	1098.2	1098.2	1097.2
152.5°	1128.9	1130.9	1132.0	1135.0	1132.0
155°	1164.7	1164.7	1163.6	1167.7	1163.6
157.5°	1195.3	1193.3	1193.3	1196.3	1193.3
160°	1221.9	1220.8	1219.8	1222.9	1217.8
162.5°	1246.4	1243.3	1242.3	1248.4	1243.3
165°	1267.8	1264.8	1262.7	1268.9	1264.8
167.5°	1285.2	1281.1	1281.1	1287.2	1281.1
170°	1299.5	1294.4	1295.4	1301.5	1294.4
172.5°	1309.7	1305.6	1305.6	1312.8	1305.6
175°	1318.9	1313.8	1312.8	1319.9	1312.8
177.5°	1323.0	1317.9	1317.9	1325.0	1316.9
180°	1321.0	1321.0	1321.0	1321.0	1321.0

(END OF REPORT)