

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033149

Luminaire Tested: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033149
REPORT IS A COMBINATION OF REPORTS P996751 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D1560UB27-4F0-XX-W2A-A
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10818.1 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 99
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	42
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35
3	80	71	64	58	73	65	59	54	54	49	46	44	41	38	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23
6	62	50	42	37	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	28	49	38	31	27	32	27	23	26	22	20	21	18	16
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13410	13410	13410	13410
5°	13376	15385	13455	11560
10°	13277	17950	13377	10142
15°	13117	20692	13209	9075
20°	12948	22438	13041	8136
25°	12699	22181	12820	7444
30°	12457	18333	12609	7087
35°	12117	13662	12250	6870
40°	11720	10291	11834	6765
45°	11114	8260	11252	6620
50°	10390	6959	10541	6553
55°	9539	6057	9688	6476
60°	8712	5334	8967	6368
65°	7935	4589	8010	6102
70°	7021	3776	7175	5619
75°	6127	2901	6086	4774
80°	4820	1907	4763	3624
85°	3173	857	2976	2113

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 17340 cd/sqm

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	1.5
10°-20°	494.0	4.6
20°-30°	784.8	7.3
30°-40°	872.1	8.1
40°-50°	793.0	7.3
50°-60°	648.1	6.0
60°-70°	462.6	4.3
70°-80°	254.6	2.4
80°-90°	73.0	0.7
90°-100°	67.3	0.6
100°-110°	443.4	4.1
110°-120°	846.6	7.8
120°-130°	1074.8	9.9
130°-140°	1149.8	10.6
140°-150°	1075.1	9.9
150°-160°	867.0	8.0
160°-170°	559.1	5.2
170°-180°	192.7	1.8
0°-30°	1438.9	13.3
0°-40°	2310.9	21.4
0°-60°	3752.1	34.7
0°-90°	4542.2	42.0
90°-120°	1357.3	12.5
90°-150°	4657.0	43.0
90°-180°	6276.0	58.0
0°-180°	10818.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1638	1929	1647	1450	1638	155
15°	1564	2650	1575	1162	1564	441
25°	1428	2814	1442	944	1428	658
35°	1238	1664	1252	837	1238	774
45°	988	933	1000	748	988	762
55°	695	610	706	653	695	625
65°	433	392	437	522	433	428
75°	213	196	211	323	213	223
85°	44	41	41	101	44	51
90°	5	46	5	46	5	7
95°	83	44	83	44	83	103
105°	457	432	457	432	457	478
115°	852	859	852	859	852	839
125°	1198	1208	1198	1208	1198	1070
135°	1487	1497	1487	1497	1487	1145
145°	1714	1723	1714	1723	1714	1071
155°	1880	1878	1880	1878	1880	867
165°	1983	1974	1983	1974	1983	560
175°	2028	2016	2028	2016	2028	193
180°	2028	2028	2028	2028	2028	

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1644.5	1660.9	1667.7	1673.2	1690.9	1696.3	1697.7	1705.9	1712.7	1714.0	1714.0
5°	1637.7	1663.6	1684.1	1703.1	1731.7	1744.0	1759.0	1775.3	1797.1	1810.8	1817.6
7.5°	1626.8	1665.0	1696.3	1729.0	1768.5	1793.1	1806.7	1850.3	1880.3	1904.8	1934.8
10°	1610.5	1659.5	1704.5	1752.2	1808.0	1838.0	1868.0	1921.1	1963.4	2011.1	2049.2
12.5°	1586.0	1650.0	1704.5	1771.3	1840.7	1876.2	1911.6	2004.2	2053.3	2095.5	2163.7
15°	1564.2	1628.2	1705.9	1774.0	1859.8	1913.0	1964.7	2024.7	2102.3	2193.6	2259.0
17.5°	1539.6	1620.0	1692.2	1787.6	1883.0	1933.4	1975.6	2068.3	2177.3	2267.2	2327.2
20°	1505.6	1587.3	1682.7	1783.5	1896.6	1936.1	1992.0	2116.0	2214.1	2302.6	2400.7
22.5°	1466.1	1561.4	1662.3	1759.0	1876.2	1959.3	2020.6	2129.6	2248.1	2350.3	2460.7
25°	1427.9	1531.5	1620.0	1752.2	1876.2	1932.0	2001.5	2131.0	2260.4	2384.4	2497.5
27.5°	1387.0	1483.8	1603.7	1708.6	1848.9	1910.2	1985.2	2126.9	2264.5	2388.5	2509.7
30°	1342.1	1445.6	1545.1	1669.1	1805.3	1884.3	1953.8	2107.8	2248.1	2377.6	2490.7
32.5°	1291.7	1389.8	1496.0	1613.2	1756.3	1836.7	1923.9	2081.9	2231.8	2343.5	2430.7
35°	1238.5	1338.0	1430.6	1550.5	1697.7	1778.1	1862.5	2036.9	2185.5	2276.7	2327.2
37.5°	1179.9	1273.9	1365.2	1483.8	1630.9	1716.8	1802.6	1971.5	2111.9	2188.2	2174.6
40°	1124.1	1208.5	1293.0	1404.7	1558.7	1650.0	1724.9	1895.2	2017.9	2050.6	2005.6
42.5°	1060.0	1132.2	1214.0	1328.4	1478.3	1564.2	1658.2	1813.5	1904.8	1891.2	1814.9
45°	987.8	1051.9	1133.6	1241.2	1393.8	1482.4	1561.4	1708.6	1775.3	1741.3	1602.3
47.5°	918.3	981.0	1047.8	1155.4	1303.9	1378.9	1459.2	1591.4	1629.6	1557.3	1418.4
50°	843.4	895.2	964.7	1066.8	1205.8	1284.8	1351.6	1457.9	1471.5	1382.9	1238.5
52.5°	771.2	814.8	881.5	982.4	1111.8	1174.5	1239.9	1333.9	1323.0	1231.7	1092.7
55°	694.9	735.8	797.1	889.7	1004.2	1064.1	1120.0	1203.1	1179.9	1085.9	964.7
57.5°	630.8	659.5	719.4	805.2	899.3	964.7	1012.3	1077.7	1042.3	948.3	835.2
60°	557.3	592.7	643.1	712.6	805.2	848.8	891.1	934.7	910.2	820.2	719.4
62.5°	490.5	517.8	561.4	628.1	700.3	739.8	784.8	812.1	787.5	704.4	619.9
65°	433.3	455.1	489.1	543.6	613.1	645.8	671.7	697.6	677.2	599.5	538.2
67.5°	370.6	389.7	418.3	461.9	520.5	543.6	568.2	585.9	562.7	510.9	451.0
70°	314.7	328.4	355.6	388.3	429.2	451.0	471.4	489.1	468.7	425.1	380.1
72.5°	257.5	268.4	292.9	316.1	352.9	367.9	382.9	396.5	389.7	348.8	312.0
75°	212.6	216.6	233.0	252.1	275.2	291.6	302.5	310.7	305.2	272.5	249.3
77.5°	160.8	166.2	178.5	193.5	213.9	223.5	230.3	238.4	231.6	205.7	189.4
80°	117.2	118.5	125.4	139.0	152.6	154.0	160.8	171.7	167.6	149.9	137.6
82.5°	74.9	79.0	81.8	89.9	99.5	102.2	106.3	109.0	107.6	96.7	92.7
85°	43.6	43.6	46.3	51.8	54.5	58.6	60.0	61.3	64.0	57.2	53.1
87.5°	19.1	20.4	20.4	21.8	24.5	24.5	25.9	27.3	28.6	27.3	23.2
90°	4.6	8.3	12.0	15.7	19.4	21.2	22.6	25.3	28.0	30.7	33.4
92.5°	22.8	22.1	21.4	20.7	20.0	19.7	21.1	23.8	26.5	29.2	31.9
95°	83.4	72.0	60.5	49.1	37.6	31.9	32.1	32.4	32.7	33.1	33.4
97.5°	159.3	166.7	174.1	181.6	189.0	192.7	175.0	139.6	104.2	68.8	33.4
100°	248.8	254.9	260.9	267.0	273.1	276.1	252.8	206.3	159.8	113.2	66.7
102.5°	348.9	352.9	357.0	361.0	365.1	367.1	369.1	373.2	377.2	381.3	385.3
105°	456.6	458.6	460.6	462.7	464.7	465.7	466.5	468.2	469.9	471.6	473.3
107.5°	555.2	556.2	557.2	558.3	559.3	559.8	561.0	563.3	565.7	568.0	570.4
110°	655.3	656.3	657.3	658.4	659.4	659.9	660.9	662.9	665.0	667.0	669.0

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	752.4	754.4	756.4	758.5	760.5	761.5	761.8	762.5	763.2	763.8	764.5
115°	852.5	853.5	854.5	855.6	856.6	857.1	856.9	856.6	856.3	855.9	855.6
117.5°	942.0	943.4	944.7	946.1	947.4	948.1	948.6	949.6	950.6	951.6	952.6
120°	1033.0	1034.4	1035.7	1037.1	1038.4	1039.1	1038.9	1038.6	1038.3	1037.9	1037.6
122.5°	1118.0	1118.7	1119.3	1120.0	1120.7	1121.0	1121.3	1122.0	1122.7	1123.4	1124.1
125°	1198.4	1199.8	1201.1	1202.5	1203.8	1204.5	1204.2	1203.5	1202.8	1202.1	1201.4
127.5°	1275.7	1276.1	1276.4	1276.8	1277.1	1277.3	1278.1	1279.8	1281.5	1283.1	1284.8
130°	1350.1	1350.4	1350.8	1351.1	1351.4	1351.6	1352.1	1353.1	1354.1	1355.1	1356.1
132.5°	1418.3	1419.0	1419.7	1420.4	1421.1	1421.4	1422.1	1423.4	1424.7	1426.1	1427.4
135°	1486.6	1486.3	1485.9	1485.6	1485.3	1485.1	1485.8	1487.1	1488.5	1489.8	1491.2
137.5°	1547.3	1547.3	1547.3	1547.3	1547.3	1547.3	1548.1	1549.8	1551.5	1553.2	1554.9
140°	1606.4	1607.1	1607.8	1608.5	1609.2	1609.5	1609.8	1610.5	1611.2	1611.8	1612.5
142.5°	1659.5	1660.9	1662.2	1663.6	1664.9	1665.6	1665.8	1666.1	1666.4	1666.8	1667.1
145°	1714.1	1715.1	1716.1	1717.2	1718.2	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7
147.5°	1756.6	1758.6	1760.6	1762.7	1764.7	1765.7	1765.5	1765.2	1764.9	1764.5	1764.2
150°	1803.6	1805.0	1806.3	1807.7	1809.0	1809.7	1809.5	1809.2	1808.9	1808.5	1808.2
152.5°	1843.1	1844.1	1845.1	1846.1	1847.1	1847.6	1847.3	1846.6	1845.9	1845.3	1844.6
155°	1879.5	1879.8	1880.2	1880.5	1880.8	1881.0	1880.5	1879.5	1878.5	1877.5	1876.5
157.5°	1911.3	1911.3	1911.3	1911.3	1911.3	1911.3	1910.6	1909.3	1908.0	1906.6	1905.3
160°	1938.7	1937.7	1936.7	1935.6	1934.6	1934.1	1933.9	1933.6	1933.3	1932.9	1932.6
162.5°	1962.9	1961.6	1960.2	1958.9	1957.6	1956.9	1956.7	1956.4	1956.0	1955.7	1955.3
165°	1982.6	1980.9	1979.3	1977.6	1975.9	1975.1	1975.1	1975.1	1975.1	1975.1	1975.1
167.5°	1999.3	1997.6	1995.9	1994.2	1992.5	1991.7	1991.5	1991.2	1990.9	1990.5	1990.2
170°	2013.0	2011.0	2009.0	2006.9	2004.9	2003.9	2004.1	2004.4	2004.7	2005.1	2005.4
172.5°	2022.1	2020.1	2018.1	2016.0	2014.0	2013.0	2013.2	2013.5	2013.8	2014.2	2014.5
175°	2028.2	2026.2	2024.1	2022.1	2020.0	2019.0	2019.2	2019.5	2019.9	2020.2	2020.6
177.5°	2032.7	2030.3	2028.0	2025.6	2023.3	2022.1	2022.4	2023.1	2023.8	2024.4	2025.1
180°	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1718.1	1742.6	1753.5	1756.3	1771.3	1761.7	1765.8	1764.4	1775.3	1776.7	1776.7
5°	1843.5	1872.1	1881.6	1895.2	1915.7	1921.1	1917.0	1925.2	1940.2	1929.3	1945.7
7.5°	1975.6	2007.0	2028.8	2058.7	2065.6	2083.3	2094.2	2103.7	2106.4	2107.8	2110.5
10°	2098.3	2137.8	2167.7	2218.2	2229.1	2238.6	2286.3	2267.2	2291.7	2283.6	2286.3
12.5°	2197.7	2275.4	2299.9	2384.4	2392.6	2425.3	2422.5	2452.5	2458.0	2468.9	2458.0
15°	2328.5	2418.4	2458.0	2505.6	2532.9	2571.0	2577.9	2618.7	2635.1	2650.1	2635.1
17.5°	2448.4	2496.1	2596.9	2635.1	2652.8	2673.2	2725.0	2740.0	2764.5	2755.0	2782.2
20°	2508.4	2576.5	2682.8	2748.2	2775.4	2794.5	2838.1	2861.3	2870.8	2870.8	2873.5
22.5°	2561.5	2659.6	2738.6	2813.6	2838.1	2851.7	2877.6	2895.3	2899.4	2902.1	2904.9
25°	2609.2	2697.8	2761.8	2804.0	2813.6	2813.6	2828.6	2817.7	2799.9	2813.6	2821.7
27.5°	2609.2	2671.9	2700.5	2715.5	2715.5	2678.7	2656.9	2611.9	2573.8	2562.9	2587.4
30°	2565.6	2594.2	2554.7	2517.9	2489.3	2464.8	2378.9	2310.8	2297.2	2287.6	2324.4
32.5°	2464.8	2428.0	2350.3	2244.0	2201.8	2145.9	2079.2	2027.4	1996.1	1985.2	1977.0
35°	2286.3	2190.9	2090.1	1947.0	1917.0	1846.2	1754.9	1716.8	1665.0	1663.6	1681.3
37.5°	2091.4	1944.3	1835.3	1699.0	1656.8	1581.9	1496.0	1456.5	1421.1	1393.8	1426.5
40°	1863.9	1735.8	1569.6	1457.9	1397.9	1358.4	1286.2	1242.6	1226.3	1212.6	1233.1
42.5°	1651.4	1511.0	1381.6	1267.1	1218.1	1173.1	1125.4	1083.2	1070.9	1069.6	1084.6
45°	1440.2	1302.6	1182.7	1084.6	1053.2	1026.0	979.6	967.4	946.9	933.3	940.1
47.5°	1271.2	1129.5	1030.1	955.1	927.9	904.7	874.7	854.3	836.6	831.1	839.3
50°	1105.0	1009.6	907.4	844.8	824.3	802.5	779.4	760.3	752.1	746.7	752.1
52.5°	971.5	869.3	799.8	749.4	728.9	712.6	696.2	688.1	677.2	679.9	685.3
55°	851.6	761.6	703.1	666.3	654.0	647.2	626.8	617.2	613.1	610.4	613.1
57.5°	738.5	673.1	629.5	598.1	581.8	577.7	561.4	561.4	557.3	553.2	554.5
60°	648.6	592.7	550.5	525.9	523.2	516.4	505.5	504.1	494.6	498.7	500.0
62.5°	557.3	512.3	483.7	468.7	459.2	456.4	449.6	448.3	444.2	445.5	442.8
65°	485.1	448.3	419.7	407.4	403.3	401.9	396.5	392.4	389.7	392.4	389.7
67.5°	412.8	388.3	366.5	354.3	348.8	347.4	343.4	340.6	342.0	337.9	340.6
70°	344.7	320.2	306.6	299.8	297.0	292.9	292.9	292.9	292.9	290.2	288.9
72.5°	290.2	265.7	256.2	252.1	249.3	248.0	243.9	245.3	243.9	242.5	248.0
75°	230.3	215.3	205.7	201.7	204.4	200.3	196.2	198.9	194.8	196.2	201.7
77.5°	174.4	167.6	162.1	159.4	156.7	154.0	154.0	151.2	151.2	151.2	151.2
80°	126.7	125.4	115.8	114.5	114.5	111.7	111.7	111.7	111.7	110.4	111.7
82.5°	84.5	83.1	80.4	79.0	76.3	77.7	77.7	74.9	74.9	73.6	74.9
85°	49.1	49.1	46.3	45.0	43.6	45.0	42.2	40.9	42.2	40.9	42.2
87.5°	23.2	20.4	21.8	20.4	17.7	19.1	16.4	17.7	16.4	15.0	17.7
90°	35.4	37.4	39.5	41.5	42.5	42.8	43.5	44.2	44.8	45.5	44.8
92.5°	33.9	35.9	38.0	40.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0
95°	35.4	37.4	39.5	41.5	42.5	42.7	43.0	43.3	43.7	44.0	43.7
97.5°	35.1	36.8	38.5	40.2	41.0	41.2	41.5	41.8	42.2	42.5	42.2
100°	61.0	55.3	49.6	43.9	41.0	41.2	41.5	41.8	42.2	42.5	42.2
102.5°	309.5	233.6	157.8	81.9	44.0	44.0	44.0	44.0	44.0	44.0	44.0
105°	476.3	479.3	482.4	485.4	486.9	480.8	468.7	456.6	444.4	432.3	444.4
107.5°	572.1	573.8	575.5	577.2	578.0	578.7	580.0	581.3	582.7	584.0	582.7
110°	669.7	670.3	671.0	671.7	672.0	672.5	673.5	674.6	675.6	676.6	675.6

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	764.2	763.8	763.5	763.2	763.0	763.7	765.0	766.4	767.7	769.1	767.7
115°	856.3	856.9	857.6	858.3	858.6	858.6	858.6	858.6	858.6	858.6	858.6
117.5°	952.3	951.9	951.6	951.3	951.1	951.1	951.1	951.1	951.1	951.1	951.1
120°	1038.3	1038.9	1039.6	1040.3	1040.6	1040.3	1039.6	1038.9	1038.3	1037.6	1038.3
122.5°	1124.4	1124.8	1125.1	1125.4	1125.6	1125.3	1124.6	1123.9	1123.2	1122.5	1123.2
125°	1202.4	1203.4	1204.5	1205.5	1206.0	1206.2	1206.5	1206.8	1207.2	1207.5	1207.2
127.5°	1284.5	1284.1	1283.8	1283.5	1283.3	1283.1	1282.8	1282.5	1282.1	1281.8	1282.1
130°	1356.5	1356.8	1357.2	1357.5	1357.7	1357.7	1357.7	1357.7	1357.7	1357.7	1357.7
132.5°	1427.8	1428.1	1428.5	1428.8	1429.0	1428.8	1428.5	1428.1	1427.8	1427.4	1427.8
135°	1491.9	1492.5	1493.2	1493.9	1494.2	1494.5	1495.2	1495.9	1496.5	1497.2	1496.5
137.5°	1555.6	1556.2	1556.9	1557.6	1557.9	1557.7	1557.4	1557.1	1556.7	1556.4	1556.7
140°	1613.5	1614.5	1615.6	1616.6	1617.1	1617.3	1617.6	1617.9	1618.3	1618.6	1618.3
142.5°	1667.8	1668.5	1669.2	1669.9	1670.2	1670.2	1670.2	1670.2	1670.2	1670.2	1670.2
145°	1719.0	1719.4	1719.7	1720.0	1720.2	1720.5	1721.2	1721.9	1722.5	1723.2	1722.5
147.5°	1764.5	1764.9	1765.2	1765.5	1765.7	1765.9	1766.2	1766.5	1766.9	1767.2	1766.9
150°	1808.2	1808.2	1808.2	1808.2	1808.2	1808.4	1808.7	1809.0	1809.4	1809.7	1809.4
152.5°	1845.3	1845.9	1846.6	1847.3	1847.6	1847.4	1847.1	1846.8	1846.4	1846.1	1846.4
155°	1877.8	1879.2	1880.5	1881.8	1882.5	1882.0	1881.0	1880.0	1879.0	1878.0	1879.0
157.5°	1907.0	1908.7	1910.4	1912.1	1912.9	1912.1	1910.4	1908.7	1907.0	1905.3	1907.0
160°	1934.6	1936.6	1938.7	1940.7	1941.7	1940.7	1938.7	1936.6	1934.6	1932.6	1934.6
162.5°	1957.3	1959.3	1961.4	1963.4	1964.4	1963.2	1960.9	1958.5	1956.2	1953.8	1956.2
165°	1977.8	1980.5	1983.2	1985.9	1987.2	1985.7	1982.6	1979.6	1976.5	1973.5	1976.5
167.5°	1993.2	1996.3	1999.3	2002.4	2003.9	2002.2	1998.8	1995.5	1992.1	1988.7	1992.1
170°	2008.1	2010.8	2013.5	2016.2	2017.5	2015.8	2012.5	2009.1	2005.8	2002.4	2005.8
172.5°	2017.2	2019.9	2022.6	2025.3	2026.6	2024.7	2021.0	2017.3	2013.6	2009.9	2013.6
175°	2023.6	2026.6	2029.7	2032.7	2034.2	2032.2	2028.1	2024.1	2020.0	2016.0	2020.0
177.5°	2027.8	2030.5	2033.2	2035.9	2037.3	2035.3	2031.2	2027.1	2023.1	2019.0	2023.1
180°	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1774.0	1769.9	1764.4	1764.4	1757.6	1757.6	1746.7	1727.7	1711.3	1705.9	1708.6
5°	1925.2	1926.6	1918.4	1911.6	1899.3	1889.8	1872.1	1838.0	1827.1	1805.3	1790.3
7.5°	2098.3	2092.8	2077.8	2066.9	2064.2	2042.4	2004.2	1963.4	1930.7	1908.9	1877.5
10°	2293.1	2271.3	2249.5	2242.7	2226.3	2189.5	2145.9	2101.0	2056.0	2008.3	1955.2
12.5°	2456.6	2414.4	2413.0	2396.6	2365.3	2344.9	2293.1	2229.1	2151.4	2098.3	2038.3
15°	2632.4	2592.8	2560.1	2530.2	2515.2	2455.2	2411.6	2331.2	2238.6	2181.4	2140.5
17.5°	2757.7	2740.0	2684.1	2670.5	2650.1	2580.6	2511.1	2432.1	2351.7	2271.3	2160.9
20°	2858.5	2847.6	2810.8	2791.8	2759.1	2704.6	2620.1	2528.8	2436.2	2321.7	2218.2
22.5°	2902.1	2888.5	2858.5	2842.2	2821.7	2775.4	2703.2	2599.7	2478.4	2376.2	2265.8
25°	2816.3	2840.8	2832.6	2825.8	2817.7	2790.4	2735.9	2644.6	2526.1	2410.3	2272.7
27.5°	2622.8	2665.1	2705.9	2711.4	2725.0	2735.9	2714.1	2648.7	2549.2	2426.6	2275.4
30°	2362.6	2381.7	2464.8	2489.3	2508.4	2577.9	2618.7	2602.4	2526.1	2415.7	2276.7
32.5°	2028.8	2079.2	2163.7	2222.2	2274.0	2351.7	2458.0	2500.2	2472.9	2383.0	2245.4
35°	1712.7	1772.6	1870.7	1945.7	1997.4	2107.8	2233.1	2324.4	2358.5	2313.5	2190.9
37.5°	1453.8	1526.0	1613.2	1641.8	1701.8	1838.0	2011.1	2137.8	2220.9	2225.0	2129.6
40°	1259.0	1295.7	1365.2	1408.8	1467.4	1581.9	1750.8	1918.4	2043.8	2086.0	2035.6
42.5°	1094.1	1122.7	1174.5	1227.6	1280.8	1368.0	1523.3	1680.0	1848.9	1933.4	1932.0
45°	963.3	993.3	1028.7	1072.3	1109.1	1203.1	1325.7	1486.5	1632.3	1763.1	1795.8
47.5°	848.8	874.7	918.3	937.4	961.9	1050.5	1156.8	1306.6	1457.9	1607.8	1645.9
50°	764.4	786.2	816.1	828.4	855.7	921.1	1008.3	1129.5	1297.1	1434.7	1505.6
52.5°	688.1	704.4	727.6	737.1	756.2	805.2	884.3	979.6	1118.6	1260.3	1359.8
55°	622.7	633.6	649.9	660.8	674.4	718.0	776.6	862.5	982.4	1105.0	1201.7
57.5°	561.4	569.5	585.9	591.3	602.2	636.3	677.2	749.4	859.7	968.7	1062.8
60°	504.1	509.6	519.1	531.4	539.6	562.7	600.9	660.8	749.4	848.8	925.1
62.5°	449.6	457.8	460.5	466.0	472.8	494.6	524.6	568.2	645.8	727.6	808.0
65°	393.8	400.6	406.0	407.4	414.2	430.6	457.8	496.0	546.4	617.2	692.2
67.5°	342.0	346.1	348.8	354.3	361.1	369.2	391.0	419.7	466.0	523.2	583.2
70°	294.3	294.3	298.4	299.8	307.9	317.5	327.0	354.3	395.1	441.5	482.3
72.5°	242.5	249.3	248.0	254.8	253.4	260.2	272.5	290.2	320.2	357.0	396.5
75°	197.6	201.7	201.7	201.7	204.4	209.8	216.6	233.0	256.2	286.1	309.3
77.5°	154.0	156.7	156.7	156.7	158.1	163.5	170.3	181.2	197.6	215.3	228.9
80°	110.4	113.1	113.1	115.8	115.8	117.2	124.0	129.4	137.6	151.2	164.9
82.5°	74.9	76.3	79.0	79.0	77.7	80.4	81.8	87.2	95.4	98.1	107.6
85°	40.9	42.2	43.6	43.6	45.0	47.7	46.3	51.8	51.8	57.2	60.0
87.5°	16.4	19.1	19.1	17.7	19.1	19.1	19.1	21.8	23.2	24.5	23.2
90°	44.2	43.5	42.8	42.5	41.5	39.5	37.4	35.4	33.4	30.7	28.0
92.5°	41.0	41.0	41.0	41.0	40.0	38.0	35.9	33.9	31.9	29.2	26.5
95°	43.3	43.0	42.7	42.5	41.5	39.5	37.4	35.4	33.4	33.1	32.7
97.5°	41.8	41.5	41.2	41.0	40.2	38.5	36.8	35.1	33.4	68.8	104.2
100°	41.8	41.5	41.2	41.0	43.9	49.6	55.3	61.0	66.7	113.2	159.8
102.5°	44.0	44.0	44.0	44.0	81.9	157.8	233.6	309.5	385.3	381.3	377.2
105°	456.6	468.7	480.8	486.9	485.4	482.4	479.3	476.3	473.3	471.6	469.9
107.5°	581.3	580.0	578.7	578.0	577.2	575.5	573.8	572.1	570.4	568.0	565.7
110°	674.6	673.5	672.5	672.0	671.7	671.0	670.3	669.7	669.0	667.0	665.0

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	766.4	765.0	763.7	763.0	763.2	763.5	763.8	764.2	764.5	763.8	763.2
115°	858.6	858.6	858.6	858.6	858.3	857.6	856.9	856.3	855.6	855.9	856.3
117.5°	951.1	951.1	951.1	951.1	951.3	951.6	951.9	952.3	952.6	951.6	950.6
120°	1038.9	1039.6	1040.3	1040.6	1040.3	1039.6	1038.9	1038.3	1037.6	1037.9	1038.3
122.5°	1123.9	1124.6	1125.3	1125.6	1125.4	1125.1	1124.8	1124.4	1124.1	1123.4	1122.7
125°	1206.8	1206.5	1206.2	1206.0	1205.5	1204.5	1203.4	1202.4	1201.4	1202.1	1202.8
127.5°	1282.5	1282.8	1283.1	1283.3	1283.5	1283.8	1284.1	1284.5	1284.8	1283.1	1281.5
130°	1357.7	1357.7	1357.7	1357.7	1357.5	1357.2	1356.8	1356.5	1356.1	1355.1	1354.1
132.5°	1428.1	1428.5	1428.8	1429.0	1428.8	1428.5	1428.1	1427.8	1427.4	1426.1	1424.7
135°	1495.9	1495.2	1494.5	1494.2	1493.9	1493.2	1492.5	1491.9	1491.2	1489.8	1488.5
137.5°	1557.1	1557.4	1557.7	1557.9	1557.6	1556.9	1556.2	1555.6	1554.9	1553.2	1551.5
140°	1617.9	1617.6	1617.3	1617.1	1616.6	1615.6	1614.5	1613.5	1612.5	1611.8	1611.2
142.5°	1670.2	1670.2	1670.2	1670.2	1669.9	1669.2	1668.5	1667.8	1667.1	1666.8	1666.4
145°	1721.9	1721.2	1720.5	1720.2	1720.0	1719.7	1719.4	1719.0	1718.7	1718.7	1718.7
147.5°	1766.5	1766.2	1765.9	1765.7	1765.5	1765.2	1764.9	1764.5	1764.2	1764.5	1764.9
150°	1809.0	1808.7	1808.4	1808.2	1808.2	1808.2	1808.2	1808.2	1808.2	1808.5	1808.9
152.5°	1846.8	1847.1	1847.4	1847.6	1847.3	1846.6	1845.9	1845.3	1844.6	1845.3	1845.9
155°	1880.0	1881.0	1882.0	1882.5	1881.8	1880.5	1879.2	1877.8	1876.5	1877.5	1878.5
157.5°	1908.7	1910.4	1912.1	1912.9	1912.1	1910.4	1908.7	1907.0	1905.3	1906.6	1908.0
160°	1936.6	1938.7	1940.7	1941.7	1940.7	1938.7	1936.6	1934.6	1932.6	1932.9	1933.3
162.5°	1958.5	1960.9	1963.2	1964.4	1963.4	1961.4	1959.3	1957.3	1955.3	1955.7	1956.0
165°	1979.6	1982.6	1985.7	1987.2	1985.9	1983.2	1980.5	1977.8	1975.1	1975.1	1975.1
167.5°	1995.5	1998.8	2002.2	2003.9	2002.4	1999.3	1996.3	1993.2	1990.2	1990.5	1990.9
170°	2009.1	2012.5	2015.8	2017.5	2016.2	2013.5	2010.8	2008.1	2005.4	2005.1	2004.7
172.5°	2017.3	2021.0	2024.7	2026.6	2025.3	2022.6	2019.9	2017.2	2014.5	2014.2	2013.8
175°	2024.1	2028.1	2032.2	2034.2	2032.7	2029.7	2026.6	2023.6	2020.6	2020.2	2019.9
177.5°	2027.1	2031.2	2035.3	2037.3	2035.9	2033.2	2030.5	2027.8	2025.1	2024.4	2023.8
180°	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1696.3	1690.9	1686.8	1686.8	1674.5	1662.3	1655.4	1652.7	1650.0	1639.1	1624.1
5°	1765.8	1748.1	1735.8	1723.6	1703.1	1681.3	1659.5	1647.3	1629.6	1605.0	1587.3
7.5°	1843.5	1801.2	1787.6	1772.6	1731.7	1695.0	1665.0	1639.1	1610.5	1579.1	1547.8
10°	1908.9	1863.9	1833.9	1808.0	1754.9	1705.9	1660.9	1622.7	1586.0	1545.1	1506.9
12.5°	1971.5	1907.5	1876.2	1838.0	1782.2	1711.3	1652.7	1605.0	1550.5	1508.3	1462.0
15°	2058.7	1951.1	1899.3	1874.8	1799.9	1716.8	1645.9	1575.1	1530.1	1466.1	1425.2
17.5°	2072.4	1985.2	1951.1	1888.4	1798.5	1704.5	1622.7	1551.9	1483.8	1426.5	1373.4
20°	2120.1	2005.6	1951.1	1911.6	1793.1	1697.7	1607.8	1516.5	1451.1	1389.8	1329.8
22.5°	2150.0	2020.6	1963.4	1900.7	1787.6	1673.2	1566.9	1487.9	1407.5	1344.8	1297.1
25°	2141.9	2012.4	1948.4	1889.8	1752.2	1637.7	1542.4	1441.5	1366.6	1298.5	1235.8
27.5°	2137.8	1992.0	1923.9	1858.5	1729.0	1609.1	1489.2	1407.5	1324.4	1245.3	1199.0
30°	2126.9	1966.1	1887.1	1816.2	1681.3	1556.0	1453.8	1358.4	1275.3	1203.1	1141.8
32.5°	2090.1	1922.5	1846.2	1769.9	1629.6	1504.2	1400.7	1312.1	1229.0	1154.0	1095.5
35°	2041.0	1870.7	1787.6	1707.2	1566.9	1440.2	1344.8	1252.1	1174.5	1102.3	1046.4
37.5°	1992.0	1810.8	1733.1	1640.5	1511.0	1378.9	1280.8	1197.6	1125.4	1050.5	989.2
40°	1921.1	1739.9	1654.1	1575.1	1423.8	1299.8	1209.9	1135.0	1064.1	993.3	941.5
42.5°	1824.4	1662.3	1573.7	1486.5	1344.8	1222.2	1135.0	1068.2	1001.4	942.9	885.6
45°	1726.3	1568.2	1489.2	1411.6	1257.6	1141.8	1061.4	1000.1	944.2	880.2	833.9
47.5°	1607.8	1474.2	1395.2	1318.9	1173.1	1057.3	983.7	926.5	874.7	821.6	778.0
50°	1486.5	1370.7	1298.5	1219.4	1080.5	975.6	903.3	855.7	813.4	763.0	727.6
52.5°	1355.7	1254.9	1193.6	1117.3	994.6	897.9	824.3	776.6	741.2	704.4	673.1
55°	1216.7	1143.1	1077.7	1016.4	900.6	813.4	748.0	705.8	681.3	647.2	619.9
57.5°	1091.4	1020.5	981.0	911.5	810.7	724.9	673.1	637.7	609.0	588.6	566.8
60°	960.6	903.3	859.7	809.3	720.8	648.6	594.1	573.6	543.6	528.7	519.1
62.5°	835.2	794.3	753.5	715.3	636.3	568.2	527.3	501.4	483.7	468.7	460.5
65°	716.7	678.5	649.9	615.9	550.5	496.0	457.8	437.4	419.7	415.6	406.0
67.5°	600.9	584.5	553.2	525.9	470.1	427.8	399.2	373.3	363.8	359.7	351.5
70°	502.8	483.7	459.2	436.0	393.8	357.0	331.1	321.6	307.9	306.6	297.0
72.5°	414.2	391.0	373.3	355.6	324.3	291.6	278.0	264.3	257.5	252.1	248.0
75°	328.4	312.0	299.8	284.8	257.5	235.7	216.6	211.2	207.1	205.7	203.0
77.5°	245.3	234.4	228.9	213.9	194.8	175.8	167.6	159.4	159.4	156.7	158.1
80°	174.4	167.6	160.8	152.6	136.3	128.1	121.3	115.8	113.1	111.7	113.1
82.5°	110.4	106.3	104.9	99.5	88.6	84.5	79.0	74.9	74.9	74.9	74.9
85°	61.3	61.3	61.3	53.1	49.1	45.0	42.2	40.9	40.9	40.9	42.2
87.5°	25.9	25.9	21.8	21.8	20.4	17.7	16.4	16.4	17.7	17.7	19.1
90°	25.3	22.6	21.2	19.4	15.7	12.0	8.3	4.6	8.3	12.0	15.7
92.5°	23.8	21.1	19.7	20.0	20.7	21.4	22.1	22.8	22.1	21.4	20.7
95°	32.4	32.1	31.9	37.6	49.1	60.5	72.0	83.4	72.0	60.5	49.1
97.5°	139.6	175.0	192.7	189.0	181.6	174.1	166.7	159.3	166.7	174.1	181.6
100°	206.3	252.8	276.1	273.1	267.0	260.9	254.9	248.8	254.9	260.9	267.0
102.5°	373.2	369.1	367.1	365.1	361.0	357.0	352.9	348.9	352.9	357.0	361.0
105°	468.2	466.5	465.7	464.7	462.7	460.6	458.6	456.6	458.6	460.6	462.7
107.5°	563.3	561.0	559.8	559.3	558.3	557.2	556.2	555.2	556.2	557.2	558.3
110°	662.9	660.9	659.9	659.4	658.4	657.3	656.3	655.3	656.3	657.3	658.4

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	762.5	761.8	761.5	760.5	758.5	756.4	754.4	752.4	754.4	756.4	758.5
115°	856.6	856.9	857.1	856.6	855.6	854.5	853.5	852.5	853.5	854.5	855.6
117.5°	949.6	948.6	948.1	947.4	946.1	944.7	943.4	942.0	943.4	944.7	946.1
120°	1038.6	1038.9	1039.1	1038.4	1037.1	1035.7	1034.4	1033.0	1034.4	1035.7	1037.1
122.5°	1122.0	1121.3	1121.0	1120.7	1120.0	1119.3	1118.7	1118.0	1118.7	1119.3	1120.0
125°	1203.5	1204.2	1204.5	1203.8	1202.5	1201.1	1199.8	1198.4	1199.8	1201.1	1202.5
127.5°	1279.8	1278.1	1277.3	1277.1	1276.8	1276.4	1276.1	1275.7	1276.1	1276.4	1276.8
130°	1353.1	1352.1	1351.6	1351.4	1351.1	1350.8	1350.4	1350.1	1350.4	1350.8	1351.1
132.5°	1423.4	1422.1	1421.4	1421.1	1420.4	1419.7	1419.0	1418.3	1419.0	1419.7	1420.4
135°	1487.1	1485.8	1485.1	1485.3	1485.6	1485.9	1486.3	1486.6	1486.3	1485.9	1485.6
137.5°	1549.8	1548.1	1547.3	1547.3	1547.3	1547.3	1547.3	1547.3	1547.3	1547.3	1547.3
140°	1610.5	1609.8	1609.5	1609.2	1608.5	1607.8	1607.1	1606.4	1607.1	1607.8	1608.5
142.5°	1666.1	1665.8	1665.6	1664.9	1663.6	1662.2	1660.9	1659.5	1660.9	1662.2	1663.6
145°	1718.7	1718.7	1718.7	1718.2	1717.2	1716.1	1715.1	1714.1	1715.1	1716.1	1717.2
147.5°	1765.2	1765.5	1765.7	1764.7	1762.7	1760.6	1758.6	1756.6	1758.6	1760.6	1762.7
150°	1809.2	1809.5	1809.7	1809.0	1807.7	1806.3	1805.0	1803.6	1805.0	1806.3	1807.7
152.5°	1846.6	1847.3	1847.6	1847.1	1846.1	1845.1	1844.1	1843.1	1844.1	1845.1	1846.1
155°	1879.5	1880.5	1881.0	1880.8	1880.5	1880.2	1879.8	1879.5	1879.8	1880.2	1880.5
157.5°	1909.3	1910.6	1911.3	1911.3	1911.3	1911.3	1911.3	1911.3	1911.3	1911.3	1911.3
160°	1933.6	1933.9	1934.1	1934.6	1935.6	1936.7	1937.7	1938.7	1937.7	1936.7	1935.6
162.5°	1956.4	1956.7	1956.9	1957.6	1958.9	1960.2	1961.6	1962.9	1961.6	1960.2	1958.9
165°	1975.1	1975.1	1975.1	1975.9	1977.6	1979.3	1980.9	1982.6	1980.9	1979.3	1977.6
167.5°	1991.2	1991.5	1991.7	1992.5	1994.2	1995.9	1997.6	1999.3	1997.6	1995.9	1994.2
170°	2004.4	2004.1	2003.9	2004.9	2006.9	2009.0	2011.0	2013.0	2011.0	2009.0	2006.9
172.5°	2013.5	2013.2	2013.0	2014.0	2016.0	2018.1	2020.1	2022.1	2020.1	2018.1	2016.0
175°	2019.5	2019.2	2019.0	2020.0	2022.1	2024.1	2026.2	2028.2	2026.2	2024.1	2022.1
177.5°	2023.1	2022.4	2022.1	2023.3	2025.6	2028.0	2030.3	2032.7	2030.3	2028.0	2025.6
180°	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1620.0	1614.6	1617.3	1603.7	1591.4	1573.7	1558.7	1556.0	1553.3	1561.4	1556.0
5°	1573.7	1566.9	1560.1	1543.7	1519.2	1504.2	1482.4	1481.0	1472.9	1460.6	1463.3
7.5°	1523.3	1519.2	1509.7	1483.8	1462.0	1436.1	1418.4	1403.4	1396.6	1385.7	1381.6
10°	1482.4	1467.4	1459.2	1430.6	1404.7	1377.5	1354.3	1343.4	1331.2	1321.6	1314.8
12.5°	1426.5	1422.5	1399.3	1376.1	1354.3	1323.0	1305.3	1273.9	1257.6	1265.8	1263.0
15°	1389.8	1370.7	1365.2	1332.5	1295.7	1275.3	1242.6	1222.2	1215.4	1203.1	1188.1
17.5°	1340.7	1328.4	1309.4	1279.4	1237.2	1208.5	1185.4	1166.3	1158.1	1141.8	1129.5
20°	1294.4	1273.9	1259.0	1231.7	1190.8	1154.0	1125.4	1113.2	1092.7	1079.1	1072.3
22.5°	1252.1	1237.2	1215.4	1174.5	1139.1	1103.6	1069.6	1051.9	1032.8	1024.6	1013.7
25°	1200.4	1175.8	1160.9	1115.9	1077.7	1049.1	1017.8	994.6	983.7	970.1	967.4
27.5°	1150.0	1126.8	1109.1	1069.6	1023.2	986.5	967.4	951.0	932.0	932.0	925.1
30°	1099.5	1083.2	1055.9	1017.8	974.2	938.8	917.0	902.0	895.2	889.7	888.4
32.5°	1049.1	1027.3	1011.0	959.2	926.5	893.8	877.5	865.2	857.0	855.7	857.0
35°	997.4	972.8	956.5	910.2	877.5	847.5	840.7	829.8	825.7	824.3	831.1
37.5°	942.9	923.8	903.3	865.2	828.4	810.7	797.1	793.0	791.6	799.8	802.5
40°	892.4	876.1	857.0	816.1	788.9	769.8	763.0	758.9	764.4	772.5	776.6
42.5°	844.8	821.6	806.6	769.8	745.3	734.4	726.2	726.2	731.7	741.2	748.0
45°	794.3	776.6	761.6	728.9	707.1	694.9	693.5	694.9	701.7	708.5	716.7
47.5°	745.3	727.6	711.2	684.0	664.9	658.1	656.7	658.1	669.0	678.5	688.1
50°	700.3	681.3	666.3	640.4	625.4	617.2	618.6	625.4	633.6	647.2	659.5
52.5°	647.2	633.6	619.9	596.8	583.2	577.7	581.8	587.2	602.2	611.8	626.8
55°	595.4	583.2	572.3	554.5	543.6	539.6	542.3	550.5	562.7	579.1	596.8
57.5°	547.7	534.1	523.2	510.9	498.7	500.0	501.4	512.3	527.3	542.3	562.7
60°	494.6	486.4	476.9	461.9	456.4	456.4	460.5	472.8	486.4	510.9	528.7
62.5°	446.9	436.0	429.2	419.7	411.5	412.8	422.4	433.3	449.6	470.1	493.2
65°	397.9	385.6	380.1	372.0	369.2	370.6	377.4	393.8	411.5	429.2	451.0
67.5°	343.4	339.3	333.8	325.6	328.4	329.7	336.5	350.2	369.2	387.0	411.5
70°	297.0	288.9	287.5	280.7	280.7	284.8	298.4	307.9	325.6	344.7	370.6
72.5°	248.0	241.2	241.2	235.7	239.8	243.9	250.7	264.3	280.7	299.8	321.6
75°	197.6	194.8	197.6	194.8	194.8	201.7	209.8	220.7	238.4	258.9	276.6
77.5°	152.6	152.6	151.2	155.3	155.3	159.4	170.3	181.2	194.8	211.2	230.3
80°	111.7	111.7	111.7	115.8	119.9	119.9	126.7	140.3	152.6	163.5	181.2
82.5°	76.3	76.3	76.3	79.0	84.5	84.5	92.7	100.8	114.5	124.0	132.2
85°	46.3	46.3	45.0	47.7	49.1	53.1	60.0	65.4	72.2	80.4	88.6
87.5°	20.4	20.4	21.8	23.2	24.5	27.3	30.0	32.7	39.5	42.2	46.3
90°	19.4	21.2	22.6	25.3	28.0	30.7	33.4	35.4	37.4	39.5	41.5
92.5°	20.0	19.7	21.1	23.8	26.5	29.2	31.9	33.9	35.9	38.0	40.0
95°	37.6	31.9	32.1	32.4	32.7	33.1	33.4	35.4	37.4	39.5	41.5
97.5°	189.0	192.7	175.0	139.6	104.2	68.8	33.4	35.1	36.8	38.5	40.2
100°	273.1	276.1	252.8	206.3	159.8	113.2	66.7	61.0	55.3	49.6	43.9
102.5°	365.1	367.1	369.1	373.2	377.2	381.3	385.3	309.5	233.6	157.8	81.9
105°	464.7	465.7	466.5	468.2	469.9	471.6	473.3	476.3	479.3	482.4	485.4
107.5°	559.3	559.8	561.0	563.3	565.7	568.0	570.4	572.1	573.8	575.5	577.2
110°	659.4	659.9	660.9	662.9	665.0	667.0	669.0	669.7	670.3	671.0	671.7

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	760.5	761.5	761.8	762.5	763.2	763.8	764.5	764.2	763.8	763.5	763.2
115°	856.6	857.1	856.9	856.6	856.3	855.9	855.6	856.3	856.9	857.6	858.3
117.5°	947.4	948.1	948.6	949.6	950.6	951.6	952.6	952.3	951.9	951.6	951.3
120°	1038.4	1039.1	1038.9	1038.6	1038.3	1037.9	1037.6	1038.3	1038.9	1039.6	1040.3
122.5°	1120.7	1121.0	1121.3	1122.0	1122.7	1123.4	1124.1	1124.4	1124.8	1125.1	1125.4
125°	1203.8	1204.5	1204.2	1203.5	1202.8	1202.1	1201.4	1202.4	1203.4	1204.5	1205.5
127.5°	1277.1	1277.3	1278.1	1279.8	1281.5	1283.1	1284.8	1284.5	1284.1	1283.8	1283.5
130°	1351.4	1351.6	1352.1	1353.1	1354.1	1355.1	1356.1	1356.5	1356.8	1357.2	1357.5
132.5°	1421.1	1421.4	1422.1	1423.4	1424.7	1426.1	1427.4	1427.8	1428.1	1428.5	1428.8
135°	1485.3	1485.1	1485.8	1487.1	1488.5	1489.8	1491.2	1491.9	1492.5	1493.2	1493.9
137.5°	1547.3	1547.3	1548.1	1549.8	1551.5	1553.2	1554.9	1555.6	1556.2	1556.9	1557.6
140°	1609.2	1609.5	1609.8	1610.5	1611.2	1611.8	1612.5	1613.5	1614.5	1615.6	1616.6
142.5°	1664.9	1665.6	1665.8	1666.1	1666.4	1666.8	1667.1	1667.8	1668.5	1669.2	1669.9
145°	1718.2	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1719.0	1719.4	1719.7	1720.0
147.5°	1764.7	1765.7	1765.5	1765.2	1764.9	1764.5	1764.2	1764.5	1764.9	1765.2	1765.5
150°	1809.0	1809.7	1809.5	1809.2	1808.9	1808.5	1808.2	1808.2	1808.2	1808.2	1808.2
152.5°	1847.1	1847.6	1847.3	1846.6	1845.9	1845.3	1844.6	1845.3	1845.9	1846.6	1847.3
155°	1880.8	1881.0	1880.5	1879.5	1878.5	1877.5	1876.5	1877.8	1879.2	1880.5	1881.8
157.5°	1911.3	1911.3	1910.6	1909.3	1908.0	1906.6	1905.3	1907.0	1908.7	1910.4	1912.1
160°	1934.6	1934.1	1933.9	1933.6	1933.3	1932.9	1932.6	1934.6	1936.6	1938.7	1940.7
162.5°	1957.6	1956.9	1956.7	1956.4	1956.0	1955.7	1955.3	1957.3	1959.3	1961.4	1963.4
165°	1975.9	1975.1	1975.1	1975.1	1975.1	1975.1	1975.1	1977.8	1980.5	1983.2	1985.9
167.5°	1992.5	1991.7	1991.5	1991.2	1990.9	1990.5	1990.2	1993.2	1996.3	1999.3	2002.4
170°	2004.9	2003.9	2004.1	2004.4	2004.7	2005.1	2005.4	2008.1	2010.8	2013.5	2016.2
172.5°	2014.0	2013.0	2013.2	2013.5	2013.8	2014.2	2014.5	2017.2	2019.9	2022.6	2025.3
175°	2020.0	2019.0	2019.2	2019.5	2019.9	2020.2	2020.6	2023.6	2026.6	2029.7	2032.7
177.5°	2023.3	2022.1	2022.4	2023.1	2023.8	2024.4	2025.1	2027.8	2030.5	2033.2	2035.9
180°	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1551.9	1550.5	1543.7	1546.4	1538.3	1541.0	1545.1	1546.4	1551.9	1547.8	1546.4
5°	1456.5	1453.8	1449.7	1445.6	1444.3	1449.7	1440.2	1442.9	1445.6	1449.7	1455.2
7.5°	1378.9	1377.5	1373.4	1366.6	1363.9	1361.1	1362.5	1372.0	1370.7	1369.3	1378.9
10°	1308.0	1309.4	1301.2	1299.8	1291.7	1290.3	1291.7	1294.4	1298.5	1303.9	1305.3
12.5°	1234.4	1252.1	1237.2	1231.7	1219.4	1226.3	1229.0	1216.7	1223.5	1227.6	1248.1
15°	1188.1	1179.9	1170.4	1170.4	1164.9	1162.2	1155.4	1164.9	1170.4	1178.6	1175.8
17.5°	1124.1	1110.4	1105.0	1099.5	1100.9	1106.4	1091.4	1113.2	1113.2	1117.3	1110.4
20°	1068.2	1057.3	1050.5	1047.8	1043.7	1041.0	1039.6	1045.0	1053.2	1055.9	1062.8
22.5°	1009.6	1009.6	998.7	994.6	991.9	987.8	994.6	990.5	996.0	1001.4	1012.3
25°	960.6	960.6	956.5	951.0	946.9	944.2	948.3	946.9	951.0	957.8	960.6
27.5°	921.1	917.0	915.6	914.2	912.9	914.2	912.9	917.0	921.1	922.4	919.7
30°	887.0	882.9	884.3	884.3	885.6	884.3	882.9	887.0	888.4	885.6	887.0
32.5°	855.7	855.7	858.4	859.7	859.7	861.1	862.5	859.7	861.1	857.0	858.4
35°	829.8	832.5	835.2	836.6	837.9	836.6	839.3	837.9	835.2	832.5	831.1
37.5°	803.9	806.6	812.1	813.4	817.5	818.9	816.1	816.1	814.8	809.3	806.6
40°	776.6	779.4	786.2	790.3	793.0	797.1	794.3	794.3	788.9	783.4	779.4
42.5°	750.7	756.2	763.0	767.1	772.5	772.5	772.5	769.8	763.0	757.6	753.5
45°	724.9	726.2	735.8	742.6	748.0	748.0	748.0	743.9	739.8	728.9	723.5
47.5°	696.2	700.3	711.2	718.0	723.5	724.9	724.9	720.8	712.6	703.1	696.2
50°	664.9	671.7	684.0	693.5	700.3	703.1	699.0	696.2	686.7	675.8	667.6
52.5°	634.9	643.1	658.1	666.3	675.8	677.2	675.8	671.7	660.8	645.8	639.0
55°	605.0	611.8	628.1	641.7	649.9	652.6	649.9	643.1	629.5	614.5	607.7
57.5°	572.3	581.8	599.5	613.1	622.7	624.0	621.3	614.5	603.6	584.5	575.0
60°	538.2	550.5	568.2	581.8	594.1	595.4	592.7	583.2	569.5	550.5	542.3
62.5°	504.1	513.7	534.1	549.1	558.6	565.4	560.0	550.5	536.8	517.8	505.5
65°	464.6	478.2	496.0	509.6	520.5	521.8	519.1	510.9	496.0	475.5	466.0
67.5°	426.5	436.0	453.7	471.4	475.5	479.6	475.5	467.3	455.1	437.4	423.7
70°	380.1	388.3	410.1	422.4	427.8	431.9	429.2	421.0	410.1	393.8	382.9
72.5°	333.8	340.6	361.1	370.6	381.5	380.1	378.8	373.3	358.3	347.4	340.6
75°	284.8	292.9	306.6	318.8	322.9	322.9	322.9	318.8	309.3	291.6	284.8
77.5°	239.8	243.9	254.8	261.6	265.7	267.1	265.7	258.9	253.4	241.2	237.1
80°	183.9	194.8	203.0	204.4	209.8	209.8	209.8	207.1	201.7	189.4	188.0
82.5°	139.0	141.7	149.9	154.0	156.7	155.3	155.3	149.9	148.5	141.7	139.0
85°	94.0	98.1	96.7	102.2	103.6	100.8	100.8	103.6	96.7	98.1	94.0
87.5°	51.8	51.8	54.5	53.1	58.6	58.6	55.9	57.2	54.5	53.1	51.8
90°	42.5	42.8	43.5	44.2	44.8	45.5	44.8	44.2	43.5	42.8	42.5
92.5°	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0	41.0
95°	42.5	42.7	43.0	43.3	43.7	44.0	43.7	43.3	43.0	42.7	42.5
97.5°	41.0	41.2	41.5	41.8	42.2	42.5	42.2	41.8	41.5	41.2	41.0
100°	41.0	41.2	41.5	41.8	42.2	42.5	42.2	41.8	41.5	41.2	41.0
102.5°	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0	44.0
105°	486.9	480.8	468.7	456.6	444.4	432.3	444.4	456.6	468.7	480.8	486.9
107.5°	578.0	578.7	580.0	581.3	582.7	584.0	582.7	581.3	580.0	578.7	578.0
110°	672.0	672.5	673.5	674.6	675.6	676.6	675.6	674.6	673.5	672.5	672.0

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	763.0	763.7	765.0	766.4	767.7	769.1	767.7	766.4	765.0	763.7	763.0
115°	858.6	858.6	858.6	858.6	858.6	858.6	858.6	858.6	858.6	858.6	858.6
117.5°	951.1	951.1	951.1	951.1	951.1	951.1	951.1	951.1	951.1	951.1	951.1
120°	1040.6	1040.3	1039.6	1038.9	1038.3	1037.6	1038.3	1038.9	1039.6	1040.3	1040.6
122.5°	1125.6	1125.3	1124.6	1123.9	1123.2	1122.5	1123.2	1123.9	1124.6	1125.3	1125.6
125°	1206.0	1206.2	1206.5	1206.8	1207.2	1207.5	1207.2	1206.8	1206.5	1206.2	1206.0
127.5°	1283.3	1283.1	1282.8	1282.5	1282.1	1281.8	1282.1	1282.5	1282.8	1283.1	1283.3
130°	1357.7	1357.7	1357.7	1357.7	1357.7	1357.7	1357.7	1357.7	1357.7	1357.7	1357.7
132.5°	1429.0	1428.8	1428.5	1428.1	1427.8	1427.4	1427.8	1428.1	1428.5	1428.8	1429.0
135°	1494.2	1494.5	1495.2	1495.9	1496.5	1497.2	1496.5	1495.9	1495.2	1494.5	1494.2
137.5°	1557.9	1557.7	1557.4	1557.1	1556.7	1556.4	1556.7	1557.1	1557.4	1557.7	1557.9
140°	1617.1	1617.3	1617.6	1617.9	1618.3	1618.6	1618.3	1617.9	1617.6	1617.3	1617.1
142.5°	1670.2	1670.2	1670.2	1670.2	1670.2	1670.2	1670.2	1670.2	1670.2	1670.2	1670.2
145°	1720.2	1720.5	1721.2	1721.9	1722.5	1723.2	1722.5	1721.9	1721.2	1720.5	1720.2
147.5°	1765.7	1765.9	1766.2	1766.5	1766.9	1767.2	1766.9	1766.5	1766.2	1765.9	1765.7
150°	1808.2	1808.4	1808.7	1809.0	1809.4	1809.7	1809.4	1809.0	1808.7	1808.4	1808.2
152.5°	1847.6	1847.4	1847.1	1846.8	1846.4	1846.1	1846.4	1846.8	1847.1	1847.4	1847.6
155°	1882.5	1882.0	1881.0	1880.0	1879.0	1878.0	1879.0	1880.0	1881.0	1882.0	1882.5
157.5°	1912.9	1912.1	1910.4	1908.7	1907.0	1905.3	1907.0	1908.7	1910.4	1912.1	1912.9
160°	1941.7	1940.7	1938.7	1936.6	1934.6	1932.6	1934.6	1936.6	1938.7	1940.7	1941.7
162.5°	1964.4	1963.2	1960.9	1958.5	1956.2	1953.8	1956.2	1958.5	1960.9	1963.2	1964.4
165°	1987.2	1985.7	1982.6	1979.6	1976.5	1973.5	1976.5	1979.6	1982.6	1985.7	1987.2
167.5°	2003.9	2002.2	1998.8	1995.5	1992.1	1988.7	1992.1	1995.5	1998.8	2002.2	2003.9
170°	2017.5	2015.8	2012.5	2009.1	2005.8	2002.4	2005.8	2009.1	2012.5	2015.8	2017.5
172.5°	2026.6	2024.7	2021.0	2017.3	2013.6	2009.9	2013.6	2017.3	2021.0	2024.7	2026.6
175°	2034.2	2032.2	2028.1	2024.1	2020.0	2016.0	2020.0	2024.1	2028.1	2032.2	2034.2
177.5°	2037.3	2035.3	2031.2	2027.1	2023.1	2019.0	2023.1	2027.1	2031.2	2035.3	2037.3
180°	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5	1644.5
2.5°	1546.4	1554.6	1546.4	1551.9	1554.6	1561.4	1564.2	1576.4	1580.5	1590.0	1590.0
5°	1453.8	1457.9	1459.2	1464.7	1470.1	1483.8	1493.3	1511.0	1531.5	1534.2	1546.4
7.5°	1378.9	1385.7	1396.6	1392.5	1402.0	1422.5	1434.7	1456.5	1477.0	1487.9	1502.8
10°	1312.1	1320.3	1324.4	1328.4	1346.2	1363.9	1382.9	1397.9	1425.2	1441.5	1453.8
12.5°	1257.6	1250.8	1259.0	1273.9	1294.4	1305.3	1331.2	1354.3	1374.8	1392.5	1403.4
15°	1186.7	1192.2	1200.4	1226.3	1231.7	1259.0	1268.5	1294.4	1332.5	1348.9	1362.5
17.5°	1118.6	1136.3	1152.7	1162.2	1178.6	1200.4	1227.6	1256.2	1280.8	1299.8	1316.2
20°	1064.1	1081.8	1091.4	1098.2	1114.5	1144.5	1170.4	1205.8	1237.2	1252.1	1273.9
22.5°	1020.5	1020.5	1034.1	1054.6	1064.1	1092.7	1114.5	1152.7	1186.7	1205.8	1226.3
25°	966.0	974.2	985.1	1002.8	1016.4	1039.6	1070.9	1103.6	1140.4	1156.8	1182.7
27.5°	921.1	930.6	945.6	949.7	963.3	983.7	1016.4	1051.9	1090.0	1107.7	1129.5
30°	887.0	892.4	897.9	906.1	918.3	936.0	963.3	994.6	1041.0	1054.6	1081.8
32.5°	857.0	859.7	862.5	869.3	876.1	893.8	915.6	949.7	987.8	1008.3	1032.8
35°	829.8	827.0	828.4	832.5	839.3	846.1	869.3	897.9	933.3	957.8	976.9
37.5°	803.9	798.4	797.1	797.1	799.8	808.0	825.7	850.2	888.4	908.8	927.9
40°	775.3	769.8	767.1	765.7	764.4	769.8	783.4	808.0	837.9	857.0	878.8
42.5°	748.0	742.6	735.8	734.4	731.7	734.4	743.9	767.1	793.0	812.1	829.8
45°	720.8	711.2	703.1	697.6	699.0	694.9	701.7	719.4	749.4	761.6	779.4
47.5°	690.8	679.9	669.0	663.5	658.1	660.8	663.5	678.5	704.4	716.7	734.4
50°	662.2	647.2	634.9	628.1	624.0	621.3	624.0	639.0	658.1	669.0	684.0
52.5°	629.5	614.5	602.2	591.3	585.9	581.8	583.2	596.8	614.5	625.4	640.4
55°	599.5	580.4	564.1	550.5	546.4	545.0	543.6	553.2	568.2	579.1	591.3
57.5°	565.4	546.4	528.7	512.3	504.1	502.8	502.8	505.5	524.6	532.7	539.6
60°	531.4	510.9	491.9	476.9	464.6	460.5	459.2	464.6	474.2	482.3	491.9
62.5°	493.2	472.8	449.6	436.0	423.7	412.8	416.9	418.3	431.9	436.0	444.2
65°	456.4	433.3	414.2	392.4	378.8	372.0	369.2	372.0	382.9	384.2	389.7
67.5°	414.2	392.4	369.2	354.3	342.0	329.7	327.0	327.0	332.5	336.5	343.4
70°	373.3	351.5	325.6	309.3	297.0	286.1	282.0	280.7	284.8	287.5	294.3
72.5°	325.6	303.8	284.8	267.1	252.1	243.9	239.8	237.1	241.2	243.9	245.3
75°	275.2	257.5	238.4	220.7	211.2	203.0	197.6	193.5	196.2	196.2	196.2
77.5°	227.5	209.8	194.8	182.6	170.3	160.8	156.7	152.6	154.0	154.0	156.7
80°	177.1	164.9	152.6	141.7	130.8	122.6	119.9	115.8	113.1	111.7	111.7
82.5°	130.8	121.3	110.4	100.8	95.4	87.2	84.5	79.0	79.0	77.7	77.7
85°	87.2	81.8	70.9	64.0	60.0	55.9	53.1	50.4	46.3	46.3	45.0
87.5°	46.3	43.6	40.9	32.7	32.7	28.6	27.3	25.9	21.8	23.2	23.2
90°	41.5	39.5	37.4	35.4	33.4	30.7	28.0	25.3	22.6	21.2	19.4
92.5°	40.0	38.0	35.9	33.9	31.9	29.2	26.5	23.8	21.1	19.7	20.0
95°	41.5	39.5	37.4	35.4	33.4	33.1	32.7	32.4	32.1	31.9	37.6
97.5°	40.2	38.5	36.8	35.1	33.4	68.8	104.2	139.6	175.0	192.7	189.0
100°	43.9	49.6	55.3	61.0	66.7	113.2	159.8	206.3	252.8	276.1	273.1
102.5°	81.9	157.8	233.6	309.5	385.3	381.3	377.2	373.2	369.1	367.1	365.1
105°	485.4	482.4	479.3	476.3	473.3	471.6	469.9	468.2	466.5	465.7	464.7
107.5°	577.2	575.5	573.8	572.1	570.4	568.0	565.7	563.3	561.0	559.8	559.3
110°	671.7	671.0	670.3	669.7	669.0	667.0	665.0	662.9	660.9	659.9	659.4

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	763.2	763.5	763.8	764.2	764.5	763.8	763.2	762.5	761.8	761.5	760.5
115°	858.3	857.6	856.9	856.3	855.6	855.9	856.3	856.6	856.9	857.1	856.6
117.5°	951.3	951.6	951.9	952.3	952.6	951.6	950.6	949.6	948.6	948.1	947.4
120°	1040.3	1039.6	1038.9	1038.3	1037.6	1037.9	1038.3	1038.6	1038.9	1039.1	1038.4
122.5°	1125.4	1125.1	1124.8	1124.4	1124.1	1123.4	1122.7	1122.0	1121.3	1121.0	1120.7
125°	1205.5	1204.5	1203.4	1202.4	1201.4	1202.1	1202.8	1203.5	1204.2	1204.5	1203.8
127.5°	1283.5	1283.8	1284.1	1284.5	1284.8	1283.1	1281.5	1279.8	1278.1	1277.3	1277.1
130°	1357.5	1357.2	1356.8	1356.5	1356.1	1355.1	1354.1	1353.1	1352.1	1351.6	1351.4
132.5°	1428.8	1428.5	1428.1	1427.8	1427.4	1426.1	1424.7	1423.4	1422.1	1421.4	1421.1
135°	1493.9	1493.2	1492.5	1491.9	1491.2	1489.8	1488.5	1487.1	1485.8	1485.1	1485.3
137.5°	1557.6	1556.9	1556.2	1555.6	1554.9	1553.2	1551.5	1549.8	1548.1	1547.3	1547.3
140°	1616.6	1615.6	1614.5	1613.5	1612.5	1611.8	1611.2	1610.5	1609.8	1609.5	1609.2
142.5°	1669.9	1669.2	1668.5	1667.8	1667.1	1666.8	1666.4	1666.1	1665.8	1665.6	1664.9
145°	1720.0	1719.7	1719.4	1719.0	1718.7	1718.7	1718.7	1718.7	1718.7	1718.7	1718.2
147.5°	1765.5	1765.2	1764.9	1764.5	1764.2	1764.5	1764.9	1765.2	1765.5	1765.7	1764.7
150°	1808.2	1808.2	1808.2	1808.2	1808.2	1808.5	1808.9	1809.2	1809.5	1809.7	1809.0
152.5°	1847.3	1846.6	1845.9	1845.3	1844.6	1845.3	1845.9	1846.6	1847.3	1847.6	1847.1
155°	1881.8	1880.5	1879.2	1877.8	1876.5	1877.5	1878.5	1879.5	1880.5	1881.0	1880.8
157.5°	1912.1	1910.4	1908.7	1907.0	1905.3	1906.6	1908.0	1909.3	1910.6	1911.3	1911.3
160°	1940.7	1938.7	1936.6	1934.6	1932.6	1932.9	1933.3	1933.6	1933.9	1934.1	1934.6
162.5°	1963.4	1961.4	1959.3	1957.3	1955.3	1955.7	1956.0	1956.4	1956.7	1956.9	1957.6
165°	1985.9	1983.2	1980.5	1977.8	1975.1	1975.1	1975.1	1975.1	1975.1	1975.1	1975.9
167.5°	2002.4	1999.3	1996.3	1993.2	1990.2	1990.5	1990.9	1991.2	1991.5	1991.7	1992.5
170°	2016.2	2013.5	2010.8	2008.1	2005.4	2005.1	2004.7	2004.4	2004.1	2003.9	2004.9
172.5°	2025.3	2022.6	2019.9	2017.2	2014.5	2014.2	2013.8	2013.5	2013.2	2013.0	2014.0
175°	2032.7	2029.7	2026.6	2023.6	2020.6	2020.2	2019.9	2019.5	2019.2	2019.0	2020.0
177.5°	2035.9	2033.2	2030.5	2027.8	2025.1	2024.4	2023.8	2023.1	2022.4	2022.1	2023.3
180°	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2	2028.2

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1644.5	1644.5	1644.5	1644.5
2.5°	1599.6	1613.2	1625.5	1644.5
5°	1564.2	1583.2	1609.1	1637.7
7.5°	1523.3	1553.3	1587.3	1626.8
10°	1485.1	1519.2	1562.8	1610.5
12.5°	1445.6	1486.5	1534.2	1586.0
15°	1400.7	1441.5	1494.7	1564.2
17.5°	1359.8	1408.8	1466.1	1539.6
20°	1312.1	1358.4	1421.1	1505.6
22.5°	1269.9	1323.0	1392.5	1466.1
25°	1223.5	1269.9	1339.3	1427.9
27.5°	1177.2	1234.4	1301.2	1387.0
30°	1132.2	1179.9	1252.1	1342.1
32.5°	1083.2	1140.4	1207.2	1291.7
35°	1030.1	1084.6	1147.2	1238.5
37.5°	982.4	1035.5	1099.5	1179.9
40°	929.2	985.1	1043.7	1124.1
42.5°	877.5	927.9	986.5	1060.0
45°	827.0	870.6	923.8	987.8
47.5°	775.3	812.1	861.1	918.3
50°	719.4	758.9	795.7	843.4
52.5°	667.6	701.7	731.7	771.2
55°	617.2	640.4	664.9	694.9
57.5°	564.1	581.8	599.5	630.8
60°	510.9	527.3	536.8	557.3
62.5°	459.2	466.0	478.2	490.5
65°	401.9	411.5	418.3	433.3
67.5°	350.2	354.3	361.1	370.6
70°	295.7	305.2	307.9	314.7
72.5°	249.3	253.4	256.2	257.5
75°	197.6	201.7	204.4	212.6
77.5°	155.3	154.0	159.4	160.8
80°	114.5	110.4	111.7	117.2
82.5°	74.9	76.3	74.9	74.9
85°	46.3	45.0	42.2	43.6
87.5°	20.4	20.4	19.1	19.1
90°	15.7	12.0	8.3	4.6
92.5°	20.7	21.4	22.1	22.8
95°	49.1	60.5	72.0	83.4
97.5°	181.6	174.1	166.7	159.3
100°	267.0	260.9	254.9	248.8
102.5°	361.0	357.0	352.9	348.9
105°	462.7	460.6	458.6	456.6
107.5°	558.3	557.2	556.2	555.2
110°	658.4	657.3	656.3	655.3

TEST NUMBER: P1033149

CATALOG NUMBER: S124DIW-B1020D1560UB27-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	758.5	756.4	754.4	752.4
115°	855.6	854.5	853.5	852.5
117.5°	946.1	944.7	943.4	942.0
120°	1037.1	1035.7	1034.4	1033.0
122.5°	1120.0	1119.3	1118.7	1118.0
125°	1202.5	1201.1	1199.8	1198.4
127.5°	1276.8	1276.4	1276.1	1275.7
130°	1351.1	1350.8	1350.4	1350.1
132.5°	1420.4	1419.7	1419.0	1418.3
135°	1485.6	1485.9	1486.3	1486.6
137.5°	1547.3	1547.3	1547.3	1547.3
140°	1608.5	1607.8	1607.1	1606.4
142.5°	1663.6	1662.2	1660.9	1659.5
145°	1717.2	1716.1	1715.1	1714.1
147.5°	1762.7	1760.6	1758.6	1756.6
150°	1807.7	1806.3	1805.0	1803.6
152.5°	1846.1	1845.1	1844.1	1843.1
155°	1880.5	1880.2	1879.8	1879.5
157.5°	1911.3	1911.3	1911.3	1911.3
160°	1935.6	1936.7	1937.7	1938.7
162.5°	1958.9	1960.2	1961.6	1962.9
165°	1977.6	1979.3	1980.9	1982.6
167.5°	1994.2	1995.9	1997.6	1999.3
170°	2006.9	2009.0	2011.0	2013.0
172.5°	2016.0	2018.1	2020.1	2022.1
175°	2022.1	2024.1	2026.2	2028.2
177.5°	2025.6	2028.0	2030.3	2032.7
180°	2028.2	2028.2	2028.2	2028.2

(END OF REPORT)