

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032696

Luminaire Tested: S124DIW-B575D1050UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032696
REPORT IS A COMBINATION OF REPORTS P997628 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D1050UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6613.0 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032696

CATALOG NUMBER: S124DIW-B575D1050UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032696

CATALOG NUMBER: S124DIW-B575D1050UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41			33
1	93	89	85	81	84	80	77	74	64	61	59	49	47	46	35	34	33			26
2	85	77	71	66	76	70	64	60	55	52	48	42	40	37	30	29	27			22
3	77	67	60	54	69	61	55	50	49	44	40	37	34	31	26	24	23			18
4	70	59	52	46	63	54	47	42	43	38	34	33	29	27	23	21	19			15
5	64	53	45	39	58	48	41	35	38	33	29	29	26	23	21	19	17			13
6	59	47	39	33	53	43	36	31	34	29	25	26	23	20	19	17	15			11
7	55	42	35	29	49	38	32	27	31	26	22	24	20	17	17	15	13			10
8	50	38	31	25	45	35	28	23	28	23	19	22	18	15	16	13	11			9
9	47	35	27	22	42	32	25	21	26	21	17	20	16	14	15	12	10			8
10	44	32	25	20	39	29	23	18	24	19	15	18	15	12	13	11	9			7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5642	5642	5642
5°	5658	5495	5505
10°	5621	5387	5372
15°	5568	5266	5221
20°	5490	5133	5075
25°	5403	4988	4917
30°	5307	4845	4756
35°	5200	4698	4613
40°	5114	4557	4465
45°	4986	4424	4334
50°	4877	4274	4196
55°	4765	4129	4037
60°	4591	3949	3887
65°	4399	3754	3706
70°	4165	3531	3498
75°	3841	3285	3299
80°	3475	3032	3092
85°	2991	2780	2924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 90°
Luminance: 5056 cd/sqm

TEST NUMBER: P1032696

CATALOG NUMBER: S124DIW-B575D1050UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	1.0
10°-20°	187.8	2.8
20°-30°	284.0	4.3
30°-40°	343.6	5.2
40°-50°	363.2	5.5
50°-60°	341.9	5.2
60°-70°	283.7	4.3
70°-80°	199.1	3.0
80°-90°	115.1	1.7
90°-100°	112.4	1.7
100°-110°	349.8	5.3
110°-120°	606.7	9.2
120°-130°	746.7	11.3
130°-140°	786.9	11.9
140°-150°	729.9	11.0
150°-160°	587.3	8.9
160°-170°	378.8	5.7
170°-180°	130.5	2.0
0°-30°	537.4	8.1
0°-40°	881.0	13.3
0°-60°	1586.1	24.0
0°-90°	2183.9	33.0
90°-120°	1068.9	16.2
90°-150°	3332.5	50.4
90°-180°	4429.0	67.0
0°-180°	6613.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	692	692	692	692	692	
5°	693	690	685	691	690	66
15°	664	665	662	669	669	187
25°	608	612	614	623	624	280
35°	532	541	549	559	562	333
45°	443	458	473	486	490	343
55°	347	363	387	402	407	309
65°	240	265	291	311	317	238
75°	133	162	194	216	223	142
85°	41	74	108	132	140	43
90°	16	58	99	128	136	11
95°	67	57	90	117	125	78
105°	316	338	372	400	370	332
115°	582	592	616	635	640	573
125°	815	818	836	853	859	728
135°	1008	1008	1017	1032	1038	777
145°	1162	1164	1164	1170	1175	726
155°	1273	1274	1271	1275	1272	587
165°	1343	1338	1338	1346	1337	380
175°	1374	1368	1369	1378	1366	131
180°	1374	1374	1374	1374	1374	

TEST NUMBER: P1032696

CATALOG NUMBER: S124DIW-B575D1050UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	691.9	691.9	691.9	691.9	691.9
2.5°	695.0	692.7	686.5	691.9	691.1
5°	692.7	690.4	684.9	691.1	690.4
7.5°	688.0	686.5	681.8	688.8	688.0
10°	681.8	681.1	677.2	684.2	683.4
12.5°	673.3	673.3	671.0	677.2	677.2
15°	664.0	664.8	662.5	669.4	668.7
17.5°	651.6	653.9	653.2	660.1	659.4
20°	638.4	640.8	641.5	649.3	649.3
22.5°	623.7	626.8	628.4	636.1	637.7
25°	607.5	612.1	614.4	623.0	623.7
27.5°	589.6	596.6	599.7	607.5	608.2
30°	571.8	578.0	583.4	592.0	593.5
32.5°	552.4	560.2	566.4	576.5	578.0
35°	531.5	540.8	548.6	559.4	561.7
37.5°	510.6	521.4	530.7	541.6	543.9
40°	490.5	500.5	511.4	523.0	526.1
42.5°	467.2	478.8	492.0	505.2	507.5
45°	443.2	457.9	472.6	485.8	489.7
47.5°	420.7	435.4	452.5	465.7	470.3
50°	395.9	413.0	430.0	445.5	450.2
52.5°	371.1	388.2	408.3	423.8	428.5
55°	347.1	363.4	386.6	402.1	406.8
57.5°	320.0	340.1	362.6	381.2	385.1
60°	293.7	313.8	339.4	357.2	363.4
62.5°	268.1	290.6	316.1	333.9	340.1
65°	240.2	265.0	291.3	310.7	316.9
67.5°	213.8	240.2	268.1	287.5	293.7
70°	186.7	213.1	242.5	263.4	268.9
72.5°	160.4	187.5	219.3	239.4	245.6
75°	133.3	161.9	194.5	216.2	223.1
77.5°	107.7	137.9	172.0	193.7	201.5
80°	84.5	115.4	149.5	172.8	179.0
82.5°	61.2	93.8	127.8	151.9	158.8
85°	41.1	73.6	108.5	131.7	139.5
87.5°	25.6	57.3	91.4	113.9	120.9
90°	15.5	57.8	99.3	128.0	136.2
92.5°	27.0	52.1	93.7	121.5	127.7
95°	66.6	57.2	90.0	117.1	125.1
97.5°	117.2	162.3	86.1	111.4	119.5
100°	177.0	215.7	104.1	107.5	114.0
102.5°	244.8	274.3	316.0	105.0	111.2
105°	316.3	338.0	371.7	400.3	369.6
107.5°	383.1	399.3	433.7	458.1	467.7
110°	450.1	464.0	497.4	517.2	526.5

TEST NUMBER: P1032696

CATALOG NUMBER: S124DIW-B575D1050UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	515.1	530.5	558.2	574.2	584.5
115°	582.1	592.2	615.9	635.1	640.5
117.5°	642.7	651.5	677.8	693.1	699.3
120°	703.7	710.1	731.5	749.1	753.2
122.5°	761.2	763.3	786.2	802.7	806.1
125°	814.9	818.2	835.5	853.3	859.0
127.5°	867.3	867.5	888.1	901.1	905.5
130°	916.8	917.1	932.5	947.6	952.2
132.5°	963.1	964.3	977.7	992.0	995.6
135°	1008.5	1007.5	1017.1	1031.5	1038.2
137.5°	1049.6	1048.9	1057.1	1070.8	1073.7
140°	1089.7	1091.0	1093.8	1107.0	1111.9
142.5°	1124.9	1129.1	1129.3	1139.8	1142.9
145°	1161.9	1164.2	1164.2	1169.9	1175.0
147.5°	1190.7	1196.1	1195.1	1196.9	1201.0
150°	1222.6	1225.9	1224.8	1224.8	1225.9
152.5°	1248.5	1251.6	1249.5	1251.6	1250.5
155°	1273.1	1274.2	1271.1	1275.2	1272.1
157.5°	1294.7	1294.7	1290.6	1295.8	1290.6
160°	1313.2	1310.1	1309.1	1315.3	1309.1
162.5°	1329.7	1325.6	1324.5	1330.7	1323.5
165°	1343.0	1337.9	1337.9	1346.1	1336.9
167.5°	1354.3	1349.2	1348.2	1357.4	1347.1
170°	1363.6	1357.4	1358.4	1366.7	1356.4
172.5°	1369.7	1363.6	1364.6	1372.8	1361.5
175°	1373.8	1367.7	1368.7	1378.0	1365.6
177.5°	1376.9	1369.7	1371.8	1380.0	1367.7
180°	1373.8	1373.8	1373.8	1373.8	1373.8

(END OF REPORT)