

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032710

Luminaire Tested: S124DIW-B575D1340UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032710
REPORT IS A COMBINATION OF REPORTS P997693 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D1340UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7665.0 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032710

CATALOG NUMBER: S124DIW-B575D1340UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1032710

CATALOG NUMBER: S124DIW-B575D1340UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	92	88	84	80	82	79	75	72	61	59	57	46	44	43	31	30	29
2	84	76	70	65	75	68	63	59	53	50	47	40	37	35	27	25	24
3	76	67	60	54	68	60	54	49	47	43	39	35	32	29	24	22	20
4	70	59	51	45	62	53	46	41	41	37	33	31	28	25	21	19	17
5	64	52	44	38	57	47	40	35	37	32	28	28	24	21	19	17	15
6	58	47	39	33	52	42	35	30	33	28	24	25	21	19	17	15	13
7	54	42	34	29	48	38	31	26	30	25	21	22	19	16	15	13	11
8	50	38	30	25	44	34	28	23	27	22	19	20	17	14	14	12	10
9	46	34	27	22	41	31	25	20	25	20	17	19	15	13	13	11	9
10	43	31	24	20	39	28	22	18	23	18	15	17	14	11	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5594	5594	5594
5°	5610	5448	5458
10°	5574	5341	5326
15°	5521	5220	5177
20°	5444	5090	5032
25°	5357	4946	4875
30°	5263	4804	4716
35°	5156	4658	4574
40°	5070	4518	4427
45°	4944	4387	4297
50°	4836	4238	4161
55°	4725	4094	4002
60°	4552	3915	3854
65°	4362	3723	3675
70°	4130	3502	3469
75°	3807	3256	3272
80°	3442	3008	3066
85°	2962	2757	2899

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 5284 cd/sqm

TEST NUMBER: P1032710

CATALOG NUMBER: S124DIW-B575D1340UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	0.8
10°-20°	186.2	2.4
20°-30°	281.6	3.7
30°-40°	340.7	4.4
40°-50°	360.2	4.7
50°-60°	339.0	4.4
60°-70°	281.3	3.7
70°-80°	197.4	2.6
80°-90°	114.8	1.5
90°-100°	123.3	1.6
100°-110°	425.1	5.5
110°-120°	750.9	9.8
120°-130°	930.0	12.1
130°-140°	983.1	12.8
140°-150°	913.4	11.9
150°-160°	735.3	9.6
160°-170°	474.2	6.2
170°-180°	163.4	2.1
0°-30°	532.8	7.0
0°-40°	873.5	11.4
0°-60°	1572.7	20.5
0°-90°	2166.2	28.3
90°-120°	1299.3	17.0
90°-150°	4125.9	53.8
90°-180°	5499.0	71.7
0°-180°	7665.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	686	686	686	686	686	
5°	687	684	679	685	684	65
15°	658	659	657	664	663	186
25°	602	607	609	618	618	277
35°	527	536	544	555	557	330
45°	439	454	469	482	486	340
55°	344	360	383	399	403	307
65°	238	263	289	308	314	236
75°	132	161	193	214	221	140
85°	41	73	108	131	138	42
90°	16	61	104	134	143	12
95°	81	62	95	124	132	95
105°	394	417	452	483	443	413
115°	728	738	762	781	787	717
125°	1019	1024	1040	1059	1065	911
135°	1262	1261	1272	1286	1294	973
145°	1454	1458	1458	1464	1469	909
155°	1594	1595	1591	1596	1593	735
165°	1682	1675	1675	1685	1674	475
175°	1720	1712	1714	1725	1710	164
180°	1720	1720	1720	1720	1720	

TEST NUMBER: P1032710

CATALOG NUMBER: S124DIW-B575D1340UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	686.0	686.0	686.0	686.0	686.0
2.5°	689.1	686.8	680.7	686.0	685.3
5°	686.8	684.5	679.1	685.3	684.5
7.5°	682.2	680.7	676.1	683.0	682.2
10°	676.1	675.3	671.4	678.4	677.6
12.5°	667.6	667.6	665.3	671.4	671.4
15°	658.4	659.2	656.8	663.8	663.0
17.5°	646.1	648.4	647.6	654.5	653.8
20°	633.0	635.3	636.1	643.8	643.8
22.5°	618.4	621.5	623.0	630.7	632.3
25°	602.3	606.9	609.2	617.7	618.4
27.5°	584.6	591.5	594.6	602.3	603.1
30°	567.0	573.1	578.5	586.9	588.5
32.5°	547.8	555.4	561.6	571.6	573.1
35°	527.0	536.2	543.9	554.7	557.0
37.5°	506.3	517.0	526.2	537.0	539.3
40°	486.3	496.3	507.0	518.6	521.6
42.5°	463.3	474.8	487.8	500.9	503.2
45°	439.4	454.0	468.6	481.7	485.5
47.5°	417.2	431.8	448.7	461.7	466.3
50°	392.6	409.5	426.4	441.7	446.4
52.5°	368.0	384.9	404.9	420.2	424.8
55°	344.2	360.3	383.4	398.7	403.3
57.5°	317.3	337.3	359.5	378.0	381.8
60°	291.2	311.1	336.5	354.2	360.3
62.5°	265.8	288.1	313.4	331.1	337.3
65°	238.2	262.7	288.9	308.1	314.2
67.5°	212.0	238.2	265.8	285.0	291.2
70°	185.1	211.3	240.5	261.2	266.6
72.5°	159.0	185.9	217.4	237.4	243.5
75°	132.1	160.6	192.8	214.3	221.3
77.5°	106.8	136.7	170.6	192.1	199.7
80°	83.7	114.5	148.3	171.3	177.5
82.5°	60.7	93.0	126.8	150.6	157.5
85°	40.7	73.0	107.6	130.6	138.3
87.5°	25.4	56.9	90.7	112.9	119.8
90°	16.2	61.0	104.4	134.3	143.1
92.5°	30.8	55.1	98.4	127.7	133.8
95°	80.8	62.3	95.1	123.6	131.8
97.5°	144.3	194.9	91.3	117.7	125.9
100°	219.5	262.5	115.0	113.8	120.5
102.5°	304.4	336.7	381.3	111.8	118.0
105°	394.1	417.3	452.1	482.9	442.8
107.5°	477.8	494.7	530.6	556.3	566.7
110°	561.9	576.5	611.1	631.4	641.4

TEST NUMBER: P1032710

CATALOG NUMBER: S124DIW-B575D1340UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	643.5	660.4	688.3	704.0	715.3
115°	727.6	738.4	761.7	781.2	786.6
117.5°	803.5	813.3	840.2	855.0	861.1
120°	879.9	887.4	908.4	926.3	929.9
122.5°	952.0	954.5	977.9	994.5	997.3
125°	1019.4	1023.8	1040.4	1058.9	1064.8
127.5°	1085.0	1085.5	1107.4	1119.9	1124.0
130°	1147.3	1147.8	1163.9	1179.1	1183.7
132.5°	1205.2	1207.0	1221.4	1235.7	1239.0
135°	1262.3	1261.0	1271.5	1286.4	1293.6
137.5°	1313.7	1313.0	1322.5	1336.6	1339.2
140°	1363.9	1365.8	1369.1	1382.9	1388.1
142.5°	1408.2	1413.4	1413.9	1424.9	1427.9
145°	1454.5	1457.6	1457.6	1463.5	1469.2
147.5°	1490.6	1497.5	1496.2	1498.3	1502.6
150°	1530.4	1534.8	1533.5	1533.5	1534.8
152.5°	1563.1	1567.0	1564.4	1567.0	1565.7
155°	1594.0	1595.3	1591.4	1596.5	1592.7
157.5°	1621.0	1621.0	1615.8	1622.3	1615.8
160°	1644.1	1640.3	1639.0	1646.7	1639.0
162.5°	1664.7	1659.6	1658.3	1666.0	1657.0
165°	1681.5	1675.0	1675.0	1685.3	1673.7
167.5°	1695.6	1689.2	1687.9	1699.5	1686.6
170°	1707.2	1699.5	1700.8	1711.0	1698.2
172.5°	1714.9	1707.2	1708.5	1718.8	1704.6
175°	1720.1	1712.3	1713.6	1725.2	1709.8
177.5°	1723.9	1714.9	1717.5	1727.8	1712.3
180°	1720.1	1720.1	1720.1	1720.1	1720.1

(END OF REPORT)