

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032731

Luminaire Tested: S124DIW-B575D1560UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032731
REPORT IS A COMBINATION OF REPORTS P997767 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D1560UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8817.0 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032731

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032731

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	36	36	28
1	93	89	85	82	83	79	76	73	62	60	58	46	45	44	32	31	30	30	30	24
2	85	77	71	66	75	69	64	60	54	51	48	41	39	37	28	27	26	26	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	22	22	17
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19	19	19	14
5	65	53	46	40	57	48	41	36	38	33	29	29	25	23	20	18	16	16	16	13
6	59	48	40	34	53	43	36	31	34	29	26	26	22	20	18	16	14	14	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13	13	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	11	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	10	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7885	7885	7885
5°	7892	7659	7668
10°	7825	7446	7394
15°	7713	7193	7084
20°	7569	6920	6765
25°	7409	6631	6420
30°	7214	6318	6042
35°	7012	5999	5676
40°	6802	5655	5287
45°	6582	5309	4923
50°	6338	4974	4521
55°	6073	4585	4121
60°	5801	4156	3705
65°	5492	3714	3235
70°	5133	3182	2732
75°	4599	2565	2188
80°	3920	1854	1539
85°	3042	1033	828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6582 cd/sqm

TEST NUMBER: P1032731

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	1.0
10°-20°	256.8	2.9
20°-30°	377.9	4.3
30°-40°	439.3	5.0
40°-50°	439.3	5.0
50°-60°	384.2	4.4
60°-70°	285.2	3.2
70°-80°	161.8	1.8
80°-90°	50.6	0.6
90°-100°	67.9	0.8
100°-110°	447.3	5.1
110°-120°	854.0	9.7
120°-130°	1084.2	12.3
130°-140°	1159.8	13.2
140°-150°	1084.5	12.3
150°-160°	874.6	9.9
160°-170°	564.0	6.4
170°-180°	194.4	2.2
0°-30°	725.8	8.2
0°-40°	1165.1	13.2
0°-60°	1988.6	22.6
0°-90°	2486.2	28.2
90°-120°	1369.2	15.5
90°-150°	4697.7	53.3
90°-180°	6331.0	71.8
0°-180°	8817.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	967	967	967	967	967	
5°	966	963	955	963	962	92
15°	920	917	905	910	907	259
25°	833	828	817	818	814	383
35°	717	711	700	695	691	448
45°	585	580	567	559	556	451
55°	442	440	429	420	415	396
65°	300	296	288	280	277	297
75°	160	156	152	149	148	169
85°	42	42	40	40	40	45
90°	5	21	34	43	46	7
95°	84	32	34	43	44	104
105°	461	470	477	491	436	482
115°	860	865	863	866	866	847
125°	1209	1215	1212	1216	1218	1080
135°	1500	1498	1504	1507	1510	1156
145°	1729	1734	1734	1735	1738	1080
155°	1896	1898	1893	1899	1894	874
165°	2000	1992	1992	2005	1991	565
175°	2046	2037	2038	2052	2034	195
180°	2046	2046	2046	2046	2046	

TEST NUMBER: P1032731

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	967.0	967.0	967.0	967.0	967.0
2.5°	970.1	967.8	959.3	967.0	966.2
5°	966.2	963.1	954.6	963.1	961.6
7.5°	959.3	956.2	946.9	953.8	953.1
10°	949.2	946.1	936.0	942.2	940.7
12.5°	936.0	932.9	922.1	929.0	926.7
15°	919.7	916.6	905.0	909.7	907.3
17.5°	901.1	897.3	886.4	889.5	888.0
20°	880.2	876.3	864.7	867.0	865.5
22.5°	857.7	852.3	840.7	845.4	842.3
25°	833.0	827.5	816.7	817.5	814.4
27.5°	805.1	799.6	789.6	788.0	784.1
30°	777.2	771.0	760.9	757.8	753.9
32.5°	747.7	742.3	731.5	727.6	723.7
35°	716.7	711.3	700.5	695.0	691.2
37.5°	684.2	679.5	667.9	662.5	657.1
40°	652.4	646.2	634.6	626.8	623.0
42.5°	618.3	615.2	602.1	592.8	590.4
45°	585.0	579.6	567.2	558.7	556.3
47.5°	550.1	546.3	534.6	525.3	519.1
50°	514.5	511.4	500.5	489.7	485.1
52.5°	479.6	475.8	464.1	454.8	448.6
55°	442.4	440.1	429.3	420.0	415.3
57.5°	407.6	405.2	394.4	385.1	380.4
60°	371.1	367.3	357.2	350.2	346.4
62.5°	335.5	332.4	321.6	315.4	311.5
65°	299.9	296.0	288.2	280.5	276.6
67.5°	263.4	260.3	252.6	244.8	244.1
70°	230.1	224.7	218.5	212.3	210.0
72.5°	194.5	189.1	184.4	179.8	177.4
75°	159.6	155.7	151.9	148.8	148.0
77.5°	125.5	124.0	120.1	119.3	117.0
80°	95.3	93.0	91.4	89.9	89.1
82.5°	65.9	65.1	65.1	64.3	63.5
85°	41.8	41.8	40.3	40.3	39.5
87.5°	20.1	19.4	18.6	18.6	18.6
90°	4.6	21.4	33.7	42.8	45.9
92.5°	23.0	19.9	32.1	41.3	41.3
95°	84.2	32.1	33.7	42.8	44.4
97.5°	160.7	194.3	33.7	41.3	42.8
100°	251.0	278.5	67.3	41.3	42.8
102.5°	352.0	370.3	388.7	44.4	44.4
105°	460.6	469.8	477.4	491.2	436.1
107.5°	560.1	564.7	575.4	583.0	589.1
110°	661.1	665.6	674.8	677.9	682.5

TEST NUMBER: P1032731

CATALOG NUMBER: S124DIW-B575D1560UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	759.0	768.2	771.2	769.7	775.8
115°	860.0	864.6	863.0	866.1	866.1
117.5°	950.3	956.4	961.0	959.5	959.5
120°	1042.1	1048.2	1046.7	1049.7	1046.7
122.5°	1127.8	1130.8	1133.9	1135.4	1132.4
125°	1208.9	1215.0	1211.9	1216.5	1218.1
127.5°	1286.9	1288.5	1296.1	1294.6	1293.0
130°	1361.9	1363.4	1368.0	1369.6	1369.6
132.5°	1430.8	1433.8	1439.9	1441.5	1439.9
135°	1499.6	1498.1	1504.2	1507.3	1510.3
137.5°	1560.8	1560.8	1568.5	1571.5	1570.0
140°	1620.5	1623.6	1626.6	1631.2	1632.8
142.5°	1674.1	1680.2	1681.7	1684.8	1684.8
145°	1729.2	1733.7	1733.7	1735.3	1738.3
147.5°	1772.0	1781.2	1779.7	1781.2	1782.7
150°	1819.4	1825.6	1824.0	1824.0	1825.6
152.5°	1859.2	1863.8	1860.8	1863.8	1862.3
155°	1896.0	1897.5	1892.9	1899.0	1894.4
157.5°	1928.1	1928.1	1922.0	1929.6	1922.0
160°	1955.6	1951.0	1949.5	1958.7	1949.5
162.5°	1980.1	1974.0	1972.5	1981.6	1970.9
165°	2000.0	1992.4	1992.4	2004.6	1990.8
167.5°	2016.8	2009.2	2007.7	2021.4	2006.1
170°	2030.6	2021.4	2023.0	2035.2	2019.9
172.5°	2039.8	2030.6	2032.1	2044.4	2027.5
175°	2045.9	2036.7	2038.3	2052.0	2033.7
177.5°	2050.5	2039.8	2042.9	2055.1	2036.7
180°	2045.9	2045.9	2045.9	2045.9	2045.9

(END OF REPORT)