

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032747

Luminaire Tested: S124DIW-B575D470UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032747
REPORT IS A COMBINATION OF REPORTS P997834 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D470UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4398.0 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032747

CATALOG NUMBER: S124DIW-B575D470UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1032747

CATALOG NUMBER: S124DIW-B575D470UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	87	92	88	85	82	76	74	71	65	63	62	55	54	53
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	48	46	44
3	82	73	65	59	76	68	61	56	59	54	50	51	47	44	43	40	38
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	37	41	36	32	35	31	28
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25
7	59	47	39	33	55	44	37	31	38	33	28	33	29	25	29	25	22
8	55	42	35	29	51	40	33	28	35	29	25	31	26	22	26	23	20
9	51	39	31	26	48	36	30	25	32	27	23	28	24	20	24	21	18
10	48	36	28	23	44	34	27	22	30	24	20	26	22	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7920	7920	7920
5°	7927	7692	7702
10°	7860	7479	7426
15°	7747	7225	7116
20°	7603	6951	6794
25°	7441	6660	6449
30°	7246	6347	6069
35°	7043	6026	5701
40°	6832	5680	5310
45°	6611	5333	4946
50°	6367	4997	4541
55°	6100	4605	4140
60°	5828	4175	3721
65°	5516	3730	3249
70°	5156	3196	2744
75°	4619	2575	2199
80°	3936	1862	1546
85°	3056	1038	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6611 cd/sqm

TEST NUMBER: P1032747

CATALOG NUMBER: S124DIW-B575D470UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	2.1
10°-20°	257.9	5.9
20°-30°	379.6	8.6
30°-40°	441.2	10.0
40°-50°	441.2	10.0
50°-60°	385.9	8.8
60°-70°	286.5	6.5
70°-80°	162.5	3.7
80°-90°	47.8	1.1
90°-100°	20.4	0.5
100°-110°	134.5	3.1
110°-120°	256.8	5.8
120°-130°	326.0	7.4
130°-140°	348.8	7.9
140°-150°	326.1	7.4
150°-160°	263.0	6.0
160°-170°	169.6	3.9
170°-180°	58.5	1.3
0°-30°	729.1	16.6
0°-40°	1170.3	26.6
0°-60°	1997.4	45.4
0°-90°	2494.3	56.7
90°-120°	411.7	9.4
90°-150°	1412.7	32.1
90°-180°	1904.0	43.3
0°-180°	4398.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	921	909	914	911	260
25°	837	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	149	149	170
85°	42	42	40	40	40	45
90°	1	6	10	13	14	4
95°	25	10	10	13	13	31
105°	138	141	144	148	131	145
115°	259	260	260	260	260	255
125°	364	365	364	366	366	325
135°	451	450	452	453	454	347
145°	520	521	521	522	523	325
155°	570	571	569	571	570	263
165°	601	599	599	603	599	170
175°	615	612	613	617	612	59
180°	615	615	615	615	615	

TEST NUMBER: P1032747

CATALOG NUMBER: S124DIW-B575D470UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	971.3	971.3	971.3	971.3	971.3
2.5°	974.4	972.1	963.5	971.3	970.5
5°	970.5	967.4	958.8	967.4	965.8
7.5°	963.5	960.4	951.1	958.1	957.3
10°	953.4	950.3	940.2	946.4	944.8
12.5°	940.2	937.0	926.1	933.2	930.8
15°	923.8	920.7	909.0	913.7	911.4
17.5°	905.1	901.2	890.3	893.5	891.9
20°	884.1	880.2	868.6	870.9	869.3
22.5°	861.6	856.1	844.4	849.1	846.0
25°	836.6	831.2	820.3	821.1	818.0
27.5°	808.6	803.2	793.1	791.5	787.6
30°	780.6	774.4	764.3	761.2	757.3
32.5°	751.0	745.6	734.7	730.8	726.9
35°	719.9	714.5	703.6	698.1	694.2
37.5°	687.2	682.5	670.9	665.4	660.0
40°	655.3	649.1	637.4	629.6	625.7
42.5°	621.1	618.0	604.7	595.4	593.0
45°	587.6	582.2	569.7	561.1	558.8
47.5°	552.6	548.7	537.0	527.7	521.4
50°	516.8	513.7	502.8	491.9	487.2
52.5°	481.8	477.9	466.2	456.8	450.6
55°	444.4	442.1	431.2	421.8	417.2
57.5°	409.4	407.0	396.1	386.8	382.1
60°	372.8	368.9	358.8	351.8	347.9
62.5°	337.0	333.9	323.0	316.8	312.9
65°	301.2	297.3	289.5	281.7	277.8
67.5°	264.6	261.5	253.7	245.9	245.2
70°	231.1	225.7	219.5	213.2	210.9
72.5°	195.3	189.9	185.2	180.6	178.2
75°	160.3	156.4	152.5	149.4	148.7
77.5°	126.1	124.5	120.6	119.9	117.5
80°	95.7	93.4	91.8	90.3	89.5
82.5°	66.2	65.4	65.4	64.6	63.8
85°	42.0	42.0	40.5	40.5	39.7
87.5°	20.2	19.5	18.7	18.7	18.7
90°	1.4	6.4	10.1	12.9	13.8
92.5°	6.9	6.0	9.7	12.4	12.4
95°	25.3	9.7	10.1	12.9	13.3
97.5°	48.3	58.4	10.1	12.4	12.9
100°	75.5	83.7	20.2	12.4	12.9
102.5°	105.8	111.4	116.9	13.3	13.3
105°	138.5	141.3	143.6	147.7	131.1
107.5°	168.4	169.8	173.0	175.3	177.2
110°	198.8	200.2	202.9	203.8	205.2

TEST NUMBER: P1032747

CATALOG NUMBER: S124DIW-B575D470UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	228.2	231.0	231.9	231.5	233.3
115°	258.6	260.0	259.5	260.4	260.4
117.5°	285.8	287.6	289.0	288.5	288.5
120°	313.4	315.2	314.7	315.7	314.7
122.5°	339.1	340.1	341.0	341.4	340.5
125°	363.5	365.4	364.4	365.8	366.3
127.5°	387.0	387.5	389.8	389.3	388.8
130°	409.5	410.0	411.4	411.8	411.8
132.5°	430.2	431.2	433.0	433.5	433.0
135°	451.0	450.5	452.3	453.3	454.2
137.5°	469.4	469.4	471.7	472.6	472.1
140°	487.3	488.2	489.1	490.5	491.0
142.5°	503.4	505.3	505.7	506.6	506.6
145°	520.0	521.4	521.4	521.8	522.7
147.5°	532.9	535.6	535.2	535.6	536.1
150°	547.1	549.0	548.5	548.5	549.0
152.5°	559.1	560.5	559.5	560.5	560.0
155°	570.1	570.6	569.2	571.1	569.7
157.5°	579.8	579.8	578.0	580.3	578.0
160°	588.1	586.7	586.2	589.0	586.2
162.5°	595.4	593.6	593.1	595.9	592.7
165°	601.4	599.1	599.1	602.8	598.7
167.5°	606.5	604.2	603.7	607.9	603.3
170°	610.6	607.9	608.3	612.0	607.4
172.5°	613.4	610.6	611.1	614.8	609.7
175°	615.2	612.5	612.9	617.1	611.5
177.5°	616.6	613.4	614.3	618.0	612.5
180°	615.2	615.2	615.2	615.2	615.2

(END OF REPORT)