

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033204

Luminaire Tested: S124DIW-B1020D470UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033204
REPORT IS A COMBINATION OF REPORTS P996880 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1020D470UB50-4F0-XX-W2A-F
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6057.0 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033204

CATALOG NUMBER: S124DIW-B1020D470UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1033204

CATALOG NUMBER: S124DIW-B1020D470UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20					20				20
RC	80				70				50					30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	74	88	81	75	70	73	68	64	65	61	58	58	55	53	49
3	85	75	67	61	80	71	64	59	64	59	54	57	53	49	51	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	36
5	72	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24	22
9	53	40	33	27	50	39	31	27	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13448	13448	13448
5°	13460	13062	13078
10°	13345	12698	12610
15°	13154	12268	12082
20°	12910	11802	11537
25°	12635	11309	10949
30°	12302	10776	10304
35°	11959	10230	9681
40°	11601	9644	9017
45°	11225	9055	8397
50°	10810	8485	7710
55°	10358	7818	7028
60°	9895	7088	6318
65°	9365	6335	5518
70°	8757	5427	4659
75°	7844	4374	3732
80°	6683	3162	2626
85°	5196	1760	1413

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11225 cd/sqm

TEST NUMBER: P1033204

CATALOG NUMBER: S124DIW-B1020D470UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.4	2.6
10°-20°	437.9	7.2
20°-30°	644.5	10.6
30°-40°	749.2	12.4
40°-50°	749.1	12.4
50°-60°	655.2	10.8
60°-70°	486.5	8.0
70°-80°	276.0	4.6
80°-90°	80.3	1.3
90°-100°	19.6	0.3
100°-110°	128.8	2.1
110°-120°	245.9	4.1
120°-130°	312.2	5.2
130°-140°	333.9	5.5
140°-150°	312.3	5.2
150°-160°	251.8	4.2
160°-170°	162.4	2.7
170°-180°	56.0	0.9
0°-30°	1237.9	20.4
0°-40°	1987.1	32.8
0°-60°	3391.5	56.0
0°-90°	4234.2	69.9
90°-120°	394.2	6.5
90°-150°	1352.6	22.3
90°-180°	1823.0	30.1
0°-180°	6057.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1649	1649	1649	1649	1649	
5°	1648	1643	1628	1643	1640	156
15°	1569	1563	1544	1551	1547	442
25°	1421	1411	1393	1394	1389	654
35°	1222	1213	1195	1185	1179	764
45°	998	988	967	953	949	769
55°	755	751	732	716	708	676
65°	511	505	492	478	472	506
75°	272	266	259	254	252	289
85°	71	71	69	69	67	77
90°	1	6	10	12	13	6
95°	24	9	10	12	13	30
105°	133	135	138	141	126	139
115°	248	249	248	249	249	244
125°	348	350	349	350	351	311
135°	432	431	433	434	435	333
145°	498	499	499	500	500	311
155°	546	546	545	547	545	252
165°	576	574	574	577	573	163
175°	589	586	587	591	586	56
180°	589	589	589	589	589	

TEST NUMBER: P1033204

CATALOG NUMBER: S124DIW-B1020D470UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1649.2	1649.2	1649.2	1649.2	1649.2
2.5°	1654.5	1650.5	1636.0	1649.2	1647.9
5°	1647.9	1642.6	1628.1	1642.6	1640.0
7.5°	1636.0	1630.7	1614.8	1626.7	1625.4
10°	1618.8	1613.5	1596.3	1606.9	1604.3
12.5°	1596.3	1591.1	1572.6	1584.5	1580.5
15°	1568.6	1563.3	1543.5	1551.4	1547.4
17.5°	1536.9	1530.3	1511.8	1517.1	1514.4
20°	1501.2	1494.6	1474.8	1478.7	1476.1
22.5°	1462.9	1453.6	1433.8	1441.7	1436.4
25°	1420.6	1411.3	1392.8	1394.2	1388.9
27.5°	1373.0	1363.8	1346.6	1343.9	1337.3
30°	1325.4	1314.9	1297.7	1292.4	1285.8
32.5°	1275.2	1266.0	1247.5	1240.9	1234.3
35°	1222.4	1213.1	1194.6	1185.4	1178.8
37.5°	1166.9	1158.9	1139.1	1129.9	1120.6
40°	1112.7	1102.1	1082.3	1069.1	1062.5
42.5°	1054.5	1049.3	1026.8	1010.9	1007.0
45°	997.7	988.5	967.3	952.8	948.8
47.5°	938.2	931.6	911.8	896.0	885.4
50°	877.5	872.2	853.7	835.2	827.2
52.5°	818.0	811.4	791.6	775.7	765.1
55°	754.6	750.6	732.1	716.2	708.3
57.5°	695.1	691.1	672.6	656.8	648.8
60°	633.0	626.4	609.2	597.3	590.7
62.5°	572.2	566.9	548.4	537.8	531.2
65°	511.4	504.8	491.6	478.4	471.8
67.5°	449.3	444.0	430.8	417.6	416.3
70°	392.5	383.2	372.7	362.1	358.1
72.5°	331.7	322.4	314.5	306.6	302.6
75°	272.2	265.6	259.0	253.7	252.4
77.5°	214.1	211.4	204.8	203.5	199.5
80°	162.5	158.6	155.9	153.3	152.0
82.5°	112.3	111.0	111.0	109.7	108.4
85°	71.4	71.4	68.7	68.7	67.4
87.5°	34.4	33.0	31.7	31.7	31.7
90°	1.3	6.2	9.7	12.3	13.2
92.5°	6.6	5.7	9.3	11.9	11.9
95°	24.2	9.3	9.7	12.3	12.8
97.5°	46.3	56.0	9.7	11.9	12.3
100°	72.3	80.2	19.4	11.9	12.3
102.5°	101.3	106.6	111.9	12.8	12.8
105°	132.6	135.3	137.5	141.4	125.6
107.5°	161.3	162.6	165.7	167.9	169.6
110°	190.3	191.7	194.3	195.2	196.5

TEST NUMBER: P1033204

CATALOG NUMBER: S124DIW-B1020D470UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.5	221.2	222.1	221.6	223.4
115°	247.6	248.9	248.5	249.4	249.4
117.5°	273.6	275.4	276.7	276.2	276.2
120°	300.0	301.8	301.4	302.2	301.4
122.5°	324.7	325.6	326.5	326.9	326.0
125°	348.1	349.8	348.9	350.3	350.7
127.5°	370.5	371.0	373.2	372.7	372.3
130°	392.1	392.6	393.9	394.3	394.3
132.5°	412.0	412.8	414.6	415.0	414.6
135°	431.8	431.3	433.1	434.0	434.9
137.5°	449.4	449.4	451.6	452.5	452.0
140°	466.6	467.5	468.3	469.7	470.1
142.5°	482.0	483.8	484.2	485.1	485.1
145°	497.9	499.2	499.2	499.6	500.5
147.5°	510.2	512.8	512.4	512.8	513.3
150°	523.9	525.6	525.2	525.2	525.6
152.5°	535.3	536.6	535.8	536.6	536.2
155°	545.9	546.3	545.0	546.8	545.4
157.5°	555.1	555.1	553.4	555.6	553.4
160°	563.1	561.8	561.3	564.0	561.3
162.5°	570.1	568.4	567.9	570.6	567.5
165°	575.9	573.6	573.6	577.2	573.2
167.5°	580.7	578.5	578.1	582.0	577.6
170°	584.7	582.0	582.5	586.0	581.6
172.5°	587.3	584.7	585.1	588.6	583.8
175°	589.1	586.4	586.9	590.8	585.5
177.5°	590.4	587.3	588.2	591.7	586.4
180°	589.1	589.1	589.1	589.1	589.1

(END OF REPORT)