

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032774

Luminaire Tested: S124DIW-B795D1050UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032774
REPORT IS A COMBINATION OF REPORTS P997962 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D1050UB2750-4F0-XX-W2A-F1_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6840.0 lumens
Efficiency: N/A
Efficacy: 101.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032774

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032774

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	30	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1032774

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	1.8
10°-20°	340.7	5.0
20°-30°	501.4	7.3
30°-40°	582.8	8.5
40°-50°	582.8	8.5
50°-60°	509.7	7.5
60°-70°	378.4	5.5
70°-80°	214.7	3.1
80°-90°	64.2	0.9
90°-100°	83.3	1.2
100°-110°	249.4	3.6
110°-120°	423.7	6.2
120°-130°	558.7	8.2
130°-140°	627.6	9.2
140°-150°	616.8	9.0
150°-160°	518.8	7.6
160°-170°	345.2	5.0
170°-180°	120.9	1.8
0°-30°	963.0	14.1
0°-40°	1545.9	22.6
0°-60°	2638.4	38.6
0°-90°	3295.7	48.2
90°-120°	756.3	11.1
90°-150°	2559.4	37.4
90°-180°	3544.0	51.8
0°-180°	6840.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	3	14	22	28	30	8
95°	59	68	75	78	78	64
105°	230	231	235	238	241	244
115°	431	431	429	428	427	425
125°	627	627	626	624	622	559
135°	809	815	815	813	810	626
145°	983	987	988	987	984	615
155°	1126	1126	1125	1129	1125	518
165°	1226	1223	1221	1227	1223	346
175°	1275	1270	1270	1276	1270	121
180°	1277	1277	1277	1277	1277	

TEST NUMBER: P1032774

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	3.0	13.8	21.7	27.7	29.6
92.5°	25.7	38.5	43.5	46.4	47.4
95°	59.3	68.2	75.1	78.0	78.0
97.5°	94.8	102.7	110.6	114.6	114.6
100°	138.3	142.3	151.2	153.1	153.1
102.5°	183.8	184.7	192.6	195.6	196.6
105°	230.2	231.2	235.1	238.1	241.1
107.5°	278.6	279.6	280.6	284.5	283.5
110°	328.0	330.0	329.0	327.0	330.0



TEST NUMBER: P1032774

CATALOG NUMBER: S124DIW-B795D1050UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	379.4	379.4	377.4	377.4	377.4
115°	430.7	430.7	428.8	427.8	426.8
117.5°	479.1	479.1	478.2	475.2	472.2
120°	527.6	531.5	528.5	523.6	525.6
122.5°	577.9	578.9	577.9	575.0	570.0
125°	627.3	627.3	626.3	624.4	622.4
127.5°	671.8	674.8	672.8	670.8	669.8
130°	719.2	722.2	722.2	720.2	716.2
132.5°	767.6	769.6	768.6	766.6	765.6
135°	809.1	815.0	815.0	813.1	810.1
137.5°	855.5	858.5	860.5	857.5	858.5
140°	902.0	903.9	903.9	903.0	902.0
142.5°	944.5	946.4	945.4	945.4	945.4
145°	983.0	986.9	987.9	986.9	984.0
147.5°	1022.5	1027.4	1026.5	1025.5	1024.5
150°	1058.1	1062.0	1062.0	1062.0	1061.0
152.5°	1091.7	1093.6	1094.6	1097.6	1094.6
155°	1126.2	1126.2	1125.2	1129.2	1125.2
157.5°	1155.9	1153.9	1153.9	1156.9	1153.9
160°	1181.6	1180.6	1179.6	1182.5	1177.6
162.5°	1205.3	1202.3	1201.3	1207.2	1202.3
165°	1226.0	1223.0	1221.1	1227.0	1223.0
167.5°	1242.8	1238.9	1238.9	1244.8	1238.9
170°	1256.6	1251.7	1252.7	1258.6	1251.7
172.5°	1266.5	1262.6	1262.6	1269.5	1262.6
175°	1275.4	1270.5	1269.5	1276.4	1269.5
177.5°	1279.4	1274.4	1274.4	1281.3	1273.4
180°	1277.4	1277.4	1277.4	1277.4	1277.4

(END OF REPORT)