

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032793

Luminaire Tested: S124DIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032793
REPORT IS A COMBINATION OF REPORTS P998034 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D1340UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8458.0 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032793

CATALOG NUMBER: S124DIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032793

CATALOG NUMBER: S124DIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33
3	79	70	63	57	72	64	57	52	52	48	44	42	38	36	32	30	28
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	27	47	37	30	25	31	25	22	25	21	18	19	17	15
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	33	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1032793

CATALOG NUMBER: S124DIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	1.4
10°-20°	340.7	4.0
20°-30°	501.4	5.9
30°-40°	582.8	6.9
40°-50°	582.8	6.9
50°-60°	509.7	6.0
60°-70°	378.4	4.5
70°-80°	214.7	2.5
80°-90°	64.9	0.8
90°-100°	55.4	0.7
100°-110°	364.6	4.3
110°-120°	696.3	8.2
120°-130°	883.9	10.5
130°-140°	945.6	11.2
140°-150°	884.2	10.5
150°-160°	713.1	8.4
160°-170°	459.9	5.4
170°-180°	158.5	1.9
0°-30°	963.0	11.4
0°-40°	1545.9	18.3
0°-60°	2638.4	31.2
0°-90°	3296.4	39.0
90°-120°	1116.3	13.2
90°-150°	3830.1	45.3
90°-180°	5162.0	61.0
0°-180°	8458.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	4	18	27	35	37	7
95°	69	26	27	35	36	85
105°	376	383	389	400	356	393
115°	701	705	704	706	706	690
125°	986	991	988	992	993	880
135°	1223	1221	1226	1229	1231	942
145°	1410	1414	1414	1415	1417	881
155°	1546	1547	1543	1548	1544	713
165°	1631	1624	1624	1634	1623	461
175°	1668	1661	1662	1673	1658	159
180°	1668	1668	1668	1668	1668	

TEST NUMBER: P1032793

CATALOG NUMBER: S124DIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	3.7	17.5	27.4	34.9	37.4
92.5°	18.7	16.2	26.2	33.7	33.7
95°	68.6	26.2	27.4	34.9	36.2
97.5°	131.0	158.4	27.4	33.7	34.9
100°	204.6	227.1	54.9	33.7	34.9
102.5°	287.0	301.9	316.9	36.2	36.2
105°	375.5	383.0	389.3	400.5	355.6
107.5°	456.6	460.4	469.1	475.3	480.3
110°	539.0	542.7	550.2	552.7	556.4

TEST NUMBER: P1032793

CATALOG NUMBER: S124DIW-B795D1340UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	618.8	626.3	628.8	627.5	632.5
115°	701.2	704.9	703.7	706.1	706.1
117.5°	774.8	779.8	783.5	782.3	782.3
120°	849.6	854.6	853.4	855.9	853.4
122.5°	919.5	922.0	924.5	925.7	923.2
125°	985.6	990.6	988.1	991.9	993.1
127.5°	1049.2	1050.5	1056.7	1055.5	1054.2
130°	1110.4	1111.6	1115.4	1116.6	1116.6
132.5°	1166.5	1169.0	1174.0	1175.3	1174.0
135°	1222.7	1221.4	1226.4	1228.9	1231.4
137.5°	1272.6	1272.6	1278.8	1281.3	1280.0
140°	1321.2	1323.7	1326.2	1330.0	1331.2
142.5°	1364.9	1369.9	1371.1	1373.6	1373.6
145°	1409.8	1413.5	1413.5	1414.8	1417.3
147.5°	1444.7	1452.2	1451.0	1452.2	1453.5
150°	1483.4	1488.4	1487.2	1487.2	1488.4
152.5°	1515.8	1519.6	1517.1	1519.6	1518.3
155°	1545.8	1547.0	1543.3	1548.3	1544.5
157.5°	1572.0	1572.0	1567.0	1573.2	1567.0
160°	1594.4	1590.7	1589.5	1596.9	1589.5
162.5°	1614.4	1609.4	1608.2	1615.7	1606.9
165°	1630.6	1624.4	1624.4	1634.4	1623.1
167.5°	1644.4	1638.1	1636.9	1648.1	1635.6
170°	1655.6	1648.1	1649.3	1659.3	1646.8
172.5°	1663.1	1655.6	1656.8	1666.8	1653.1
175°	1668.1	1660.6	1661.8	1673.0	1658.1
177.5°	1671.8	1663.1	1665.6	1675.5	1660.6
180°	1668.1	1668.1	1668.1	1668.1	1668.1

(END OF REPORT)