

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032798

Luminaire Tested: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032798
REPORT IS A COMBINATION OF REPORTS P998086 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9515.0 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43			36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	38	37			31
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	33	31			26
3	79	70	63	57	71	63	57	53	52	47	44	41	38	35	30	28	27			22
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23			19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20			17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18			15
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16			13
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14			12
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	15	13			11
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	13	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10118	10118	10118	10118
5°	10093	11608	10152	8722
10°	10017	13543	10094	7652
15°	9897	15612	9966	6847
20°	9769	16930	9840	6139
25°	9582	16736	9674	5616
30°	9399	13833	9513	5347
35°	9143	10308	9243	5184
40°	8842	7766	8929	5104
45°	8385	6232	8490	4995
50°	7840	5251	7953	4944
55°	7197	4570	7310	4886
60°	6573	4025	6766	4805
65°	5987	3463	6043	4604
70°	5299	2849	5412	4240
75°	4622	2188	4591	3602
80°	3636	1439	3595	2734
85°	2394	646	2241	1595

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 13083 cd/sqm

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.8	1.3
10°-20°	372.7	3.9
20°-30°	592.2	6.2
30°-40°	658.0	6.9
40°-50°	598.4	6.3
50°-60°	489.0	5.1
60°-70°	349.0	3.7
70°-80°	192.1	2.0
80°-90°	56.0	0.6
90°-100°	65.3	0.7
100°-110°	430.0	4.5
110°-120°	821.1	8.6
120°-130°	1042.4	11.0
130°-140°	1115.2	11.7
140°-150°	1042.8	11.0
150°-160°	840.9	8.8
160°-170°	542.3	5.7
170°-180°	186.9	2.0
0°-30°	1085.7	11.4
0°-40°	1743.6	18.3
0°-60°	2831.0	29.8
0°-90°	3428.1	36.0
90°-120°	1316.5	13.8
90°-150°	4516.8	47.5
90°-180°	6087.0	64.0
0°-180°	9515.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1241	1241	1241	1241	1241	
5°	1236	1456	1243	1094	1236	117
15°	1180	2000	1188	877	1180	333
25°	1077	2123	1088	712	1077	496
35°	934	1255	945	631	934	584
45°	745	704	755	564	745	575
55°	524	461	532	492	524	472
65°	327	296	330	394	327	323
75°	160	148	159	244	160	168
85°	33	31	31	76	33	38
90°	4	44	4	44	4	6
95°	81	43	81	43	81	100
105°	443	419	443	419	443	463
115°	827	833	827	833	827	814
125°	1162	1171	1162	1171	1162	1038
135°	1442	1452	1442	1452	1442	1111
145°	1663	1671	1663	1671	1663	1039
155°	1823	1822	1823	1822	1823	841
165°	1923	1914	1923	1914	1923	543
175°	1967	1955	1967	1955	1967	187
180°	1967	1967	1967	1967	1967	

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1240.8	1253.2	1258.3	1262.4	1275.8	1279.9	1280.9	1287.1	1292.2	1293.3	1293.3
5°	1235.7	1255.2	1270.6	1285.0	1306.6	1315.9	1327.2	1339.5	1356.0	1366.3	1371.4
7.5°	1227.5	1256.3	1279.9	1304.6	1334.4	1352.9	1363.2	1396.1	1418.7	1437.2	1459.8
10°	1215.1	1252.1	1286.1	1322.1	1364.2	1386.8	1409.4	1449.5	1481.4	1517.4	1546.2
12.5°	1196.6	1244.9	1286.1	1336.4	1388.9	1415.6	1442.3	1512.2	1549.2	1581.1	1632.5
15°	1180.2	1228.5	1287.1	1338.5	1403.3	1443.4	1482.4	1527.7	1586.3	1655.1	1704.5
17.5°	1161.7	1222.3	1276.8	1348.8	1420.7	1458.8	1490.6	1560.6	1642.8	1710.6	1755.9
20°	1136.0	1197.7	1269.6	1345.7	1431.0	1460.8	1503.0	1596.5	1670.6	1737.4	1811.4
22.5°	1106.2	1178.1	1254.2	1327.2	1415.6	1478.3	1524.6	1606.8	1696.3	1773.4	1856.6
25°	1077.4	1155.5	1222.3	1322.1	1415.6	1457.8	1510.2	1607.8	1705.5	1799.1	1884.4
27.5°	1046.5	1119.5	1210.0	1289.2	1395.0	1441.3	1497.8	1604.8	1708.6	1802.1	1893.6
30°	1012.6	1090.7	1165.8	1259.3	1362.1	1421.8	1474.2	1590.4	1696.3	1793.9	1879.2
32.5°	974.6	1048.6	1128.8	1217.2	1325.1	1385.8	1451.6	1570.8	1683.9	1768.2	1834.0
35°	934.5	1009.5	1079.4	1169.9	1280.9	1341.6	1405.3	1536.9	1649.0	1717.8	1755.9
37.5°	890.3	961.2	1030.1	1119.5	1230.6	1295.3	1360.1	1487.6	1593.5	1651.0	1640.7
40°	848.1	911.9	975.6	1059.9	1176.1	1244.9	1301.5	1430.0	1522.5	1547.2	1513.3
42.5°	799.8	854.3	916.0	1002.3	1115.4	1180.2	1251.1	1368.3	1437.2	1426.9	1369.3
45°	745.3	793.6	855.3	936.5	1051.7	1118.5	1178.1	1289.2	1339.5	1313.8	1209.0
47.5°	692.9	740.2	790.6	871.8	983.8	1040.4	1101.0	1200.7	1229.5	1175.0	1070.2
50°	636.4	675.4	727.8	805.0	909.8	969.4	1019.8	1100.0	1110.3	1043.5	934.5
52.5°	581.9	614.8	665.1	741.2	838.9	886.2	935.5	1006.4	998.2	929.3	824.5
55°	524.3	555.1	601.4	671.3	757.7	802.9	845.0	907.8	890.3	819.3	727.8
57.5°	476.0	497.6	542.8	607.6	678.5	727.8	763.8	813.2	786.4	715.5	630.2
60°	420.5	447.2	485.2	537.7	607.6	640.5	672.3	705.2	686.7	618.9	542.8
62.5°	370.1	390.7	423.5	473.9	528.4	558.2	592.1	612.7	594.2	531.5	467.8
65°	326.9	343.4	369.1	410.2	462.6	487.3	506.8	526.4	510.9	452.3	406.1
67.5°	279.6	294.0	315.6	348.5	392.7	410.2	428.7	442.1	424.6	385.5	340.3
70°	237.5	247.8	268.3	293.0	323.8	340.3	355.7	369.1	353.6	320.7	286.8
72.5°	194.3	202.5	221.0	238.5	266.3	277.6	288.9	299.2	294.0	263.2	235.4
75°	160.4	163.5	175.8	190.2	207.7	220.0	228.2	234.4	230.3	205.6	188.1
77.5°	121.3	125.4	134.7	146.0	161.4	168.6	173.7	179.9	174.8	155.2	142.9
80°	88.4	89.4	94.6	104.9	115.1	116.2	121.3	129.5	126.4	113.1	103.8
82.5°	56.5	59.6	61.7	67.9	75.0	77.1	80.2	82.2	81.2	73.0	69.9
85°	32.9	32.9	35.0	39.1	41.1	44.2	45.2	46.3	48.3	43.2	40.1
87.5°	14.4	15.4	15.4	16.4	18.5	18.5	19.5	20.6	21.6	20.6	17.5
90°	4.4	8.0	11.6	15.2	18.8	20.6	21.9	24.5	27.2	29.8	32.4
92.5°	22.1	21.4	20.8	20.1	19.4	19.1	20.4	23.0	25.7	28.3	30.9
95°	80.9	69.8	58.7	47.6	36.5	30.9	31.1	31.4	31.7	32.1	32.4
97.5°	154.5	161.7	168.9	176.1	183.3	186.9	169.7	135.4	101.1	66.7	32.4
100°	241.3	247.2	253.1	259.0	264.9	267.8	245.2	200.1	155.0	109.8	64.7
102.5°	338.4	342.3	346.3	350.2	354.1	356.1	358.1	362.0	365.9	369.8	373.7
105°	442.9	444.9	446.8	448.8	450.7	451.7	452.5	454.1	455.8	457.4	459.0
107.5°	538.5	539.5	540.5	541.4	542.4	542.9	544.0	546.3	548.6	550.9	553.2
110°	635.6	636.6	637.6	638.5	639.5	640.0	641.0	642.9	644.9	646.8	648.8

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	729.8	731.8	733.7	735.7	737.6	738.6	738.9	739.6	740.2	740.9	741.5
115°	826.9	827.9	828.9	829.8	830.8	831.3	831.1	830.8	830.5	830.1	829.8
117.5°	913.7	915.0	916.3	917.6	918.9	919.6	920.1	921.1	922.0	923.0	924.0
120°	1001.9	1003.2	1004.5	1005.8	1007.1	1007.8	1007.6	1007.3	1007.0	1006.7	1006.4
122.5°	1084.3	1085.0	1085.6	1086.3	1087.0	1087.3	1087.6	1088.3	1088.9	1089.6	1090.2
125°	1162.3	1163.6	1164.9	1166.2	1167.5	1168.2	1167.9	1167.2	1166.6	1165.9	1165.3
127.5°	1237.4	1237.7	1238.0	1238.3	1238.6	1238.8	1239.6	1241.3	1242.9	1244.6	1246.2
130°	1309.4	1309.7	1310.1	1310.4	1310.7	1310.9	1311.4	1312.4	1313.3	1314.3	1315.3
132.5°	1375.7	1376.3	1377.0	1377.6	1378.3	1378.6	1379.3	1380.6	1381.9	1383.2	1384.5
135°	1441.9	1441.6	1441.2	1440.9	1440.6	1440.4	1441.1	1442.4	1443.7	1445.0	1446.3
137.5°	1500.7	1500.7	1500.7	1500.7	1500.7	1500.7	1501.5	1503.2	1504.8	1506.5	1508.1
140°	1558.1	1558.7	1559.4	1560.0	1560.7	1561.0	1561.3	1562.0	1562.7	1563.3	1564.0
142.5°	1609.6	1610.9	1612.2	1613.5	1614.8	1615.5	1615.7	1616.0	1616.3	1616.6	1616.9
145°	1662.6	1663.6	1664.6	1665.5	1666.5	1667.0	1667.0	1667.0	1667.0	1667.0	1667.0
147.5°	1703.8	1705.8	1707.7	1709.7	1711.6	1712.6	1712.4	1712.1	1711.8	1711.4	1711.1
150°	1749.4	1750.7	1752.0	1753.3	1754.6	1755.2	1755.0	1754.7	1754.4	1754.1	1753.8
152.5°	1787.6	1788.6	1789.6	1790.5	1791.5	1792.0	1791.7	1791.0	1790.4	1789.7	1789.1
155°	1822.9	1823.2	1823.6	1823.9	1824.2	1824.4	1823.9	1822.9	1822.0	1821.0	1820.0
157.5°	1853.8	1853.8	1853.8	1853.8	1853.8	1853.8	1853.1	1851.8	1850.5	1849.2	1847.9
160°	1880.3	1879.3	1878.3	1877.4	1876.4	1875.9	1875.7	1875.4	1875.1	1874.7	1874.4
162.5°	1903.8	1902.5	1901.2	1899.9	1898.6	1898.0	1897.8	1897.5	1897.2	1896.8	1896.5
165°	1923.0	1921.4	1919.7	1918.1	1916.4	1915.6	1915.6	1915.6	1915.6	1915.6	1915.6
167.5°	1939.2	1937.6	1935.9	1934.3	1932.6	1931.8	1931.6	1931.3	1931.0	1930.6	1930.3
170°	1952.4	1950.4	1948.5	1946.5	1944.6	1943.6	1943.8	1944.1	1944.4	1944.7	1945.0
172.5°	1961.2	1959.2	1957.3	1955.3	1953.4	1952.4	1952.6	1952.9	1953.2	1953.6	1953.9
175°	1967.1	1965.1	1963.2	1961.2	1959.3	1958.3	1958.5	1958.8	1959.1	1959.5	1959.8
177.5°	1971.5	1969.2	1966.9	1964.6	1962.3	1961.2	1961.5	1962.2	1962.9	1963.5	1964.2
180°	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1296.4	1314.9	1323.1	1325.1	1336.4	1329.2	1332.3	1331.3	1339.5	1340.6	1340.6
5°	1390.9	1412.5	1419.7	1430.0	1445.4	1449.5	1446.4	1452.6	1463.9	1455.7	1468.0
7.5°	1490.6	1514.3	1530.7	1553.4	1558.5	1571.9	1580.1	1587.3	1589.3	1590.4	1592.4
10°	1583.2	1613.0	1635.6	1673.6	1681.9	1689.1	1725.0	1710.6	1729.2	1723.0	1725.0
12.5°	1658.2	1716.8	1735.3	1799.1	1805.2	1829.9	1827.8	1850.5	1854.6	1862.8	1854.6
15°	1756.9	1824.8	1854.6	1890.6	1911.1	1939.9	1945.0	1975.9	1988.2	1999.5	1988.2
17.5°	1847.4	1883.4	1959.4	1988.2	2001.6	2017.0	2056.1	2067.4	2085.9	2078.7	2099.2
20°	1892.6	1944.0	2024.2	2073.5	2094.1	2108.5	2141.4	2158.9	2166.1	2166.1	2168.1
22.5°	1932.7	2006.7	2066.3	2122.9	2141.4	2151.7	2171.2	2184.6	2187.7	2189.7	2191.8
25°	1968.7	2035.5	2083.8	2115.7	2122.9	2122.9	2134.2	2126.0	2112.6	2122.9	2129.1
27.5°	1968.7	2016.0	2037.6	2048.9	2048.9	2021.1	2004.7	1970.7	1942.0	1933.7	1952.2
30°	1935.8	1957.4	1927.6	1899.8	1878.2	1859.7	1794.9	1743.5	1733.3	1726.1	1753.8
32.5°	1859.7	1832.0	1773.4	1693.2	1661.3	1619.2	1568.8	1529.7	1506.1	1497.8	1491.7
35°	1725.0	1653.1	1577.0	1469.1	1446.4	1393.0	1324.1	1295.3	1256.3	1255.2	1268.6
37.5°	1578.0	1467.0	1384.8	1282.0	1250.1	1193.5	1128.8	1099.0	1072.2	1051.7	1076.4
40°	1406.4	1309.7	1184.3	1100.0	1054.8	1024.9	970.5	937.6	925.2	915.0	930.4
42.5°	1246.0	1140.1	1042.4	956.1	919.1	885.1	849.2	817.3	808.0	807.0	818.3
45°	1086.6	982.8	892.3	818.3	794.7	774.1	739.2	729.9	714.5	704.2	709.3
47.5°	959.2	852.2	777.2	720.7	700.1	682.6	660.0	644.6	631.2	627.1	633.3
50°	833.7	761.8	684.7	637.4	622.0	605.5	588.0	573.6	567.5	563.4	567.5
52.5°	733.0	655.9	603.5	565.4	550.0	537.7	525.3	519.2	510.9	513.0	517.1
55°	642.5	574.7	530.5	502.7	493.5	488.3	472.9	465.7	462.6	460.6	462.6
57.5°	557.2	507.8	475.0	451.3	439.0	435.9	423.5	423.5	420.5	417.4	418.4
60°	489.3	447.2	415.3	396.8	394.8	389.6	381.4	380.4	373.2	376.3	377.3
62.5°	420.5	386.5	365.0	353.6	346.4	344.4	339.3	338.2	335.1	336.2	334.1
65°	366.0	338.2	316.6	307.4	304.3	303.3	299.2	296.1	294.0	296.1	294.0
67.5°	311.5	293.0	276.5	267.3	263.2	262.1	259.1	257.0	258.0	255.0	257.0
70°	260.1	241.6	231.3	226.2	224.1	221.0	221.0	221.0	221.0	219.0	217.9
72.5°	219.0	200.5	193.3	190.2	188.1	187.1	184.0	185.0	184.0	183.0	187.1
75°	173.7	162.4	155.2	152.1	154.2	151.1	148.0	150.1	147.0	148.0	152.1
77.5°	131.6	126.4	122.3	120.3	118.2	116.2	116.2	114.1	114.1	114.1	114.1
80°	95.6	94.6	87.4	86.4	86.4	84.3	84.3	84.3	84.3	83.3	84.3
82.5°	63.7	62.7	60.7	59.6	57.6	58.6	58.6	56.5	56.5	55.5	56.5
85°	37.0	37.0	35.0	33.9	32.9	33.9	31.9	30.8	31.9	30.8	31.9
87.5°	17.5	15.4	16.4	15.4	13.4	14.4	12.3	13.4	12.3	11.3	13.4
90°	34.4	36.3	38.3	40.2	41.2	41.5	42.2	42.8	43.5	44.1	43.5
92.5°	32.9	34.8	36.8	38.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7
95°	34.4	36.3	38.3	40.2	41.2	41.4	41.7	42.0	42.4	42.7	42.4
97.5°	34.0	35.6	37.3	38.9	39.7	39.9	40.2	40.5	40.9	41.2	40.9
100°	59.1	53.6	48.0	42.5	39.7	39.9	40.2	40.5	40.9	41.2	40.9
102.5°	300.1	226.6	153.0	79.5	42.7	42.7	42.7	42.7	42.7	42.7	42.7
105°	462.0	464.9	467.9	470.8	472.3	466.4	454.6	442.9	431.1	419.3	431.1
107.5°	554.8	556.5	558.1	559.8	560.6	561.2	562.5	563.8	565.1	566.4	565.1
110°	649.5	650.1	650.8	651.5	651.8	652.3	653.3	654.2	655.2	656.2	655.2

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	741.2	740.9	740.6	740.3	740.1	740.7	742.0	743.3	744.6	745.9	744.6
115°	830.4	831.1	831.7	832.4	832.7	832.7	832.7	832.7	832.7	832.7	832.7
117.5°	923.7	923.3	923.0	922.7	922.5	922.5	922.5	922.5	922.5	922.5	922.5
120°	1007.0	1007.7	1008.3	1009.0	1009.3	1009.0	1008.3	1007.7	1007.0	1006.4	1007.0
122.5°	1090.5	1090.9	1091.2	1091.5	1091.7	1091.4	1090.7	1090.1	1089.4	1088.8	1089.4
125°	1166.3	1167.3	1168.2	1169.2	1169.7	1169.9	1170.2	1170.5	1170.8	1171.1	1170.8
127.5°	1245.9	1245.5	1245.2	1244.9	1244.7	1244.5	1244.2	1243.9	1243.5	1243.2	1243.5
130°	1315.6	1316.0	1316.3	1316.6	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8
132.5°	1384.8	1385.2	1385.5	1385.8	1386.0	1385.8	1385.5	1385.2	1384.8	1384.5	1384.8
135°	1446.9	1447.6	1448.2	1448.9	1449.2	1449.5	1450.2	1450.9	1451.5	1452.2	1451.5
137.5°	1508.7	1509.4	1510.0	1510.7	1511.0	1510.8	1510.5	1510.2	1509.8	1509.5	1509.8
140°	1565.0	1566.0	1566.9	1567.9	1568.4	1568.6	1568.9	1569.2	1569.6	1569.9	1569.6
142.5°	1617.6	1618.2	1618.9	1619.6	1619.9	1619.9	1619.9	1619.9	1619.9	1619.9	1619.9
145°	1667.3	1667.6	1667.9	1668.2	1668.4	1668.7	1669.4	1670.1	1670.7	1671.4	1670.7
147.5°	1711.4	1711.8	1712.1	1712.4	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1	1713.8
150°	1753.8	1753.8	1753.8	1753.8	1753.8	1754.0	1754.3	1754.6	1754.9	1755.2	1754.9
152.5°	1789.7	1790.4	1791.0	1791.7	1792.0	1791.8	1791.5	1791.2	1790.9	1790.6	1790.9
155°	1821.3	1822.6	1823.9	1825.2	1825.9	1825.4	1824.4	1823.5	1822.5	1821.5	1822.5
157.5°	1849.5	1851.2	1852.8	1854.5	1855.3	1854.5	1852.8	1851.2	1849.5	1847.9	1849.5
160°	1876.4	1878.3	1880.3	1882.2	1883.2	1882.2	1880.3	1878.3	1876.4	1874.4	1876.4
162.5°	1898.5	1900.4	1902.4	1904.3	1905.3	1904.2	1901.9	1899.6	1897.3	1895.0	1897.3
165°	1918.2	1920.8	1923.5	1926.1	1927.4	1925.9	1923.0	1920.0	1917.1	1914.1	1917.1
167.5°	1933.3	1936.2	1939.2	1942.1	1943.6	1942.0	1938.7	1935.4	1932.2	1928.9	1932.2
170°	1947.6	1950.2	1952.9	1955.5	1956.8	1955.2	1951.9	1948.6	1945.4	1942.1	1945.4
172.5°	1956.5	1959.1	1961.7	1964.3	1965.6	1963.8	1960.2	1956.7	1953.1	1949.5	1953.1
175°	1962.7	1965.7	1968.6	1971.5	1973.0	1971.0	1967.1	1963.2	1959.2	1955.3	1959.2
177.5°	1966.8	1969.4	1972.0	1974.6	1975.9	1973.9	1970.0	1966.1	1962.2	1958.3	1962.2
180°	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1338.5	1335.4	1331.3	1331.3	1326.2	1326.2	1317.9	1303.5	1291.2	1287.1	1289.2
5°	1452.6	1453.6	1447.5	1442.3	1433.1	1425.9	1412.5	1386.8	1378.6	1362.1	1350.8
7.5°	1583.2	1579.1	1567.8	1559.5	1557.5	1541.0	1512.2	1481.4	1456.7	1440.3	1416.6
10°	1730.2	1713.7	1697.3	1692.1	1679.8	1652.1	1619.2	1585.2	1551.3	1515.3	1475.2
12.5°	1853.5	1821.7	1820.6	1808.3	1784.7	1769.2	1730.2	1681.9	1623.3	1583.2	1537.9
15°	1986.2	1956.3	1931.7	1909.1	1897.8	1852.5	1819.6	1759.0	1689.1	1645.9	1615.0
17.5°	2080.7	2067.4	2025.2	2014.9	1999.5	1947.1	1894.7	1835.0	1774.4	1713.7	1630.5
20°	2156.8	2148.6	2120.8	2106.4	2081.8	2040.6	1976.9	1908.0	1838.1	1751.8	1673.6
22.5°	2189.7	2179.4	2156.8	2144.5	2129.1	2094.1	2039.6	1961.5	1870.0	1792.9	1709.6
25°	2124.9	2143.5	2137.3	2132.1	2126.0	2105.4	2064.3	1995.4	1906.0	1818.6	1714.8
27.5°	1979.0	2010.8	2041.7	2045.8	2056.1	2064.3	2047.8	1998.5	1923.5	1830.9	1716.8
30°	1782.6	1797.0	1859.7	1878.2	1892.6	1945.0	1975.9	1963.5	1906.0	1822.7	1717.8
32.5°	1530.7	1568.8	1632.5	1676.7	1715.8	1774.4	1854.6	1886.4	1865.9	1798.0	1694.2
35°	1292.2	1337.5	1411.5	1468.0	1507.1	1590.4	1684.9	1753.8	1779.5	1745.6	1653.1
37.5°	1096.9	1151.4	1217.2	1238.8	1284.0	1386.8	1517.4	1613.0	1675.7	1678.8	1606.8
40°	949.9	977.7	1030.1	1063.0	1107.2	1193.5	1321.0	1447.5	1542.1	1573.9	1535.9
42.5°	825.5	847.1	886.2	926.3	966.4	1032.1	1149.3	1267.6	1395.0	1458.8	1457.8
45°	726.8	749.4	776.2	809.1	836.8	907.8	1000.3	1121.6	1231.6	1330.3	1354.9
47.5°	640.5	660.0	692.9	707.3	725.8	792.6	872.8	985.9	1100.0	1213.1	1241.9
50°	576.7	593.2	615.8	625.0	645.6	695.0	760.7	852.2	978.7	1082.5	1136.0
52.5°	519.2	531.5	549.0	556.2	570.6	607.6	667.2	739.2	844.0	950.9	1026.0
55°	469.8	478.0	490.4	498.6	508.9	541.8	586.0	650.7	741.2	833.7	906.7
57.5°	423.5	429.7	442.1	446.2	454.4	480.1	510.9	565.4	648.7	730.9	801.9
60°	380.4	384.5	391.7	400.9	407.1	424.6	453.4	498.6	565.4	640.5	698.0
62.5°	339.3	345.4	347.5	351.6	356.7	373.2	395.8	428.7	487.3	549.0	609.6
65°	297.1	302.2	306.4	307.4	312.5	324.9	345.4	374.2	412.2	465.7	522.2
67.5°	258.0	261.1	263.2	267.3	272.4	278.6	295.0	316.6	351.6	394.8	440.0
70°	222.1	222.1	225.1	226.2	232.3	239.5	246.7	267.3	298.1	333.1	363.9
72.5°	183.0	188.1	187.1	192.2	191.2	196.4	205.6	219.0	241.6	269.3	299.2
75°	149.1	152.1	152.1	152.1	154.2	158.3	163.5	175.8	193.3	215.9	233.4
77.5°	116.2	118.2	118.2	118.2	119.3	123.4	128.5	136.7	149.1	162.4	172.7
80°	83.3	85.3	85.3	87.4	87.4	88.4	93.6	97.7	103.8	114.1	124.4
82.5°	56.5	57.6	59.6	59.6	58.6	60.7	61.7	65.8	72.0	74.0	81.2
85°	30.8	31.9	32.9	32.9	33.9	36.0	35.0	39.1	39.1	43.2	45.2
87.5°	12.3	14.4	14.4	13.4	14.4	14.4	14.4	16.4	17.5	18.5	17.5
90°	42.8	42.2	41.5	41.2	40.2	38.3	36.3	34.4	32.4	29.8	27.2
92.5°	39.7	39.7	39.7	39.7	38.7	36.8	34.8	32.9	30.9	28.3	25.7
95°	42.0	41.7	41.4	41.2	40.2	38.3	36.3	34.4	32.4	32.1	31.7
97.5°	40.5	40.2	39.9	39.7	38.9	37.3	35.6	34.0	32.4	66.7	101.1
100°	40.5	40.2	39.9	39.7	42.5	48.0	53.6	59.1	64.7	109.8	155.0
102.5°	42.7	42.7	42.7	42.7	79.5	153.0	226.6	300.1	373.7	369.8	365.9
105°	442.9	454.6	466.4	472.3	470.8	467.9	464.9	462.0	459.0	457.4	455.8
107.5°	563.8	562.5	561.2	560.6	559.8	558.1	556.5	554.8	553.2	550.9	548.6
110°	654.2	653.3	652.3	651.8	651.5	650.8	650.1	649.5	648.8	646.8	644.9

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	743.3	742.0	740.7	740.1	740.3	740.6	740.9	741.2	741.5	740.9	740.2
115°	832.7	832.7	832.7	832.7	832.4	831.7	831.1	830.4	829.8	830.1	830.5
117.5°	922.5	922.5	922.5	922.5	922.7	923.0	923.3	923.7	924.0	923.0	922.0
120°	1007.7	1008.3	1009.0	1009.3	1009.0	1008.3	1007.7	1007.0	1006.4	1006.7	1007.0
122.5°	1090.1	1090.7	1091.4	1091.7	1091.5	1091.2	1090.9	1090.5	1090.2	1089.6	1088.9
125°	1170.5	1170.2	1169.9	1169.7	1169.2	1168.2	1167.3	1166.3	1165.3	1165.9	1166.6
127.5°	1243.9	1244.2	1244.5	1244.7	1244.9	1245.2	1245.5	1245.9	1246.2	1244.6	1242.9
130°	1316.8	1316.8	1316.8	1316.8	1316.6	1316.3	1316.0	1315.6	1315.3	1314.3	1313.3
132.5°	1385.2	1385.5	1385.8	1386.0	1385.8	1385.5	1385.2	1384.8	1384.5	1383.2	1381.9
135°	1450.9	1450.2	1449.5	1449.2	1448.9	1448.2	1447.6	1446.9	1446.3	1445.0	1443.7
137.5°	1510.2	1510.5	1510.8	1511.0	1510.7	1510.0	1509.4	1508.7	1508.1	1506.5	1504.8
140°	1569.2	1568.9	1568.6	1568.4	1567.9	1566.9	1566.0	1565.0	1564.0	1563.3	1562.7
142.5°	1619.9	1619.9	1619.9	1619.9	1619.6	1618.9	1618.2	1617.6	1616.9	1616.6	1616.3
145°	1670.1	1669.4	1668.7	1668.4	1668.2	1667.9	1667.6	1667.3	1667.0	1667.0	1667.0
147.5°	1713.4	1713.1	1712.8	1712.6	1712.4	1712.1	1711.8	1711.4	1711.1	1711.4	1711.8
150°	1754.6	1754.3	1754.0	1753.8	1753.8	1753.8	1753.8	1753.8	1753.8	1754.1	1754.4
152.5°	1791.2	1791.5	1791.8	1792.0	1791.7	1791.0	1790.4	1789.7	1789.1	1789.7	1790.4
155°	1823.5	1824.4	1825.4	1825.9	1825.2	1823.9	1822.6	1821.3	1820.0	1821.0	1822.0
157.5°	1851.2	1852.8	1854.5	1855.3	1854.5	1852.8	1851.2	1849.5	1847.9	1849.2	1850.5
160°	1878.3	1880.3	1882.2	1883.2	1882.2	1880.3	1878.3	1876.4	1874.4	1874.7	1875.1
162.5°	1899.6	1901.9	1904.2	1905.3	1904.3	1902.4	1900.4	1898.5	1896.5	1896.8	1897.2
165°	1920.0	1923.0	1925.9	1927.4	1926.1	1923.5	1920.8	1918.2	1915.6	1915.6	1915.6
167.5°	1935.4	1938.7	1942.0	1943.6	1942.1	1939.2	1936.2	1933.3	1930.3	1930.6	1931.0
170°	1948.6	1951.9	1955.2	1956.8	1955.5	1952.9	1950.2	1947.6	1945.0	1944.7	1944.4
172.5°	1956.7	1960.2	1963.8	1965.6	1964.3	1961.7	1959.1	1956.5	1953.9	1953.6	1953.2
175°	1963.2	1967.1	1971.0	1973.0	1971.5	1968.6	1965.7	1962.7	1959.8	1959.5	1959.1
177.5°	1966.1	1970.0	1973.9	1975.9	1974.6	1972.0	1969.4	1966.8	1964.2	1963.5	1962.9
180°	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1279.9	1275.8	1272.7	1272.7	1263.5	1254.2	1249.1	1247.0	1244.9	1236.7	1225.4
5°	1332.3	1319.0	1309.7	1300.5	1285.0	1268.6	1252.1	1242.9	1229.5	1211.0	1197.7
7.5°	1390.9	1359.1	1348.8	1337.5	1306.6	1278.9	1256.3	1236.7	1215.1	1191.5	1167.8
10°	1440.3	1406.4	1383.7	1364.2	1324.1	1287.1	1253.2	1224.4	1196.6	1165.8	1137.0
12.5°	1487.6	1439.2	1415.6	1386.8	1344.7	1291.2	1247.0	1211.0	1169.9	1138.0	1103.1
15°	1553.4	1472.1	1433.1	1414.6	1358.0	1295.3	1241.9	1188.4	1154.5	1106.2	1075.3
17.5°	1563.6	1497.8	1472.1	1424.9	1357.0	1286.1	1224.4	1170.9	1119.5	1076.4	1036.3
20°	1599.6	1513.3	1472.1	1442.3	1352.9	1280.9	1213.1	1144.2	1094.9	1048.6	1003.4
22.5°	1622.2	1524.6	1481.4	1434.1	1348.8	1262.4	1182.2	1122.6	1062.0	1014.7	978.7
25°	1616.1	1518.4	1470.1	1425.9	1322.1	1235.7	1163.7	1087.7	1031.1	979.7	932.4
27.5°	1613.0	1503.0	1451.6	1402.2	1304.6	1214.1	1123.6	1062.0	999.2	939.6	904.7
30°	1604.8	1483.5	1423.8	1370.4	1268.6	1174.0	1096.9	1024.9	962.2	907.8	861.5
32.5°	1577.0	1450.6	1393.0	1335.4	1229.5	1134.9	1056.8	990.0	927.3	870.7	826.5
35°	1540.0	1411.5	1348.8	1288.1	1182.2	1086.6	1014.7	944.8	886.2	831.7	789.5
37.5°	1503.0	1366.3	1307.7	1237.8	1140.1	1040.4	966.4	903.6	849.2	792.6	746.4
40°	1449.5	1312.8	1248.0	1188.4	1074.3	980.7	912.9	856.4	802.9	749.4	710.4
42.5°	1376.5	1254.2	1187.4	1121.6	1014.7	922.1	856.4	806.0	755.6	711.4	668.2
45°	1302.5	1183.3	1123.6	1065.0	948.9	861.5	800.8	754.6	712.4	664.1	629.2
47.5°	1213.1	1112.3	1052.7	995.1	885.1	797.8	742.2	699.1	660.0	619.9	587.0
50°	1121.6	1034.2	979.7	920.1	815.2	736.1	681.6	645.6	613.7	575.7	549.0
52.5°	1022.9	946.8	900.6	843.0	750.5	677.5	622.0	586.0	559.3	531.5	507.8
55°	918.0	862.5	813.2	766.9	679.5	613.7	564.4	532.5	514.0	488.3	467.8
57.5°	823.5	770.0	740.2	687.8	611.7	546.9	507.8	481.1	459.5	444.1	427.7
60°	724.8	681.6	648.7	610.7	543.8	489.3	448.2	432.8	410.2	398.9	391.7
62.5°	630.2	599.3	568.5	539.7	480.1	428.7	397.8	378.3	365.0	353.6	347.5
65°	540.7	512.0	490.4	464.7	415.3	374.2	345.4	330.0	316.6	313.6	306.4
67.5°	453.4	441.0	417.4	396.8	354.7	322.8	301.2	281.7	274.5	271.4	265.2
70°	379.3	365.0	346.4	329.0	297.1	269.3	249.8	242.6	232.3	231.3	224.1
72.5°	312.5	295.0	281.7	268.3	244.7	220.0	209.7	199.4	194.3	190.2	187.1
75°	247.8	235.4	226.2	214.9	194.3	177.8	163.5	159.3	156.3	155.2	153.2
77.5°	185.0	176.8	172.7	161.4	147.0	132.6	126.4	120.3	120.3	118.2	119.3
80°	131.6	126.4	121.3	115.1	102.8	96.6	91.5	87.4	85.3	84.3	85.3
82.5°	83.3	80.2	79.2	75.0	66.8	63.7	59.6	56.5	56.5	56.5	56.5
85°	46.3	46.3	46.3	40.1	37.0	33.9	31.9	30.8	30.8	30.8	31.9
87.5°	19.5	19.5	16.4	16.4	15.4	13.4	12.3	12.3	13.4	13.4	14.4
90°	24.5	21.9	20.6	18.8	15.2	11.6	8.0	4.4	8.0	11.6	15.2
92.5°	23.0	20.4	19.1	19.4	20.1	20.8	21.4	22.1	21.4	20.8	20.1
95°	31.4	31.1	30.9	36.5	47.6	58.7	69.8	80.9	69.8	58.7	47.6
97.5°	135.4	169.7	186.9	183.3	176.1	168.9	161.7	154.5	161.7	168.9	176.1
100°	200.1	245.2	267.8	264.9	259.0	253.1	247.2	241.3	247.2	253.1	259.0
102.5°	362.0	358.1	356.1	354.1	350.2	346.3	342.3	338.4	342.3	346.3	350.2
105°	454.1	452.5	451.7	450.7	448.8	446.8	444.9	442.9	444.9	446.8	448.8
107.5°	546.3	544.0	542.9	542.4	541.4	540.5	539.5	538.5	539.5	540.5	541.4
110°	642.9	641.0	640.0	639.5	638.5	637.6	636.6	635.6	636.6	637.6	638.5

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	739.6	738.9	738.6	737.6	735.7	733.7	731.8	729.8	731.8	733.7	735.7
115°	830.8	831.1	831.3	830.8	829.8	828.9	827.9	826.9	827.9	828.9	829.8
117.5°	921.1	920.1	919.6	918.9	917.6	916.3	915.0	913.7	915.0	916.3	917.6
120°	1007.3	1007.6	1007.8	1007.1	1005.8	1004.5	1003.2	1001.9	1003.2	1004.5	1005.8
122.5°	1088.3	1087.6	1087.3	1087.0	1086.3	1085.6	1085.0	1084.3	1085.0	1085.6	1086.3
125°	1167.2	1167.9	1168.2	1167.5	1166.2	1164.9	1163.6	1162.3	1163.6	1164.9	1166.2
127.5°	1241.3	1239.6	1238.8	1238.6	1238.3	1238.0	1237.7	1237.4	1237.7	1238.0	1238.3
130°	1312.4	1311.4	1310.9	1310.7	1310.4	1310.1	1309.7	1309.4	1309.7	1310.1	1310.4
132.5°	1380.6	1379.3	1378.6	1378.3	1377.6	1377.0	1376.3	1375.7	1376.3	1377.0	1377.6
135°	1442.4	1441.1	1440.4	1440.6	1440.9	1441.2	1441.6	1441.9	1441.6	1441.2	1440.9
137.5°	1503.2	1501.5	1500.7	1500.7	1500.7	1500.7	1500.7	1500.7	1500.7	1500.7	1500.7
140°	1562.0	1561.3	1561.0	1560.7	1560.0	1559.4	1558.7	1558.1	1558.7	1559.4	1560.0
142.5°	1616.0	1615.7	1615.5	1614.8	1613.5	1612.2	1610.9	1609.6	1610.9	1612.2	1613.5
145°	1667.0	1667.0	1667.0	1666.5	1665.5	1664.6	1663.6	1662.6	1663.6	1664.6	1665.5
147.5°	1712.1	1712.4	1712.6	1711.6	1709.7	1707.7	1705.8	1703.8	1705.8	1707.7	1709.7
150°	1754.7	1755.0	1755.2	1754.6	1753.3	1752.0	1750.7	1749.4	1750.7	1752.0	1753.3
152.5°	1791.0	1791.7	1792.0	1791.5	1790.5	1789.6	1788.6	1787.6	1788.6	1789.6	1790.5
155°	1822.9	1823.9	1824.4	1824.2	1823.9	1823.6	1823.2	1822.9	1823.2	1823.6	1823.9
157.5°	1851.8	1853.1	1853.8	1853.8	1853.8	1853.8	1853.8	1853.8	1853.8	1853.8	1853.8
160°	1875.4	1875.7	1875.9	1876.4	1877.4	1878.3	1879.3	1880.3	1879.3	1878.3	1877.4
162.5°	1897.5	1897.8	1898.0	1898.6	1899.9	1901.2	1902.5	1903.8	1902.5	1901.2	1899.9
165°	1915.6	1915.6	1915.6	1916.4	1918.1	1919.7	1921.4	1923.0	1921.4	1919.7	1918.1
167.5°	1931.3	1931.6	1931.8	1932.6	1934.3	1935.9	1937.6	1939.2	1937.6	1935.9	1934.3
170°	1944.1	1943.8	1943.6	1944.6	1946.5	1948.5	1950.4	1952.4	1950.4	1948.5	1946.5
172.5°	1952.9	1952.6	1952.4	1953.4	1955.3	1957.3	1959.2	1961.2	1959.2	1957.3	1955.3
175°	1958.8	1958.5	1958.3	1959.3	1961.2	1963.2	1965.1	1967.1	1965.1	1963.2	1961.2
177.5°	1962.2	1961.5	1961.2	1962.3	1964.6	1966.9	1969.2	1971.5	1969.2	1966.9	1964.6
180°	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1222.3	1218.2	1220.3	1210.0	1200.7	1187.4	1176.1	1174.0	1172.0	1178.1	1174.0
5°	1187.4	1182.2	1177.1	1164.8	1146.3	1134.9	1118.5	1117.5	1111.3	1102.1	1104.1
7.5°	1149.3	1146.3	1139.1	1119.5	1103.1	1083.5	1070.2	1058.9	1053.7	1045.5	1042.4
10°	1118.5	1107.2	1101.0	1079.4	1059.9	1039.3	1021.9	1013.6	1004.4	997.2	992.1
12.5°	1076.4	1073.3	1055.8	1038.3	1021.9	998.2	984.9	961.2	948.9	955.0	953.0
15°	1048.6	1034.2	1030.1	1005.4	977.7	962.2	937.6	922.1	917.0	907.8	896.4
17.5°	1011.6	1002.3	987.9	965.3	933.5	911.9	894.4	880.0	873.8	861.5	852.2
20°	976.6	961.2	949.9	929.3	898.5	870.7	849.2	839.9	824.5	814.2	809.1
22.5°	944.8	933.5	917.0	886.2	859.4	832.7	807.0	793.6	779.2	773.1	764.9
25°	905.7	887.2	875.9	842.0	813.2	791.6	767.9	750.5	742.2	732.0	729.9
27.5°	867.7	850.2	836.8	807.0	772.1	744.3	729.9	717.6	703.2	703.2	698.0
30°	829.6	817.3	796.7	767.9	735.0	708.3	691.9	680.6	675.4	671.3	670.3
32.5°	791.6	775.1	762.8	723.7	699.1	674.4	662.1	652.8	646.6	645.6	646.6
35°	752.5	734.0	721.7	686.7	662.1	639.4	634.3	626.1	623.0	622.0	627.1
37.5°	711.4	697.0	681.6	652.8	625.0	611.7	601.4	598.3	597.3	603.5	605.5
40°	673.4	661.0	646.6	615.8	595.2	580.8	575.7	572.6	576.7	582.9	586.0
42.5°	637.4	619.9	608.6	580.8	562.3	554.1	547.9	547.9	552.1	559.3	564.4
45°	599.3	586.0	574.7	550.0	533.5	524.3	523.3	524.3	529.4	534.6	540.7
47.5°	562.3	549.0	536.6	516.1	501.7	496.5	495.5	496.5	504.8	512.0	519.2
50°	528.4	514.0	502.7	483.2	471.9	465.7	466.7	471.9	478.0	488.3	497.6
52.5°	488.3	478.0	467.8	450.3	440.0	435.9	439.0	443.1	454.4	461.6	472.9
55°	449.3	440.0	431.8	418.4	410.2	407.1	409.2	415.3	424.6	436.9	450.3
57.5°	413.3	403.0	394.8	385.5	376.3	377.3	378.3	386.5	397.8	409.2	424.6
60°	373.2	367.0	359.8	348.5	344.4	344.4	347.5	356.7	367.0	385.5	398.9
62.5°	337.2	329.0	323.8	316.6	310.5	311.5	318.7	326.9	339.3	354.7	372.1
65°	300.2	290.9	286.8	280.7	278.6	279.6	284.8	297.1	310.5	323.8	340.3
67.5°	259.1	256.0	251.9	245.7	247.8	248.8	253.9	264.2	278.6	292.0	310.5
70°	224.1	217.9	216.9	211.8	211.8	214.9	225.1	232.3	245.7	260.1	279.6
72.5°	187.1	182.0	182.0	177.8	180.9	184.0	189.2	199.4	211.8	226.2	242.6
75°	149.1	147.0	149.1	147.0	147.0	152.1	158.3	166.5	179.9	195.3	208.7
77.5°	115.1	115.1	114.1	117.2	117.2	120.3	128.5	136.7	147.0	159.3	173.7
80°	84.3	84.3	84.3	87.4	90.5	90.5	95.6	105.9	115.1	123.4	136.7
82.5°	57.6	57.6	57.6	59.6	63.7	63.7	69.9	76.1	86.4	93.6	99.7
85°	35.0	35.0	33.9	36.0	37.0	40.1	45.2	49.3	54.5	60.7	66.8
87.5°	15.4	15.4	16.4	17.5	18.5	20.6	22.6	24.7	29.8	31.9	35.0
90°	18.8	20.6	21.9	24.5	27.2	29.8	32.4	34.4	36.3	38.3	40.2
92.5°	19.4	19.1	20.4	23.0	25.7	28.3	30.9	32.9	34.8	36.8	38.7
95°	36.5	30.9	31.1	31.4	31.7	32.1	32.4	34.4	36.3	38.3	40.2
97.5°	183.3	186.9	169.7	135.4	101.1	66.7	32.4	34.0	35.6	37.3	38.9
100°	264.9	267.8	245.2	200.1	155.0	109.8	64.7	59.1	53.6	48.0	42.5
102.5°	354.1	356.1	358.1	362.0	365.9	369.8	373.7	300.1	226.6	153.0	79.5
105°	450.7	451.7	452.5	454.1	455.8	457.4	459.0	462.0	464.9	467.9	470.8
107.5°	542.4	542.9	544.0	546.3	548.6	550.9	553.2	554.8	556.5	558.1	559.8
110°	639.5	640.0	641.0	642.9	644.9	646.8	648.8	649.5	650.1	650.8	651.5

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	737.6	738.6	738.9	739.6	740.2	740.9	741.5	741.2	740.9	740.6	740.3
115°	830.8	831.3	831.1	830.8	830.5	830.1	829.8	830.4	831.1	831.7	832.4
117.5°	918.9	919.6	920.1	921.1	922.0	923.0	924.0	923.7	923.3	923.0	922.7
120°	1007.1	1007.8	1007.6	1007.3	1007.0	1006.7	1006.4	1007.0	1007.7	1008.3	1009.0
122.5°	1087.0	1087.3	1087.6	1088.3	1088.9	1089.6	1090.2	1090.5	1090.9	1091.2	1091.5
125°	1167.5	1168.2	1167.9	1167.2	1166.6	1165.9	1165.3	1166.3	1167.3	1168.2	1169.2
127.5°	1238.6	1238.8	1239.6	1241.3	1242.9	1244.6	1246.2	1245.9	1245.5	1245.2	1244.9
130°	1310.7	1310.9	1311.4	1312.4	1313.3	1314.3	1315.3	1315.6	1316.0	1316.3	1316.6
132.5°	1378.3	1378.6	1379.3	1380.6	1381.9	1383.2	1384.5	1384.8	1385.2	1385.5	1385.8
135°	1440.6	1440.4	1441.1	1442.4	1443.7	1445.0	1446.3	1446.9	1447.6	1448.2	1448.9
137.5°	1500.7	1500.7	1501.5	1503.2	1504.8	1506.5	1508.1	1508.7	1509.4	1510.0	1510.7
140°	1560.7	1561.0	1561.3	1562.0	1562.7	1563.3	1564.0	1565.0	1566.0	1566.9	1567.9
142.5°	1614.8	1615.5	1615.7	1616.0	1616.3	1616.6	1616.9	1617.6	1618.2	1618.9	1619.6
145°	1666.5	1667.0	1667.0	1667.0	1667.0	1667.0	1667.0	1667.3	1667.6	1667.9	1668.2
147.5°	1711.6	1712.6	1712.4	1712.1	1711.8	1711.4	1711.1	1711.4	1711.8	1712.1	1712.4
150°	1754.6	1755.2	1755.0	1754.7	1754.4	1754.1	1753.8	1753.8	1753.8	1753.8	1753.8
152.5°	1791.5	1792.0	1791.7	1791.0	1790.4	1789.7	1789.1	1789.7	1790.4	1791.0	1791.7
155°	1824.2	1824.4	1823.9	1822.9	1822.0	1821.0	1820.0	1821.3	1822.6	1823.9	1825.2
157.5°	1853.8	1853.8	1853.1	1851.8	1850.5	1849.2	1847.9	1849.5	1851.2	1852.8	1854.5
160°	1876.4	1875.9	1875.7	1875.4	1875.1	1874.7	1874.4	1876.4	1878.3	1880.3	1882.2
162.5°	1898.6	1898.0	1897.8	1897.5	1897.2	1896.8	1896.5	1898.5	1900.4	1902.4	1904.3
165°	1916.4	1915.6	1915.6	1915.6	1915.6	1915.6	1915.6	1918.2	1920.8	1923.5	1926.1
167.5°	1932.6	1931.8	1931.6	1931.3	1931.0	1930.6	1930.3	1933.3	1936.2	1939.2	1942.1
170°	1944.6	1943.6	1943.8	1944.1	1944.4	1944.7	1945.0	1947.6	1950.2	1952.9	1955.5
172.5°	1953.4	1952.4	1952.6	1952.9	1953.2	1953.6	1953.9	1956.5	1959.1	1961.7	1964.3
175°	1959.3	1958.3	1958.5	1958.8	1959.1	1959.5	1959.8	1962.7	1965.7	1968.6	1971.5
177.5°	1962.3	1961.2	1961.5	1962.2	1962.9	1963.5	1964.2	1966.8	1969.4	1972.0	1974.6
180°	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1170.9	1169.9	1164.8	1166.8	1160.7	1162.7	1165.8	1166.8	1170.9	1167.8	1166.8
5°	1099.0	1096.9	1093.8	1090.7	1089.7	1093.8	1086.6	1088.7	1090.7	1093.8	1097.9
7.5°	1040.4	1039.3	1036.3	1031.1	1029.1	1027.0	1028.0	1035.2	1034.2	1033.2	1040.4
10°	986.9	987.9	981.8	980.7	974.6	973.5	974.6	976.6	979.7	983.8	984.9
12.5°	931.4	944.8	933.5	929.3	920.1	925.2	927.3	918.0	923.2	926.3	941.7
15°	896.4	890.3	883.1	883.1	879.0	876.9	871.8	879.0	883.1	889.2	887.2
17.5°	848.1	837.8	833.7	829.6	830.7	834.8	823.5	839.9	839.9	843.0	837.8
20°	806.0	797.8	792.6	790.6	787.5	785.4	784.4	788.5	794.7	796.7	801.9
22.5°	761.8	761.8	753.5	750.5	748.4	745.3	750.5	747.4	751.5	755.6	763.8
25°	724.8	724.8	721.7	717.6	714.5	712.4	715.5	714.5	717.6	722.7	724.8
27.5°	695.0	691.9	690.8	689.8	688.8	689.8	688.8	691.9	695.0	696.0	693.9
30°	669.3	666.2	667.2	667.2	668.2	667.2	666.2	669.3	670.3	668.2	669.3
32.5°	645.6	645.6	647.7	648.7	648.7	649.7	650.7	648.7	649.7	646.6	647.7
35°	626.1	628.1	630.2	631.2	632.2	631.2	633.3	632.2	630.2	628.1	627.1
37.5°	606.5	608.6	612.7	613.7	616.8	617.8	615.8	615.8	614.8	610.7	608.6
40°	586.0	588.0	593.2	596.3	598.3	601.4	599.3	599.3	595.2	591.1	588.0
42.5°	566.4	570.6	575.7	578.8	582.9	582.9	582.9	580.8	575.7	571.6	568.5
45°	546.9	547.9	555.1	560.3	564.4	564.4	564.4	561.3	558.2	550.0	545.9
47.5°	525.3	528.4	536.6	541.8	545.9	546.9	546.9	543.8	537.7	530.5	525.3
50°	501.7	506.8	516.1	523.3	528.4	530.5	527.4	525.3	518.1	509.9	503.7
52.5°	479.1	485.2	496.5	502.7	509.9	510.9	509.9	506.8	498.6	487.3	482.1
55°	456.4	461.6	473.9	484.2	490.4	492.4	490.4	485.2	475.0	463.6	458.5
57.5°	431.8	439.0	452.3	462.6	469.8	470.8	468.8	463.6	455.4	441.0	433.8
60°	406.1	415.3	428.7	439.0	448.2	449.3	447.2	440.0	429.7	415.3	409.2
62.5°	380.4	387.6	403.0	414.3	421.5	426.6	422.5	415.3	405.0	390.7	381.4
65°	350.6	360.8	374.2	384.5	392.7	393.7	391.7	385.5	374.2	358.8	351.6
67.5°	321.8	329.0	342.3	355.7	358.8	361.9	358.8	352.6	343.4	330.0	319.7
70°	286.8	293.0	309.4	318.7	322.8	325.9	323.8	317.7	309.4	297.1	288.9
72.5°	251.9	257.0	272.4	279.6	287.8	286.8	285.8	281.7	270.4	262.1	257.0
75°	214.9	221.0	231.3	240.6	243.6	243.6	243.6	240.6	233.4	220.0	214.9
77.5°	180.9	184.0	192.2	197.4	200.5	201.5	200.5	195.3	191.2	182.0	178.9
80°	138.8	147.0	153.2	154.2	158.3	158.3	158.3	156.3	152.1	142.9	141.9
82.5°	104.9	106.9	113.1	116.2	118.2	117.2	117.2	113.1	112.1	106.9	104.9
85°	70.9	74.0	73.0	77.1	78.1	76.1	76.1	78.1	73.0	74.0	70.9
87.5°	39.1	39.1	41.1	40.1	44.2	44.2	42.1	43.2	41.1	40.1	39.1
90°	41.2	41.5	42.2	42.8	43.5	44.1	43.5	42.8	42.2	41.5	41.2
92.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7
95°	41.2	41.4	41.7	42.0	42.4	42.7	42.4	42.0	41.7	41.4	41.2
97.5°	39.7	39.9	40.2	40.5	40.9	41.2	40.9	40.5	40.2	39.9	39.7
100°	39.7	39.9	40.2	40.5	40.9	41.2	40.9	40.5	40.2	39.9	39.7
102.5°	42.7	42.7	42.7	42.7	42.7	42.7	42.7	42.7	42.7	42.7	42.7
105°	472.3	466.4	454.6	442.9	431.1	419.3	431.1	442.9	454.6	466.4	472.3
107.5°	560.6	561.2	562.5	563.8	565.1	566.4	565.1	563.8	562.5	561.2	560.6
110°	651.8	652.3	653.3	654.2	655.2	656.2	655.2	654.2	653.3	652.3	651.8

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	740.1	740.7	742.0	743.3	744.6	745.9	744.6	743.3	742.0	740.7	740.1
115°	832.7	832.7	832.7	832.7	832.7	832.7	832.7	832.7	832.7	832.7	832.7
117.5°	922.5	922.5	922.5	922.5	922.5	922.5	922.5	922.5	922.5	922.5	922.5
120°	1009.3	1009.0	1008.3	1007.7	1007.0	1006.4	1007.0	1007.7	1008.3	1009.0	1009.3
122.5°	1091.7	1091.4	1090.7	1090.1	1089.4	1088.8	1089.4	1090.1	1090.7	1091.4	1091.7
125°	1169.7	1169.9	1170.2	1170.5	1170.8	1171.1	1170.8	1170.5	1170.2	1169.9	1169.7
127.5°	1244.7	1244.5	1244.2	1243.9	1243.5	1243.2	1243.5	1243.9	1244.2	1244.5	1244.7
130°	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8	1316.8
132.5°	1386.0	1385.8	1385.5	1385.2	1384.8	1384.5	1384.8	1385.2	1385.5	1385.8	1386.0
135°	1449.2	1449.5	1450.2	1450.9	1451.5	1452.2	1451.5	1450.9	1450.2	1449.5	1449.2
137.5°	1511.0	1510.8	1510.5	1510.2	1509.8	1509.5	1509.8	1510.2	1510.5	1510.8	1511.0
140°	1568.4	1568.6	1568.9	1569.2	1569.6	1569.9	1569.6	1569.2	1568.9	1568.6	1568.4
142.5°	1619.9	1619.9	1619.9	1619.9	1619.9	1619.9	1619.9	1619.9	1619.9	1619.9	1619.9
145°	1668.4	1668.7	1669.4	1670.1	1670.7	1671.4	1670.7	1670.1	1669.4	1668.7	1668.4
147.5°	1712.6	1712.8	1713.1	1713.4	1713.8	1714.1	1713.8	1713.4	1713.1	1712.8	1712.6
150°	1753.8	1754.0	1754.3	1754.6	1754.9	1755.2	1754.9	1754.6	1754.3	1754.0	1753.8
152.5°	1792.0	1791.8	1791.5	1791.2	1790.9	1790.6	1790.9	1791.2	1791.5	1791.8	1792.0
155°	1825.9	1825.4	1824.4	1823.5	1822.5	1821.5	1822.5	1823.5	1824.4	1825.4	1825.9
157.5°	1855.3	1854.5	1852.8	1851.2	1849.5	1847.9	1849.5	1851.2	1852.8	1854.5	1855.3
160°	1883.2	1882.2	1880.3	1878.3	1876.4	1874.4	1876.4	1878.3	1880.3	1882.2	1883.2
162.5°	1905.3	1904.2	1901.9	1899.6	1897.3	1895.0	1897.3	1899.6	1901.9	1904.2	1905.3
165°	1927.4	1925.9	1923.0	1920.0	1917.1	1914.1	1917.1	1920.0	1923.0	1925.9	1927.4
167.5°	1943.6	1942.0	1938.7	1935.4	1932.2	1928.9	1932.2	1935.4	1938.7	1942.0	1943.6
170°	1956.8	1955.2	1951.9	1948.6	1945.4	1942.1	1945.4	1948.6	1951.9	1955.2	1956.8
172.5°	1965.6	1963.8	1960.2	1956.7	1953.1	1949.5	1953.1	1956.7	1960.2	1963.8	1965.6
175°	1973.0	1971.0	1967.1	1963.2	1959.2	1955.3	1959.2	1963.2	1967.1	1971.0	1973.0
177.5°	1975.9	1973.9	1970.0	1966.1	1962.2	1958.3	1962.2	1966.1	1970.0	1973.9	1975.9
180°	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8	1240.8
2.5°	1166.8	1173.0	1166.8	1170.9	1173.0	1178.1	1180.2	1189.4	1192.5	1199.7	1199.7
5°	1096.9	1100.0	1101.0	1105.1	1109.2	1119.5	1126.7	1140.1	1155.5	1157.6	1166.8
7.5°	1040.4	1045.5	1053.7	1050.7	1057.8	1073.3	1082.5	1099.0	1114.4	1122.6	1133.9
10°	990.0	996.2	999.2	1002.3	1015.7	1029.1	1043.5	1054.8	1075.3	1087.7	1096.9
12.5°	948.9	943.7	949.9	961.2	976.6	984.9	1004.4	1021.9	1037.3	1050.7	1058.9
15°	895.4	899.5	905.7	925.2	929.3	949.9	957.1	976.6	1005.4	1017.8	1028.0
17.5°	844.0	857.4	869.7	876.9	889.2	905.7	926.3	947.8	966.4	980.7	993.1
20°	802.9	816.3	823.5	828.6	840.9	863.5	883.1	909.8	933.5	944.8	961.2
22.5°	770.0	770.0	780.3	795.7	802.9	824.5	840.9	869.7	895.4	909.8	925.2
25°	728.9	735.0	743.3	756.6	766.9	784.4	808.0	832.7	860.5	872.8	892.3
27.5°	695.0	702.1	713.5	716.5	726.8	742.2	766.9	793.6	822.4	835.8	852.2
30°	669.3	673.4	677.5	683.6	692.9	706.3	726.8	750.5	785.4	795.7	816.3
32.5°	646.6	648.7	650.7	655.9	661.0	674.4	690.8	716.5	745.3	760.7	779.2
35°	626.1	624.0	625.0	628.1	633.3	638.4	655.9	677.5	704.2	722.7	737.1
37.5°	606.5	602.4	601.4	601.4	603.5	609.6	623.0	641.5	670.3	685.7	700.1
40°	585.0	580.8	578.8	577.8	576.7	580.8	591.1	609.6	632.2	646.6	663.1
42.5°	564.4	560.3	555.1	554.1	552.1	554.1	561.3	578.8	598.3	612.7	626.1
45°	543.8	536.6	530.5	526.4	527.4	524.3	529.4	542.8	565.4	574.7	588.0
47.5°	521.2	513.0	504.8	500.7	496.5	498.6	500.7	512.0	531.5	540.7	554.1
50°	499.6	488.3	479.1	473.9	470.8	468.8	470.8	482.1	496.5	504.8	516.1
52.5°	475.0	463.6	454.4	446.2	442.1	439.0	440.0	450.3	463.6	471.9	483.2
55°	452.3	437.9	425.6	415.3	412.2	411.2	410.2	417.4	428.7	436.9	446.2
57.5°	426.6	412.2	398.9	386.5	380.4	379.3	379.3	381.4	395.8	402.0	407.1
60°	400.9	385.5	371.1	359.8	350.6	347.5	346.4	350.6	357.8	363.9	371.1
62.5°	372.1	356.7	339.3	329.0	319.7	311.5	314.6	315.6	325.9	329.0	335.1
65°	344.4	326.9	312.5	296.1	285.8	280.7	278.6	280.7	288.9	289.9	294.0
67.5°	312.5	296.1	278.6	267.3	258.0	248.8	246.7	246.7	250.8	253.9	259.1
70°	281.7	265.2	245.7	233.4	224.1	215.9	212.8	211.8	214.9	216.9	222.1
72.5°	245.7	229.3	214.9	201.5	190.2	184.0	180.9	178.9	182.0	184.0	185.0
75°	207.7	194.3	179.9	166.5	159.3	153.2	149.1	146.0	148.0	148.0	148.0
77.5°	171.7	158.3	147.0	137.8	128.5	121.3	118.2	115.1	116.2	116.2	118.2
80°	133.6	124.4	115.1	106.9	98.7	92.5	90.5	87.4	85.3	84.3	84.3
82.5°	98.7	91.5	83.3	76.1	72.0	65.8	63.7	59.6	59.6	58.6	58.6
85°	65.8	61.7	53.5	48.3	45.2	42.1	40.1	38.0	35.0	35.0	33.9
87.5°	35.0	32.9	30.8	24.7	24.7	21.6	20.6	19.5	16.4	17.5	17.5
90°	40.2	38.3	36.3	34.4	32.4	29.8	27.2	24.5	21.9	20.6	18.8
92.5°	38.7	36.8	34.8	32.9	30.9	28.3	25.7	23.0	20.4	19.1	19.4
95°	40.2	38.3	36.3	34.4	32.4	32.1	31.7	31.4	31.1	30.9	36.5
97.5°	38.9	37.3	35.6	34.0	32.4	66.7	101.1	135.4	169.7	186.9	183.3
100°	42.5	48.0	53.6	59.1	64.7	109.8	155.0	200.1	245.2	267.8	264.9
102.5°	79.5	153.0	226.6	300.1	373.7	369.8	365.9	362.0	358.1	356.1	354.1
105°	470.8	467.9	464.9	462.0	459.0	457.4	455.8	454.1	452.5	451.7	450.7
107.5°	559.8	558.1	556.5	554.8	553.2	550.9	548.6	546.3	544.0	542.9	542.4
110°	651.5	650.8	650.1	649.5	648.8	646.8	644.9	642.9	641.0	640.0	639.5

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	740.3	740.6	740.9	741.2	741.5	740.9	740.2	739.6	738.9	738.6	737.6
115°	832.4	831.7	831.1	830.4	829.8	830.1	830.5	830.8	831.1	831.3	830.8
117.5°	922.7	923.0	923.3	923.7	924.0	923.0	922.0	921.1	920.1	919.6	918.9
120°	1009.0	1008.3	1007.7	1007.0	1006.4	1006.7	1007.0	1007.3	1007.6	1007.8	1007.1
122.5°	1091.5	1091.2	1090.9	1090.5	1090.2	1089.6	1088.9	1088.3	1087.6	1087.3	1087.0
125°	1169.2	1168.2	1167.3	1166.3	1165.3	1165.9	1166.6	1167.2	1167.9	1168.2	1167.5
127.5°	1244.9	1245.2	1245.5	1245.9	1246.2	1244.6	1242.9	1241.3	1239.6	1238.8	1238.6
130°	1316.6	1316.3	1316.0	1315.6	1315.3	1314.3	1313.3	1312.4	1311.4	1310.9	1310.7
132.5°	1385.8	1385.5	1385.2	1384.8	1384.5	1383.2	1381.9	1380.6	1379.3	1378.6	1378.3
135°	1448.9	1448.2	1447.6	1446.9	1446.3	1445.0	1443.7	1442.4	1441.1	1440.4	1440.6
137.5°	1510.7	1510.0	1509.4	1508.7	1508.1	1506.5	1504.8	1503.2	1501.5	1500.7	1500.7
140°	1567.9	1566.9	1566.0	1565.0	1564.0	1563.3	1562.7	1562.0	1561.3	1561.0	1560.7
142.5°	1619.6	1618.9	1618.2	1617.6	1616.9	1616.6	1616.3	1616.0	1615.7	1615.5	1614.8
145°	1668.2	1667.9	1667.6	1667.3	1667.0	1667.0	1667.0	1667.0	1667.0	1667.0	1666.5
147.5°	1712.4	1712.1	1711.8	1711.4	1711.1	1711.4	1711.8	1712.1	1712.4	1712.6	1711.6
150°	1753.8	1753.8	1753.8	1753.8	1753.8	1754.1	1754.4	1754.7	1755.0	1755.2	1754.6
152.5°	1791.7	1791.0	1790.4	1789.7	1789.1	1789.7	1790.4	1791.0	1791.7	1792.0	1791.5
155°	1825.2	1823.9	1822.6	1821.3	1820.0	1821.0	1822.0	1822.9	1823.9	1824.4	1824.2
157.5°	1854.5	1852.8	1851.2	1849.5	1847.9	1849.2	1850.5	1851.8	1853.1	1853.8	1853.8
160°	1882.2	1880.3	1878.3	1876.4	1874.4	1874.7	1875.1	1875.4	1875.7	1875.9	1876.4
162.5°	1904.3	1902.4	1900.4	1898.5	1896.5	1896.8	1897.2	1897.5	1897.8	1898.0	1898.6
165°	1926.1	1923.5	1920.8	1918.2	1915.6	1915.6	1915.6	1915.6	1915.6	1915.6	1916.4
167.5°	1942.1	1939.2	1936.2	1933.3	1930.3	1930.6	1931.0	1931.3	1931.6	1931.8	1932.6
170°	1955.5	1952.9	1950.2	1947.6	1945.0	1944.7	1944.4	1944.1	1943.8	1943.6	1944.6
172.5°	1964.3	1961.7	1959.1	1956.5	1953.9	1953.6	1953.2	1952.9	1952.6	1952.4	1953.4
175°	1971.5	1968.6	1965.7	1962.7	1959.8	1959.5	1959.1	1958.8	1958.5	1958.3	1959.3
177.5°	1974.6	1972.0	1969.4	1966.8	1964.2	1963.5	1962.9	1962.2	1961.5	1961.2	1962.3
180°	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1	1967.1

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1240.8	1240.8	1240.8	1240.8
2.5°	1206.9	1217.2	1226.4	1240.8
5°	1180.2	1194.6	1214.1	1235.7
7.5°	1149.3	1172.0	1197.7	1227.5
10°	1120.6	1146.3	1179.2	1215.1
12.5°	1090.7	1121.6	1157.6	1196.6
15°	1056.8	1087.7	1127.8	1180.2
17.5°	1026.0	1063.0	1106.2	1161.7
20°	990.0	1024.9	1072.2	1136.0
22.5°	958.1	998.2	1050.7	1106.2
25°	923.2	958.1	1010.6	1077.4
27.5°	888.2	931.4	981.8	1046.5
30°	854.3	890.3	944.8	1012.6
32.5°	817.3	860.5	910.8	974.6
35°	777.2	818.3	865.6	934.5
37.5°	741.2	781.3	829.6	890.3
40°	701.1	743.3	787.5	848.1
42.5°	662.1	700.1	744.3	799.8
45°	624.0	656.9	697.0	745.3
47.5°	585.0	612.7	649.7	692.9
50°	542.8	572.6	600.4	636.4
52.5°	503.7	529.4	552.1	581.9
55°	465.7	483.2	501.7	524.3
57.5°	425.6	439.0	452.3	476.0
60°	385.5	397.8	405.0	420.5
62.5°	346.4	351.6	360.8	370.1
65°	303.3	310.5	315.6	326.9
67.5°	264.2	267.3	272.4	279.6
70°	223.1	230.3	232.3	237.5
72.5°	188.1	191.2	193.3	194.3
75°	149.1	152.1	154.2	160.4
77.5°	117.2	116.2	120.3	121.3
80°	86.4	83.3	84.3	88.4
82.5°	56.5	57.6	56.5	56.5
85°	35.0	33.9	31.9	32.9
87.5°	15.4	15.4	14.4	14.4
90°	15.2	11.6	8.0	4.4
92.5°	20.1	20.8	21.4	22.1
95°	47.6	58.7	69.8	80.9
97.5°	176.1	168.9	161.7	154.5
100°	259.0	253.1	247.2	241.3
102.5°	350.2	346.3	342.3	338.4
105°	448.8	446.8	444.9	442.9
107.5°	541.4	540.5	539.5	538.5
110°	638.5	637.6	636.6	635.6

TEST NUMBER: P1032798

CATALOG NUMBER: S124DIW-B795D1560UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	735.7	733.7	731.8	729.8
115°	829.8	828.9	827.9	826.9
117.5°	917.6	916.3	915.0	913.7
120°	1005.8	1004.5	1003.2	1001.9
122.5°	1086.3	1085.6	1085.0	1084.3
125°	1166.2	1164.9	1163.6	1162.3
127.5°	1238.3	1238.0	1237.7	1237.4
130°	1310.4	1310.1	1309.7	1309.4
132.5°	1377.6	1377.0	1376.3	1375.7
135°	1440.9	1441.2	1441.6	1441.9
137.5°	1500.7	1500.7	1500.7	1500.7
140°	1560.0	1559.4	1558.7	1558.1
142.5°	1613.5	1612.2	1610.9	1609.6
145°	1665.5	1664.6	1663.6	1662.6
147.5°	1709.7	1707.7	1705.8	1703.8
150°	1753.3	1752.0	1750.7	1749.4
152.5°	1790.5	1789.6	1788.6	1787.6
155°	1823.9	1823.6	1823.2	1822.9
157.5°	1853.8	1853.8	1853.8	1853.8
160°	1877.4	1878.3	1879.3	1880.3
162.5°	1899.9	1901.2	1902.5	1903.8
165°	1918.1	1919.7	1921.4	1923.0
167.5°	1934.3	1935.9	1937.6	1939.2
170°	1946.5	1948.5	1950.4	1952.4
172.5°	1955.3	1957.3	1959.2	1961.2
175°	1961.2	1963.2	1965.1	1967.1
177.5°	1964.6	1966.9	1969.2	1971.5
180°	1967.1	1967.1	1967.1	1967.1

(END OF REPORT)